

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333495-927

Luminaire Tested: **S125RDIP-S375D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333495-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D365U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2187.3 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	36	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	2.1
10°-20°	127.4	5.8
20°-30°	184.7	8.4
30°-40°	210.5	9.6
40°-50°	205.2	9.4
50°-60°	172.7	7.9
60°-70°	121.1	5.5
70°-80°	62.2	2.8
80°-90°	16.5	0.8
90°-100°	100.7	4.6
100°-110°	216.4	9.9
110°-120°	203.1	9.3
120°-130°	164.6	7.5
130°-140°	132.1	6.0
140°-150°	99.7	4.6
150°-160°	70.1	3.2
160°-170°	41.4	1.9
170°-180°	13.5	0.6
0°-30°	357.7	16.4
0°-40°	568.2	26.0
0°-60°	946.1	43.3
0°-90°	1145.9	52.4
90°-120°	520.1	23.8
90°-150°	916.4	41.9
90°-180°	1041.0	47.6
0°-180°	2187.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	0	2	4	6	6	1
95°	9	27	248	113	66	10
105°	32	44	203	400	371	33
115°	57	68	163	351	413	56
125°	78	92	156	279	326	70
135°	92	110	155	234	270	71
145°	107	122	156	194	213	67
155°	122	131	152	171	179	56
165°	133	137	146	154	157	38
175°	139	139	140	141	141	13
180°	139	139	139	139	139	



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.8	6.4	6.0	5.7	5.4	5.2	5.2	5.2	5.2	5.3	5.3
90°	0.3	0.6	1.1	1.7	2.2	2.8	3.1	3.6	3.9	4.5	4.8
92.5°	3.4	4.1	6.5	10.0	14.8	23.0	38.3	63.8	91.7	90.2	73.0
95°	9.3	9.5	11.7	14.8	21.0	33.6	63.5	125.2	202.4	248.0	242.7
97.5°	15.4	15.7	17.3	20.4	25.9	34.9	54.7	99.9	180.8	264.9	307.1
100°	19.6	20.1	21.3	24.3	29.7	38.1	54.3	90.7	161.3	252.8	322.8
102.5°	24.3	24.6	25.5	28.8	33.7	41.9	56.3	86.9	146.5	231.6	313.4
105°	31.6	31.6	33.0	35.8	40.3	48.2	60.4	85.4	132.1	203.0	283.4
107.5°	38.8	39.4	40.7	43.0	47.7	54.7	66.6	87.9	126.1	183.3	252.6
110°	44.0	44.5	45.6	48.2	52.4	59.7	71.1	90.5	124.3	174.1	235.2



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.1	49.7	50.5	53.1	57.3	64.3	75.3	93.6	124.3	168.7	222.2
115°	56.6	57.1	58.0	60.4	64.6	71.7	82.1	98.2	125.2	163.0	208.0
117.5°	63.3	64.1	65.0	67.5	72.3	79.1	88.9	103.6	127.0	160.1	199.6
120°	67.7	68.6	69.7	72.2	77.0	84.0	93.8	107.3	128.8	158.8	194.9
122.5°	72.5	73.0	74.0	76.5	81.7	88.7	98.5	111.2	130.3	157.6	190.8
125°	78.4	79.0	80.3	82.9	88.2	95.5	104.7	116.8	133.0	156.2	185.4
127.5°	83.0	83.9	85.6	88.9	94.5	101.8	110.7	121.8	135.9	155.6	180.3
130°	86.0	86.8	89.0	92.7	98.5	105.8	114.5	125.2	137.8	155.1	177.0
132.5°	88.2	89.3	92.0	96.0	102.1	109.4	118.1	128.1	139.7	155.1	174.3
135°	91.8	92.9	96.3	100.8	106.7	114.2	122.9	132.1	142.5	155.1	171.0
137.5°	96.4	97.3	100.4	104.9	110.7	118.4	126.4	135.1	145.0	155.4	168.2
140°	99.1	100.0	103.3	107.8	113.1	120.6	128.8	137.2	146.2	155.7	166.8
142.5°	102.3	102.8	106.0	110.5	115.6	122.7	130.3	138.3	146.8	155.9	165.7
145°	106.9	107.5	110.3	114.2	119.3	125.7	133.0	140.0	147.5	155.7	164.1
147.5°	111.9	112.2	114.6	118.3	122.6	128.3	134.7	141.0	147.8	155.0	162.3
150°	114.8	115.3	117.3	121.0	124.8	129.6	135.8	141.6	147.8	154.2	161.0
152.5°	118.0	118.3	120.0	123.2	126.9	131.2	136.9	142.1	147.6	153.4	159.4
155°	122.1	122.1	123.7	126.5	129.4	133.2	138.0	142.5	146.9	151.8	156.8
157.5°	125.8	125.7	127.1	129.4	131.9	134.9	138.9	142.8	146.2	150.0	154.3
160°	128.3	127.9	129.0	131.0	133.2	135.8	139.4	142.8	145.6	148.9	152.3
162.5°	130.2	130.0	131.1	132.8	134.6	136.7	139.9	142.6	144.9	147.6	150.5
165°	133.2	132.7	133.6	134.9	136.1	137.8	140.0	142.2	143.9	145.6	147.8
167.5°	135.3	135.0	135.5	136.3	137.0	138.2	140.0	141.6	142.4	143.6	145.2
170°	136.7	136.3	136.7	137.2	137.8	138.6	140.0	141.1	141.6	142.5	143.6
172.5°	137.5	137.0	137.3	137.8	138.2	138.6	139.7	140.7	140.8	141.2	142.0
175°	138.6	138.0	138.3	138.6	138.6	138.6	139.4	140.0	139.7	139.7	140.0
177.5°	139.1	138.6	138.6	138.9	138.6	138.6	139.1	139.3	138.9	138.9	139.1
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	5.4	5.5	5.5	5.6	5.5	5.5	5.5	5.4
90°	5.1	5.3	5.6	6.2	6.2	6.2	6.4	6.4
92.5°	49.6	36.0	27.1	23.0	19.4	18.7	18.3	17.8
95°	201.3	158.8	124.3	100.8	80.9	72.5	70.3	65.8
97.5°	299.8	270.0	236.4	203.7	186.4	170.7	162.6	159.0
100°	344.4	330.7	301.8	272.7	253.3	233.2	222.8	218.4
102.5°	359.3	367.8	354.0	334.3	313.6	299.3	288.0	284.7
105°	350.5	388.9	401.2	398.2	389.1	379.9	374.3	371.0
107.5°	318.9	370.1	401.7	416.4	420.9	420.9	419.0	416.8
110°	295.6	348.9	388.3	412.1	424.7	430.0	432.0	432.0



TEST NUMBER: P333495-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.3	327.8	367.7	395.8	414.2	423.3	428.2	430.2
115°	254.2	297.6	336.0	366.5	388.3	401.7	409.6	413.2
117.5°	239.3	276.7	309.7	337.8	359.6	373.5	381.3	383.5
120°	231.2	264.8	295.6	320.3	341.0	354.4	362.0	364.2
122.5°	225.2	256.4	283.8	306.8	325.3	337.6	345.2	347.2
125°	216.4	244.9	269.3	289.5	305.1	316.6	322.8	325.6
127.5°	207.5	234.1	256.8	275.7	289.9	300.1	305.9	307.1
130°	201.8	226.5	248.3	266.6	280.5	289.8	295.4	297.1
132.5°	196.2	219.4	239.2	256.7	270.7	279.9	285.0	286.9
135°	189.0	208.3	226.2	242.2	254.5	263.7	268.8	270.5
137.5°	182.8	198.4	213.3	226.9	237.9	246.3	251.0	252.8
140°	179.4	192.6	205.5	217.2	227.6	234.9	239.1	240.5
142.5°	176.6	187.7	198.8	209.0	217.8	223.9	227.9	229.1
145°	172.8	181.4	190.1	197.6	204.4	209.1	212.2	213.3
147.5°	169.1	176.2	182.9	188.6	193.9	197.7	199.5	200.0
150°	167.2	173.3	178.6	183.6	187.8	191.2	192.3	192.6
152.5°	164.9	170.4	175.2	179.2	182.7	185.4	186.5	186.8
155°	161.5	166.0	169.9	173.0	175.8	177.8	178.6	178.9
157.5°	158.2	161.8	164.9	167.3	169.5	171.1	171.9	171.8
160°	156.0	158.8	161.5	163.5	165.5	166.8	167.4	167.2
162.5°	153.4	156.1	158.4	160.2	161.7	162.8	163.0	162.9
165°	150.0	152.0	153.7	155.1	156.2	156.8	156.8	156.8
167.5°	146.8	148.1	149.4	150.4	151.0	151.5	151.2	151.1
170°	145.0	145.8	146.7	147.3	147.8	148.1	148.1	147.8
172.5°	143.0	143.9	144.5	144.8	144.9	145.4	145.0	144.7
175°	140.9	140.9	141.4	141.4	141.4	141.6	141.1	140.9
177.5°	139.3	139.5	139.5	139.5	139.3	139.5	138.9	138.9
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9

(END OF REPORT)