

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333506-927

Luminaire Tested: **S125RDIP-S375D810U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333506-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3368.1 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	82	78	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	22	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	1.4
10°-20°	127.4	3.8
20°-30°	184.7	5.5
30°-40°	210.5	6.3
40°-50°	205.2	6.1
50°-60°	172.7	5.1
60°-70°	121.1	3.6
70°-80°	62.2	1.8
80°-90°	17.5	0.5
90°-100°	53.3	1.6
100°-110°	157.4	4.7
110°-120°	266.7	7.9
120°-130°	350.9	10.4
130°-140°	393.2	11.7
140°-150°	385.4	11.4
150°-160°	323.7	9.6
160°-170°	215.2	6.4
170°-180°	75.3	2.2
0°-30°	357.7	10.6
0°-40°	568.2	16.9
0°-60°	946.1	28.1
0°-90°	1146.9	34.1
90°-120°	477.4	14.2
90°-150°	1607.0	47.7
90°-180°	2221.0	65.9
0°-180°	3368.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	6	10	13	15	3
95°	40	42	48	52	53	43
105°	141	144	148	152	154	151
115°	267	269	271	270	270	264
125°	390	393	394	393	392	349
135°	507	510	511	511	509	390
145°	614	616	618	618	616	384
155°	702	702	703	705	702	323
165°	764	763	763	765	762	215
175°	794	792	792	795	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.9	6.7	6.4	6.2	5.9	5.9	6.0	6.1	6.3	6.3	6.5
90°	0.6	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6
92.5°	15.0	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7
95°	40.2	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6
97.5°	66.9	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8
100°	86.7	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0
102.5°	108.1	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0
105°	141.2	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9
107.5°	177.9	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3
110°	203.2	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	228.9	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1
115°	267.0	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5
117.5°	305.1	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4
120°	328.9	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6
122.5°	354.7	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3
125°	389.6	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7
127.5°	426.8	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5
130°	449.1	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3
132.5°	471.4	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1
135°	506.7	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0
137.5°	540.0	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0
140°	561.3	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5
142.5°	582.6	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6
145°	613.9	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2
147.5°	642.9	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0
150°	662.2	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1
152.5°	678.0	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2
155°	702.4	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6
157.5°	724.3	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1
160°	737.1	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5
162.5°	748.5	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0
165°	763.8	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7
167.5°	776.7	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0
170°	783.6	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0
172.5°	788.5	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9
175°	794.2	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5
177.5°	797.0	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	6.7	6.8	6.9	7.0	7.1	7.1	7.1	7.1
90°	11.2	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	25.6	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	49.6	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	77.8	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	97.3	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	117.3	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	149.7	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	184.7	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.0	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333506-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.3	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.5	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.6	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.2	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.4	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.4	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.1	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.9	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.2	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	566.7	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	587.8	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.3	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.6	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.2	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	724.6	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.0	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	748.6	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.3	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	775.9	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	782.8	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	787.7	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	793.3	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	795.8	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)