

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332928

Luminaire Tested: **S124RDIP-S795D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332928
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D365U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4672.5 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	53
3	86	76	69	63	81	72	66	60	65	60	55	58	54	50	52	49	46
4	79	68	60	53	74	64	57	51	58	52	47	52	47	44	46	43	40
5	72	60	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25
9	54	41	34	29	51	40	32	28	36	30	26	33	28	24	30	26	23
10	50	38	31	26	48	36	30	25	33	28	24	30	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.5	2.8
10°-20°	363.9	7.8
20°-30°	525.5	11.2
30°-40°	595.6	12.7
40°-50°	575.2	12.3
50°-60°	478.3	10.2
60°-70°	330.3	7.1
70°-80°	167.4	3.6
80°-90°	44.3	0.9
90°-100°	16.2	0.3
100°-110°	103.0	2.2
110°-120°	197.1	4.2
120°-130°	250.2	5.4
130°-140°	267.7	5.7
140°-150°	250.4	5.4
150°-160°	201.9	4.3
160°-170°	130.2	2.8
170°-180°	44.9	1.0
0°-30°	1019.8	21.8
0°-40°	1615.5	34.6
0°-60°	2668.9	57.1
0°-90°	3210.9	68.7
90°-120°	316.3	6.8
90°-150°	1084.6	23.2
90°-180°	1462.0	31.3
0°-180°	4672.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	1	5	8	10	11	4
95°	19	8	8	10	10	25
105°	106	108	110	113	101	111
115°	199	200	199	200	200	195
125°	279	280	280	281	281	249
135°	346	346	347	348	349	267
145°	399	400	400	401	402	249
155°	438	438	437	438	438	202
165°	462	460	460	463	460	130
175°	472	470	471	474	470	45
180°	472	472	472	472	472	



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	19.8	18.4	17.1	15.8	14.4	13.7	13.7	13.6	13.5	13.5	13.4
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.6	6.2	6.9	7.5	8.0
95°	19.4	16.8	14.1	11.4	8.8	7.5	7.5	7.6	7.7	7.8	8.2
97.5°	41.3	42.9	44.6	46.3	47.9	44.4	35.6	26.9	18.1	9.3	9.4
100°	58.0	59.4	60.8	62.2	63.6	58.9	48.1	37.2	26.4	15.6	14.2
102.5°	76.6	77.7	78.7	79.7	80.8	80.6	79.2	77.8	76.3	74.9	60.5
105°	106.4	106.8	107.3	107.8	108.3	108.7	109.1	109.5	109.9	110.3	111.0
107.5°	134.0	134.2	134.5	134.7	135.0	135.3	135.9	136.4	136.9	137.5	137.8
110°	152.7	152.9	153.1	153.4	153.6	154.0	154.4	154.9	155.4	155.9	156.0



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.8	171.2	171.6	172.0	172.5	172.8	173.0	173.2	173.4	173.7	173.6
115°	198.6	198.9	199.1	199.3	199.6	199.6	199.6	199.5	199.4	199.3	199.5
117.5°	223.7	224.0	224.3	224.7	225.0	225.2	225.4	225.6	225.7	225.9	225.9
120°	240.7	241.0	241.3	241.6	241.9	242.0	242.0	241.9	241.8	241.7	241.9
122.5°	256.5	256.7	256.9	257.1	257.3	257.4	257.5	257.6	257.7	257.9	257.9
125°	279.2	279.5	279.8	280.1	280.5	280.5	280.4	280.2	280.1	279.9	280.1
127.5°	300.7	300.8	300.8	300.9	301.0	301.2	301.6	301.9	302.3	302.7	302.6
130°	314.5	314.6	314.7	314.8	314.9	315.0	315.2	315.5	315.7	316.0	316.0
132.5°	327.3	327.4	327.5	327.7	327.8	328.0	328.3	328.6	328.9	329.2	329.3
135°	346.3	346.3	346.2	346.1	346.0	346.1	346.5	346.8	347.1	347.4	347.6
137.5°	363.2	363.3	363.3	363.3	363.4	363.6	363.9	364.2	364.6	364.9	365.1
140°	374.3	374.4	374.6	374.7	374.9	375.0	375.2	375.4	375.5	375.7	375.9
142.5°	384.2	384.4	384.7	385.0	385.3	385.5	385.6	385.7	385.8	385.9	386.0
145°	399.4	399.6	399.8	400.1	400.3	400.4	400.4	400.4	400.4	400.4	400.5
147.5°	411.4	411.9	412.3	412.8	413.2	413.4	413.3	413.2	413.1	413.1	413.1
150°	420.2	420.5	420.8	421.2	421.5	421.6	421.5	421.4	421.3	421.3	421.3
152.5°	427.6	427.8	428.1	428.3	428.6	428.6	428.5	428.3	428.2	428.1	428.2
155°	437.9	438.0	438.0	438.1	438.2	438.1	437.9	437.6	437.4	437.2	437.5
157.5°	446.6	446.5	446.5	446.4	446.4	446.2	446.0	445.7	445.4	445.2	445.6
160°	451.7	451.4	451.2	451.0	450.7	450.6	450.5	450.4	450.3	450.2	450.7
162.5°	456.2	455.9	455.6	455.3	455.0	454.8	454.7	454.6	454.6	454.5	455.0
165°	461.9	461.5	461.1	460.7	460.3	460.1	460.1	460.1	460.1	460.1	460.8
167.5°	466.4	466.0	465.6	465.2	464.8	464.6	464.5	464.5	464.4	464.4	465.1
170°	469.0	468.5	468.0	467.6	467.1	466.9	467.0	467.1	467.1	467.2	467.8
172.5°	470.7	470.2	469.7	469.3	468.8	468.6	468.7	468.8	468.8	468.9	469.5
175°	472.5	472.0	471.6	471.1	470.6	470.4	470.5	470.6	470.7	470.7	471.5
177.5°	473.4	472.9	472.5	472.0	471.6	471.4	471.6	471.7	471.8	471.9	472.5
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	13.3	13.2	13.1	13.2	13.4	13.6	13.8	14.0
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	8.4	8.9	9.4	9.6	9.7	9.7	9.7	9.8
95°	8.7	9.2	9.7	9.9	10.0	10.1	10.2	10.2
97.5°	9.4	9.5	9.5	9.6	9.7	9.7	9.8	9.9
100°	12.9	11.5	10.2	9.6	9.7	9.7	9.8	9.9
102.5°	46.1	31.7	17.3	10.1	10.1	10.1	10.2	10.2
105°	111.7	112.4	113.1	112.0	109.2	106.4	103.5	100.7
107.5°	138.2	138.5	138.9	139.2	139.5	139.8	140.1	140.4
110°	156.2	156.3	156.5	156.7	156.9	157.2	157.4	157.6



TEST NUMBER: P332928

CATALOG NUMBER: S124RDIP-S795D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.6	173.6	173.5	173.7	174.0	174.3	174.6	174.9
115°	199.6	199.8	200.0	200.0	200.0	200.0	200.0	200.0
117.5°	225.8	225.8	225.8	225.7	225.7	225.7	225.7	225.6
120°	242.0	242.2	242.4	242.4	242.2	242.0	241.9	241.7
122.5°	258.0	258.1	258.2	258.2	258.0	257.9	257.7	257.6
125°	280.4	280.6	280.8	281.0	281.1	281.2	281.2	281.3
127.5°	302.6	302.5	302.5	302.4	302.4	302.3	302.2	302.2
130°	316.1	316.2	316.3	316.3	316.3	316.3	316.3	316.3
132.5°	329.4	329.5	329.6	329.6	329.5	329.4	329.4	329.3
135°	347.7	347.9	348.0	348.2	348.3	348.5	348.7	348.8
137.5°	365.3	365.5	365.6	365.7	365.6	365.6	365.5	365.5
140°	376.1	376.4	376.6	376.8	376.9	376.9	377.0	377.1
142.5°	386.2	386.4	386.5	386.6	386.7	386.7	386.7	386.7
145°	400.6	400.7	400.7	400.8	401.0	401.2	401.3	401.5
147.5°	413.2	413.3	413.3	413.4	413.5	413.5	413.6	413.7
150°	421.3	421.3	421.3	421.3	421.4	421.5	421.5	421.6
152.5°	428.3	428.4	428.6	428.6	428.5	428.5	428.5	428.4
155°	437.8	438.1	438.4	438.5	438.2	438.0	437.8	437.5
157.5°	446.0	446.4	446.8	446.8	446.4	446.0	445.6	445.2
160°	451.2	451.7	452.1	452.1	451.7	451.2	450.7	450.2
162.5°	455.4	455.9	456.4	456.3	455.8	455.3	454.7	454.2
165°	461.4	462.0	462.7	462.6	461.9	461.2	460.5	459.8
167.5°	465.8	466.5	467.1	467.1	466.3	465.5	464.7	464.0
170°	468.5	469.1	469.7	469.6	468.9	468.1	467.3	466.5
172.5°	470.2	470.8	471.4	471.3	470.5	469.6	468.8	467.9
175°	472.2	472.9	473.6	473.5	472.5	471.6	470.6	469.7
177.5°	473.0	473.5	474.0	473.8	473.1	472.3	471.6	470.8
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5

(END OF REPORT)