

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333529-927

Luminaire Tested: **S125RDIP-S610D590U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333529-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3756.2 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	44	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	2.0
10°-20°	209.4	5.6
20°-30°	303.7	8.1
30°-40°	346.1	9.2
40°-50°	337.4	9.0
50°-60°	284.0	7.6
60°-70°	199.1	5.3
70°-80°	102.3	2.7
80°-90°	27.1	0.7
90°-100°	22.2	0.6
100°-110°	136.6	3.6
110°-120°	247.7	6.6
120°-130°	317.8	8.5
130°-140°	341.9	9.1
140°-150°	320.9	8.5
150°-160°	259.6	6.9
160°-170°	167.9	4.5
170°-180°	57.9	1.5
0°-30°	588.0	15.7
0°-40°	934.1	24.9
0°-60°	1555.4	41.4
0°-90°	1883.9	50.2
90°-120°	406.4	10.8
90°-150°	1387.0	36.9
90°-180°	1872.0	49.8
0°-180°	3756.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	0	4	7	10	11	3
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	250	248	247
125°	355	358	358	356	355	317
135°	442	445	444	443	441	341
145°	513	514	514	514	512	321
155°	565	562	563	564	561	260
165°	596	594	594	596	593	168
175°	610	607	607	611	607	58
180°	610	610	610	610	610	



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.6	10.0	9.4	8.8	8.6	8.6	8.6	8.6	8.6	8.8
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	7.0	6.4	5.9	5.3	4.7	4.8	5.4	6.0	6.6	7.2	7.8
95°	25.7	25.4	25.2	24.9	24.6	22.5	18.7	14.9	11.0	7.2	7.8
97.5°	53.8	54.3	54.9	55.4	55.9	52.4	44.9	37.3	29.8	22.3	19.4
100°	75.5	75.8	76.0	76.4	76.7	77.0	77.5	77.9	78.3	78.7	63.7
102.5°	97.5	97.9	98.3	98.7	99.0	99.3	99.6	99.9	100.1	100.4	97.5
105°	132.8	133.2	133.7	134.1	134.5	134.7	134.7	134.7	134.7	134.7	134.7
107.5°	169.6	169.6	169.6	169.6	169.6	169.7	169.8	170.1	170.3	170.5	170.5
110°	193.5	193.5	193.5	193.5	193.5	193.5	193.8	193.9	194.2	194.3	194.1



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.9	216.1	216.3	216.6	216.8	217.0	217.1	217.2	217.4	217.5	217.1
115°	249.5	250.0	250.5	251.0	251.5	251.8	251.9	252.0	252.1	252.2	251.8
117.5°	284.3	284.2	284.2	284.2	284.2	284.4	284.8	285.2	285.5	285.9	285.4
120°	306.0	305.9	305.8	305.7	305.5	305.7	306.0	306.3	306.6	306.9	306.7
122.5°	325.1	325.5	325.9	326.3	326.7	326.9	327.1	327.3	327.3	327.5	327.3
125°	354.8	355.5	356.2	356.9	357.6	358.0	358.0	358.0	358.0	358.0	357.6
127.5°	383.1	383.6	384.1	384.6	385.1	385.3	385.2	385.2	385.2	385.1	384.8
130°	400.4	400.9	401.5	402.0	402.4	402.7	402.8	403.0	403.1	403.1	402.8
132.5°	417.8	418.4	419.0	419.5	420.1	420.3	420.1	419.9	419.6	419.5	419.4
135°	442.5	443.1	443.7	444.3	444.9	445.1	444.9	444.7	444.5	444.3	444.1
137.5°	465.2	465.7	466.2	466.8	467.2	467.5	467.2	467.1	466.9	466.7	466.8
140°	480.0	480.2	480.4	480.6	480.8	480.9	480.8	480.6	480.5	480.5	480.6
142.5°	493.4	493.5	493.6	493.8	493.8	494.0	494.2	494.2	494.4	494.6	494.6
145°	513.0	513.2	513.4	513.6	513.8	513.9	513.9	513.9	513.9	513.9	514.0
147.5°	530.1	530.1	530.0	530.0	530.0	530.0	530.1	530.3	530.4	530.5	530.7
150°	541.0	540.8	540.6	540.4	540.2	540.2	540.4	540.6	540.8	541.0	541.2
152.5°	551.5	551.0	550.6	550.2	549.7	549.6	549.8	550.0	550.2	550.4	550.6
155°	565.0	564.4	563.8	563.2	562.5	562.4	562.5	562.8	562.9	563.2	563.5
157.5°	575.4	575.0	574.6	574.3	573.9	573.8	573.8	573.8	573.8	573.9	574.2
160°	582.6	582.0	581.4	580.7	580.2	580.0	580.0	580.1	580.2	580.4	580.7
162.5°	588.4	587.8	587.2	586.5	586.0	585.7	585.8	585.9	586.0	586.1	586.7
165°	596.1	595.6	594.9	594.4	593.7	593.5	593.6	593.7	593.8	593.9	594.5
167.5°	601.9	601.3	600.7	600.1	599.4	599.2	599.3	599.4	599.4	599.6	600.3
170°	605.2	604.5	603.8	603.1	602.4	602.1	602.1	602.3	602.4	602.5	603.2
172.5°	607.4	606.7	605.9	605.2	604.5	604.3	604.4	604.7	604.8	605.0	605.7
175°	609.7	609.1	608.5	607.9	607.3	607.0	607.1	607.3	607.4	607.4	608.2
177.5°	610.8	610.3	609.8	609.3	608.9	608.6	608.7	608.8	608.9	609.0	609.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	8.9	9.0	9.1	9.1	9.0	9.0	9.0	8.9
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	8.2	8.7	9.3	9.6	9.7	9.8	10.0	10.1
95°	8.2	8.7	9.3	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.7	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.7	33.7	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.7	91.8	89.0	84.2	77.3	70.5	63.7	56.9
105°	134.7	134.7	134.7	134.7	134.5	134.4	134.4	134.2
107.5°	170.6	170.6	170.6	170.4	170.2	169.8	169.5	169.2
110°	193.8	193.5	193.1	193.1	193.1	193.2	193.4	193.5



TEST NUMBER: P333529-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.7	216.3	215.9	215.7	215.6	215.4	215.3	215.2
115°	251.4	251.0	250.6	250.1	249.5	248.9	248.3	247.7
117.5°	284.9	284.3	283.8	283.4	283.2	282.9	282.7	282.4
120°	306.5	306.3	306.1	305.7	305.2	304.8	304.2	303.7
122.5°	327.1	326.9	326.7	326.3	325.7	325.1	324.6	324.0
125°	357.2	356.7	356.3	356.0	355.7	355.4	355.1	354.8
127.5°	384.6	384.4	384.2	383.7	382.9	382.2	381.5	380.7
130°	402.6	402.3	402.0	401.6	401.1	400.5	400.1	399.6
132.5°	419.3	419.2	419.2	418.9	418.4	417.9	417.4	416.9
135°	443.9	443.7	443.5	443.1	442.5	441.9	441.2	440.7
137.5°	466.8	466.8	466.8	466.6	466.1	465.6	465.1	464.5
140°	480.9	481.0	481.3	481.0	480.5	479.8	479.3	478.6
142.5°	494.6	494.6	494.7	494.4	493.8	493.2	492.6	492.0
145°	514.1	514.2	514.3	514.0	513.4	512.9	512.2	511.6
147.5°	530.8	530.9	531.0	530.7	530.0	529.3	528.5	527.8
150°	541.4	541.6	541.8	541.5	540.7	539.9	539.1	538.3
152.5°	550.8	551.0	551.2	551.0	550.2	549.5	548.7	548.0
155°	563.8	564.0	564.4	564.1	563.3	562.5	561.7	560.9
157.5°	574.5	574.8	575.1	574.9	574.1	573.2	572.4	571.6
160°	581.1	581.5	581.9	581.7	580.9	580.1	579.3	578.5
162.5°	587.2	587.8	588.4	588.2	587.3	586.5	585.6	584.6
165°	595.1	595.7	596.3	596.2	595.4	594.6	593.8	592.9
167.5°	601.0	601.7	602.5	602.4	601.5	600.6	599.7	598.7
170°	604.1	604.9	605.7	605.6	604.8	603.8	602.9	602.1
172.5°	606.4	607.2	607.9	607.8	606.9	606.0	605.1	604.2
175°	609.0	609.8	610.7	610.6	609.7	608.8	607.9	607.0
177.5°	610.1	610.7	611.2	611.2	610.5	609.9	609.3	608.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7

(END OF REPORT)