

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333535-927

Luminaire Tested: **S125RDIP-S610D810U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333535-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D810U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4450.8 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	49	38	31	27	32	27	23	26	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	1.7
10°-20°	209.4	4.7
20°-30°	303.7	6.8
30°-40°	346.1	7.8
40°-50°	337.4	7.6
50°-60°	284.0	6.4
60°-70°	199.1	4.5
70°-80°	102.3	2.3
80°-90°	27.6	0.6
90°-100°	30.4	0.7
100°-110°	187.2	4.2
110°-120°	339.5	7.6
120°-130°	435.7	9.8
130°-140°	468.6	10.5
140°-150°	439.8	9.9
150°-160°	355.8	8.0
160°-170°	230.1	5.2
170°-180°	79.4	1.8
0°-30°	588.0	13.2
0°-40°	934.1	21.0
0°-60°	1555.4	34.9
0°-90°	1884.4	42.3
90°-120°	557.0	12.5
90°-150°	1901.1	42.7
90°-180°	2566.0	57.7
0°-180°	4450.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	1	6	10	13	15	3
95°	35	32	10	13	13	45
105°	182	184	185	185	184	193
115°	342	345	346	343	340	339
125°	486	490	491	488	486	434
135°	606	610	609	608	604	467
145°	703	704	704	705	701	440
155°	774	771	772	773	769	357
165°	817	814	814	817	813	231
175°	836	832	833	837	832	80
180°	836	836	836	836	836	



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.7	10.1	9.6	9.1	8.9	9.0	9.0	9.1	9.2	9.3
90°	0.6	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6
92.5°	9.5	8.8	8.0	7.2	6.5	6.5	7.4	8.2	9.0	9.9	10.6
95°	35.3	34.9	34.5	34.1	33.7	30.8	25.6	20.4	15.1	9.9	10.6
97.5°	73.8	74.5	75.2	76.0	76.7	71.9	61.6	51.2	40.8	30.5	26.6
100°	103.5	103.9	104.3	104.7	105.1	105.6	106.2	106.7	107.3	107.8	87.3
102.5°	133.7	134.2	134.8	135.2	135.8	136.2	136.6	136.9	137.2	137.5	133.6
105°	182.1	182.7	183.2	183.8	184.3	184.6	184.6	184.6	184.6	184.6	184.6
107.5°	232.4	232.4	232.4	232.4	232.4	232.6	232.8	233.1	233.4	233.7	233.7
110°	265.1	265.1	265.1	265.1	265.1	265.3	265.5	265.9	266.1	266.4	266.0



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.9	296.2	296.5	296.9	297.2	297.5	297.6	297.8	297.9	298.1	297.6
115°	342.0	342.7	343.3	344.0	344.8	345.2	345.3	345.4	345.5	345.7	345.2
117.5°	389.7	389.7	389.6	389.6	389.6	389.8	390.3	390.9	391.4	391.9	391.2
120°	419.4	419.3	419.1	419.0	418.8	419.0	419.4	419.9	420.3	420.6	420.4
122.5°	445.7	446.2	446.7	447.3	447.7	448.1	448.3	448.5	448.7	448.9	448.6
125°	486.3	487.3	488.2	489.3	490.2	490.7	490.7	490.7	490.7	490.7	490.1
127.5°	525.1	525.8	526.5	527.2	527.8	528.1	528.1	528.0	527.9	527.8	527.5
130°	548.9	549.6	550.2	551.0	551.7	552.1	552.2	552.3	552.5	552.6	552.2
132.5°	572.7	573.5	574.3	575.0	575.9	576.2	575.8	575.5	575.2	574.9	574.8
135°	606.5	607.4	608.2	609.0	609.8	610.1	609.8	609.5	609.3	609.0	608.7
137.5°	637.6	638.3	639.1	639.8	640.5	640.7	640.5	640.2	640.0	639.7	639.8
140°	657.9	658.2	658.5	658.8	659.0	659.1	658.9	658.9	658.7	658.5	658.9
142.5°	676.3	676.4	676.6	676.8	676.9	677.1	677.3	677.5	677.7	677.9	677.9
145°	703.1	703.5	703.7	704.0	704.3	704.4	704.4	704.4	704.4	704.4	704.6
147.5°	726.7	726.7	726.6	726.5	726.5	726.5	726.7	726.8	727.1	727.2	727.4
150°	741.6	741.3	741.0	740.8	740.5	740.5	740.8	741.0	741.3	741.6	741.9
152.5°	756.0	755.3	754.7	754.2	753.5	753.4	753.6	753.9	754.2	754.5	754.7
155°	774.4	773.6	772.8	771.9	771.1	770.8	771.1	771.3	771.7	771.9	772.3
157.5°	788.6	788.1	787.7	787.2	786.6	786.4	786.5	786.5	786.5	786.6	787.0
160°	798.6	797.7	796.9	796.1	795.3	795.0	795.0	795.2	795.4	795.4	796.0
162.5°	806.5	805.6	804.9	804.0	803.2	802.9	803.0	803.1	803.3	803.4	804.1
165°	817.1	816.3	815.5	814.7	813.8	813.5	813.7	813.8	813.9	814.0	814.9
167.5°	825.1	824.3	823.4	822.5	821.7	821.3	821.4	821.6	821.7	821.9	822.8
170°	829.6	828.5	827.6	826.6	825.7	825.3	825.4	825.5	825.7	825.9	827.0
172.5°	832.5	831.6	830.6	829.7	828.6	828.3	828.5	828.8	829.0	829.3	830.3
175°	835.8	834.9	834.1	833.3	832.4	832.1	832.2	832.3	832.5	832.7	833.8
177.5°	837.3	836.5	835.9	835.3	834.6	834.3	834.4	834.5	834.6	834.7	835.5
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	9.5	9.6	9.7	9.8	9.8	9.7	9.7	9.7
90°	11.3	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	11.3	12.0	12.7	13.1	13.3	13.5	13.7	13.9
95°	11.3	12.0	12.7	13.0	13.0	13.0	13.0	13.0
97.5°	22.7	18.9	15.0	13.0	13.0	13.0	13.0	13.0
100°	66.8	46.3	25.7	15.2	14.7	14.1	13.5	13.0
102.5°	129.8	125.9	122.0	115.4	106.0	96.6	87.3	78.0
105°	184.6	184.6	184.6	184.6	184.4	184.3	184.1	184.0
107.5°	233.8	233.8	233.8	233.6	233.2	232.7	232.3	232.0
110°	265.5	265.1	264.7	264.6	264.7	264.9	265.0	265.1



TEST NUMBER: P333535-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.1	296.5	296.0	295.6	295.5	295.2	295.1	294.9
115°	344.6	344.0	343.5	342.8	342.0	341.1	340.3	339.5
117.5°	390.5	389.8	389.0	388.5	388.2	387.8	387.5	387.1
120°	420.1	419.9	419.5	419.1	418.4	417.7	417.0	416.3
122.5°	448.4	448.1	447.8	447.3	446.5	445.7	444.9	444.1
125°	489.6	489.0	488.5	488.0	487.6	487.1	486.7	486.3
127.5°	527.2	527.0	526.6	525.9	525.0	523.9	522.9	521.9
130°	551.8	551.4	551.0	550.4	549.7	549.1	548.3	547.6
132.5°	574.7	574.6	574.6	574.2	573.5	572.8	572.1	571.5
135°	608.5	608.2	607.9	607.4	606.5	605.7	604.8	604.0
137.5°	639.8	639.8	639.9	639.6	638.9	638.2	637.5	636.8
140°	659.1	659.4	659.7	659.4	658.5	657.7	656.9	656.1
142.5°	678.0	678.0	678.1	677.7	676.9	676.0	675.3	674.4
145°	704.6	704.8	705.0	704.6	703.8	703.0	702.1	701.3
147.5°	727.5	727.7	727.9	727.5	726.4	725.5	724.5	723.5
150°	742.1	742.4	742.7	742.3	741.2	740.1	738.9	737.8
152.5°	755.0	755.3	755.6	755.2	754.2	753.2	752.3	751.2
155°	772.8	773.2	773.6	773.2	772.1	771.0	769.9	768.8
157.5°	787.4	787.9	788.3	788.0	786.9	785.8	784.7	783.5
160°	796.5	797.1	797.6	797.4	796.3	795.2	794.1	793.0
162.5°	804.9	805.7	806.4	806.3	805.0	803.8	802.6	801.5
165°	815.7	816.5	817.4	817.2	816.1	815.0	813.9	812.8
167.5°	823.9	824.8	825.9	825.7	824.4	823.2	822.0	820.8
170°	828.0	829.1	830.2	830.1	828.9	827.7	826.4	825.2
172.5°	831.2	832.3	833.3	833.1	831.9	830.7	829.4	828.1
175°	834.8	835.9	837.0	836.9	835.8	834.5	833.3	832.0
177.5°	836.3	837.0	837.8	837.8	836.9	836.0	835.1	834.2
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8

(END OF REPORT)