

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333573-927

Luminaire Tested: **S125RDIP-S850D1035U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333573-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5517.1 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	40	41	37	34	33	31	28	25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	1.9
10°-20°	286.2	5.2
20°-30°	415.1	7.5
30°-40°	473.1	8.6
40°-50°	461.1	8.4
50°-60°	388.2	7.0
60°-70°	272.1	4.9
70°-80°	139.9	2.5
80°-90°	37.5	0.7
90°-100°	284.3	5.2
100°-110°	611.2	11.1
110°-120°	573.6	10.4
120°-130°	464.9	8.4
130°-140°	373.0	6.8
140°-150°	281.5	5.1
150°-160°	198.2	3.6
160°-170°	116.8	2.1
170°-180°	38.0	0.7
0°-30°	803.8	14.6
0°-40°	1276.8	23.1
0°-60°	2126.1	38.5
0°-90°	2575.6	46.7
90°-120°	1469.1	26.6
90°-150°	2588.5	46.9
90°-180°	2941.0	53.3
0°-180°	5517.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	7	13	17	18	4
95°	26	77	701	318	186	28
105°	89	125	573	1129	1048	94
115°	160	193	460	992	1167	157
125°	221	259	441	789	920	196
135°	259	312	438	662	764	201
145°	302	346	440	548	603	189
155°	345	371	429	484	505	159
165°	376	387	411	436	443	106
175°	391	391	395	399	398	37
180°	392	392	392	392	392	



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.3	14.4	13.7	13.0	12.3	12.0	12.0	12.2	12.2	12.4	12.6
90°	0.8	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5
92.5°	9.7	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4
95°	26.1	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6
97.5°	43.3	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5
100°	55.4	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8
102.5°	68.7	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3
105°	89.4	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3
107.5°	109.6	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6
110°	124.1	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.7	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6
115°	159.8	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6
117.5°	178.7	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7
120°	191.4	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4
122.5°	204.7	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0
125°	221.4	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6
127.5°	234.6	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3
130°	242.8	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8
132.5°	249.1	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2
135°	259.4	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2
137.5°	272.4	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2
140°	280.0	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3
142.5°	288.8	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2
145°	302.1	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4
147.5°	316.0	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5
150°	324.2	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7
152.5°	333.1	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3
155°	344.8	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8
157.5°	355.2	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9
160°	362.2	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2
162.5°	367.9	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2
165°	376.4	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6
167.5°	382.1	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1
170°	386.0	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7
172.5°	388.5	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2
175°	391.4	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4
177.5°	392.8	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	12.8	12.9	13.1	13.3	13.2	13.0	13.0	12.8
90°	14.3	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.1	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	568.6	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	846.8	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	972.7	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1015.1	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	990.1	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	900.9	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	835.1	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333573-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	783.2	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	718.0	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	676.0	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	653.2	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	636.1	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	611.3	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	586.0	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	570.2	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	554.4	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	533.8	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	516.4	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	506.9	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	498.7	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	487.9	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	477.8	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	472.1	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	465.8	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	456.3	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	446.8	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	440.5	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	433.6	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	423.9	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	414.7	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	409.6	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	403.9	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	393.5	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)