

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332523-935

Luminaire Tested: **S124DIP-S350D1035U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332523-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D1035U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4863.2 lumens  
Efficiency: N/A  
Efficacy: 130.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	59	58	46	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4106	4106	4106
5°	4118	4068	4099
10°	4092	4036	4055
15°	4043	3978	3989
20°	3978	3907	3911
25°	3902	3827	3815
30°	3811	3731	3697
35°	3714	3631	3582
40°	3616	3518	3453
45°	3513	3406	3342
50°	3399	3307	3204
55°	3275	3178	3074
60°	3152	3034	2942
65°	3012	2896	2779
70°	2858	2712	2608
75°	2617	2492	2427
80°	2329	2236	2176
85°	2038	1964	1927



TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.9	1.0
10°-20°	135.0	2.8
20°-30°	198.6	4.1
30°-40°	230.9	4.7
40°-50°	230.9	4.7
50°-60°	202.0	4.2
60°-70°	150.0	3.1
70°-80°	85.2	1.8
80°-90°	27.9	0.6
90°-100°	39.3	0.8
100°-110°	250.6	5.2
110°-120°	479.4	9.9
120°-130°	608.6	12.5
130°-140°	651.1	13.4
140°-150°	608.9	12.5
150°-160°	491.0	10.1
160°-170°	316.7	6.5
170°-180°	109.2	2.2
0°-30°	381.5	7.8
0°-40°	612.4	12.6
0°-60°	1045.3	21.5
0°-90°	1308.5	26.9
90°-120°	769.3	15.8
90°-150°	2637.9	54.2
90°-180°	3555.0	73.1
0°-180°	4863.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	508	506	502	506	506	48
15°	484	482	476	478	477	136
25°	438	435	430	430	428	201
35°	377	374	368	366	364	236
45°	308	305	298	294	293	237
55°	233	231	226	221	218	208
65°	158	156	152	148	146	156
75°	84	82	80	78	78	89
85°	22	22	21	21	21	24
90°	3	12	19	24	26	3
95°	47	20	19	24	25	61
105°	259	264	268	274	245	271
115°	483	485	485	486	486	475
125°	679	682	681	683	684	606
135°	842	842	845	847	848	649
145°	971	974	974	975	976	607
155°	1065	1066	1063	1066	1064	491
165°	1123	1119	1119	1125	1118	317
175°	1149	1144	1145	1152	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	509.9	509.7	509.5	509.3	509.0	508.5	507.7	507.0	506.2	505.3	506.1
5°	508.2	507.8	507.5	507.1	506.8	506.1	505.1	504.1	503.1	502.0	503.1
7.5°	503.5	503.1	502.7	502.4	502.0	501.3	500.2	499.1	498.0	496.9	497.7
10°	499.2	498.9	498.5	498.2	497.8	497.1	495.8	494.6	493.5	492.3	493.0
12.5°	493.7	493.4	493.0	492.6	492.2	491.5	490.2	489.0	487.7	486.5	487.2
15°	483.7	483.4	483.0	482.7	482.3	481.5	480.1	478.7	477.3	476.0	476.6
17.5°	471.7	471.3	470.9	470.5	469.9	469.1	467.8	466.5	465.2	463.9	464.3
20°	463.0	462.5	462.1	461.6	461.2	460.3	458.9	457.5	456.2	454.8	455.1
22.5°	453.5	452.9	452.3	451.7	451.1	450.1	448.8	447.5	446.1	444.7	445.2
25°	438.1	437.5	436.9	436.2	435.6	434.6	433.3	432.0	430.8	429.6	429.6
27.5°	420.5	419.8	419.2	418.5	417.9	417.0	415.8	414.7	413.5	412.2	412.1
30°	408.8	408.0	407.3	406.6	405.9	404.9	403.7	402.5	401.4	400.2	399.8
32.5°	396.4	395.7	395.0	394.4	393.7	392.8	391.6	390.3	389.1	387.8	387.4
35°	376.9	376.3	375.7	375.1	374.4	373.5	372.2	370.9	369.7	368.4	367.8
37.5°	356.5	355.9	355.3	354.8	354.2	353.3	351.9	350.5	349.1	347.8	347.1
40°	343.1	342.4	341.7	341.0	340.3	339.2	337.9	336.5	335.1	333.8	332.9
42.5°	328.8	328.4	328.0	327.5	327.1	326.1	324.6	323.0	321.6	320.1	319.0
45°	307.7	307.0	306.4	305.8	305.1	304.1	302.6	301.2	299.8	298.3	297.3
47.5°	285.6	285.2	284.7	284.3	283.9	283.0	281.6	280.3	279.0	277.6	276.5
50°	270.6	270.3	269.9	269.5	269.1	268.4	267.1	265.8	264.5	263.3	262.0
52.5°	256.0	255.5	255.0	254.6	254.2	253.3	251.9	250.6	249.3	248.0	246.8
55°	232.7	232.5	232.1	231.9	231.6	230.8	229.5	228.3	227.0	225.8	224.7
57.5°	210.5	210.3	209.9	209.7	209.3	208.5	207.2	206.0	204.7	203.5	202.5
60°	195.2	194.8	194.3	193.8	193.4	192.6	191.4	190.2	189.1	187.9	187.1
62.5°	180.2	179.9	179.4	179.1	178.7	177.9	176.6	175.4	174.1	172.9	172.1
65°	157.7	157.3	156.8	156.4	155.9	155.2	154.3	153.4	152.5	151.6	150.7
67.5°	135.1	134.7	134.2	133.8	133.4	132.8	131.9	131.0	130.2	129.2	128.4
70°	121.1	120.4	119.8	119.2	118.5	117.8	117.1	116.4	115.6	114.9	114.2
72.5°	106.1	105.4	104.8	104.2	103.5	102.9	102.3	101.8	101.2	100.6	100.0
75°	83.9	83.5	83.1	82.6	82.1	81.7	81.3	80.8	80.3	79.9	79.6
77.5°	62.9	62.7	62.4	62.3	62.1	61.7	61.4	61.0	60.5	60.2	60.0
80°	50.1	49.9	49.6	49.3	49.1	48.8	48.6	48.5	48.3	48.1	47.9
82.5°	37.7	37.6	37.5	37.4	37.2	37.1	37.1	37.1	37.0	37.0	36.9
85°	22.0	22.0	22.0	22.0	22.0	22.0	21.7	21.5	21.4	21.2	21.2
87.5°	9.0	9.3	9.7	10.1	10.4	10.7	10.9	11.1	11.4	11.6	11.8
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	10.8	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4
95°	47.3	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1
97.5°	100.4	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8
100°	140.9	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6
102.5°	186.3	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1
105°	258.7	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9
107.5°	325.9	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2
110°	371.3	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4



TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3
115°	483.0	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2
117.5°	544.1	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3
120°	585.3	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3
122.5°	623.8	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3
125°	679.0	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3
127.5°	731.2	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0
130°	765.0	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6
132.5°	795.9	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9
135°	842.3	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2
137.5°	883.4	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9
140°	910.2	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2
142.5°	934.3	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8
145°	971.2	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0
147.5°	1000.7	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8
150°	1021.9	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5
152.5°	1039.8	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4
155°	1065.0	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9
157.5°	1086.1	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7
160°	1098.5	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1
162.5°	1109.5	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5
165°	1123.3	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6
167.5°	1134.4	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1
170°	1140.6	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8
172.5°	1144.7	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9
175°	1149.2	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6
177.5°	1151.2	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	506.8	507.6	508.2	508.6	508.5	508.4	508.3	508.2
5°	504.1	505.1	506.1	506.4	506.3	506.1	505.9	505.8
7.5°	498.4	499.3	500.1	500.4	500.3	500.2	500.1	500.0
10°	493.8	494.5	495.2	495.5	495.3	495.1	494.9	494.7
12.5°	488.0	488.8	489.7	489.9	489.7	489.4	489.1	488.9
15°	477.1	477.6	478.2	478.3	478.0	477.8	477.5	477.3
17.5°	464.6	464.9	465.3	465.4	465.2	465.0	464.9	464.7
20°	455.4	455.6	455.9	456.0	455.7	455.6	455.4	455.2
22.5°	445.7	446.2	446.7	446.8	446.4	446.1	445.7	445.5
25°	429.7	429.8	429.9	429.8	429.4	429.0	428.7	428.3
27.5°	411.8	411.6	411.4	411.0	410.6	410.2	409.7	409.2
30°	399.5	399.2	398.7	398.4	397.9	397.4	397.0	396.6
32.5°	386.9	386.5	386.1	385.6	385.2	384.7	384.3	383.8
35°	367.1	366.5	365.8	365.3	364.9	364.5	363.9	363.5
37.5°	346.4	345.7	345.0	344.4	343.8	343.2	342.6	342.0
40°	332.0	331.1	330.2	329.5	329.0	328.6	328.1	327.7
42.5°	318.0	316.9	315.9	315.2	314.9	314.6	314.3	314.0
45°	296.4	295.3	294.4	293.7	293.4	293.2	292.9	292.7
47.5°	275.3	274.2	273.1	272.2	271.6	270.9	270.2	269.5
50°	260.7	259.5	258.2	257.3	256.8	256.2	255.6	255.1
52.5°	245.7	244.6	243.5	242.5	241.9	241.2	240.5	239.8
55°	223.6	222.5	221.4	220.6	220.1	219.6	219.0	218.4
57.5°	201.5	200.4	199.4	198.6	198.1	197.6	197.1	196.5
60°	186.2	185.5	184.6	184.0	183.6	183.0	182.6	182.2
62.5°	171.4	170.7	169.9	169.3	168.8	168.4	168.0	167.5
65°	149.8	148.9	148.0	147.3	146.9	146.4	145.9	145.5
67.5°	127.5	126.7	125.8	125.3	125.2	125.0	124.9	124.8
70°	113.5	112.8	112.0	111.5	111.2	111.0	110.7	110.5
72.5°	99.4	98.8	98.2	97.8	97.6	97.3	97.0	96.8
75°	79.1	78.8	78.4	78.2	78.1	78.0	77.9	77.8
77.5°	59.9	59.8	59.8	59.6	59.3	59.1	58.8	58.6
80°	47.7	47.5	47.4	47.3	47.1	47.0	46.9	46.8
82.5°	36.8	36.7	36.6	36.5	36.4	36.2	36.2	36.1
85°	21.2	21.2	21.2	21.2	21.1	21.0	20.8	20.8
87.5°	12.1	12.3	12.5	12.7	12.7	12.8	12.9	13.0
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	20.5	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	21.2	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	22.9	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	31.3	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	112.2	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	271.6	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.0	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	379.8	380.2	380.6	381.1	381.6	382.2	382.8	383.3





TEST NUMBER: P332523-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	422.2	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.5	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.2	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.6	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	681.9	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.9	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	768.8	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.1	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	845.7	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.4	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	914.8	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.3	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.2	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1004.9	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1041.6	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1064.7	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1107.6	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1122.1	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1132.7	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1139.4	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1143.5	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1148.3	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1150.2	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)