

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333578-927

Luminaire Tested: **S125RDIP-S850D1205U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333578-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D1205U927-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5876.8 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.4	1.7
10°-20°	286.2	4.9
20°-30°	415.1	7.1
30°-40°	473.1	8.0
40°-50°	461.1	7.8
50°-60°	388.2	6.6
60°-70°	272.1	4.6
70°-80°	139.9	2.4
80°-90°	37.9	0.6
90°-100°	79.2	1.3
100°-110°	234.0	4.0
110°-120°	396.3	6.7
120°-130°	521.5	8.9
130°-140°	584.4	9.9
140°-150°	572.7	9.7
150°-160°	481.1	8.2
160°-170°	319.8	5.4
170°-180°	111.9	1.9
0°-30°	803.8	13.7
0°-40°	1276.8	21.7
0°-60°	2126.1	36.2
0°-90°	2576.0	43.8
90°-120°	709.5	12.1
90°-150°	2388.1	40.6
90°-180°	3301.0	56.2
0°-180°	5876.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	8	15	19	22	5
95°	60	62	71	77	79	64
105°	210	215	220	225	228	224
115°	397	400	402	401	400	392
125°	579	584	586	584	583	518
135°	753	758	760	759	756	580
145°	912	916	919	919	916	570
155°	1044	1044	1045	1048	1044	481
165°	1135	1133	1134	1137	1132	320
175°	1180	1177	1176	1181	1176	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.3	14.7	13.9	13.2	12.5	12.3	12.4	12.5	12.7	12.8	13.0
90°	1.0	2.5	4.2	5.9	7.4	9.0	10.5	11.9	13.3	14.7	15.8
92.5°	22.3	23.4	24.6	25.7	26.9	28.3	30.1	31.8	33.6	35.3	36.7
95°	59.8	60.2	60.7	61.1	61.5	62.7	64.7	66.8	68.8	70.9	72.3
97.5°	99.4	99.6	99.7	99.9	100.1	101.6	104.4	107.2	110.0	112.9	114.2
100°	128.9	128.9	128.9	128.9	128.9	130.2	132.8	135.5	138.2	140.9	142.7
102.5°	160.6	161.4	162.2	163.0	163.8	164.9	166.3	167.6	169.0	170.3	172.3
105°	209.8	210.9	211.9	212.9	214.0	215.1	216.3	217.5	218.8	220.0	221.3
107.5°	264.4	265.4	266.4	267.4	268.5	269.4	270.4	271.3	272.3	273.2	273.9
110°	302.0	302.9	304.0	305.0	306.0	306.8	307.4	308.1	308.7	309.3	309.9



TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	340.2	340.8	341.3	341.8	342.4	343.0	343.8	344.6	345.3	346.1	346.4
115°	396.7	397.6	398.4	399.2	400.1	400.6	401.1	401.5	401.9	402.3	402.1
117.5°	453.4	453.8	454.2	454.6	455.0	455.3	455.7	456.1	456.4	456.8	456.9
120°	488.8	489.8	490.8	491.9	492.9	493.5	493.7	493.9	494.2	494.3	494.3
122.5°	527.1	527.5	527.8	528.2	528.5	529.0	529.6	530.1	530.6	531.2	531.0
125°	579.0	580.3	581.5	582.7	583.9	584.6	584.9	585.0	585.3	585.5	585.0
127.5°	634.3	634.9	635.6	636.4	637.1	637.5	637.8	638.0	638.3	638.5	638.3
130°	667.4	668.4	669.5	670.5	671.5	672.2	672.6	673.0	673.4	673.8	673.7
132.5°	700.5	702.2	703.9	705.6	707.3	708.1	708.0	707.9	707.8	707.7	707.5
135°	753.0	754.2	755.5	756.7	758.0	758.7	758.8	759.1	759.2	759.5	759.5
137.5°	802.3	803.5	804.7	805.9	807.1	807.9	808.3	808.8	809.3	809.7	809.9
140°	834.0	835.0	836.1	837.1	838.1	838.9	839.6	840.2	840.7	841.4	841.8
142.5°	865.7	866.6	867.4	868.2	869.1	870.0	870.7	871.5	872.3	873.1	873.3
145°	912.3	913.1	913.9	914.7	915.5	916.2	916.9	917.5	918.1	918.7	918.7
147.5°	955.4	955.8	956.2	956.7	957.1	957.6	958.1	958.6	959.1	959.6	960.0
150°	984.0	983.9	983.7	983.5	983.3	983.6	984.4	985.2	986.0	986.8	986.8
152.5°	1007.7	1007.9	1008.2	1008.5	1008.8	1009.1	1009.4	1009.7	1010.1	1010.4	1010.9
155°	1043.9	1043.9	1043.9	1043.9	1043.9	1044.0	1044.3	1044.4	1044.7	1044.8	1045.7
157.5°	1076.3	1075.9	1075.4	1075.0	1074.5	1074.4	1074.6	1074.8	1075.0	1075.2	1076.0
160°	1095.4	1094.9	1094.2	1093.6	1093.0	1092.8	1093.0	1093.2	1093.4	1093.6	1094.4
162.5°	1112.4	1112.0	1111.5	1111.0	1110.6	1110.4	1110.4	1110.5	1110.5	1110.6	1111.5
165°	1135.0	1134.6	1134.2	1133.9	1133.4	1133.3	1133.5	1133.7	1133.9	1134.1	1135.0
167.5°	1154.2	1153.3	1152.5	1151.8	1150.9	1150.5	1150.5	1150.5	1150.5	1150.5	1151.8
170°	1164.5	1163.7	1162.8	1162.1	1161.3	1160.8	1160.8	1160.8	1160.8	1160.8	1162.1
172.5°	1171.9	1171.1	1170.2	1169.4	1168.6	1168.2	1168.2	1168.2	1168.2	1168.2	1169.4
175°	1180.1	1179.3	1178.5	1177.7	1176.9	1176.5	1176.5	1176.5	1176.5	1176.5	1177.7
177.5°	1184.4	1183.8	1183.0	1182.4	1181.8	1181.4	1181.2	1181.1	1180.8	1180.7	1181.7
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	13.2	13.5	13.6	13.7	13.7	13.7	13.6	13.6
90°	16.8	17.8	18.9	19.6	20.3	20.8	21.5	22.1
92.5°	38.0	39.4	40.7	41.7	42.1	42.5	43.0	43.4
95°	73.8	75.2	76.6	77.6	78.0	78.3	78.7	79.1
97.5°	115.6	116.9	118.3	119.1	119.3	119.5	119.8	120.0
100°	144.5	146.4	148.2	149.3	149.7	150.1	150.6	151.0
102.5°	174.3	176.3	178.3	179.6	180.2	180.8	181.3	181.9
105°	222.4	223.7	224.9	225.9	226.5	227.0	227.7	228.3
107.5°	274.4	275.0	275.7	276.0	275.9	275.9	275.8	275.8
110°	310.5	311.2	311.7	312.0	311.7	311.6	311.3	311.2





TEST NUMBER: P333578-927

CATALOG NUMBER: S125RDIP-S850D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.7	347.0	347.3	347.2	346.9	346.5	346.1	345.8
115°	401.9	401.6	401.5	401.2	401.1	400.8	400.6	400.4
117.5°	457.1	457.2	457.4	457.1	456.3	455.5	454.6	453.8
120°	494.3	494.3	494.3	493.9	493.1	492.3	491.5	490.7
122.5°	530.8	530.7	530.5	530.1	529.4	528.8	528.1	527.5
125°	584.6	584.2	583.8	583.5	583.4	583.1	582.9	582.7
127.5°	638.1	637.9	637.7	637.4	637.0	636.5	636.1	635.7
130°	673.4	673.2	673.0	672.7	672.3	671.9	671.5	671.1
132.5°	707.3	707.1	706.9	706.5	705.9	705.4	704.8	704.3
135°	759.5	759.5	759.5	759.1	758.2	757.4	756.6	755.7
137.5°	810.2	810.5	810.7	810.3	809.3	808.3	807.2	806.2
140°	842.2	842.6	843.0	842.7	841.7	840.7	839.6	838.6
142.5°	873.5	873.8	874.0	873.6	872.6	871.6	870.6	869.6
145°	918.7	918.7	918.7	918.4	917.8	917.2	916.6	915.9
147.5°	960.6	961.1	961.6	961.1	959.7	958.3	957.0	955.5
150°	986.8	986.8	986.8	986.7	986.2	985.8	985.4	985.0
152.5°	1011.4	1011.9	1012.3	1012.3	1011.5	1010.7	1010.0	1009.3
155°	1046.5	1047.3	1048.1	1048.0	1046.9	1045.9	1045.0	1043.9
157.5°	1076.8	1077.7	1078.5	1078.2	1076.9	1075.5	1074.2	1072.9
160°	1095.3	1096.1	1096.9	1096.8	1095.7	1094.7	1093.7	1092.7
162.5°	1112.5	1113.5	1114.5	1114.4	1113.2	1112.0	1110.8	1109.6
165°	1135.8	1136.5	1137.4	1137.2	1136.0	1134.7	1133.5	1132.3
167.5°	1152.9	1154.2	1155.4	1155.4	1154.1	1152.9	1151.6	1150.3
170°	1163.2	1164.5	1165.7	1165.6	1164.2	1162.8	1161.3	1159.9
172.5°	1170.6	1171.9	1173.1	1173.1	1171.8	1170.5	1169.3	1168.0
175°	1178.9	1180.1	1181.4	1181.3	1179.9	1178.5	1176.9	1175.5
177.5°	1182.6	1183.7	1184.6	1184.6	1183.4	1182.3	1181.1	1180.0
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9

(END OF REPORT)