

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333553-927

Luminaire Tested: **S125RDIP-S850D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333553-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D365U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3734.2 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	56	53	50
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	52	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	43	40	37
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	35	58	47	40	34	43	36	32	39	33	30	35	31	27	25
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	2.7
10°-20°	286.2	7.7
20°-30°	415.1	11.1
30°-40°	473.1	12.7
40°-50°	461.1	12.3
50°-60°	388.2	10.4
60°-70°	272.1	7.3
70°-80°	139.9	3.7
80°-90°	36.1	1.0
90°-100°	13.7	0.4
100°-110°	84.6	2.3
110°-120°	153.4	4.1
120°-130°	196.9	5.3
130°-140°	211.8	5.7
140°-150°	198.8	5.3
150°-160°	160.8	4.3
160°-170°	104.0	2.8
170°-180°	35.9	1.0
0°-30°	803.8	21.5
0°-40°	1276.8	34.2
0°-60°	2126.1	56.9
0°-90°	2574.2	68.9
90°-120°	251.8	6.7
90°-150°	859.3	23.0
90°-180°	1160.0	31.1
0°-180°	3734.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	0	3	4	6	7	3
95°	16	15	4	6	6	20
105°	82	83	83	83	83	87
115°	155	156	156	155	153	153
125°	220	222	222	221	220	196
135°	274	276	275	275	273	211
145°	318	318	318	319	317	199
155°	350	348	349	350	348	161
165°	369	368	368	369	367	104
175°	378	376	376	378	376	36
180°	378	378	378	378	378	



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.2	14.3	13.3	12.4	11.5	11.0	10.9	10.9	10.9	10.8	10.9
90°	0.3	0.8	1.3	1.7	2.3	2.8	3.2	3.6	4.0	4.5	4.8
92.5°	4.3	4.0	3.6	3.2	2.9	2.9	3.3	3.7	4.1	4.5	4.8
95°	15.9	15.8	15.6	15.4	15.2	13.9	11.6	9.2	6.8	4.5	4.8
97.5°	33.4	33.7	34.0	34.3	34.7	32.5	27.8	23.1	18.5	13.8	12.0
100°	46.7	47.0	47.1	47.3	47.5	47.7	48.0	48.2	48.5	48.7	39.5
102.5°	60.4	60.7	60.9	61.2	61.4	61.6	61.7	61.9	62.0	62.2	60.4
105°	82.3	82.5	82.9	83.1	83.3	83.4	83.4	83.4	83.4	83.4	83.4
107.5°	105.0	105.0	105.0	105.0	105.0	105.1	105.3	105.4	105.5	105.6	105.6
110°	119.9	119.9	119.9	119.9	119.9	119.9	120.0	120.2	120.3	120.4	120.3



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.7	133.9	134.0	134.2	134.4	134.4	134.5	134.6	134.7	134.8	134.5
115°	154.6	154.9	155.2	155.5	155.8	156.0	156.1	156.1	156.2	156.2	156.0
117.5°	176.1	176.1	176.1	176.1	176.1	176.2	176.4	176.7	176.9	177.1	176.8
120°	189.6	189.5	189.5	189.4	189.3	189.4	189.6	189.7	190.0	190.1	190.0
122.5°	201.5	201.7	201.9	202.2	202.4	202.6	202.6	202.7	202.8	202.9	202.8
125°	219.8	220.2	220.7	221.1	221.6	221.8	221.8	221.8	221.8	221.8	221.5
127.5°	237.3	237.7	238.0	238.3	238.6	238.8	238.7	238.7	238.6	238.6	238.4
130°	248.1	248.4	248.7	249.1	249.4	249.5	249.6	249.6	249.7	249.8	249.6
132.5°	258.9	259.2	259.6	259.9	260.3	260.4	260.3	260.2	260.0	259.8	259.8
135°	274.2	274.5	274.9	275.3	275.6	275.8	275.6	275.5	275.4	275.3	275.1
137.5°	288.2	288.5	288.8	289.1	289.5	289.6	289.5	289.4	289.2	289.1	289.1
140°	297.4	297.5	297.6	297.8	297.9	297.9	297.9	297.8	297.7	297.7	297.8
142.5°	305.7	305.8	305.9	305.9	305.9	306.0	306.2	306.3	306.3	306.4	306.4
145°	317.8	318.0	318.1	318.2	318.3	318.4	318.4	318.4	318.4	318.4	318.5
147.5°	328.4	328.4	328.4	328.4	328.4	328.4	328.4	328.5	328.6	328.7	328.8
150°	335.2	335.1	334.9	334.8	334.7	334.7	334.8	334.9	335.1	335.2	335.3
152.5°	341.7	341.4	341.1	340.9	340.6	340.5	340.6	340.8	340.9	341.0	341.1
155°	350.1	349.7	349.3	348.9	348.6	348.4	348.6	348.6	348.8	348.9	349.1
157.5°	356.5	356.2	356.0	355.8	355.6	355.5	355.5	355.5	355.5	355.5	355.7
160°	360.9	360.6	360.2	359.8	359.5	359.3	359.3	359.4	359.5	359.6	359.8
162.5°	364.6	364.2	363.8	363.4	363.1	362.9	363.0	363.0	363.1	363.1	363.5
165°	369.3	369.0	368.6	368.2	367.9	367.7	367.7	367.8	367.9	368.0	368.3
167.5°	373.0	372.6	372.2	371.8	371.4	371.2	371.3	371.4	371.5	371.5	371.9
170°	374.9	374.5	374.1	373.7	373.2	373.0	373.1	373.1	373.2	373.3	373.8
172.5°	376.3	375.9	375.4	375.0	374.5	374.4	374.5	374.6	374.7	374.9	375.3
175°	377.7	377.4	377.0	376.6	376.3	376.1	376.1	376.2	376.3	376.4	376.8
177.5°	378.4	378.1	377.8	377.6	377.2	377.1	377.2	377.2	377.2	377.3	377.6
180°	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	10.9	10.9	11.0	11.0	10.9	10.8	10.7	10.5
90°	5.1	5.4	5.7	5.9	6.2	6.3	6.5	6.7
92.5°	5.1	5.4	5.7	5.9	6.0	6.1	6.2	6.3
95°	5.1	5.4	5.7	5.9	5.9	5.9	5.9	5.9
97.5°	10.3	8.5	6.7	5.9	5.9	5.9	5.9	5.9
100°	30.2	20.9	11.6	6.9	6.7	6.4	6.1	5.9
102.5°	58.6	56.9	55.1	52.1	47.9	43.7	39.5	35.3
105°	83.4	83.4	83.4	83.4	83.3	83.3	83.3	83.2
107.5°	105.7	105.7	105.7	105.6	105.4	105.2	105.0	104.8
110°	120.0	119.9	119.7	119.6	119.7	119.7	119.8	119.9



TEST NUMBER: P333553-927

CATALOG NUMBER: S125RDIP-S850D365U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	134.3	134.0	133.8	133.6	133.6	133.5	133.4	133.3
115°	155.7	155.5	155.3	155.0	154.6	154.2	153.8	153.4
117.5°	176.5	176.2	175.9	175.6	175.5	175.3	175.2	175.0
120°	189.9	189.7	189.6	189.4	189.1	188.8	188.5	188.1
122.5°	202.6	202.6	202.4	202.2	201.8	201.5	201.1	200.7
125°	221.3	221.0	220.8	220.5	220.4	220.2	220.0	219.8
127.5°	238.3	238.1	238.1	237.7	237.3	236.8	236.4	235.9
130°	249.4	249.2	249.1	248.7	248.5	248.2	247.9	247.6
132.5°	259.8	259.8	259.7	259.5	259.2	258.9	258.6	258.3
135°	275.0	274.9	274.7	274.5	274.2	273.8	273.4	273.0
137.5°	289.2	289.2	289.2	289.1	288.8	288.4	288.1	287.8
140°	297.9	298.0	298.2	298.0	297.7	297.3	296.9	296.5
142.5°	306.4	306.5	306.5	306.3	305.9	305.5	305.2	304.8
145°	318.5	318.5	318.6	318.5	318.1	317.7	317.3	317.0
147.5°	328.8	328.9	329.0	328.8	328.4	327.9	327.5	327.0
150°	335.4	335.6	335.6	335.5	335.0	334.5	334.0	333.5
152.5°	341.3	341.4	341.5	341.4	340.9	340.5	340.0	339.5
155°	349.3	349.4	349.7	349.5	349.0	348.5	348.0	347.5
157.5°	355.9	356.1	356.3	356.2	355.7	355.1	354.7	354.2
160°	360.0	360.3	360.5	360.4	359.9	359.4	358.9	358.5
162.5°	363.8	364.2	364.6	364.4	363.8	363.3	362.8	362.3
165°	368.7	369.1	369.5	369.4	368.9	368.4	367.9	367.4
167.5°	372.4	372.8	373.3	373.2	372.6	372.1	371.5	371.0
170°	374.2	374.8	375.3	375.3	374.7	374.1	373.5	373.0
172.5°	375.7	376.2	376.6	376.6	376.0	375.4	374.9	374.3
175°	377.3	377.9	378.3	378.3	377.7	377.2	376.6	376.0
177.5°	378.0	378.3	378.7	378.7	378.3	377.9	377.5	377.1
180°	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7

(END OF REPORT)