

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333561-927

Luminaire Tested: **S125RDIP-S850D590U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333561-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D590U927-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4255.5 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	53	50	46	46	43	41
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.4	2.4
10°-20°	286.2	6.7
20°-30°	415.1	9.8
30°-40°	473.1	11.1
40°-50°	461.1	10.8
50°-60°	388.2	9.1
60°-70°	272.1	6.4
70°-80°	139.9	3.3
80°-90°	36.6	0.9
90°-100°	162.5	3.8
100°-110°	349.2	8.2
110°-120°	327.8	7.7
120°-130°	265.6	6.2
130°-140°	213.2	5.0
140°-150°	160.9	3.8
150°-160°	113.2	2.7
160°-170°	66.7	1.6
170°-180°	21.7	0.5
0°-30°	803.8	18.9
0°-40°	1276.8	30.0
0°-60°	2126.1	50.0
0°-90°	2574.7	60.5
90°-120°	839.5	19.7
90°-150°	1479.1	34.8
90°-180°	1681.0	39.5
0°-180°	4255.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	0	4	7	9	10	3
95°	15	44	400	182	106	16
105°	51	71	328	645	599	54
115°	91	110	263	567	667	90
125°	126	148	252	451	526	112
135°	148	178	250	378	436	115
145°	173	198	251	313	344	108
155°	197	212	245	277	289	91
165°	215	221	235	249	253	61
175°	224	224	226	228	227	21
180°	224	224	224	224	224	



TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.2	14.3	13.5	12.6	11.8	11.3	11.3	11.3	11.2	11.3	11.4
90°	0.5	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7
92.5°	5.5	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0
95°	14.9	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8
97.5°	24.8	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7
100°	31.6	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0
102.5°	39.2	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8
105°	51.1	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3
107.5°	62.7	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8
110°	71.0	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6



TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.3	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6
115°	91.3	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7
117.5°	102.1	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1
120°	109.3	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5
122.5°	116.9	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0
125°	126.5	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1
127.5°	134.0	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0
130°	138.7	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6
132.5°	142.4	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2
135°	148.2	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1
137.5°	155.7	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5
140°	159.9	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3
142.5°	165.0	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5
145°	172.6	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8
147.5°	180.5	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0
150°	185.3	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8
152.5°	190.4	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3
155°	197.0	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0
157.5°	203.0	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1
160°	207.0	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8
162.5°	210.2	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0
165°	215.1	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6
167.5°	218.3	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3
170°	220.5	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8
172.5°	222.0	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3
175°	223.7	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9
177.5°	224.5	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	11.5	11.6	11.6	11.8	11.6	11.5	11.4	11.3
90°	8.2	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	80.1	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	324.9	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	483.9	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	555.8	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	580.0	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	565.8	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	514.8	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	477.2	563.1	626.8	665.2	685.5	694.1	697.3	697.3





TEST NUMBER: P333561-927

CATALOG NUMBER: S125RDIP-S850D590U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	447.6	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	410.3	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	386.3	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	373.3	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	363.5	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	349.3	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	334.9	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	325.8	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	316.8	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	305.0	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	295.1	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	289.6	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	284.9	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	278.8	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	273.1	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	269.7	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	266.2	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	260.7	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	255.3	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	251.7	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	247.7	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	242.2	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	236.9	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	234.1	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	230.8	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	224.8	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)