

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332608-935

Luminaire Tested: **S124DIP-S795D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332608-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D1035U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6136.1 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 107 | 107 | 107 | 107 | 99 | 99 | 99 | 99 | 83 | 83 | 83 | 69 | 69 | 69 | 56 | 56 | 56 | 50 |
| 1 | 98 | 94 | 90 | 86 | 90 | 87 | 83 | 80 | 73 | 71 | 69 | 61 | 59 | 58 | 50 | 49 | 48 | 42 |
| 2 | 89 | 82 | 76 | 71 | 82 | 76 | 71 | 66 | 64 | 61 | 57 | 54 | 51 | 49 | 44 | 42 | 40 | 36 |
| 3 | 82 | 72 | 65 | 59 | 75 | 67 | 61 | 56 | 57 | 52 | 48 | 48 | 44 | 41 | 39 | 37 | 35 | 31 |
| 4 | 75 | 64 | 56 | 50 | 69 | 60 | 53 | 47 | 51 | 46 | 41 | 43 | 39 | 36 | 35 | 32 | 30 | 26 |
| 5 | 69 | 57 | 49 | 43 | 63 | 53 | 46 | 41 | 46 | 40 | 36 | 38 | 34 | 31 | 32 | 29 | 26 | 23 |
| 6 | 63 | 51 | 43 | 38 | 58 | 48 | 41 | 36 | 41 | 36 | 31 | 35 | 31 | 27 | 29 | 26 | 23 | 20 |
| 7 | 59 | 46 | 39 | 33 | 54 | 43 | 36 | 31 | 37 | 32 | 28 | 32 | 27 | 24 | 26 | 23 | 21 | 18 |
| 8 | 54 | 42 | 35 | 29 | 50 | 39 | 33 | 28 | 34 | 29 | 25 | 29 | 25 | 22 | 24 | 21 | 19 | 16 |
| 9 | 51 | 39 | 31 | 26 | 47 | 36 | 29 | 25 | 31 | 26 | 22 | 27 | 22 | 19 | 22 | 19 | 17 | 15 |
| 10 | 47 | 35 | 28 | 23 | 44 | 33 | 27 | 22 | 29 | 24 | 20 | 25 | 21 | 18 | 21 | 18 | 15 | 13 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|-------|------|------|------|
| 0° | 8924 | 8924 | 8924 | 8924 |
| 5° | 10509 | 8947 | 7897 | 8947 |
| 10° | 12582 | 8908 | 7110 | 8908 |
| 15° | 14888 | 8818 | 6529 | 8818 |
| 20° | 16578 | 8725 | 6010 | 8725 |
| 25° | 16846 | 8590 | 5653 | 8590 |
| 30° | 14334 | 8460 | 5540 | 8460 |
| 35° | 11020 | 8250 | 5542 | 8250 |
| 40° | 8590 | 8001 | 5647 | 8001 |
| 45° | 7162 | 7628 | 5740 | 7628 |
| 50° | 6303 | 7171 | 5936 | 7171 |
| 55° | 5775 | 6625 | 6175 | 6625 |
| 60° | 5412 | 6135 | 6462 | 6135 |
| 65° | 5037 | 5589 | 6701 | 5589 |
| 70° | 4605 | 5049 | 6852 | 5049 |
| 75° | 4114 | 4442 | 6772 | 4442 |
| 80° | 3450 | 3640 | 6555 | 3640 |
| 85° | 2547 | 2631 | 6280 | 2631 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 107.7 | 1.8 |
| 10°-20° | 331.9 | 5.4 |
| 20°-30° | 526.4 | 8.6 |
| 30°-40° | 585.8 | 9.5 |
| 40°-50° | 533.2 | 8.7 |
| 50°-60° | 435.7 | 7.1 |
| 60°-70° | 311.1 | 5.1 |
| 70°-80° | 171.3 | 2.8 |
| 80°-90° | 50.1 | 0.8 |
| 90°-100° | 73.3 | 1.2 |
| 100°-110° | 217.1 | 3.5 |
| 110°-120° | 368.5 | 6.0 |
| 120°-130° | 485.9 | 7.9 |
| 130°-140° | 545.7 | 8.9 |
| 140°-150° | 536.2 | 8.7 |
| 150°-160° | 451.0 | 7.4 |
| 160°-170° | 300.1 | 4.9 |
| 170°-180° | 105.1 | 1.7 |
| 0°-30° | 966.0 | 15.7 |
| 0°-40° | 1551.8 | 25.3 |
| 0°-60° | 2520.7 | 41.1 |
| 0°-90° | 3053.2 | 49.8 |
| 90°-120° | 658.9 | 10.7 |
| 90°-150° | 2226.8 | 36.3 |
| 90°-180° | 3083.0 | 50.2 |
| 0°-180° | 6136.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|------|------|------|------|------|------|
| 0° | 1105 | 1105 | 1105 | 1105 | 1105 | |
| 5° | 1297 | 1104 | 974 | 1104 | 1297 | 132 |
| 15° | 1781 | 1055 | 781 | 1055 | 1781 | 503 |
| 25° | 1891 | 964 | 635 | 964 | 1891 | 834 |
| 35° | 1118 | 837 | 562 | 837 | 1118 | 710 |
| 45° | 627 | 668 | 503 | 668 | 627 | 494 |
| 55° | 410 | 471 | 439 | 471 | 410 | 371 |
| 65° | 264 | 293 | 351 | 293 | 264 | 261 |
| 75° | 132 | 142 | 217 | 142 | 132 | 140 |
| 85° | 28 | 28 | 68 | 28 | 28 | 34 |
| 90° | 26 | 3 | 26 | 3 | 26 | 14 |
| 95° | 68 | 52 | 68 | 52 | 68 | 71 |
| 105° | 210 | 200 | 210 | 200 | 210 | 221 |
| 115° | 371 | 375 | 371 | 375 | 371 | 367 |
| 125° | 541 | 546 | 541 | 546 | 541 | 483 |
| 135° | 705 | 704 | 705 | 704 | 705 | 544 |
| 145° | 856 | 855 | 856 | 855 | 856 | 536 |
| 155° | 979 | 980 | 979 | 980 | 979 | 451 |
| 165° | 1064 | 1066 | 1064 | 1066 | 1064 | 300 |
| 175° | 1104 | 1110 | 1104 | 1110 | 1104 | 105 |
| 180° | 1111 | 1111 | 1111 | 1111 | 1111 | |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1176.5 | 1176.1 | 1172.4 | 1171.7 | 1169.2 | 1165.9 | 1165.1 | 1159.3 | 1147.5 | 1142.0 | 1140.6 |
| 5° | 1296.8 | 1306.0 | 1294.1 | 1291.8 | 1290.4 | 1275.3 | 1267.5 | 1258.4 | 1237.3 | 1224.9 | 1215.3 |
| 7.5° | 1440.5 | 1441.5 | 1436.3 | 1432.1 | 1420.5 | 1407.2 | 1387.5 | 1366.4 | 1341.4 | 1315.2 | 1295.5 |
| 10° | 1534.9 | 1538.6 | 1532.7 | 1531.7 | 1508.4 | 1493.7 | 1464.4 | 1439.7 | 1411.3 | 1379.7 | 1350.8 |
| 12.5° | 1634.6 | 1629.4 | 1626.4 | 1606.8 | 1602.5 | 1575.8 | 1541.7 | 1516.2 | 1472.5 | 1436.1 | 1397.7 |
| 15° | 1781.3 | 1771.2 | 1764.8 | 1737.8 | 1724.5 | 1687.4 | 1651.2 | 1623.3 | 1566.1 | 1511.6 | 1470.3 |
| 17.5° | 1867.3 | 1877.4 | 1862.6 | 1851.5 | 1817.1 | 1791.1 | 1754.2 | 1695.6 | 1650.8 | 1583.1 | 1531.1 |
| 20° | 1929.7 | 1930.5 | 1922.4 | 1910.9 | 1883.9 | 1850.9 | 1810.6 | 1746.5 | 1692.9 | 1625.6 | 1554.2 |
| 22.5° | 1946.5 | 1946.7 | 1943.2 | 1932.5 | 1912.0 | 1885.3 | 1844.7 | 1791.1 | 1726.2 | 1653.0 | 1581.7 |
| 25° | 1891.2 | 1889.4 | 1893.5 | 1905.4 | 1897.6 | 1889.4 | 1866.0 | 1826.2 | 1765.7 | 1688.3 | 1611.4 |
| 27.5° | 1685.7 | 1698.3 | 1721.6 | 1750.8 | 1779.1 | 1800.6 | 1806.6 | 1798.5 | 1761.0 | 1697.4 | 1616.8 |
| 30° | 1537.7 | 1553.2 | 1570.6 | 1599.9 | 1656.7 | 1689.3 | 1724.9 | 1752.0 | 1736.9 | 1686.0 | 1610.9 |
| 32.5° | 1375.0 | 1378.9 | 1404.7 | 1438.0 | 1490.0 | 1552.6 | 1609.2 | 1664.1 | 1682.3 | 1655.6 | 1593.0 |
| 35° | 1118.2 | 1124.6 | 1152.5 | 1185.5 | 1249.2 | 1325.7 | 1410.8 | 1486.9 | 1549.5 | 1574.8 | 1542.7 |
| 37.5° | 912.5 | 930.9 | 950.6 | 986.1 | 1042.2 | 1110.9 | 1199.5 | 1297.8 | 1391.3 | 1454.0 | 1464.6 |
| 40° | 815.1 | 826.6 | 840.8 | 867.7 | 915.3 | 983.2 | 1059.1 | 1171.8 | 1271.2 | 1360.9 | 1390.3 |
| 42.5° | 738.1 | 744.9 | 753.5 | 778.0 | 814.2 | 881.7 | 951.1 | 1050.2 | 1150.0 | 1257.2 | 1306.3 |
| 45° | 627.3 | 634.2 | 648.8 | 663.1 | 690.5 | 737.3 | 801.8 | 883.3 | 983.6 | 1087.1 | 1177.8 |
| 47.5° | 547.3 | 551.7 | 560.4 | 575.6 | 598.9 | 629.7 | 682.3 | 750.4 | 843.3 | 943.7 | 1040.3 |
| 50° | 501.9 | 505.5 | 512.4 | 526.2 | 544.0 | 571.4 | 614.5 | 678.2 | 751.0 | 852.2 | 946.9 |
| 52.5° | 466.0 | 467.4 | 472.5 | 481.8 | 496.0 | 519.1 | 554.4 | 607.1 | 674.8 | 765.0 | 859.5 |
| 55° | 410.3 | 412.2 | 416.7 | 423.6 | 435.9 | 450.6 | 477.6 | 516.9 | 576.1 | 654.4 | 736.3 |
| 57.5° | 364.5 | 365.8 | 369.6 | 372.3 | 382.5 | 394.3 | 415.2 | 443.2 | 488.0 | 554.4 | 627.6 |
| 60° | 335.2 | 334.2 | 338.9 | 341.1 | 348.0 | 358.1 | 374.1 | 401.1 | 440.1 | 493.6 | 560.9 |
| 62.5° | 306.6 | 305.3 | 309.2 | 312.2 | 316.2 | 324.8 | 337.9 | 359.0 | 390.6 | 439.0 | 497.2 |
| 65° | 263.7 | 261.9 | 264.2 | 267.9 | 271.6 | 276.1 | 285.8 | 304.5 | 329.7 | 364.5 | 408.9 |
| 67.5° | 220.7 | 222.7 | 223.0 | 224.8 | 227.0 | 233.2 | 239.8 | 253.0 | 270.8 | 298.7 | 336.3 |
| 70° | 195.1 | 195.5 | 197.3 | 197.3 | 198.7 | 204.2 | 209.7 | 217.5 | 234.9 | 260.5 | 291.2 |
| 72.5° | 169.4 | 171.3 | 170.7 | 172.1 | 173.1 | 176.8 | 180.8 | 188.2 | 203.0 | 222.1 | 248.0 |
| 75° | 131.9 | 133.3 | 133.3 | 133.7 | 135.1 | 136.5 | 139.7 | 145.2 | 155.7 | 169.9 | 187.8 |
| 77.5° | 96.2 | 96.3 | 96.9 | 98.7 | 98.7 | 100.8 | 103.2 | 107.6 | 112.8 | 122.5 | 133.5 |
| 80° | 74.2 | 75.1 | 74.6 | 75.6 | 75.6 | 77.4 | 78.3 | 83.8 | 86.1 | 92.5 | 101.2 |
| 82.5° | 54.4 | 55.3 | 55.2 | 56.5 | 57.3 | 57.6 | 58.9 | 61.0 | 63.4 | 69.1 | 72.6 |
| 85° | 27.5 | 28.4 | 27.5 | 28.4 | 29.8 | 30.2 | 31.6 | 32.0 | 33.9 | 35.3 | 38.5 |
| 87.5° | 13.2 | 14.2 | 14.1 | 14.5 | 15.1 | 15.3 | 15.5 | 14.9 | 16.1 | 16.3 | 17.4 |
| 90° | 25.7 | 25.4 | 25.1 | 24.6 | 24.3 | 23.5 | 22.4 | 21.2 | 20.1 | 18.9 | 17.4 |
| 92.5° | 38.1 | 38.0 | 37.7 | 37.5 | 37.3 | 36.8 | 36.1 | 35.4 | 34.7 | 34.0 | 33.0 |
| 95° | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 | 67.6 | 67.1 | 66.5 | 65.9 | 65.3 | 64.0 |
| 97.5° | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 | 106.1 | 105.4 | 104.7 | 104.0 | 103.3 | 101.8 |
| 100° | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 | 133.0 | 132.6 | 132.2 | 131.9 | 131.5 | 129.8 |
| 102.5° | 163.4 | 163.3 | 163.2 | 163.0 | 162.8 | 162.5 | 162.0 | 161.4 | 160.9 | 160.4 | 158.8 |
| 105° | 209.7 | 209.1 | 208.5 | 207.9 | 207.4 | 206.8 | 206.3 | 205.7 | 205.1 | 204.6 | 203.8 |
| 107.5° | 254.7 | 254.8 | 254.8 | 254.9 | 254.9 | 254.6 | 254.1 | 253.6 | 253.0 | 252.5 | 252.4 |
| 110° | 287.1 | 286.5 | 285.9 | 285.3 | 284.7 | 284.6 | 285.0 | 285.4 | 285.8 | 286.2 | 286.4 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 320.0 | 319.9 | 319.8 | 319.7 | 319.6 | 319.6 | 319.6 | 319.7 | 319.8 | 319.9 | 320.2 |
| 115° | 371.3 | 371.4 | 371.6 | 371.9 | 372.0 | 372.2 | 372.4 | 372.6 | 372.8 | 373.0 | 373.3 |
| 117.5° | 420.1 | 420.4 | 420.9 | 421.2 | 421.6 | 422.1 | 422.8 | 423.4 | 424.0 | 424.7 | 425.0 |
| 120° | 457.2 | 456.8 | 456.4 | 456.1 | 455.6 | 456.0 | 456.9 | 457.9 | 458.8 | 459.8 | 460.4 |
| 122.5° | 488.1 | 488.8 | 489.5 | 490.2 | 490.9 | 491.5 | 492.2 | 492.8 | 493.5 | 494.1 | 494.4 |
| 125° | 541.4 | 541.8 | 542.2 | 542.6 | 542.9 | 543.3 | 543.7 | 544.1 | 544.5 | 544.8 | 545.0 |
| 127.5° | 590.7 | 591.1 | 591.3 | 591.7 | 591.9 | 592.3 | 592.7 | 593.1 | 593.5 | 593.8 | 594.2 |
| 130° | 623.0 | 623.8 | 624.6 | 625.3 | 626.1 | 626.7 | 627.1 | 627.5 | 627.8 | 628.2 | 628.2 |
| 132.5° | 657.5 | 657.7 | 658.1 | 658.3 | 658.7 | 659.0 | 659.4 | 659.8 | 660.1 | 660.6 | 660.6 |
| 135° | 704.7 | 705.2 | 705.8 | 706.5 | 707.0 | 707.5 | 707.8 | 708.3 | 708.6 | 709.0 | 709.0 |
| 137.5° | 754.4 | 754.2 | 754.1 | 754.1 | 753.9 | 754.1 | 754.6 | 755.1 | 755.6 | 756.1 | 755.8 |
| 140° | 784.6 | 784.8 | 785.0 | 785.2 | 785.4 | 785.6 | 785.7 | 786.0 | 786.2 | 786.4 | 786.4 |
| 142.5° | 814.9 | 814.9 | 814.9 | 815.0 | 815.0 | 815.1 | 815.1 | 815.1 | 815.2 | 815.2 | 815.4 |
| 145° | 855.9 | 856.5 | 857.1 | 857.6 | 858.2 | 858.6 | 858.8 | 859.0 | 859.2 | 859.4 | 859.2 |
| 147.5° | 897.6 | 897.8 | 897.9 | 898.1 | 898.3 | 898.5 | 898.6 | 898.8 | 899.0 | 899.1 | 899.2 |
| 150° | 923.0 | 923.2 | 923.3 | 923.6 | 923.8 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 |
| 152.5° | 946.3 | 946.8 | 947.4 | 947.9 | 948.4 | 948.4 | 947.9 | 947.4 | 947.0 | 946.5 | 946.4 |
| 155° | 978.9 | 979.6 | 980.4 | 981.1 | 981.9 | 981.9 | 981.1 | 980.4 | 979.6 | 978.9 | 979.0 |
| 157.5° | 1007.9 | 1008.6 | 1009.2 | 1009.9 | 1010.5 | 1010.6 | 1010.0 | 1009.4 | 1008.8 | 1008.2 | 1008.3 |
| 160° | 1024.4 | 1025.4 | 1026.3 | 1027.3 | 1028.2 | 1028.4 | 1027.9 | 1027.3 | 1026.7 | 1026.1 | 1026.3 |
| 162.5° | 1041.6 | 1042.6 | 1043.5 | 1044.5 | 1045.4 | 1045.3 | 1044.3 | 1043.3 | 1042.2 | 1041.2 | 1041.5 |
| 165° | 1063.9 | 1064.7 | 1065.5 | 1066.3 | 1067.0 | 1066.8 | 1065.7 | 1064.5 | 1063.3 | 1062.2 | 1062.6 |
| 167.5° | 1080.0 | 1081.1 | 1082.3 | 1083.5 | 1084.7 | 1084.7 | 1083.6 | 1082.4 | 1081.2 | 1080.1 | 1080.0 |
| 170° | 1088.8 | 1090.2 | 1091.5 | 1092.9 | 1094.2 | 1094.3 | 1093.1 | 1092.0 | 1090.9 | 1089.7 | 1089.5 |
| 172.5° | 1096.4 | 1097.8 | 1099.1 | 1100.4 | 1101.7 | 1101.8 | 1100.4 | 1099.2 | 1097.9 | 1096.6 | 1096.6 |
| 175° | 1104.3 | 1105.7 | 1107.0 | 1108.4 | 1109.7 | 1109.7 | 1108.4 | 1107.0 | 1105.7 | 1104.3 | 1104.5 |
| 177.5° | 1108.5 | 1109.7 | 1110.9 | 1112.2 | 1113.4 | 1113.4 | 1112.3 | 1111.3 | 1110.2 | 1109.1 | 1109.1 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1140.9 | 1135.8 | 1132.1 | 1129.2 | 1121.2 | 1116.4 | 1112.8 | 1107.6 | 1101.7 | 1095.5 | 1087.8 |
| 5° | 1205.7 | 1190.1 | 1178.7 | 1161.2 | 1144.8 | 1131.0 | 1116.9 | 1104.1 | 1088.5 | 1071.5 | 1059.1 |
| 7.5° | 1273.8 | 1250.6 | 1220.9 | 1195.2 | 1166.2 | 1141.0 | 1118.5 | 1095.5 | 1071.4 | 1048.2 | 1026.8 |
| 10° | 1317.0 | 1287.2 | 1254.2 | 1215.3 | 1178.7 | 1146.2 | 1115.9 | 1086.7 | 1058.3 | 1029.8 | 1005.6 |
| 12.5° | 1363.5 | 1326.4 | 1277.6 | 1232.2 | 1191.1 | 1147.6 | 1111.2 | 1075.3 | 1041.0 | 1011.2 | 982.8 |
| 15° | 1425.9 | 1372.3 | 1316.0 | 1255.2 | 1201.1 | 1150.3 | 1100.4 | 1055.1 | 1016.6 | 977.1 | 949.7 |
| 17.5° | 1464.3 | 1398.0 | 1333.6 | 1270.0 | 1204.6 | 1140.5 | 1086.7 | 1034.3 | 986.2 | 947.0 | 912.4 |
| 20° | 1489.6 | 1423.7 | 1343.5 | 1279.9 | 1202.0 | 1136.1 | 1073.8 | 1015.6 | 965.3 | 923.6 | 887.9 |
| 22.5° | 1511.6 | 1435.4 | 1355.2 | 1271.4 | 1193.9 | 1124.0 | 1055.8 | 997.3 | 945.9 | 902.0 | 867.7 |
| 25° | 1523.5 | 1436.0 | 1349.0 | 1265.7 | 1177.8 | 1094.8 | 1033.0 | 964.4 | 909.4 | 863.2 | 826.6 |
| 27.5° | 1524.7 | 1431.2 | 1332.8 | 1240.2 | 1149.4 | 1072.3 | 994.2 | 932.9 | 875.8 | 826.9 | 791.7 |
| 30° | 1520.7 | 1423.2 | 1317.4 | 1217.1 | 1126.0 | 1042.2 | 974.5 | 907.6 | 849.5 | 800.9 | 764.2 |
| 32.5° | 1507.9 | 1406.4 | 1297.6 | 1191.5 | 1097.1 | 1015.1 | 945.1 | 881.6 | 824.9 | 777.1 | 738.7 |
| 35° | 1470.8 | 1370.5 | 1254.6 | 1144.4 | 1047.7 | 964.8 | 901.6 | 837.1 | 780.3 | 734.9 | 697.8 |
| 37.5° | 1412.8 | 1322.2 | 1204.4 | 1090.2 | 995.3 | 912.1 | 849.5 | 791.1 | 739.9 | 693.8 | 655.8 |
| 40° | 1362.3 | 1282.6 | 1164.5 | 1053.2 | 950.6 | 871.4 | 812.8 | 759.2 | 708.4 | 664.9 | 628.7 |
| 42.5° | 1304.1 | 1234.6 | 1125.7 | 1007.8 | 908.9 | 829.3 | 772.1 | 724.0 | 676.1 | 635.9 | 599.8 |
| 45° | 1200.1 | 1154.4 | 1051.8 | 942.9 | 839.8 | 764.7 | 710.2 | 668.1 | 627.8 | 588.4 | 558.2 |
| 47.5° | 1080.7 | 1058.1 | 971.7 | 868.2 | 770.4 | 696.4 | 649.1 | 610.2 | 574.9 | 541.6 | 514.9 |
| 50° | 1000.6 | 989.5 | 914.9 | 815.1 | 721.7 | 652.0 | 604.4 | 571.0 | 540.8 | 511.5 | 486.3 |
| 52.5° | 921.4 | 921.0 | 853.8 | 762.3 | 675.9 | 608.8 | 561.5 | 530.4 | 504.2 | 480.4 | 457.7 |
| 55° | 800.5 | 813.2 | 760.6 | 679.1 | 601.7 | 541.2 | 498.7 | 470.7 | 452.5 | 432.7 | 415.8 |
| 57.5° | 689.3 | 710.6 | 667.2 | 595.4 | 530.8 | 475.1 | 438.1 | 417.1 | 397.5 | 385.6 | 373.3 |
| 60° | 616.8 | 637.0 | 603.0 | 542.6 | 481.7 | 434.1 | 398.8 | 380.0 | 363.1 | 354.9 | 346.2 |
| 62.5° | 552.3 | 570.3 | 545.2 | 489.1 | 436.3 | 390.5 | 360.8 | 342.7 | 331.2 | 322.3 | 316.5 |
| 65° | 460.2 | 475.3 | 453.8 | 413.0 | 367.7 | 331.1 | 306.8 | 292.6 | 281.6 | 277.9 | 271.6 |
| 67.5° | 372.0 | 385.7 | 374.1 | 339.5 | 303.2 | 275.3 | 256.4 | 242.8 | 236.3 | 233.1 | 228.5 |
| 70° | 319.6 | 333.4 | 321.0 | 290.8 | 262.9 | 239.5 | 221.6 | 213.9 | 207.0 | 205.6 | 199.1 |
| 72.5° | 275.3 | 284.6 | 272.2 | 248.7 | 224.7 | 205.1 | 191.2 | 183.0 | 179.5 | 177.0 | 173.6 |
| 75° | 206.6 | 214.7 | 206.6 | 188.2 | 171.3 | 157.6 | 145.6 | 142.4 | 138.3 | 136.9 | 134.7 |
| 77.5° | 146.2 | 153.3 | 147.0 | 135.5 | 122.9 | 112.3 | 105.9 | 101.8 | 100.8 | 98.4 | 99.5 |
| 80° | 111.8 | 116.3 | 110.4 | 102.5 | 92.5 | 85.2 | 80.6 | 78.3 | 75.6 | 74.6 | 76.5 |
| 82.5° | 80.2 | 82.2 | 79.2 | 74.0 | 66.5 | 61.7 | 58.6 | 56.0 | 55.4 | 55.6 | 55.6 |
| 85° | 41.7 | 41.2 | 40.7 | 36.2 | 33.9 | 30.7 | 28.8 | 28.4 | 27.9 | 28.8 | 29.8 |
| 87.5° | 17.0 | 17.1 | 16.4 | 14.6 | 13.2 | 11.6 | 10.8 | 10.1 | 10.8 | 11.6 | 12.4 |
| 90° | 15.8 | 14.3 | 12.8 | 11.0 | 8.9 | 6.8 | 4.6 | 2.6 | 4.6 | 6.8 | 8.9 |
| 92.5° | 31.9 | 30.8 | 29.8 | 28.0 | 25.6 | 23.2 | 20.8 | 18.4 | 20.8 | 23.2 | 25.6 |
| 95° | 62.7 | 61.3 | 59.9 | 58.5 | 56.7 | 55.0 | 53.3 | 51.6 | 53.3 | 55.0 | 56.7 |
| 97.5° | 100.1 | 98.6 | 97.0 | 95.6 | 94.2 | 92.8 | 91.4 | 90.1 | 91.4 | 92.8 | 94.2 |
| 100° | 128.0 | 126.3 | 124.6 | 123.4 | 122.6 | 121.8 | 121.1 | 120.3 | 121.1 | 121.8 | 122.6 |
| 102.5° | 157.2 | 155.7 | 154.1 | 153.2 | 152.8 | 152.6 | 152.2 | 152.0 | 152.2 | 152.6 | 152.8 |
| 105° | 203.0 | 202.2 | 201.5 | 201.0 | 200.8 | 200.6 | 200.4 | 200.3 | 200.4 | 200.6 | 200.8 |
| 107.5° | 252.3 | 252.2 | 252.0 | 251.8 | 251.7 | 251.4 | 251.2 | 251.0 | 251.2 | 251.4 | 251.7 |
| 110° | 286.5 | 286.7 | 287.0 | 286.9 | 286.5 | 286.1 | 285.7 | 285.3 | 285.7 | 286.1 | 286.5 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 320.6 | 320.9 | 321.2 | 321.4 | 321.3 | 321.2 | 321.2 | 321.1 | 321.2 | 321.2 | 321.3 |
| 115° | 373.8 | 374.1 | 374.5 | 374.7 | 374.7 | 374.7 | 374.7 | 374.7 | 374.7 | 374.7 | 374.7 |
| 117.5° | 425.2 | 425.5 | 425.8 | 425.9 | 425.7 | 425.5 | 425.4 | 425.2 | 425.4 | 425.5 | 425.7 |
| 120° | 460.9 | 461.5 | 462.1 | 462.0 | 461.2 | 460.5 | 459.7 | 458.9 | 459.7 | 460.5 | 461.2 |
| 122.5° | 494.6 | 495.0 | 495.2 | 495.2 | 494.9 | 494.6 | 494.3 | 494.0 | 494.3 | 494.6 | 494.9 |
| 125° | 545.3 | 545.4 | 545.6 | 545.7 | 545.7 | 545.7 | 545.7 | 545.7 | 545.7 | 545.7 | 545.7 |
| 127.5° | 594.4 | 594.8 | 595.0 | 595.0 | 594.3 | 593.7 | 593.2 | 592.6 | 593.2 | 593.7 | 594.3 |
| 130° | 628.2 | 628.2 | 628.2 | 627.9 | 627.3 | 626.8 | 626.2 | 625.6 | 626.2 | 626.8 | 627.3 |
| 132.5° | 660.8 | 661.0 | 661.2 | 661.0 | 660.6 | 660.1 | 659.8 | 659.4 | 659.8 | 660.1 | 660.6 |
| 135° | 709.0 | 709.0 | 709.0 | 708.4 | 707.3 | 706.1 | 705.0 | 703.9 | 705.0 | 706.1 | 707.3 |
| 137.5° | 755.5 | 755.2 | 754.8 | 754.5 | 753.9 | 753.4 | 752.9 | 752.3 | 752.9 | 753.4 | 753.9 |
| 140° | 786.4 | 786.4 | 786.4 | 786.2 | 785.7 | 785.4 | 785.0 | 784.6 | 785.0 | 785.4 | 785.7 |
| 142.5° | 815.5 | 815.7 | 815.8 | 815.7 | 815.4 | 814.9 | 814.6 | 814.2 | 814.6 | 814.9 | 815.4 |
| 145° | 859.0 | 858.8 | 858.6 | 858.2 | 857.4 | 856.6 | 855.8 | 855.1 | 855.8 | 856.6 | 857.4 |
| 147.5° | 899.4 | 899.6 | 899.7 | 899.3 | 898.5 | 897.5 | 896.6 | 895.7 | 896.6 | 897.5 | 898.5 |
| 150° | 923.9 | 923.9 | 923.9 | 923.5 | 922.7 | 922.0 | 921.2 | 920.4 | 921.2 | 922.0 | 922.7 |
| 152.5° | 946.2 | 946.1 | 945.9 | 945.6 | 945.2 | 944.7 | 944.3 | 943.8 | 944.3 | 944.7 | 945.2 |
| 155° | 979.2 | 979.4 | 979.6 | 979.7 | 979.7 | 979.7 | 979.7 | 979.7 | 979.7 | 979.7 | 979.7 |
| 157.5° | 1008.3 | 1008.3 | 1008.4 | 1008.6 | 1008.9 | 1009.3 | 1009.6 | 1010.0 | 1009.6 | 1009.3 | 1008.9 |
| 160° | 1026.5 | 1026.7 | 1026.9 | 1027.1 | 1027.3 | 1027.4 | 1027.6 | 1027.9 | 1027.6 | 1027.4 | 1027.3 |
| 162.5° | 1041.6 | 1041.8 | 1042.0 | 1042.3 | 1042.8 | 1043.4 | 1043.9 | 1044.3 | 1043.9 | 1043.4 | 1042.8 |
| 165° | 1063.0 | 1063.3 | 1063.8 | 1064.2 | 1064.8 | 1065.4 | 1065.9 | 1066.5 | 1065.9 | 1065.4 | 1064.8 |
| 167.5° | 1080.0 | 1080.0 | 1080.0 | 1080.3 | 1081.2 | 1081.9 | 1082.7 | 1083.6 | 1082.7 | 1081.9 | 1081.2 |
| 170° | 1089.3 | 1089.2 | 1088.9 | 1089.3 | 1090.3 | 1091.2 | 1092.2 | 1093.1 | 1092.2 | 1091.2 | 1090.3 |
| 172.5° | 1096.5 | 1096.5 | 1096.4 | 1096.8 | 1097.6 | 1098.5 | 1099.2 | 1100.0 | 1099.2 | 1098.5 | 1097.6 |
| 175° | 1104.7 | 1104.9 | 1105.1 | 1105.7 | 1106.6 | 1107.6 | 1108.5 | 1109.5 | 1108.5 | 1107.6 | 1106.6 |
| 177.5° | 1109.1 | 1109.1 | 1109.1 | 1109.5 | 1110.3 | 1111.0 | 1111.8 | 1112.6 | 1111.8 | 1111.0 | 1110.3 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1084.2 | 1080.9 | 1076.1 | 1069.5 | 1064.0 | 1058.2 | 1056.7 | 1054.5 | 1058.9 | 1055.2 | 1054.1 |
| 5° | 1048.6 | 1039.0 | 1026.7 | 1012.4 | 1004.2 | 992.3 | 990.0 | 985.4 | 980.9 | 980.4 | 975.8 |
| 7.5° | 1011.0 | 996.9 | 980.7 | 966.2 | 952.8 | 939.8 | 931.3 | 929.4 | 922.7 | 918.8 | 914.2 |
| 10° | 986.8 | 969.4 | 950.6 | 936.9 | 921.4 | 907.6 | 897.9 | 892.5 | 887.9 | 882.9 | 878.3 |
| 12.5° | 958.2 | 939.7 | 924.3 | 909.4 | 890.9 | 880.5 | 864.6 | 855.1 | 854.2 | 854.3 | 842.4 |
| 15° | 925.0 | 906.6 | 882.9 | 861.8 | 851.7 | 831.6 | 822.9 | 811.8 | 805.0 | 798.1 | 792.6 |
| 17.5° | 887.0 | 864.2 | 845.6 | 821.4 | 802.2 | 786.2 | 774.7 | 768.1 | 757.8 | 748.0 | 741.0 |
| 20° | 863.2 | 838.9 | 819.2 | 793.6 | 772.5 | 752.8 | 743.2 | 734.0 | 726.3 | 718.0 | 710.2 |
| 22.5° | 839.0 | 813.6 | 789.5 | 764.7 | 745.0 | 724.3 | 715.0 | 702.5 | 695.1 | 690.5 | 682.8 |
| 25° | 800.9 | 773.4 | 746.0 | 722.1 | 702.0 | 683.6 | 671.3 | 661.7 | 653.4 | 649.8 | 644.7 |
| 27.5° | 759.5 | 732.2 | 705.7 | 678.6 | 655.7 | 642.5 | 632.6 | 625.3 | 620.5 | 615.7 | 613.5 |
| 30° | 733.1 | 704.7 | 676.3 | 651.2 | 630.1 | 616.8 | 607.6 | 602.6 | 598.9 | 596.7 | 594.3 |
| 32.5° | 706.4 | 678.4 | 648.5 | 625.5 | 606.7 | 594.9 | 587.9 | 582.8 | 581.0 | 580.1 | 579.4 |
| 35° | 663.5 | 635.2 | 607.6 | 587.0 | 569.2 | 564.6 | 558.6 | 555.9 | 555.0 | 558.2 | 559.6 |
| 37.5° | 622.0 | 595.6 | 570.4 | 550.4 | 538.7 | 532.0 | 529.9 | 530.1 | 533.4 | 536.2 | 539.5 |
| 40° | 595.3 | 569.6 | 545.9 | 528.4 | 517.5 | 513.3 | 512.4 | 514.7 | 518.3 | 521.6 | 525.2 |
| 42.5° | 569.3 | 544.0 | 522.4 | 506.1 | 498.4 | 494.6 | 495.2 | 497.5 | 502.6 | 506.5 | 512.0 |
| 45° | 528.9 | 507.8 | 486.7 | 473.5 | 467.1 | 468.0 | 468.0 | 472.1 | 477.2 | 483.1 | 489.0 |
| 47.5° | 490.9 | 469.7 | 452.3 | 441.2 | 437.8 | 437.0 | 439.6 | 445.0 | 452.2 | 459.6 | 467.9 |
| 50° | 465.2 | 445.1 | 430.0 | 419.9 | 416.2 | 417.6 | 421.3 | 426.3 | 435.0 | 444.2 | 452.9 |
| 52.5° | 439.2 | 420.9 | 406.9 | 397.5 | 395.0 | 397.4 | 401.1 | 409.1 | 416.7 | 426.6 | 437.1 |
| 55° | 398.8 | 383.2 | 372.3 | 365.4 | 364.5 | 365.8 | 370.0 | 378.7 | 389.7 | 402.1 | 412.2 |
| 57.5° | 358.6 | 345.6 | 335.5 | 330.8 | 331.2 | 332.5 | 339.3 | 349.7 | 361.4 | 374.5 | 387.5 |
| 60° | 331.6 | 319.6 | 311.4 | 307.7 | 308.2 | 310.9 | 319.2 | 328.8 | 343.5 | 356.3 | 370.0 |
| 62.5° | 305.9 | 295.4 | 287.6 | 284.3 | 283.6 | 289.6 | 297.6 | 307.5 | 322.2 | 336.5 | 351.3 |
| 65° | 264.7 | 256.4 | 250.0 | 248.2 | 249.6 | 254.2 | 264.2 | 277.5 | 289.9 | 305.0 | 320.6 |
| 67.5° | 224.4 | 217.6 | 213.2 | 214.0 | 215.7 | 222.5 | 230.9 | 242.3 | 256.3 | 272.0 | 287.4 |
| 70° | 198.7 | 192.3 | 188.6 | 189.1 | 191.8 | 200.1 | 207.4 | 218.9 | 234.0 | 250.0 | 262.9 |
| 72.5° | 172.4 | 168.2 | 164.9 | 166.8 | 169.5 | 175.2 | 184.3 | 195.8 | 209.1 | 224.0 | 237.5 |
| 75° | 132.3 | 132.3 | 130.5 | 131.9 | 136.0 | 141.5 | 148.4 | 160.2 | 173.6 | 185.5 | 196.5 |
| 77.5° | 98.2 | 97.2 | 98.3 | 100.0 | 102.4 | 108.9 | 116.8 | 125.3 | 135.3 | 147.1 | 156.3 |
| 80° | 75.1 | 75.6 | 77.8 | 80.6 | 81.5 | 86.5 | 94.8 | 102.5 | 110.4 | 120.5 | 129.2 |
| 82.5° | 56.4 | 56.9 | 58.0 | 61.6 | 62.4 | 67.8 | 73.2 | 80.9 | 88.0 | 94.8 | 102.0 |
| 85° | 30.7 | 30.7 | 33.0 | 34.4 | 36.6 | 40.3 | 43.5 | 48.0 | 54.5 | 59.1 | 66.0 |
| 87.5° | 13.9 | 14.3 | 16.0 | 17.0 | 18.5 | 20.7 | 21.6 | 25.8 | 27.6 | 29.6 | 33.1 |
| 90° | 11.0 | 12.8 | 14.3 | 15.8 | 17.4 | 18.9 | 20.1 | 21.2 | 22.4 | 23.5 | 24.3 |
| 92.5° | 28.0 | 29.8 | 30.8 | 31.9 | 33.0 | 34.0 | 34.7 | 35.4 | 36.1 | 36.8 | 37.3 |
| 95° | 58.5 | 59.9 | 61.3 | 62.7 | 64.0 | 65.3 | 65.9 | 66.5 | 67.1 | 67.6 | 67.9 |
| 97.5° | 95.6 | 97.0 | 98.6 | 100.1 | 101.8 | 103.3 | 104.0 | 104.7 | 105.4 | 106.1 | 106.4 |
| 100° | 123.4 | 124.6 | 126.3 | 128.0 | 129.8 | 131.5 | 131.9 | 132.2 | 132.6 | 133.0 | 133.2 |
| 102.5° | 153.2 | 154.1 | 155.7 | 157.2 | 158.8 | 160.4 | 160.9 | 161.4 | 162.0 | 162.5 | 162.8 |
| 105° | 201.0 | 201.5 | 202.2 | 203.0 | 203.8 | 204.6 | 205.1 | 205.7 | 206.3 | 206.8 | 207.4 |
| 107.5° | 251.8 | 252.0 | 252.2 | 252.3 | 252.4 | 252.5 | 253.0 | 253.6 | 254.1 | 254.6 | 254.9 |
| 110° | 286.9 | 287.0 | 286.7 | 286.5 | 286.4 | 286.2 | 285.8 | 285.4 | 285.0 | 284.6 | 284.7 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 321.4 | 321.2 | 320.9 | 320.6 | 320.2 | 319.9 | 319.8 | 319.7 | 319.6 | 319.6 | 319.6 |
| 115° | 374.7 | 374.5 | 374.1 | 373.8 | 373.3 | 373.0 | 372.8 | 372.6 | 372.4 | 372.2 | 372.0 |
| 117.5° | 425.9 | 425.8 | 425.5 | 425.2 | 425.0 | 424.7 | 424.0 | 423.4 | 422.8 | 422.1 | 421.6 |
| 120° | 462.0 | 462.1 | 461.5 | 460.9 | 460.4 | 459.8 | 458.8 | 457.9 | 456.9 | 456.0 | 455.6 |
| 122.5° | 495.2 | 495.2 | 495.0 | 494.6 | 494.4 | 494.1 | 493.5 | 492.8 | 492.2 | 491.5 | 490.9 |
| 125° | 545.7 | 545.6 | 545.4 | 545.3 | 545.0 | 544.8 | 544.5 | 544.1 | 543.7 | 543.3 | 542.9 |
| 127.5° | 595.0 | 595.0 | 594.8 | 594.4 | 594.2 | 593.8 | 593.5 | 593.1 | 592.7 | 592.3 | 591.9 |
| 130° | 627.9 | 628.2 | 628.2 | 628.2 | 628.2 | 628.2 | 627.8 | 627.5 | 627.1 | 626.7 | 626.1 |
| 132.5° | 661.0 | 661.2 | 661.0 | 660.8 | 660.6 | 660.6 | 660.1 | 659.8 | 659.4 | 659.0 | 658.7 |
| 135° | 708.4 | 709.0 | 709.0 | 709.0 | 709.0 | 709.0 | 708.6 | 708.3 | 707.8 | 707.5 | 707.0 |
| 137.5° | 754.5 | 754.8 | 755.2 | 755.5 | 755.8 | 756.1 | 755.6 | 755.1 | 754.6 | 754.1 | 753.9 |
| 140° | 786.2 | 786.4 | 786.4 | 786.4 | 786.4 | 786.4 | 786.2 | 786.0 | 785.7 | 785.6 | 785.4 |
| 142.5° | 815.7 | 815.8 | 815.7 | 815.5 | 815.4 | 815.2 | 815.2 | 815.1 | 815.1 | 815.1 | 815.0 |
| 145° | 858.2 | 858.6 | 858.8 | 859.0 | 859.2 | 859.4 | 859.2 | 859.0 | 858.8 | 858.6 | 858.2 |
| 147.5° | 899.3 | 899.7 | 899.6 | 899.4 | 899.2 | 899.1 | 899.0 | 898.8 | 898.6 | 898.5 | 898.3 |
| 150° | 923.5 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.8 |
| 152.5° | 945.6 | 945.9 | 946.1 | 946.2 | 946.4 | 946.5 | 947.0 | 947.4 | 947.9 | 948.4 | 948.4 |
| 155° | 979.7 | 979.6 | 979.4 | 979.2 | 979.0 | 978.9 | 979.6 | 980.4 | 981.1 | 981.9 | 981.9 |
| 157.5° | 1008.6 | 1008.4 | 1008.3 | 1008.3 | 1008.3 | 1008.2 | 1008.8 | 1009.4 | 1010.0 | 1010.6 | 1010.5 |
| 160° | 1027.1 | 1026.9 | 1026.7 | 1026.5 | 1026.3 | 1026.1 | 1026.7 | 1027.3 | 1027.9 | 1028.4 | 1028.2 |
| 162.5° | 1042.3 | 1042.0 | 1041.8 | 1041.6 | 1041.5 | 1041.2 | 1042.2 | 1043.3 | 1044.3 | 1045.3 | 1045.4 |
| 165° | 1064.2 | 1063.8 | 1063.3 | 1063.0 | 1062.6 | 1062.2 | 1063.3 | 1064.5 | 1065.7 | 1066.8 | 1067.0 |
| 167.5° | 1080.3 | 1080.0 | 1080.0 | 1080.0 | 1080.0 | 1080.1 | 1081.2 | 1082.4 | 1083.6 | 1084.7 | 1084.7 |
| 170° | 1089.3 | 1088.9 | 1089.2 | 1089.3 | 1089.5 | 1089.7 | 1090.9 | 1092.0 | 1093.1 | 1094.3 | 1094.2 |
| 172.5° | 1096.8 | 1096.4 | 1096.5 | 1096.5 | 1096.6 | 1096.6 | 1097.9 | 1099.2 | 1100.4 | 1101.8 | 1101.7 |
| 175° | 1105.7 | 1105.1 | 1104.9 | 1104.7 | 1104.5 | 1104.3 | 1105.7 | 1107.0 | 1108.4 | 1109.7 | 1109.7 |
| 177.5° | 1109.5 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1110.2 | 1111.3 | 1112.3 | 1113.4 | 1113.4 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1053.3 | 1052.7 | 1050.1 | 1049.7 | 1050.1 | 1052.7 | 1053.3 | 1054.1 | 1055.2 | 1058.9 | 1054.5 |
| 5° | 973.1 | 970.8 | 969.4 | 974.5 | 969.4 | 970.8 | 973.1 | 975.8 | 980.4 | 980.9 | 985.4 |
| 7.5° | 912.5 | 910.7 | 906.6 | 905.4 | 906.6 | 910.7 | 912.5 | 914.2 | 918.8 | 922.7 | 929.4 |
| 10° | 873.7 | 871.8 | 868.2 | 867.3 | 868.2 | 871.8 | 873.7 | 878.3 | 882.9 | 887.9 | 892.5 |
| 12.5° | 836.3 | 832.7 | 831.9 | 832.8 | 831.9 | 832.7 | 836.3 | 842.4 | 854.3 | 854.2 | 855.1 |
| 15° | 786.7 | 784.9 | 779.8 | 781.2 | 779.8 | 784.9 | 786.7 | 792.6 | 798.1 | 805.0 | 811.8 |
| 17.5° | 737.8 | 735.6 | 729.4 | 734.9 | 729.4 | 735.6 | 737.8 | 741.0 | 748.0 | 757.8 | 768.1 |
| 20° | 707.1 | 703.4 | 700.2 | 699.6 | 700.2 | 703.4 | 707.1 | 710.2 | 718.0 | 726.3 | 734.0 |
| 22.5° | 677.7 | 674.4 | 674.2 | 671.1 | 674.2 | 674.4 | 677.7 | 682.8 | 690.5 | 695.1 | 702.5 |
| 25° | 641.1 | 637.9 | 637.0 | 634.6 | 637.0 | 637.9 | 641.1 | 644.7 | 649.8 | 653.4 | 661.7 |
| 27.5° | 612.9 | 611.4 | 609.8 | 610.4 | 609.8 | 611.4 | 612.9 | 613.5 | 615.7 | 620.5 | 625.3 |
| 30° | 595.7 | 595.3 | 594.3 | 594.3 | 594.3 | 595.3 | 595.7 | 594.3 | 596.7 | 598.9 | 602.6 |
| 32.5° | 581.4 | 581.3 | 581.9 | 581.9 | 581.9 | 581.3 | 581.4 | 579.4 | 580.1 | 581.0 | 582.8 |
| 35° | 561.4 | 562.7 | 563.7 | 562.3 | 563.7 | 562.7 | 561.4 | 559.6 | 558.2 | 555.0 | 555.9 |
| 37.5° | 543.3 | 544.7 | 546.0 | 547.5 | 546.0 | 544.7 | 543.3 | 539.5 | 536.2 | 533.4 | 530.1 |
| 40° | 529.3 | 532.5 | 533.5 | 535.8 | 533.5 | 532.5 | 529.3 | 525.2 | 521.6 | 518.3 | 514.7 |
| 42.5° | 516.2 | 519.7 | 522.1 | 522.5 | 522.1 | 519.7 | 516.2 | 512.0 | 506.5 | 502.6 | 497.5 |
| 45° | 495.9 | 499.6 | 502.8 | 502.8 | 502.8 | 499.6 | 495.9 | 489.0 | 483.1 | 477.2 | 472.1 |
| 47.5° | 474.9 | 480.3 | 483.5 | 484.3 | 483.5 | 480.3 | 474.9 | 467.9 | 459.6 | 452.2 | 445.0 |
| 50° | 460.6 | 467.1 | 470.3 | 472.6 | 470.3 | 467.1 | 460.6 | 452.9 | 444.2 | 435.0 | 426.3 |
| 52.5° | 446.8 | 453.1 | 457.4 | 458.7 | 457.4 | 453.1 | 446.8 | 437.1 | 426.6 | 416.7 | 409.1 |
| 55° | 422.7 | 431.8 | 436.9 | 438.7 | 436.9 | 431.8 | 422.7 | 412.2 | 402.1 | 389.7 | 378.7 |
| 57.5° | 399.9 | 408.4 | 414.2 | 415.6 | 414.2 | 408.4 | 399.9 | 387.5 | 374.5 | 361.4 | 349.7 |
| 60° | 382.4 | 391.5 | 398.8 | 400.2 | 398.8 | 391.5 | 382.4 | 370.0 | 356.3 | 343.5 | 328.8 |
| 62.5° | 364.4 | 373.9 | 380.6 | 384.1 | 380.6 | 373.9 | 364.4 | 351.3 | 336.5 | 322.2 | 307.5 |
| 65° | 333.4 | 342.9 | 349.4 | 350.8 | 349.4 | 342.9 | 333.4 | 320.6 | 305.0 | 289.9 | 277.5 |
| 67.5° | 299.5 | 309.1 | 313.3 | 316.0 | 313.3 | 309.1 | 299.5 | 287.4 | 272.0 | 256.3 | 242.3 |
| 70° | 275.7 | 283.4 | 288.0 | 290.3 | 288.0 | 283.4 | 275.7 | 262.9 | 250.0 | 234.0 | 218.9 |
| 72.5° | 248.6 | 256.7 | 262.0 | 262.4 | 262.0 | 256.7 | 248.6 | 237.5 | 224.0 | 209.1 | 195.8 |
| 75° | 207.0 | 214.3 | 217.1 | 217.1 | 217.1 | 214.3 | 207.0 | 196.5 | 185.5 | 173.6 | 160.2 |
| 77.5° | 163.8 | 167.6 | 171.1 | 171.8 | 171.1 | 167.6 | 163.8 | 156.3 | 147.1 | 135.3 | 125.3 |
| 80° | 136.0 | 138.3 | 141.0 | 141.0 | 141.0 | 138.3 | 136.0 | 129.2 | 120.5 | 110.4 | 102.5 |
| 82.5° | 107.5 | 109.3 | 112.1 | 111.8 | 112.1 | 109.3 | 107.5 | 102.0 | 94.8 | 88.0 | 80.9 |
| 85° | 65.0 | 69.1 | 68.7 | 67.8 | 68.7 | 69.1 | 65.0 | 66.0 | 59.1 | 54.5 | 48.0 |
| 87.5° | 34.3 | 34.7 | 35.8 | 36.7 | 35.8 | 34.7 | 34.3 | 33.1 | 29.6 | 27.6 | 25.8 |
| 90° | 24.6 | 25.1 | 25.4 | 25.7 | 25.4 | 25.1 | 24.6 | 24.3 | 23.5 | 22.4 | 21.2 |
| 92.5° | 37.5 | 37.7 | 38.0 | 38.1 | 38.0 | 37.7 | 37.5 | 37.3 | 36.8 | 36.1 | 35.4 |
| 95° | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 | 67.6 | 67.1 | 66.5 |
| 97.5° | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 | 106.1 | 105.4 | 104.7 |
| 100° | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 | 133.0 | 132.6 | 132.2 |
| 102.5° | 163.0 | 163.2 | 163.3 | 163.4 | 163.3 | 163.2 | 163.0 | 162.8 | 162.5 | 162.0 | 161.4 |
| 105° | 207.9 | 208.5 | 209.1 | 209.7 | 209.1 | 208.5 | 207.9 | 207.4 | 206.8 | 206.3 | 205.7 |
| 107.5° | 254.9 | 254.8 | 254.8 | 254.7 | 254.8 | 254.8 | 254.9 | 254.9 | 254.6 | 254.1 | 253.6 |
| 110° | 285.3 | 285.9 | 286.5 | 287.1 | 286.5 | 285.9 | 285.3 | 284.7 | 284.6 | 285.0 | 285.4 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 319.7 | 319.8 | 319.9 | 320.0 | 319.9 | 319.8 | 319.7 | 319.6 | 319.6 | 319.6 | 319.7 |
| 115° | 371.9 | 371.6 | 371.4 | 371.3 | 371.4 | 371.6 | 371.9 | 372.0 | 372.2 | 372.4 | 372.6 |
| 117.5° | 421.2 | 420.9 | 420.4 | 420.1 | 420.4 | 420.9 | 421.2 | 421.6 | 422.1 | 422.8 | 423.4 |
| 120° | 456.1 | 456.4 | 456.8 | 457.2 | 456.8 | 456.4 | 456.1 | 455.6 | 456.0 | 456.9 | 457.9 |
| 122.5° | 490.2 | 489.5 | 488.8 | 488.1 | 488.8 | 489.5 | 490.2 | 490.9 | 491.5 | 492.2 | 492.8 |
| 125° | 542.6 | 542.2 | 541.8 | 541.4 | 541.8 | 542.2 | 542.6 | 542.9 | 543.3 | 543.7 | 544.1 |
| 127.5° | 591.7 | 591.3 | 591.1 | 590.7 | 591.1 | 591.3 | 591.7 | 591.9 | 592.3 | 592.7 | 593.1 |
| 130° | 625.3 | 624.6 | 623.8 | 623.0 | 623.8 | 624.6 | 625.3 | 626.1 | 626.7 | 627.1 | 627.5 |
| 132.5° | 658.3 | 658.1 | 657.7 | 657.5 | 657.7 | 658.1 | 658.3 | 658.7 | 659.0 | 659.4 | 659.8 |
| 135° | 706.5 | 705.8 | 705.2 | 704.7 | 705.2 | 705.8 | 706.5 | 707.0 | 707.5 | 707.8 | 708.3 |
| 137.5° | 754.1 | 754.1 | 754.2 | 754.4 | 754.2 | 754.1 | 754.1 | 753.9 | 754.1 | 754.6 | 755.1 |
| 140° | 785.2 | 785.0 | 784.8 | 784.6 | 784.8 | 785.0 | 785.2 | 785.4 | 785.6 | 785.7 | 786.0 |
| 142.5° | 815.0 | 814.9 | 814.9 | 814.9 | 814.9 | 814.9 | 815.0 | 815.0 | 815.1 | 815.1 | 815.1 |
| 145° | 857.6 | 857.1 | 856.5 | 855.9 | 856.5 | 857.1 | 857.6 | 858.2 | 858.6 | 858.8 | 859.0 |
| 147.5° | 898.1 | 897.9 | 897.8 | 897.6 | 897.8 | 897.9 | 898.1 | 898.3 | 898.5 | 898.6 | 898.8 |
| 150° | 923.6 | 923.3 | 923.2 | 923.0 | 923.2 | 923.3 | 923.6 | 923.8 | 923.9 | 923.9 | 923.9 |
| 152.5° | 947.9 | 947.4 | 946.8 | 946.3 | 946.8 | 947.4 | 947.9 | 948.4 | 948.4 | 947.9 | 947.4 |
| 155° | 981.1 | 980.4 | 979.6 | 978.9 | 979.6 | 980.4 | 981.1 | 981.9 | 981.9 | 981.1 | 980.4 |
| 157.5° | 1009.9 | 1009.2 | 1008.6 | 1007.9 | 1008.6 | 1009.2 | 1009.9 | 1010.5 | 1010.6 | 1010.0 | 1009.4 |
| 160° | 1027.3 | 1026.3 | 1025.4 | 1024.4 | 1025.4 | 1026.3 | 1027.3 | 1028.2 | 1028.4 | 1027.9 | 1027.3 |
| 162.5° | 1044.5 | 1043.5 | 1042.6 | 1041.6 | 1042.6 | 1043.5 | 1044.5 | 1045.4 | 1045.3 | 1044.3 | 1043.3 |
| 165° | 1066.3 | 1065.5 | 1064.7 | 1063.9 | 1064.7 | 1065.5 | 1066.3 | 1067.0 | 1066.8 | 1065.7 | 1064.5 |
| 167.5° | 1083.5 | 1082.3 | 1081.1 | 1080.0 | 1081.1 | 1082.3 | 1083.5 | 1084.7 | 1084.7 | 1083.6 | 1082.4 |
| 170° | 1092.9 | 1091.5 | 1090.2 | 1088.8 | 1090.2 | 1091.5 | 1092.9 | 1094.2 | 1094.3 | 1093.1 | 1092.0 |
| 172.5° | 1100.4 | 1099.1 | 1097.8 | 1096.4 | 1097.8 | 1099.1 | 1100.4 | 1101.7 | 1101.8 | 1100.4 | 1099.2 |
| 175° | 1108.4 | 1107.0 | 1105.7 | 1104.3 | 1105.7 | 1107.0 | 1108.4 | 1109.7 | 1109.7 | 1108.4 | 1107.0 |
| 177.5° | 1112.2 | 1110.9 | 1109.7 | 1108.5 | 1109.7 | 1110.9 | 1112.2 | 1113.4 | 1113.4 | 1112.3 | 1111.3 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1056.7 | 1058.2 | 1064.0 | 1069.5 | 1076.1 | 1080.9 | 1084.2 | 1087.8 | 1095.5 | 1101.7 | 1107.6 |
| 5° | 990.0 | 992.3 | 1004.2 | 1012.4 | 1026.7 | 1039.0 | 1048.6 | 1059.1 | 1071.5 | 1088.5 | 1104.1 |
| 7.5° | 931.3 | 939.8 | 952.8 | 966.2 | 980.7 | 996.9 | 1011.0 | 1026.8 | 1048.2 | 1071.4 | 1095.5 |
| 10° | 897.9 | 907.6 | 921.4 | 936.9 | 950.6 | 969.4 | 986.8 | 1005.6 | 1029.8 | 1058.3 | 1086.7 |
| 12.5° | 864.6 | 880.5 | 890.9 | 909.4 | 924.3 | 939.7 | 958.2 | 982.8 | 1011.2 | 1041.0 | 1075.3 |
| 15° | 822.9 | 831.6 | 851.7 | 861.8 | 882.9 | 906.6 | 925.0 | 949.7 | 977.1 | 1016.6 | 1055.1 |
| 17.5° | 774.7 | 786.2 | 802.2 | 821.4 | 845.6 | 864.2 | 887.0 | 912.4 | 947.0 | 986.2 | 1034.3 |
| 20° | 743.2 | 752.8 | 772.5 | 793.6 | 819.2 | 838.9 | 863.2 | 887.9 | 923.6 | 965.3 | 1015.6 |
| 22.5° | 715.0 | 724.3 | 745.0 | 764.7 | 789.5 | 813.6 | 839.0 | 867.7 | 902.0 | 945.9 | 997.3 |
| 25° | 671.3 | 683.6 | 702.0 | 722.1 | 746.0 | 773.4 | 800.9 | 826.6 | 863.2 | 909.4 | 964.4 |
| 27.5° | 632.6 | 642.5 | 655.7 | 678.6 | 705.7 | 732.2 | 759.5 | 791.7 | 826.9 | 875.8 | 932.9 |
| 30° | 607.6 | 616.8 | 630.1 | 651.2 | 676.3 | 704.7 | 733.1 | 764.2 | 800.9 | 849.5 | 907.6 |
| 32.5° | 587.9 | 594.9 | 606.7 | 625.5 | 648.5 | 678.4 | 706.4 | 738.7 | 777.1 | 824.9 | 881.6 |
| 35° | 558.6 | 564.6 | 569.2 | 587.0 | 607.6 | 635.2 | 663.5 | 697.8 | 734.9 | 780.3 | 837.1 |
| 37.5° | 529.9 | 532.0 | 538.7 | 550.4 | 570.4 | 595.6 | 622.0 | 655.8 | 693.8 | 739.9 | 791.1 |
| 40° | 512.4 | 513.3 | 517.5 | 528.4 | 545.9 | 569.6 | 595.3 | 628.7 | 664.9 | 708.4 | 759.2 |
| 42.5° | 495.2 | 494.6 | 498.4 | 506.1 | 522.4 | 544.0 | 569.3 | 599.8 | 635.9 | 676.1 | 724.0 |
| 45° | 468.0 | 468.0 | 467.1 | 473.5 | 486.7 | 507.8 | 528.9 | 558.2 | 588.4 | 627.8 | 668.1 |
| 47.5° | 439.6 | 437.0 | 437.8 | 441.2 | 452.3 | 469.7 | 490.9 | 514.9 | 541.6 | 574.9 | 610.2 |
| 50° | 421.3 | 417.6 | 416.2 | 419.9 | 430.0 | 445.1 | 465.2 | 486.3 | 511.5 | 540.8 | 571.0 |
| 52.5° | 401.1 | 397.4 | 395.0 | 397.5 | 406.9 | 420.9 | 439.2 | 457.7 | 480.4 | 504.2 | 530.4 |
| 55° | 370.0 | 365.8 | 364.5 | 365.4 | 372.3 | 383.2 | 398.8 | 415.8 | 432.7 | 452.5 | 470.7 |
| 57.5° | 339.3 | 332.5 | 331.2 | 330.8 | 335.5 | 345.6 | 358.6 | 373.3 | 385.6 | 397.5 | 417.1 |
| 60° | 319.2 | 310.9 | 308.2 | 307.7 | 311.4 | 319.6 | 331.6 | 346.2 | 354.9 | 363.1 | 380.0 |
| 62.5° | 297.6 | 289.6 | 283.6 | 284.3 | 287.6 | 295.4 | 305.9 | 316.5 | 322.3 | 331.2 | 342.7 |
| 65° | 264.2 | 254.2 | 249.6 | 248.2 | 250.0 | 256.4 | 264.7 | 271.6 | 277.9 | 281.6 | 292.6 |
| 67.5° | 230.9 | 222.5 | 215.7 | 214.0 | 213.2 | 217.6 | 224.4 | 228.5 | 233.1 | 236.3 | 242.8 |
| 70° | 207.4 | 200.1 | 191.8 | 189.1 | 188.6 | 192.3 | 198.7 | 199.1 | 205.6 | 207.0 | 213.9 |
| 72.5° | 184.3 | 175.2 | 169.5 | 166.8 | 164.9 | 168.2 | 172.4 | 173.6 | 177.0 | 179.5 | 183.0 |
| 75° | 148.4 | 141.5 | 136.0 | 131.9 | 130.5 | 132.3 | 132.3 | 134.7 | 136.9 | 138.3 | 142.4 |
| 77.5° | 116.8 | 108.9 | 102.4 | 100.0 | 98.3 | 97.2 | 98.2 | 99.5 | 98.4 | 100.8 | 101.8 |
| 80° | 94.8 | 86.5 | 81.5 | 80.6 | 77.8 | 75.6 | 75.1 | 76.5 | 74.6 | 75.6 | 78.3 |
| 82.5° | 73.2 | 67.8 | 62.4 | 61.6 | 58.0 | 56.9 | 56.4 | 55.6 | 55.6 | 55.4 | 56.0 |
| 85° | 43.5 | 40.3 | 36.6 | 34.4 | 33.0 | 30.7 | 30.7 | 29.8 | 28.8 | 27.9 | 28.4 |
| 87.5° | 21.6 | 20.7 | 18.5 | 17.0 | 16.0 | 14.3 | 13.9 | 12.4 | 11.6 | 10.8 | 10.1 |
| 90° | 20.1 | 18.9 | 17.4 | 15.8 | 14.3 | 12.8 | 11.0 | 8.9 | 6.8 | 4.6 | 2.6 |
| 92.5° | 34.7 | 34.0 | 33.0 | 31.9 | 30.8 | 29.8 | 28.0 | 25.6 | 23.2 | 20.8 | 18.4 |
| 95° | 65.9 | 65.3 | 64.0 | 62.7 | 61.3 | 59.9 | 58.5 | 56.7 | 55.0 | 53.3 | 51.6 |
| 97.5° | 104.0 | 103.3 | 101.8 | 100.1 | 98.6 | 97.0 | 95.6 | 94.2 | 92.8 | 91.4 | 90.1 |
| 100° | 131.9 | 131.5 | 129.8 | 128.0 | 126.3 | 124.6 | 123.4 | 122.6 | 121.8 | 121.1 | 120.3 |
| 102.5° | 160.9 | 160.4 | 158.8 | 157.2 | 155.7 | 154.1 | 153.2 | 152.8 | 152.6 | 152.2 | 152.0 |
| 105° | 205.1 | 204.6 | 203.8 | 203.0 | 202.2 | 201.5 | 201.0 | 200.8 | 200.6 | 200.4 | 200.3 |
| 107.5° | 253.0 | 252.5 | 252.4 | 252.3 | 252.2 | 252.0 | 251.8 | 251.7 | 251.4 | 251.2 | 251.0 |
| 110° | 285.8 | 286.2 | 286.4 | 286.5 | 286.7 | 287.0 | 286.9 | 286.5 | 286.1 | 285.7 | 285.3 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 319.8 | 319.9 | 320.2 | 320.6 | 320.9 | 321.2 | 321.4 | 321.3 | 321.2 | 321.2 | 321.1 |
| 115° | 372.8 | 373.0 | 373.3 | 373.8 | 374.1 | 374.5 | 374.7 | 374.7 | 374.7 | 374.7 | 374.7 |
| 117.5° | 424.0 | 424.7 | 425.0 | 425.2 | 425.5 | 425.8 | 425.9 | 425.7 | 425.5 | 425.4 | 425.2 |
| 120° | 458.8 | 459.8 | 460.4 | 460.9 | 461.5 | 462.1 | 462.0 | 461.2 | 460.5 | 459.7 | 458.9 |
| 122.5° | 493.5 | 494.1 | 494.4 | 494.6 | 495.0 | 495.2 | 495.2 | 494.9 | 494.6 | 494.3 | 494.0 |
| 125° | 544.5 | 544.8 | 545.0 | 545.3 | 545.4 | 545.6 | 545.7 | 545.7 | 545.7 | 545.7 | 545.7 |
| 127.5° | 593.5 | 593.8 | 594.2 | 594.4 | 594.8 | 595.0 | 595.0 | 594.3 | 593.7 | 593.2 | 592.6 |
| 130° | 627.8 | 628.2 | 628.2 | 628.2 | 628.2 | 628.2 | 627.9 | 627.3 | 626.8 | 626.2 | 625.6 |
| 132.5° | 660.1 | 660.6 | 660.6 | 660.8 | 661.0 | 661.2 | 661.0 | 660.6 | 660.1 | 659.8 | 659.4 |
| 135° | 708.6 | 709.0 | 709.0 | 709.0 | 709.0 | 709.0 | 708.4 | 707.3 | 706.1 | 705.0 | 703.9 |
| 137.5° | 755.6 | 756.1 | 755.8 | 755.5 | 755.2 | 754.8 | 754.5 | 753.9 | 753.4 | 752.9 | 752.3 |
| 140° | 786.2 | 786.4 | 786.4 | 786.4 | 786.4 | 786.4 | 786.2 | 785.7 | 785.4 | 785.0 | 784.6 |
| 142.5° | 815.2 | 815.2 | 815.4 | 815.5 | 815.7 | 815.8 | 815.7 | 815.4 | 814.9 | 814.6 | 814.2 |
| 145° | 859.2 | 859.4 | 859.2 | 859.0 | 858.8 | 858.6 | 858.2 | 857.4 | 856.6 | 855.8 | 855.1 |
| 147.5° | 899.0 | 899.1 | 899.2 | 899.4 | 899.6 | 899.7 | 899.3 | 898.5 | 897.5 | 896.6 | 895.7 |
| 150° | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.5 | 922.7 | 922.0 | 921.2 | 920.4 |
| 152.5° | 947.0 | 946.5 | 946.4 | 946.2 | 946.1 | 945.9 | 945.6 | 945.2 | 944.7 | 944.3 | 943.8 |
| 155° | 979.6 | 978.9 | 979.0 | 979.2 | 979.4 | 979.6 | 979.7 | 979.7 | 979.7 | 979.7 | 979.7 |
| 157.5° | 1008.8 | 1008.2 | 1008.3 | 1008.3 | 1008.3 | 1008.4 | 1008.6 | 1008.9 | 1009.3 | 1009.6 | 1010.0 |
| 160° | 1026.7 | 1026.1 | 1026.3 | 1026.5 | 1026.7 | 1026.9 | 1027.1 | 1027.3 | 1027.4 | 1027.6 | 1027.9 |
| 162.5° | 1042.2 | 1041.2 | 1041.5 | 1041.6 | 1041.8 | 1042.0 | 1042.3 | 1042.8 | 1043.4 | 1043.9 | 1044.3 |
| 165° | 1063.3 | 1062.2 | 1062.6 | 1063.0 | 1063.3 | 1063.8 | 1064.2 | 1064.8 | 1065.4 | 1065.9 | 1066.5 |
| 167.5° | 1081.2 | 1080.1 | 1080.0 | 1080.0 | 1080.0 | 1080.0 | 1080.3 | 1081.2 | 1081.9 | 1082.7 | 1083.6 |
| 170° | 1090.9 | 1089.7 | 1089.5 | 1089.3 | 1089.2 | 1088.9 | 1089.3 | 1090.3 | 1091.2 | 1092.2 | 1093.1 |
| 172.5° | 1097.9 | 1096.6 | 1096.6 | 1096.5 | 1096.5 | 1096.4 | 1096.8 | 1097.6 | 1098.5 | 1099.2 | 1100.0 |
| 175° | 1105.7 | 1104.3 | 1104.5 | 1104.7 | 1104.9 | 1105.1 | 1105.7 | 1106.6 | 1107.6 | 1108.5 | 1109.5 |
| 177.5° | 1110.2 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1109.5 | 1110.3 | 1111.0 | 1111.8 | 1112.6 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1112.8 | 1116.4 | 1121.2 | 1129.2 | 1132.1 | 1135.8 | 1140.9 | 1140.6 | 1142.0 | 1147.5 | 1159.3 |
| 5° | 1116.9 | 1131.0 | 1144.8 | 1161.2 | 1178.7 | 1190.1 | 1205.7 | 1215.3 | 1224.9 | 1237.3 | 1258.4 |
| 7.5° | 1118.5 | 1141.0 | 1166.2 | 1195.2 | 1220.9 | 1250.6 | 1273.8 | 1295.5 | 1315.2 | 1341.4 | 1366.4 |
| 10° | 1115.9 | 1146.2 | 1178.7 | 1215.3 | 1254.2 | 1287.2 | 1317.0 | 1350.8 | 1379.7 | 1411.3 | 1439.7 |
| 12.5° | 1111.2 | 1147.6 | 1191.1 | 1232.2 | 1277.6 | 1326.4 | 1363.5 | 1397.7 | 1436.1 | 1472.5 | 1516.2 |
| 15° | 1100.4 | 1150.3 | 1201.1 | 1255.2 | 1316.0 | 1372.3 | 1425.9 | 1470.3 | 1511.6 | 1566.1 | 1623.3 |
| 17.5° | 1086.7 | 1140.5 | 1204.6 | 1270.0 | 1333.6 | 1398.0 | 1464.3 | 1531.1 | 1583.1 | 1650.8 | 1695.6 |
| 20° | 1073.8 | 1136.1 | 1202.0 | 1279.9 | 1343.5 | 1423.7 | 1489.6 | 1554.2 | 1625.6 | 1692.9 | 1746.5 |
| 22.5° | 1055.8 | 1124.0 | 1193.9 | 1271.4 | 1355.2 | 1435.4 | 1511.6 | 1581.7 | 1653.0 | 1726.2 | 1791.1 |
| 25° | 1033.0 | 1094.8 | 1177.8 | 1265.7 | 1349.0 | 1436.0 | 1523.5 | 1611.4 | 1688.3 | 1765.7 | 1826.2 |
| 27.5° | 994.2 | 1072.3 | 1149.4 | 1240.2 | 1332.8 | 1431.2 | 1524.7 | 1616.8 | 1697.4 | 1761.0 | 1798.5 |
| 30° | 974.5 | 1042.2 | 1126.0 | 1217.1 | 1317.4 | 1423.2 | 1520.7 | 1610.9 | 1686.0 | 1736.9 | 1752.0 |
| 32.5° | 945.1 | 1015.1 | 1097.1 | 1191.5 | 1297.6 | 1406.4 | 1507.9 | 1593.0 | 1655.6 | 1682.3 | 1664.1 |
| 35° | 901.6 | 964.8 | 1047.7 | 1144.4 | 1254.6 | 1370.5 | 1470.8 | 1542.7 | 1574.8 | 1549.5 | 1486.9 |
| 37.5° | 849.5 | 912.1 | 995.3 | 1090.2 | 1204.4 | 1322.2 | 1412.8 | 1464.6 | 1454.0 | 1391.3 | 1297.8 |
| 40° | 812.8 | 871.4 | 950.6 | 1053.2 | 1164.5 | 1282.6 | 1362.3 | 1390.3 | 1360.9 | 1271.2 | 1171.8 |
| 42.5° | 772.1 | 829.3 | 908.9 | 1007.8 | 1125.7 | 1234.6 | 1304.1 | 1306.3 | 1257.2 | 1150.0 | 1050.2 |
| 45° | 710.2 | 764.7 | 839.8 | 942.9 | 1051.8 | 1154.4 | 1200.1 | 1177.8 | 1087.1 | 983.6 | 883.3 |
| 47.5° | 649.1 | 696.4 | 770.4 | 868.2 | 971.7 | 1058.1 | 1080.7 | 1040.3 | 943.7 | 843.3 | 750.4 |
| 50° | 604.4 | 652.0 | 721.7 | 815.1 | 914.9 | 989.5 | 1000.6 | 946.9 | 852.2 | 751.0 | 678.2 |
| 52.5° | 561.5 | 608.8 | 675.9 | 762.3 | 853.8 | 921.0 | 921.4 | 859.5 | 765.0 | 674.8 | 607.1 |
| 55° | 498.7 | 541.2 | 601.7 | 679.1 | 760.6 | 813.2 | 800.5 | 736.3 | 654.4 | 576.1 | 516.9 |
| 57.5° | 438.1 | 475.1 | 530.8 | 595.4 | 667.2 | 710.6 | 689.3 | 627.6 | 554.4 | 488.0 | 443.2 |
| 60° | 398.8 | 434.1 | 481.7 | 542.6 | 603.0 | 637.0 | 616.8 | 560.9 | 493.6 | 440.1 | 401.1 |
| 62.5° | 360.8 | 390.5 | 436.3 | 489.1 | 545.2 | 570.3 | 552.3 | 497.2 | 439.0 | 390.6 | 359.0 |
| 65° | 306.8 | 331.1 | 367.7 | 413.0 | 453.8 | 475.3 | 460.2 | 408.9 | 364.5 | 329.7 | 304.5 |
| 67.5° | 256.4 | 275.3 | 303.2 | 339.5 | 374.1 | 385.7 | 372.0 | 336.3 | 298.7 | 270.8 | 253.0 |
| 70° | 221.6 | 239.5 | 262.9 | 290.8 | 321.0 | 333.4 | 319.6 | 291.2 | 260.5 | 234.9 | 217.5 |
| 72.5° | 191.2 | 205.1 | 224.7 | 248.7 | 272.2 | 284.6 | 275.3 | 248.0 | 222.1 | 203.0 | 188.2 |
| 75° | 145.6 | 157.6 | 171.3 | 188.2 | 206.6 | 214.7 | 206.6 | 187.8 | 169.9 | 155.7 | 145.2 |
| 77.5° | 105.9 | 112.3 | 122.9 | 135.5 | 147.0 | 153.3 | 146.2 | 133.5 | 122.5 | 112.8 | 107.6 |
| 80° | 80.6 | 85.2 | 92.5 | 102.5 | 110.4 | 116.3 | 111.8 | 101.2 | 92.5 | 86.1 | 83.8 |
| 82.5° | 58.6 | 61.7 | 66.5 | 74.0 | 79.2 | 82.2 | 80.2 | 72.6 | 69.1 | 63.4 | 61.0 |
| 85° | 28.8 | 30.7 | 33.9 | 36.2 | 40.7 | 41.2 | 41.7 | 38.5 | 35.3 | 33.9 | 32.0 |
| 87.5° | 10.8 | 11.6 | 13.2 | 14.6 | 16.4 | 17.1 | 17.0 | 17.4 | 16.3 | 16.1 | 14.9 |
| 90° | 4.6 | 6.8 | 8.9 | 11.0 | 12.8 | 14.3 | 15.8 | 17.4 | 18.9 | 20.1 | 21.2 |
| 92.5° | 20.8 | 23.2 | 25.6 | 28.0 | 29.8 | 30.8 | 31.9 | 33.0 | 34.0 | 34.7 | 35.4 |
| 95° | 53.3 | 55.0 | 56.7 | 58.5 | 59.9 | 61.3 | 62.7 | 64.0 | 65.3 | 65.9 | 66.5 |
| 97.5° | 91.4 | 92.8 | 94.2 | 95.6 | 97.0 | 98.6 | 100.1 | 101.8 | 103.3 | 104.0 | 104.7 |
| 100° | 121.1 | 121.8 | 122.6 | 123.4 | 124.6 | 126.3 | 128.0 | 129.8 | 131.5 | 131.9 | 132.2 |
| 102.5° | 152.2 | 152.6 | 152.8 | 153.2 | 154.1 | 155.7 | 157.2 | 158.8 | 160.4 | 160.9 | 161.4 |
| 105° | 200.4 | 200.6 | 200.8 | 201.0 | 201.5 | 202.2 | 203.0 | 203.8 | 204.6 | 205.1 | 205.7 |
| 107.5° | 251.2 | 251.4 | 251.7 | 251.8 | 252.0 | 252.2 | 252.3 | 252.4 | 252.5 | 253.0 | 253.6 |
| 110° | 285.7 | 286.1 | 286.5 | 286.9 | 287.0 | 286.7 | 286.5 | 286.4 | 286.2 | 285.8 | 285.4 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 321.2 | 321.2 | 321.3 | 321.4 | 321.2 | 320.9 | 320.6 | 320.2 | 319.9 | 319.8 | 319.7 |
| 115° | 374.7 | 374.7 | 374.7 | 374.7 | 374.5 | 374.1 | 373.8 | 373.3 | 373.0 | 372.8 | 372.6 |
| 117.5° | 425.4 | 425.5 | 425.7 | 425.9 | 425.8 | 425.5 | 425.2 | 425.0 | 424.7 | 424.0 | 423.4 |
| 120° | 459.7 | 460.5 | 461.2 | 462.0 | 462.1 | 461.5 | 460.9 | 460.4 | 459.8 | 458.8 | 457.9 |
| 122.5° | 494.3 | 494.6 | 494.9 | 495.2 | 495.2 | 495.0 | 494.6 | 494.4 | 494.1 | 493.5 | 492.8 |
| 125° | 545.7 | 545.7 | 545.7 | 545.7 | 545.6 | 545.4 | 545.3 | 545.0 | 544.8 | 544.5 | 544.1 |
| 127.5° | 593.2 | 593.7 | 594.3 | 595.0 | 595.0 | 594.8 | 594.4 | 594.2 | 593.8 | 593.5 | 593.1 |
| 130° | 626.2 | 626.8 | 627.3 | 627.9 | 628.2 | 628.2 | 628.2 | 628.2 | 628.2 | 627.8 | 627.5 |
| 132.5° | 659.8 | 660.1 | 660.6 | 661.0 | 661.2 | 661.0 | 660.8 | 660.6 | 660.6 | 660.1 | 659.8 |
| 135° | 705.0 | 706.1 | 707.3 | 708.4 | 709.0 | 709.0 | 709.0 | 709.0 | 709.0 | 708.6 | 708.3 |
| 137.5° | 752.9 | 753.4 | 753.9 | 754.5 | 754.8 | 755.2 | 755.5 | 755.8 | 756.1 | 755.6 | 755.1 |
| 140° | 785.0 | 785.4 | 785.7 | 786.2 | 786.4 | 786.4 | 786.4 | 786.4 | 786.4 | 786.2 | 786.0 |
| 142.5° | 814.6 | 814.9 | 815.4 | 815.7 | 815.8 | 815.7 | 815.5 | 815.4 | 815.2 | 815.2 | 815.1 |
| 145° | 855.8 | 856.6 | 857.4 | 858.2 | 858.6 | 858.8 | 859.0 | 859.2 | 859.4 | 859.2 | 859.0 |
| 147.5° | 896.6 | 897.5 | 898.5 | 899.3 | 899.7 | 899.6 | 899.4 | 899.2 | 899.1 | 899.0 | 898.8 |
| 150° | 921.2 | 922.0 | 922.7 | 923.5 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 | 923.9 |
| 152.5° | 944.3 | 944.7 | 945.2 | 945.6 | 945.9 | 946.1 | 946.2 | 946.4 | 946.5 | 947.0 | 947.4 |
| 155° | 979.7 | 979.7 | 979.7 | 979.7 | 979.6 | 979.4 | 979.2 | 979.0 | 978.9 | 979.6 | 980.4 |
| 157.5° | 1009.6 | 1009.3 | 1008.9 | 1008.6 | 1008.4 | 1008.3 | 1008.3 | 1008.3 | 1008.2 | 1008.8 | 1009.4 |
| 160° | 1027.6 | 1027.4 | 1027.3 | 1027.1 | 1026.9 | 1026.7 | 1026.5 | 1026.3 | 1026.1 | 1026.7 | 1027.3 |
| 162.5° | 1043.9 | 1043.4 | 1042.8 | 1042.3 | 1042.0 | 1041.8 | 1041.6 | 1041.5 | 1041.2 | 1042.2 | 1043.3 |
| 165° | 1065.9 | 1065.4 | 1064.8 | 1064.2 | 1063.8 | 1063.3 | 1063.0 | 1062.6 | 1062.2 | 1063.3 | 1064.5 |
| 167.5° | 1082.7 | 1081.9 | 1081.2 | 1080.3 | 1080.0 | 1080.0 | 1080.0 | 1080.0 | 1080.1 | 1081.2 | 1082.4 |
| 170° | 1092.2 | 1091.2 | 1090.3 | 1089.3 | 1088.9 | 1089.2 | 1089.3 | 1089.5 | 1089.7 | 1090.9 | 1092.0 |
| 172.5° | 1099.2 | 1098.5 | 1097.6 | 1096.8 | 1096.4 | 1096.5 | 1096.5 | 1096.6 | 1096.6 | 1097.9 | 1099.2 |
| 175° | 1108.5 | 1107.6 | 1106.6 | 1105.7 | 1105.1 | 1104.9 | 1104.7 | 1104.5 | 1104.3 | 1105.7 | 1107.0 |
| 177.5° | 1111.8 | 1111.0 | 1110.3 | 1109.5 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1109.1 | 1110.2 | 1111.3 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 | 1105.4 |
| 2.5° | 1165.1 | 1165.9 | 1169.2 | 1171.7 | 1172.4 | 1176.1 | 1176.5 |
| 5° | 1267.5 | 1275.3 | 1290.4 | 1291.8 | 1294.1 | 1306.0 | 1296.8 |
| 7.5° | 1387.5 | 1407.2 | 1420.5 | 1432.1 | 1436.3 | 1441.5 | 1440.5 |
| 10° | 1464.4 | 1493.7 | 1508.4 | 1531.7 | 1532.7 | 1538.6 | 1534.9 |
| 12.5° | 1541.7 | 1575.8 | 1602.5 | 1606.8 | 1626.4 | 1629.4 | 1634.6 |
| 15° | 1651.2 | 1687.4 | 1724.5 | 1737.8 | 1764.8 | 1771.2 | 1781.3 |
| 17.5° | 1754.2 | 1791.1 | 1817.1 | 1851.5 | 1862.6 | 1877.4 | 1867.3 |
| 20° | 1810.6 | 1850.9 | 1883.9 | 1910.9 | 1922.4 | 1930.5 | 1929.7 |
| 22.5° | 1844.7 | 1885.3 | 1912.0 | 1932.5 | 1943.2 | 1946.7 | 1946.5 |
| 25° | 1866.0 | 1889.4 | 1897.6 | 1905.4 | 1893.5 | 1889.4 | 1891.2 |
| 27.5° | 1806.6 | 1800.6 | 1779.1 | 1750.8 | 1721.6 | 1698.3 | 1685.7 |
| 30° | 1724.9 | 1689.3 | 1656.7 | 1599.9 | 1570.6 | 1553.2 | 1537.7 |
| 32.5° | 1609.2 | 1552.6 | 1490.0 | 1438.0 | 1404.7 | 1378.9 | 1375.0 |
| 35° | 1410.8 | 1325.7 | 1249.2 | 1185.5 | 1152.5 | 1124.6 | 1118.2 |
| 37.5° | 1199.5 | 1110.9 | 1042.2 | 986.1 | 950.6 | 930.9 | 912.5 |
| 40° | 1059.1 | 983.2 | 915.3 | 867.7 | 840.8 | 826.6 | 815.1 |
| 42.5° | 951.1 | 881.7 | 814.2 | 778.0 | 753.5 | 744.9 | 738.1 |
| 45° | 801.8 | 737.3 | 690.5 | 663.1 | 648.8 | 634.2 | 627.3 |
| 47.5° | 682.3 | 629.7 | 598.9 | 575.6 | 560.4 | 551.7 | 547.3 |
| 50° | 614.5 | 571.4 | 544.0 | 526.2 | 512.4 | 505.5 | 501.9 |
| 52.5° | 554.4 | 519.1 | 496.0 | 481.8 | 472.5 | 467.4 | 466.0 |
| 55° | 477.6 | 450.6 | 435.9 | 423.6 | 416.7 | 412.2 | 410.3 |
| 57.5° | 415.2 | 394.3 | 382.5 | 372.3 | 369.6 | 365.8 | 364.5 |
| 60° | 374.1 | 358.1 | 348.0 | 341.1 | 338.9 | 334.2 | 335.2 |
| 62.5° | 337.9 | 324.8 | 316.2 | 312.2 | 309.2 | 305.3 | 306.6 |
| 65° | 285.8 | 276.1 | 271.6 | 267.9 | 264.2 | 261.9 | 263.7 |
| 67.5° | 239.8 | 233.2 | 227.0 | 224.8 | 223.0 | 222.7 | 220.7 |
| 70° | 209.7 | 204.2 | 198.7 | 197.3 | 197.3 | 195.5 | 195.1 |
| 72.5° | 180.8 | 176.8 | 173.1 | 172.1 | 170.7 | 171.3 | 169.4 |
| 75° | 139.7 | 136.5 | 135.1 | 133.7 | 133.3 | 133.3 | 131.9 |
| 77.5° | 103.2 | 100.8 | 98.7 | 98.7 | 96.9 | 96.3 | 96.2 |
| 80° | 78.3 | 77.4 | 75.6 | 75.6 | 74.6 | 75.1 | 74.2 |
| 82.5° | 58.9 | 57.6 | 57.3 | 56.5 | 55.2 | 55.3 | 54.4 |
| 85° | 31.6 | 30.2 | 29.8 | 28.4 | 27.5 | 28.4 | 27.5 |
| 87.5° | 15.5 | 15.3 | 15.1 | 14.5 | 14.1 | 14.2 | 13.2 |
| 90° | 22.4 | 23.5 | 24.3 | 24.6 | 25.1 | 25.4 | 25.7 |
| 92.5° | 36.1 | 36.8 | 37.3 | 37.5 | 37.7 | 38.0 | 38.1 |
| 95° | 67.1 | 67.6 | 67.9 | 67.9 | 67.9 | 67.9 | 67.9 |
| 97.5° | 105.4 | 106.1 | 106.4 | 106.4 | 106.4 | 106.4 | 106.4 |
| 100° | 132.6 | 133.0 | 133.2 | 133.2 | 133.2 | 133.2 | 133.2 |
| 102.5° | 162.0 | 162.5 | 162.8 | 163.0 | 163.2 | 163.3 | 163.4 |
| 105° | 206.3 | 206.8 | 207.4 | 207.9 | 208.5 | 209.1 | 209.7 |
| 107.5° | 254.1 | 254.6 | 254.9 | 254.9 | 254.8 | 254.8 | 254.7 |
| 110° | 285.0 | 284.6 | 284.7 | 285.3 | 285.9 | 286.5 | 287.1 |



TEST NUMBER: P332608-935

CATALOG NUMBER: S124DIP-S795D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 319.6 | 319.6 | 319.6 | 319.7 | 319.8 | 319.9 | 320.0 |
| 115° | 372.4 | 372.2 | 372.0 | 371.9 | 371.6 | 371.4 | 371.3 |
| 117.5° | 422.8 | 422.1 | 421.6 | 421.2 | 420.9 | 420.4 | 420.1 |
| 120° | 456.9 | 456.0 | 455.6 | 456.1 | 456.4 | 456.8 | 457.2 |
| 122.5° | 492.2 | 491.5 | 490.9 | 490.2 | 489.5 | 488.8 | 488.1 |
| 125° | 543.7 | 543.3 | 542.9 | 542.6 | 542.2 | 541.8 | 541.4 |
| 127.5° | 592.7 | 592.3 | 591.9 | 591.7 | 591.3 | 591.1 | 590.7 |
| 130° | 627.1 | 626.7 | 626.1 | 625.3 | 624.6 | 623.8 | 623.0 |
| 132.5° | 659.4 | 659.0 | 658.7 | 658.3 | 658.1 | 657.7 | 657.5 |
| 135° | 707.8 | 707.5 | 707.0 | 706.5 | 705.8 | 705.2 | 704.7 |
| 137.5° | 754.6 | 754.1 | 753.9 | 754.1 | 754.1 | 754.2 | 754.4 |
| 140° | 785.7 | 785.6 | 785.4 | 785.2 | 785.0 | 784.8 | 784.6 |
| 142.5° | 815.1 | 815.1 | 815.0 | 815.0 | 814.9 | 814.9 | 814.9 |
| 145° | 858.8 | 858.6 | 858.2 | 857.6 | 857.1 | 856.5 | 855.9 |
| 147.5° | 898.6 | 898.5 | 898.3 | 898.1 | 897.9 | 897.8 | 897.6 |
| 150° | 923.9 | 923.9 | 923.8 | 923.6 | 923.3 | 923.2 | 923.0 |
| 152.5° | 947.9 | 948.4 | 948.4 | 947.9 | 947.4 | 946.8 | 946.3 |
| 155° | 981.1 | 981.9 | 981.9 | 981.1 | 980.4 | 979.6 | 978.9 |
| 157.5° | 1010.0 | 1010.6 | 1010.5 | 1009.9 | 1009.2 | 1008.6 | 1007.9 |
| 160° | 1027.9 | 1028.4 | 1028.2 | 1027.3 | 1026.3 | 1025.4 | 1024.4 |
| 162.5° | 1044.3 | 1045.3 | 1045.4 | 1044.5 | 1043.5 | 1042.6 | 1041.6 |
| 165° | 1065.7 | 1066.8 | 1067.0 | 1066.3 | 1065.5 | 1064.7 | 1063.9 |
| 167.5° | 1083.6 | 1084.7 | 1084.7 | 1083.5 | 1082.3 | 1081.1 | 1080.0 |
| 170° | 1093.1 | 1094.3 | 1094.2 | 1092.9 | 1091.5 | 1090.2 | 1088.8 |
| 172.5° | 1100.4 | 1101.8 | 1101.7 | 1100.4 | 1099.1 | 1097.8 | 1096.4 |
| 175° | 1108.4 | 1109.7 | 1109.7 | 1108.4 | 1107.0 | 1105.7 | 1104.3 |
| 177.5° | 1112.3 | 1113.4 | 1113.4 | 1112.2 | 1110.9 | 1109.7 | 1108.5 |
| 180° | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 | 1111.2 |

(END OF REPORT)