

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333278-830

Luminaire Tested: **S125DIP-S1090D1035U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333278-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7606.1 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	39	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.9
10°-20°	429.6	5.6
20°-30°	697.6	9.2
30°-40°	850.9	11.2
40°-50°	774.1	10.2
50°-60°	616.6	8.1
60°-70°	429.5	5.6
70°-80°	229.0	3.0
80°-90°	60.4	0.8
90°-100°	81.0	1.1
100°-110°	239.1	3.1
110°-120°	405.1	5.3
120°-130°	533.1	7.0
130°-140°	597.3	7.9
140°-150°	585.5	7.7
150°-160°	491.7	6.5
160°-170°	326.9	4.3
170°-180°	114.4	1.5
0°-30°	1271.5	16.7
0°-40°	2122.4	27.9
0°-60°	3513.1	46.2
0°-90°	4232.0	55.6
90°-120°	725.2	9.5
90°-150°	2441.1	32.1
90°-180°	3374.0	44.4
0°-180°	7606.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	23	1	23	1	23	15
95°	81	61	81	61	81	82
105°	233	214	233	214	233	247
115°	409	406	409	406	409	405
125°	596	592	596	592	596	532
135°	772	770	772	770	772	596
145°	936	933	936	933	936	584
155°	1067	1067	1067	1067	1067	491
165°	1157	1160	1157	1160	1157	326
175°	1202	1206	1202	1206	1202	114
180°	1209	1209	1209	1209	1209	



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	16.8	17.6	18.0	17.9	18.3	18.1	19.9	19.7	21.0	22.3	24.1
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9	37.5	36.1	34.3
95°	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4	73.9	72.5	70.4
97.5°	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1	116.8	115.4	112.4
100°	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7	145.8	143.9	141.3
102.5°	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1	176.2	174.1	172.7
105°	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4	226.1	224.9	223.7
107.5°	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5	279.9	279.3	278.3
110°	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4	316.8	316.1	315.6



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4	354.1	353.8	353.0
115°	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8	411.0	411.2	410.8
117.5°	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2	467.1	466.9	466.6
120°	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3	505.3	505.3	505.1
122.5°	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6	542.8	542.9	542.4
125°	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7	598.0	598.5	598.2
127.5°	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2	652.4	652.7	652.4
130°	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3	688.6	688.8	688.3
132.5°	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0	723.2	723.4	723.5
135°	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3	776.3	776.3	776.1
137.5°	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2	827.9	827.6	827.3
140°	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9	860.4	860.1	859.4
142.5°	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0	892.7	892.4	891.6
145°	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1	939.1	939.1	938.5
147.5°	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8	981.4	980.9	980.3
150°	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7	1008.7	1008.7	1007.9
152.5°	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9	1033.3	1032.8	1032.5
155°	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7	1068.8	1068.0	1067.8
157.5°	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7	1099.9	1099.1	1098.9
160°	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6	1118.7	1117.9	1117.7
162.5°	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2	1136.2	1135.2	1135.2
165°	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9	1160.2	1159.3	1159.0
167.5°	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6	1177.3	1176.0	1176.0
170°	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1	1187.9	1186.6	1186.6
172.5°	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7	1195.3	1194.1	1194.1
175°	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1	1203.8	1202.6	1202.6
177.5°	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9	1208.0	1206.9	1207.1
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	24.8	23.5	21.2	19.3	16.5	14.6	13.8	13.9	12.7	12.5	13.4
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8	23.9	25.1	26.3
95°	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2	61.5	62.0	62.4
97.5°	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6	101.8	102.0	102.2
100°	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8
102.5°	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1	164.9	165.8	166.6
105°	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5	215.6	216.6	217.7
107.5°	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2	271.3	272.3	273.4
110°	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7	309.7	310.8	311.8



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8	348.4	348.8	349.4
115°	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6	406.4	407.3	408.1
117.5°	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5	463.9	464.3	464.7
120°	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6	500.7	501.7	502.8
122.5°	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9	539.2	539.6	540.0
125°	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9	593.1	594.4	595.7
127.5°	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4	649.0	649.8	650.4
130°	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2	683.2	684.3	685.3
132.5°	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0	717.8	719.5	721.2
135°	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8	771.0	772.2	773.5
137.5°	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2	821.3	822.6	823.8
140°	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5	853.6	854.6	855.6
142.5°	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9	885.8	886.6	887.5
145°	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6	933.4	934.2	935.0
147.5°	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6	977.0	977.5	978.0
150°	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9	1005.7	1005.5	1005.3
152.5°	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0	1030.3	1030.6	1030.9
155°	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2	1099.8	1099.3	1098.8
160°	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7	1119.2	1118.5	1117.9
162.5°	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1	1136.6	1136.1	1135.7
165°	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3	1159.8	1159.4	1159.0
167.5°	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8	1178.9	1178.2	1177.3
170°	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3	1189.5	1188.6	1187.9
172.5°	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9	1197.0	1196.2	1195.3
175°	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4	1205.5	1204.7	1203.8
177.5°	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7	1210.0	1209.4	1208.6
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	14.2	15.6	15.4	16.2	16.5	17.8	17.4	19.7	20.9	22.1	21.9
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9	40.2	41.7	42.6
95°	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4	76.8	78.3	79.3
97.5°	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1	119.5	120.9	121.7
100°	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7	149.6	151.5	152.7
102.5°	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1	180.2	182.3	183.6
105°	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4	228.7	229.9	230.8
107.5°	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5	281.2	281.8	282.1
110°	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4	318.0	318.7	318.9



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4	354.7	355.0	355.0
115°	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8	410.6	410.4	410.2
117.5°	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2	467.4	467.6	467.2
120°	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3	505.3	505.3	504.9
122.5°	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6	542.4	542.2	541.9
125°	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7	597.2	596.8	596.4
127.5°	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2	652.1	651.9	651.5
130°	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3	688.2	688.0	687.7
132.5°	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0	722.8	722.6	722.2
135°	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3	776.3	776.3	775.9
137.5°	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2	828.4	828.7	828.3
140°	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9	861.3	861.8	861.4
142.5°	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0	893.2	893.4	893.1
145°	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1	939.1	939.1	938.8
147.5°	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8	982.4	982.9	982.4
150°	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7	1008.7	1008.7	1008.5
152.5°	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9	1034.3	1034.8	1034.7
155°	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7	1070.5	1071.4	1071.3
157.5°	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7	1101.5	1102.4	1102.1
160°	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6	1120.4	1121.2	1121.2
162.5°	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2	1138.2	1139.3	1139.2
165°	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9	1161.8	1162.6	1162.4
167.5°	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6	1179.8	1181.1	1181.0
170°	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1	1190.3	1191.6	1191.5
172.5°	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7	1197.9	1199.1	1199.1
175°	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1	1206.4	1207.6	1207.5
177.5°	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9	1209.9	1210.9	1210.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	23.0	22.6	22.7	23.8	22.7	22.6	23.0	21.9	22.1	20.9	19.7
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	43.1	43.5	43.9	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9
95°	79.6	80.1	80.5	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4
97.5°	122.0	122.2	122.4	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1
100°	153.1	153.4	153.9	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7
102.5°	184.2	184.7	185.4	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1
105°	231.5	232.1	232.7	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4
107.5°	282.0	282.0	282.0	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5
110°	318.7	318.5	318.3	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.6	354.2	353.8	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4
115°	409.9	409.7	409.5	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8
117.5°	466.4	465.6	464.8	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2
120°	504.1	503.2	502.4	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3
122.5°	541.2	540.5	539.9	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6
125°	596.3	596.1	595.9	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7
127.5°	651.1	650.6	650.3	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2
130°	687.2	686.8	686.4	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3
132.5°	721.6	721.0	720.5	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0
135°	775.1	774.2	773.4	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3
137.5°	827.3	826.2	825.2	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2
140°	860.4	859.3	858.3	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9
142.5°	892.0	891.0	889.9	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0
145°	938.2	937.5	936.9	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1
147.5°	981.0	979.6	978.2	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8
150°	1008.1	1007.7	1007.3	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7
152.5°	1034.0	1033.2	1032.5	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9
155°	1070.3	1069.1	1068.1	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7
157.5°	1100.8	1099.4	1098.0	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7
160°	1120.1	1119.1	1118.0	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6
162.5°	1137.9	1136.7	1135.5	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2
165°	1161.2	1159.9	1158.7	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9
167.5°	1179.8	1178.5	1177.1	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6
170°	1190.1	1188.5	1187.1	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1
172.5°	1197.8	1196.6	1195.2	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7
175°	1206.1	1204.6	1203.1	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1
177.5°	1209.7	1208.5	1207.3	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	17.4	17.8	16.5	16.2	15.4	15.6	14.2	13.4	12.5	12.7	13.9
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	37.5	36.1	34.3	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8
95°	73.9	72.5	70.4	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2
97.5°	116.8	115.4	112.4	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6
100°	145.8	143.9	141.3	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8
102.5°	176.2	174.1	172.7	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1
105°	226.1	224.9	223.7	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5
107.5°	279.9	279.3	278.3	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2
110°	316.8	316.1	315.6	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	354.1	353.8	353.0	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8
115°	411.0	411.2	410.8	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6
117.5°	467.1	466.9	466.6	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5
120°	505.3	505.3	505.1	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6
122.5°	542.8	542.9	542.4	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9
125°	598.0	598.5	598.2	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9
127.5°	652.4	652.7	652.4	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4
130°	688.6	688.8	688.3	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2
132.5°	723.2	723.4	723.5	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0
135°	776.3	776.3	776.1	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8
137.5°	827.9	827.6	827.3	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2
140°	860.4	860.1	859.4	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5
142.5°	892.7	892.4	891.6	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9
145°	939.1	939.1	938.5	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6
147.5°	981.4	980.9	980.3	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6
150°	1008.7	1008.7	1007.9	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9
152.5°	1033.3	1032.8	1032.5	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0
155°	1068.8	1068.0	1067.8	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1099.9	1099.1	1098.9	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2
160°	1118.7	1117.9	1117.7	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7
162.5°	1136.2	1135.2	1135.2	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1
165°	1160.2	1159.3	1159.0	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3
167.5°	1177.3	1176.0	1176.0	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8
170°	1187.9	1186.6	1186.6	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3
172.5°	1195.3	1194.1	1194.1	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9
175°	1203.8	1202.6	1202.6	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4
177.5°	1208.0	1206.9	1207.1	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.8	14.6	16.5	19.3	21.2	23.5	24.8	24.1	22.3	21.0	19.7
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	23.9	25.1	26.3	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9
95°	61.5	62.0	62.4	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4
97.5°	101.8	102.0	102.2	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1
100°	131.8	131.8	131.8	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7
102.5°	164.9	165.8	166.6	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1
105°	215.6	216.6	217.7	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4
107.5°	271.3	272.3	273.4	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5
110°	309.7	310.8	311.8	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.4	348.8	349.4	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4
115°	406.4	407.3	408.1	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8
117.5°	463.9	464.3	464.7	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2
120°	500.7	501.7	502.8	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3
122.5°	539.2	539.6	540.0	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6
125°	593.1	594.4	595.7	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7
127.5°	649.0	649.8	650.4	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2
130°	683.2	684.3	685.3	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3
132.5°	717.8	719.5	721.2	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0
135°	771.0	772.2	773.5	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3
137.5°	821.3	822.6	823.8	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2
140°	853.6	854.6	855.6	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9
142.5°	885.8	886.6	887.5	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0
145°	933.4	934.2	935.0	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1
147.5°	977.0	977.5	978.0	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8
150°	1005.7	1005.5	1005.3	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7
152.5°	1030.3	1030.6	1030.9	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9
155°	1067.1	1067.1	1067.1	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7
157.5°	1099.8	1099.3	1098.8	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7
160°	1119.2	1118.5	1117.9	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6
162.5°	1136.6	1136.1	1135.7	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2
165°	1159.8	1159.4	1159.0	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9
167.5°	1178.9	1178.2	1177.3	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6
170°	1189.5	1188.6	1187.9	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1
172.5°	1197.0	1196.2	1195.3	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7
175°	1205.5	1204.7	1203.8	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1
177.5°	1210.0	1209.4	1208.6	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	19.9	18.1	18.3	17.9	18.0	17.6	16.8
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	40.2	41.7	42.6	43.1	43.5	43.9	44.4
95°	76.8	78.3	79.3	79.6	80.1	80.5	81.0
97.5°	119.5	120.9	121.7	122.0	122.2	122.4	122.7
100°	149.6	151.5	152.7	153.1	153.4	153.9	154.3
102.5°	180.2	182.3	183.6	184.2	184.7	185.4	186.0
105°	228.7	229.9	230.8	231.5	232.1	232.7	233.4
107.5°	281.2	281.8	282.1	282.0	282.0	282.0	281.9
110°	318.0	318.7	318.9	318.7	318.5	318.3	318.0



TEST NUMBER: P333278-830

CATALOG NUMBER: S125DIP-S1090D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	355.0	355.0	354.6	354.2	353.8	353.5
115°	410.6	410.4	410.2	409.9	409.7	409.5	409.3
117.5°	467.4	467.6	467.2	466.4	465.6	464.8	463.9
120°	505.3	505.3	504.9	504.1	503.2	502.4	501.5
122.5°	542.4	542.2	541.9	541.2	540.5	539.9	539.2
125°	597.2	596.8	596.4	596.3	596.1	595.9	595.7
127.5°	652.1	651.9	651.5	651.1	650.6	650.3	649.9
130°	688.2	688.0	687.7	687.2	686.8	686.4	686.0
132.5°	722.8	722.6	722.2	721.6	721.0	720.5	719.8
135°	776.3	776.3	775.9	775.1	774.2	773.4	772.5
137.5°	828.4	828.7	828.3	827.3	826.2	825.2	824.2
140°	861.3	861.8	861.4	860.4	859.3	858.3	857.2
142.5°	893.2	893.4	893.1	892.0	891.0	889.9	888.8
145°	939.1	939.1	938.8	938.2	937.5	936.9	936.3
147.5°	982.4	982.9	982.4	981.0	979.6	978.2	976.8
150°	1008.7	1008.7	1008.5	1008.1	1007.7	1007.3	1006.8
152.5°	1034.3	1034.8	1034.7	1034.0	1033.2	1032.5	1031.7
155°	1070.5	1071.4	1071.3	1070.3	1069.1	1068.1	1067.1
157.5°	1101.5	1102.4	1102.1	1100.8	1099.4	1098.0	1096.6
160°	1120.4	1121.2	1121.2	1120.1	1119.1	1118.0	1116.9
162.5°	1138.2	1139.3	1139.2	1137.9	1136.7	1135.5	1134.3
165°	1161.8	1162.6	1162.4	1161.2	1159.9	1158.7	1157.4
167.5°	1179.8	1181.1	1181.0	1179.8	1178.5	1177.1	1175.8
170°	1190.3	1191.6	1191.5	1190.1	1188.5	1187.1	1185.6
172.5°	1197.9	1199.1	1199.1	1197.8	1196.6	1195.2	1193.9
175°	1206.4	1207.6	1207.5	1206.1	1204.6	1203.1	1201.6
177.5°	1209.9	1210.9	1210.9	1209.7	1208.5	1207.3	1206.2
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2

(END OF REPORT)