

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333288-830

Luminaire Tested: **S125DIP-S1090D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333288-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8306.1 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20													
RC	80									70									50									30									10									0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																				
RCR																																																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	43	43	43	37	37	37	31	31	31	27	27	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49	43	43	43	37	37	37	31	31	31	27	27	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13			
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37	37	37	31	31	31	27	27	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11			
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31	31	31	27	27	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9			
4	75	64	56	50	69	60	53	48	51	46	42	43	39	36	36	33	31	27	27	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7			
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23	23	23	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5			
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	24	21	21	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5	3	3	3			
7	59	46	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18	18	18	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5	3	3	3	1	1	1			
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	25	21	19	16	16	16	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5	3	3	3	1	1	1	0	0	0			
9	51	38	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15	15	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5	3	3	3	1	1	1	0	0	0	0	0	0			
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13	13	13	11	11	11	9	9	9	7	7	7	5	5	5	3	3	3	1	1	1	0	0	0	0	0	0	0					

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.7
10°-20°	429.6	5.2
20°-30°	697.6	8.4
30°-40°	850.9	10.2
40°-50°	774.1	9.3
50°-60°	616.6	7.4
60°-70°	429.5	5.2
70°-80°	229.0	2.8
80°-90°	60.8	0.7
90°-100°	393.7	4.7
100°-110°	846.4	10.2
110°-120°	794.4	9.6
120°-130°	643.8	7.8
130°-140°	516.6	6.2
140°-150°	389.9	4.7
150°-160°	274.4	3.3
160°-170°	161.8	1.9
170°-180°	52.6	0.6
0°-30°	1271.5	15.3
0°-40°	2122.4	25.6
0°-60°	3513.1	42.3
0°-90°	4232.4	51.0
90°-120°	2034.5	24.5
90°-150°	3584.8	43.2
90°-180°	4074.0	49.0
0°-180°	8306.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	25	1	25	1	25	19
95°	257	36	257	36	257	365
105°	1451	124	1451	124	1451	1442
115°	1616	221	1616	221	1616	1579
125°	1274	307	1274	307	1274	1152
135°	1058	359	1058	359	1058	820
145°	834	418	834	418	834	530
155°	700	478	700	478	700	326
165°	613	521	613	521	613	175
175°	551	542	551	542	551	54
180°	543	543	543	543	543	



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	17.2	18.3	18.6	18.6	19.0	18.7	20.5	20.3	21.5	22.8	24.4
90°	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7	18.7	17.5	15.4
92.5°	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1	285.9	353.1	358.8
95°	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4	949.5	970.3	791.8
97.5°	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7	1201.5	1036.2	707.1
100°	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1	1262.7	988.9	630.8
102.5°	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8	1226.0	905.7	573.0
105°	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2	1108.3	794.0	516.9
107.5°	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6	988.4	717.1	493.2
110°	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5	919.9	681.2	486.3



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7	869.1	660.2	486.3
115°	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5	813.7	637.4	489.6
117.5°	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1	780.6	626.2	496.8
120°	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7	762.2	620.9	503.8
122.5°	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0	746.5	616.6	509.9
125°	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6	725.0	611.1	520.2
127.5°	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5	705.3	608.5	531.8
130°	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7	692.2	606.7	538.9
132.5°	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7	681.6	606.7	546.7
135°	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2	669.2	606.7	557.4
137.5°	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2	658.0	608.0	567.3
140°	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0	652.7	608.9	571.7
142.5°	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6	648.4	609.8	574.3
145°	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7	641.8	608.9	577.2
147.5°	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8	635.0	606.1	578.2
150°	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8	629.7	603.4	578.2
152.5°	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1	623.6	599.9	577.4
155°	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9	613.3	593.6	575.0
157.5°	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8	603.7	587.0	572.1
160°	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0	595.8	582.7	569.5
162.5°	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4	588.8	577.4	566.8
165°	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0	578.2	569.5	562.9
167.5°	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3	568.0	561.8	556.8
170°	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3	561.8	557.4	554.2
172.5°	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4	555.7	552.2	550.6
175°	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9	547.6	546.5	546.5
177.5°	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0	544.1	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	25.3	23.8	21.5	19.6	16.6	14.6	13.7	13.9	12.6	12.5	13.6
90°	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1	2.2	4.3	6.6
92.5°	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4	16.2	25.4	39.0
95°	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1	37.2	46.0	58.1
97.5°	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0	61.4	67.5	79.6
100°	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6	78.9	83.2	95.3
102.5°	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1	96.4	99.9	112.8
105°	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8	123.8	129.2	140.2
107.5°	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7	154.0	159.2	168.2
110°	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9	174.2	178.5	188.4



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1	194.3	197.7	207.6
115°	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2	223.4	226.7	236.6
117.5°	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5	250.8	254.3	264.2
120°	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0	268.3	272.7	282.6
122.5°	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4	285.9	289.4	299.2
125°	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6	308.9	314.3	324.1
127.5°	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8	328.1	335.2	347.6
130°	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2	339.5	348.3	362.5
132.5°	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0	349.1	359.7	375.7
135°	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2	363.6	376.7	394.3
137.5°	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2	380.5	392.8	410.3
140°	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7	391.0	404.2	421.7
142.5°	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9	402.4	414.6	432.2
145°	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4	420.6	431.5	446.9
147.5°	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6	438.9	448.4	462.6
150°	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0	451.2	458.9	473.2
152.5°	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3	462.6	469.4	481.9
155°	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5	477.5	484.1	495.0
157.5°	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0	491.7	497.0	506.4
160°	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6	500.5	504.9	512.6
162.5°	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4	508.4	512.7	519.5
165°	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3	519.2	522.5	527.9
167.5°	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2	528.1	530.1	533.1
170°	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4	533.4	534.4	536.7
172.5°	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0	536.0	537.1	539.2
175°	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2	539.9	541.0	542.2
177.5°	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1	542.3	542.3	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	14.5	15.9	15.6	16.6	16.8	18.3	18.0	20.3	21.5	22.7	22.6
90°	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7	20.8	21.9	24.1
92.5°	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1	140.8	106.0	89.8
95°	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4	620.9	486.3	394.3
97.5°	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7	1056.0	924.8	796.8
100°	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1	1293.5	1180.6	1066.7
102.5°	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8	1438.9	1384.8	1307.7
105°	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2	1521.3	1569.4	1557.4
107.5°	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6	1447.8	1571.6	1628.8
110°	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5	1364.6	1519.0	1612.1



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7	1282.2	1438.4	1548.1
115°	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5	1164.2	1314.2	1433.6
117.5°	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1	1082.5	1211.7	1321.3
120°	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7	1036.0	1156.5	1252.9
122.5°	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0	1002.8	1110.1	1200.3
125°	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6	958.3	1053.6	1132.5
127.5°	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5	915.8	1004.8	1078.6
130°	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7	886.0	971.5	1042.6
132.5°	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7	858.0	935.5	1004.1
135°	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2	814.8	885.0	947.3
137.5°	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2	776.3	834.5	887.6
140°	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0	753.5	803.9	849.9
142.5°	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6	734.2	777.6	817.5
145°	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7	709.6	743.7	773.2
147.5°	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8	689.3	715.4	737.7
150°	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8	678.0	698.7	718.4
152.5°	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1	666.6	685.6	701.0
155°	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9	649.4	664.8	676.8
157.5°	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8	633.2	645.1	654.5
160°	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0	620.9	631.9	639.6
162.5°	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4	610.5	619.6	626.4
165°	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0	594.7	601.2	606.7
167.5°	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3	579.4	584.4	588.3
170°	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3	570.6	573.9	576.1
172.5°	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4	562.7	565.1	566.5
175°	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9	550.9	553.1	553.1
177.5°	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0	545.8	545.8	545.8
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	23.7	23.2	23.4	24.4	23.4	23.2	23.7	22.6	22.7	21.5	20.3
90°	24.1	24.1	25.2	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7
92.5°	75.8	73.1	71.6	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1
95°	316.5	283.6	274.9	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4
97.5°	729.2	667.9	636.1	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7
100°	991.2	912.3	871.8	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1
102.5°	1226.8	1170.7	1126.7	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8
105°	1522.3	1486.2	1464.2	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2
107.5°	1646.5	1646.3	1639.1	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6
110°	1661.4	1682.2	1689.9	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1620.2	1656.0	1675.0	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7
115°	1519.0	1571.6	1602.2	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5
117.5°	1406.7	1461.0	1491.5	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1
120°	1334.0	1386.5	1416.1	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7
122.5°	1272.6	1320.8	1350.4	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0
125°	1193.7	1238.7	1262.7	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6
127.5°	1134.2	1173.8	1196.7	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5
130°	1097.4	1133.5	1155.5	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7
132.5°	1058.9	1095.0	1115.1	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7
135°	995.5	1031.7	1051.4	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2
137.5°	930.7	963.6	981.8	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2
140°	890.4	918.9	935.3	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0
142.5°	851.9	875.9	891.5	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6
145°	799.5	818.1	830.2	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7
147.5°	758.6	773.5	780.4	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8
150°	734.9	748.0	752.4	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8
152.5°	714.7	725.2	729.6	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1
155°	687.8	695.4	698.7	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9
157.5°	663.0	669.4	672.4	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8
160°	647.2	652.7	655.0	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0
162.5°	632.4	637.0	637.4	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4
165°	611.1	613.3	613.3	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0
167.5°	590.5	592.5	591.6	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3
170°	578.2	579.4	579.4	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3
172.5°	566.8	568.8	567.1	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4
175°	553.1	554.2	552.0	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9
177.5°	545.0	545.8	543.2	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	18.0	18.3	16.8	16.6	15.6	15.9	14.5	13.6	12.5	12.6	13.9
90°	18.7	17.5	15.4	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1
92.5°	285.9	353.1	358.8	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4
95°	949.5	970.3	791.8	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1
97.5°	1201.5	1036.2	707.1	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0
100°	1262.7	988.9	630.8	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6
102.5°	1226.0	905.7	573.0	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1
105°	1108.3	794.0	516.9	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8
107.5°	988.4	717.1	493.2	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7
110°	919.9	681.2	486.3	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	869.1	660.2	486.3	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1
115°	813.7	637.4	489.6	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2
117.5°	780.6	626.2	496.8	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5
120°	762.2	620.9	503.8	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0
122.5°	746.5	616.6	509.9	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4
125°	725.0	611.1	520.2	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6
127.5°	705.3	608.5	531.8	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8
130°	692.2	606.7	538.9	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2
132.5°	681.6	606.7	546.7	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0
135°	669.2	606.7	557.4	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2
137.5°	658.0	608.0	567.3	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2
140°	652.7	608.9	571.7	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7
142.5°	648.4	609.8	574.3	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9
145°	641.8	608.9	577.2	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4
147.5°	635.0	606.1	578.2	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6
150°	629.7	603.4	578.2	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0
152.5°	623.6	599.9	577.4	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3
155°	613.3	593.6	575.0	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5
157.5°	603.7	587.0	572.1	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0
160°	595.8	582.7	569.5	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6
162.5°	588.8	577.4	566.8	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4
165°	578.2	569.5	562.9	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3
167.5°	568.0	561.8	556.8	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2
170°	561.8	557.4	554.2	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4
172.5°	555.7	552.2	550.6	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0
175°	547.6	546.5	546.5	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2
177.5°	544.1	543.2	543.2	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.7	14.6	16.6	19.6	21.5	23.8	25.3	24.4	22.8	21.5	20.3
90°	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7
92.5°	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1
95°	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4
97.5°	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7
100°	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1
102.5°	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8
105°	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2
107.5°	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6
110°	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7
115°	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5
117.5°	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1
120°	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7
122.5°	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0
125°	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6
127.5°	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5
130°	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7
132.5°	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7
135°	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2
137.5°	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2
140°	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0
142.5°	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6
145°	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7
147.5°	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8
150°	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8
152.5°	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1
155°	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9
157.5°	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8
160°	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0
162.5°	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4
165°	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0
167.5°	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3
170°	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3
172.5°	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4
175°	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9
177.5°	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	20.5	18.7	19.0	18.6	18.6	18.3	17.2
90°	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333288-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)