

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333251-830

Luminaire Tested: **S125DIP-S1090D365U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333251-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D365U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5424.8 lumens  
Efficiency: N/A  
Efficacy: 124.7 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				
1	104	100	96	93	100	96	92	89	87	85	82	80	78	76	73	71	70	66				
2	95	88	82	76	91	84	78	74	77	73	69	71	67	64	65	62	59	56				
3	87	78	70	64	83	74	67	62	68	63	58	63	58	54	58	54	51	48				
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	52	47	44	41				
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	47	42	39	36				
6	68	56	47	41	65	53	46	40	49	43	38	46	40	36	42	38	34	32				
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	39	34	30	28				
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	36	31	27	25				
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	33	28	25	23				
10	51	39	31	26	49	37	30	26	35	29	24	33	27	23	30	26	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	2.7
10°-20°	429.6	7.9
20°-30°	697.6	12.9
30°-40°	850.9	15.7
40°-50°	774.1	14.3
50°-60°	616.6	11.4
60°-70°	429.5	7.9
70°-80°	229.0	4.2
80°-90°	58.7	1.1
90°-100°	28.7	0.5
100°-110°	84.7	1.6
110°-120°	143.4	2.6
120°-130°	188.7	3.5
130°-140°	211.5	3.9
140°-150°	207.3	3.8
150°-160°	174.1	3.2
160°-170°	115.7	2.1
170°-180°	40.5	0.7
0°-30°	1271.5	23.4
0°-40°	2122.4	39.1
0°-60°	3513.1	64.8
0°-90°	4230.3	78.0
90°-120°	256.8	4.7
90°-150°	864.2	15.9
90°-180°	1195.0	22.0
0°-180°	5424.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	8	0	8	0	8	6
95°	29	22	29	22	29	29
105°	83	76	83	76	83	88
115°	145	144	145	144	145	143
125°	211	210	211	210	211	188
135°	274	272	274	272	274	211
145°	332	330	332	330	332	207
155°	378	378	378	378	378	174
165°	410	411	410	411	410	115
175°	425	427	425	427	425	40
180°	428	428	428	428	428	



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	13.9	14.8	15.3	15.2	15.6	15.6	17.5	17.5	18.9	20.4	22.3
90°	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0	5.7	5.4	4.8
92.5°	15.7	15.6	15.4	15.3	15.1	14.7	14.2	13.8	13.3	12.8	12.2
95°	28.7	28.5	28.4	28.2	28.1	27.7	27.2	26.7	26.2	25.6	24.9
97.5°	43.5	43.4	43.3	43.2	43.1	42.8	42.3	41.8	41.4	40.8	39.8
100°	54.7	54.5	54.4	54.2	54.0	53.6	53.0	52.3	51.7	51.0	50.0
102.5°	65.8	65.6	65.4	65.2	65.0	64.6	63.8	63.1	62.4	61.6	61.2
105°	82.7	82.4	82.2	81.9	81.7	81.4	81.0	80.5	80.0	79.6	79.2
107.5°	99.8	99.8	99.8	99.8	99.9	99.7	99.5	99.3	99.1	98.9	98.5
110°	112.6	112.6	112.7	112.8	112.9	112.8	112.6	112.4	112.2	112.0	111.7



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	125.3	125.4	125.5	125.6	125.6	125.5	125.5	125.4	125.3	125.0
115°	144.9	145.0	145.1	145.2	145.2	145.2	145.3	145.4	145.5	145.6	145.4
117.5°	164.2	164.6	164.9	165.1	165.4	165.5	165.5	165.4	165.3	165.3	165.1
120°	177.6	177.9	178.1	178.4	178.7	178.9	178.9	178.9	178.9	178.9	178.8
122.5°	190.9	191.1	191.3	191.6	191.8	192.0	192.0	192.1	192.2	192.2	192.0
125°	210.8	210.9	211.0	211.1	211.1	211.3	211.4	211.6	211.7	211.9	211.8
127.5°	230.1	230.2	230.4	230.5	230.6	230.7	230.8	230.9	231.0	231.0	231.0
130°	242.9	243.0	243.2	243.3	243.5	243.6	243.6	243.7	243.7	243.8	243.7
132.5°	254.9	255.1	255.2	255.4	255.7	255.8	255.9	256.0	256.0	256.1	256.2
135°	273.5	273.8	274.1	274.4	274.7	274.8	274.8	274.8	274.8	274.8	274.8
137.5°	291.7	292.1	292.5	292.8	293.2	293.4	293.3	293.2	293.1	293.0	292.8
140°	303.5	303.9	304.3	304.6	305.0	305.1	304.9	304.8	304.6	304.4	304.3
142.5°	314.7	315.1	315.4	315.8	316.1	316.3	316.2	316.1	316.0	315.9	315.7
145°	331.5	331.7	331.9	332.2	332.3	332.4	332.4	332.4	332.4	332.4	332.2
147.5°	345.8	346.3	346.8	347.3	347.8	348.0	347.8	347.6	347.4	347.2	347.0
150°	356.5	356.6	356.8	356.9	357.0	357.1	357.1	357.1	357.1	357.1	356.8
152.5°	365.2	365.5	365.8	366.1	366.3	366.4	366.2	366.0	365.8	365.6	365.5
155°	377.8	378.1	378.5	378.9	379.3	379.3	379.0	378.7	378.4	378.1	378.1
157.5°	388.2	388.7	389.2	389.7	390.2	390.3	390.0	389.6	389.4	389.1	389.0
160°	395.4	395.8	396.2	396.5	396.9	396.9	396.6	396.3	396.1	395.8	395.7
162.5°	401.5	402.0	402.4	402.8	403.3	403.3	402.9	402.6	402.3	401.9	401.9
165°	409.7	410.2	410.7	411.0	411.5	411.6	411.3	411.0	410.8	410.4	410.4
167.5°	416.3	416.7	417.2	417.6	418.1	418.1	417.6	417.3	416.8	416.3	416.3
170°	419.7	420.3	420.8	421.3	421.8	421.9	421.4	420.9	420.6	420.1	420.1
172.5°	422.6	423.1	423.6	424.0	424.5	424.5	424.0	423.7	423.2	422.7	422.7
175°	425.4	425.9	426.4	427.0	427.4	427.5	427.1	426.6	426.2	425.7	425.7
177.5°	427.0	427.4	427.8	428.3	428.7	428.7	428.4	428.0	427.6	427.3	427.3
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	23.3	22.1	20.0	18.4	15.6	14.0	13.4	13.8	12.4	12.0	12.6
90°	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4	0.9	1.5	2.1
92.5°	11.5	10.8	10.3	9.7	9.3	8.9	8.5	8.1	8.5	8.9	9.3
95°	24.1	23.5	22.7	22.2	22.1	22.0	21.8	21.7	21.8	22.0	22.1
97.5°	38.8	37.8	36.8	36.2	36.2	36.1	36.0	36.0	36.0	36.1	36.2
100°	49.0	48.1	47.1	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7
102.5°	60.6	60.1	59.7	59.3	59.0	58.7	58.4	58.1	58.4	58.7	59.0
105°	78.7	78.3	77.9	77.5	77.1	76.7	76.3	76.0	76.3	76.7	77.1
107.5°	98.2	97.8	97.6	97.2	96.8	96.4	96.0	95.7	96.0	96.4	96.8
110°	111.5	111.2	111.0	110.7	110.4	110.0	109.6	109.2	109.6	110.0	110.4





TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.7	124.4	124.1	123.9	123.7	123.5	123.3	123.1	123.3	123.5	123.7
115°	145.2	145.2	145.0	144.8	144.5	144.2	143.8	143.5	143.8	144.2	144.5
117.5°	165.0	164.9	164.8	164.7	164.5	164.4	164.2	164.1	164.2	164.4	164.5
120°	178.7	178.7	178.6	178.3	178.0	177.7	177.3	176.9	177.3	177.7	178.0
122.5°	191.8	191.6	191.4	191.2	191.1	191.1	190.9	190.8	190.9	191.1	191.1
125°	211.7	211.7	211.6	211.3	210.8	210.5	210.0	209.5	210.0	210.5	210.8
127.5°	230.9	230.8	230.7	230.5	230.3	230.1	229.8	229.5	229.8	230.1	230.3
130°	243.6	243.4	243.3	243.0	242.6	242.2	241.9	241.5	241.9	242.2	242.6
132.5°	256.2	256.2	256.3	255.9	255.3	254.8	254.1	253.5	254.1	254.8	255.3
135°	274.7	274.7	274.6	274.3	273.8	273.4	273.0	272.5	273.0	273.4	273.8
137.5°	292.7	292.6	292.4	292.1	291.6	291.2	290.8	290.4	290.8	291.2	291.6
140°	304.1	303.8	303.6	303.3	302.9	302.6	302.2	301.8	302.2	302.6	302.9
142.5°	315.4	315.1	314.8	314.5	314.2	313.9	313.6	313.3	313.6	313.9	314.2
145°	332.1	331.8	331.6	331.3	331.0	330.7	330.5	330.2	330.5	330.7	331.0
147.5°	346.9	346.8	346.6	346.4	346.2	346.0	345.9	345.7	345.9	346.0	346.2
150°	356.6	356.2	355.9	355.8	355.9	356.0	356.1	356.1	356.1	356.0	355.9
152.5°	365.4	365.3	365.1	365.0	365.0	364.9	364.8	364.7	364.8	364.9	365.0
155°	378.0	377.9	377.8	377.8	377.8	377.8	377.8	377.8	377.8	377.8	377.8
157.5°	389.0	388.9	388.8	388.9	389.0	389.2	389.4	389.5	389.4	389.2	389.0
160°	395.6	395.6	395.5	395.6	395.8	396.0	396.2	396.4	396.2	396.0	395.8
162.5°	401.9	401.8	401.8	401.9	402.1	402.3	402.4	402.6	402.4	402.3	402.1
165°	410.3	410.2	410.1	410.2	410.3	410.5	410.6	410.8	410.6	410.5	410.3
167.5°	416.3	416.3	416.3	416.5	416.8	417.1	417.4	417.6	417.4	417.1	416.8
170°	420.1	420.1	420.1	420.2	420.6	420.8	421.1	421.4	421.1	420.8	420.6
172.5°	422.7	422.7	422.7	422.9	423.2	423.5	423.8	424.0	423.8	423.5	423.2
175°	425.7	425.7	425.7	425.9	426.2	426.5	426.8	427.1	426.8	426.5	426.2
177.5°	427.4	427.4	427.5	427.6	427.9	428.1	428.4	428.6	428.4	428.1	427.9
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.3	14.4	13.9	14.6	14.7	15.8	15.4	17.5	18.6	19.7	19.2
90°	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0	6.4	6.8	7.1
92.5°	9.7	10.3	10.8	11.5	12.2	12.8	13.3	13.8	14.2	14.7	15.1
95°	22.2	22.7	23.5	24.1	24.9	25.6	26.2	26.7	27.2	27.7	28.1
97.5°	36.2	36.8	37.8	38.8	39.8	40.8	41.4	41.8	42.3	42.8	43.1
100°	46.7	47.1	48.1	49.0	50.0	51.0	51.7	52.3	53.0	53.6	54.0
102.5°	59.3	59.7	60.1	60.6	61.2	61.6	62.4	63.1	63.8	64.6	65.0
105°	77.5	77.9	78.3	78.7	79.2	79.6	80.0	80.5	81.0	81.4	81.7
107.5°	97.2	97.6	97.8	98.2	98.5	98.9	99.1	99.3	99.5	99.7	99.9
110°	110.7	111.0	111.2	111.5	111.7	112.0	112.2	112.4	112.6	112.8	112.9



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.9	124.1	124.4	124.7	125.0	125.3	125.4	125.5	125.5	125.6	125.6
115°	144.8	145.0	145.2	145.2	145.4	145.6	145.5	145.4	145.3	145.2	145.2
117.5°	164.7	164.8	164.9	165.0	165.1	165.3	165.3	165.4	165.5	165.5	165.4
120°	178.3	178.6	178.7	178.7	178.8	178.9	178.9	178.9	178.9	178.9	178.7
122.5°	191.2	191.4	191.6	191.8	192.0	192.2	192.2	192.1	192.0	192.0	191.8
125°	211.3	211.6	211.7	211.7	211.8	211.9	211.7	211.6	211.4	211.3	211.1
127.5°	230.5	230.7	230.8	230.9	231.0	231.0	231.0	230.9	230.8	230.7	230.6
130°	243.0	243.3	243.4	243.6	243.7	243.8	243.7	243.7	243.6	243.6	243.5
132.5°	255.9	256.3	256.2	256.2	256.2	256.1	256.0	256.0	255.9	255.8	255.7
135°	274.3	274.6	274.7	274.7	274.8	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	292.1	292.4	292.6	292.7	292.8	293.0	293.1	293.2	293.3	293.4	293.2
140°	303.3	303.6	303.8	304.1	304.3	304.4	304.6	304.8	304.9	305.1	305.0
142.5°	314.5	314.8	315.1	315.4	315.7	315.9	316.0	316.1	316.2	316.3	316.1
145°	331.3	331.6	331.8	332.1	332.2	332.4	332.4	332.4	332.4	332.4	332.3
147.5°	346.4	346.6	346.8	346.9	347.0	347.2	347.4	347.6	347.8	348.0	347.8
150°	355.8	355.9	356.2	356.6	356.8	357.1	357.1	357.1	357.1	357.1	357.0
152.5°	365.0	365.1	365.3	365.4	365.5	365.6	365.8	366.0	366.2	366.4	366.3
155°	377.8	377.8	377.9	378.0	378.1	378.1	378.4	378.7	379.0	379.3	379.3
157.5°	388.9	388.8	388.9	389.0	389.0	389.1	389.4	389.6	390.0	390.3	390.2
160°	395.6	395.5	395.6	395.6	395.7	395.8	396.1	396.3	396.6	396.9	396.9
162.5°	401.9	401.8	401.8	401.9	401.9	401.9	402.3	402.6	402.9	403.3	403.3
165°	410.2	410.1	410.2	410.3	410.4	410.4	410.8	411.0	411.3	411.6	411.5
167.5°	416.5	416.3	416.3	416.3	416.3	416.3	416.8	417.3	417.6	418.1	418.1
170°	420.2	420.1	420.1	420.1	420.1	420.1	420.6	420.9	421.4	421.9	421.8
172.5°	422.9	422.7	422.7	422.7	422.7	422.7	423.2	423.7	424.0	424.5	424.5
175°	425.9	425.7	425.7	425.7	425.7	425.7	426.2	426.6	427.1	427.5	427.4
177.5°	427.6	427.5	427.4	427.4	427.3	427.3	427.6	428.0	428.4	428.7	428.7
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	20.3	19.8	19.9	20.9	19.9	19.8	20.3	19.2	19.7	18.6	17.5
90°	7.4	7.5	7.7	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0
92.5°	15.3	15.4	15.6	15.7	15.6	15.4	15.3	15.1	14.7	14.2	13.8
95°	28.2	28.4	28.5	28.7	28.5	28.4	28.2	28.1	27.7	27.2	26.7
97.5°	43.2	43.3	43.4	43.5	43.4	43.3	43.2	43.1	42.8	42.3	41.8
100°	54.2	54.4	54.5	54.7	54.5	54.4	54.2	54.0	53.6	53.0	52.3
102.5°	65.2	65.4	65.6	65.8	65.6	65.4	65.2	65.0	64.6	63.8	63.1
105°	81.9	82.2	82.4	82.7	82.4	82.2	81.9	81.7	81.4	81.0	80.5
107.5°	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.9	99.7	99.5	99.3
110°	112.8	112.7	112.6	112.6	112.6	112.7	112.8	112.9	112.8	112.6	112.4



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	125.5	125.4	125.3	125.2	125.3	125.4	125.5	125.6	125.6	125.5	125.5
115°	145.2	145.1	145.0	144.9	145.0	145.1	145.2	145.2	145.2	145.3	145.4
117.5°	165.1	164.9	164.6	164.2	164.6	164.9	165.1	165.4	165.5	165.5	165.4
120°	178.4	178.1	177.9	177.6	177.9	178.1	178.4	178.7	178.9	178.9	178.9
122.5°	191.6	191.3	191.1	190.9	191.1	191.3	191.6	191.8	192.0	192.0	192.1
125°	211.1	211.0	210.9	210.8	210.9	211.0	211.1	211.1	211.3	211.4	211.6
127.5°	230.5	230.4	230.2	230.1	230.2	230.4	230.5	230.6	230.7	230.8	230.9
130°	243.3	243.2	243.0	242.9	243.0	243.2	243.3	243.5	243.6	243.6	243.7
132.5°	255.4	255.2	255.1	254.9	255.1	255.2	255.4	255.7	255.8	255.9	256.0
135°	274.4	274.1	273.8	273.5	273.8	274.1	274.4	274.7	274.8	274.8	274.8
137.5°	292.8	292.5	292.1	291.7	292.1	292.5	292.8	293.2	293.4	293.3	293.2
140°	304.6	304.3	303.9	303.5	303.9	304.3	304.6	305.0	305.1	304.9	304.8
142.5°	315.8	315.4	315.1	314.7	315.1	315.4	315.8	316.1	316.3	316.2	316.1
145°	332.2	331.9	331.7	331.5	331.7	331.9	332.2	332.3	332.4	332.4	332.4
147.5°	347.3	346.8	346.3	345.8	346.3	346.8	347.3	347.8	348.0	347.8	347.6
150°	356.9	356.8	356.6	356.5	356.6	356.8	356.9	357.0	357.1	357.1	357.1
152.5°	366.1	365.8	365.5	365.2	365.5	365.8	366.1	366.3	366.4	366.2	366.0
155°	378.9	378.5	378.1	377.8	378.1	378.5	378.9	379.3	379.3	379.0	378.7
157.5°	389.7	389.2	388.7	388.2	388.7	389.2	389.7	390.2	390.3	390.0	389.6
160°	396.5	396.2	395.8	395.4	395.8	396.2	396.5	396.9	396.9	396.6	396.3
162.5°	402.8	402.4	402.0	401.5	402.0	402.4	402.8	403.3	403.3	402.9	402.6
165°	411.0	410.7	410.2	409.7	410.2	410.7	411.0	411.5	411.6	411.3	411.0
167.5°	417.6	417.2	416.7	416.3	416.7	417.2	417.6	418.1	418.1	417.6	417.3
170°	421.3	420.8	420.3	419.7	420.3	420.8	421.3	421.8	421.9	421.4	420.9
172.5°	424.0	423.6	423.1	422.6	423.1	423.6	424.0	424.5	424.5	424.0	423.7
175°	427.0	426.4	425.9	425.4	425.9	426.4	427.0	427.4	427.5	427.1	426.6
177.5°	428.3	427.8	427.4	427.0	427.4	427.8	428.3	428.7	428.7	428.4	428.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	15.4	15.8	14.7	14.6	13.9	14.4	13.3	12.6	12.0	12.4	13.8
90°	5.7	5.4	4.8	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4
92.5°	13.3	12.8	12.2	11.5	10.8	10.3	9.7	9.3	8.9	8.5	8.1
95°	26.2	25.6	24.9	24.1	23.5	22.7	22.2	22.1	22.0	21.8	21.7
97.5°	41.4	40.8	39.8	38.8	37.8	36.8	36.2	36.2	36.1	36.0	36.0
100°	51.7	51.0	50.0	49.0	48.1	47.1	46.7	46.7	46.7	46.7	46.7
102.5°	62.4	61.6	61.2	60.6	60.1	59.7	59.3	59.0	58.7	58.4	58.1
105°	80.0	79.6	79.2	78.7	78.3	77.9	77.5	77.1	76.7	76.3	76.0
107.5°	99.1	98.9	98.5	98.2	97.8	97.6	97.2	96.8	96.4	96.0	95.7
110°	112.2	112.0	111.7	111.5	111.2	111.0	110.7	110.4	110.0	109.6	109.2



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.4	125.3	125.0	124.7	124.4	124.1	123.9	123.7	123.5	123.3	123.1
115°	145.5	145.6	145.4	145.2	145.2	145.0	144.8	144.5	144.2	143.8	143.5
117.5°	165.3	165.3	165.1	165.0	164.9	164.8	164.7	164.5	164.4	164.2	164.1
120°	178.9	178.9	178.8	178.7	178.7	178.6	178.3	178.0	177.7	177.3	176.9
122.5°	192.2	192.2	192.0	191.8	191.6	191.4	191.2	191.1	191.1	190.9	190.8
125°	211.7	211.9	211.8	211.7	211.7	211.6	211.3	210.8	210.5	210.0	209.5
127.5°	231.0	231.0	231.0	230.9	230.8	230.7	230.5	230.3	230.1	229.8	229.5
130°	243.7	243.8	243.7	243.6	243.4	243.3	243.0	242.6	242.2	241.9	241.5
132.5°	256.0	256.1	256.2	256.2	256.2	256.3	255.9	255.3	254.8	254.1	253.5
135°	274.8	274.8	274.8	274.7	274.7	274.6	274.3	273.8	273.4	273.0	272.5
137.5°	293.1	293.0	292.8	292.7	292.6	292.4	292.1	291.6	291.2	290.8	290.4
140°	304.6	304.4	304.3	304.1	303.8	303.6	303.3	302.9	302.6	302.2	301.8
142.5°	316.0	315.9	315.7	315.4	315.1	314.8	314.5	314.2	313.9	313.6	313.3
145°	332.4	332.4	332.2	332.1	331.8	331.6	331.3	331.0	330.7	330.5	330.2
147.5°	347.4	347.2	347.0	346.9	346.8	346.6	346.4	346.2	346.0	345.9	345.7
150°	357.1	357.1	356.8	356.6	356.2	355.9	355.8	355.9	356.0	356.1	356.1
152.5°	365.8	365.6	365.5	365.4	365.3	365.1	365.0	365.0	364.9	364.8	364.7
155°	378.4	378.1	378.1	378.0	377.9	377.8	377.8	377.8	377.8	377.8	377.8
157.5°	389.4	389.1	389.0	389.0	388.9	388.8	388.9	389.0	389.2	389.4	389.5
160°	396.1	395.8	395.7	395.6	395.6	395.5	395.6	395.8	396.0	396.2	396.4
162.5°	402.3	401.9	401.9	401.9	401.8	401.8	401.9	402.1	402.3	402.4	402.6
165°	410.8	410.4	410.4	410.3	410.2	410.1	410.2	410.3	410.5	410.6	410.8
167.5°	416.8	416.3	416.3	416.3	416.3	416.3	416.5	416.8	417.1	417.4	417.6
170°	420.6	420.1	420.1	420.1	420.1	420.1	420.2	420.6	420.8	421.1	421.4
172.5°	423.2	422.7	422.7	422.7	422.7	422.7	422.9	423.2	423.5	423.8	424.0
175°	426.2	425.7	425.7	425.7	425.7	425.7	425.9	426.2	426.5	426.8	427.1
177.5°	427.6	427.3	427.3	427.4	427.4	427.5	427.6	427.9	428.1	428.4	428.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.4	14.0	15.6	18.4	20.0	22.1	23.3	22.3	20.4	18.9	17.5
90°	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0
92.5°	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3	13.8
95°	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2	26.7
97.5°	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4	41.8
100°	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7	52.3
102.5°	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4	63.1
105°	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0	80.5
107.5°	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1	99.3
110°	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2	112.4





TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4	125.5
115°	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5	145.4
117.5°	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3	165.4
120°	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9	178.9
122.5°	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2	192.1
125°	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7	211.6
127.5°	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0	230.9
130°	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7	243.7
132.5°	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0	256.0
135°	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8	274.8
137.5°	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1	293.2
140°	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6	304.8
142.5°	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0	316.1
145°	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4	332.4
147.5°	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4	347.6
150°	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1	357.1
152.5°	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8	366.0
155°	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4	378.7
157.5°	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4	389.6
160°	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1	396.3
162.5°	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3	402.6
165°	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8	411.0
167.5°	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8	417.3
170°	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6	420.9
172.5°	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2	423.7
175°	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2	426.6
177.5°	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6	428.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	17.5	15.6	15.6	15.2	15.3	14.8	13.9
90°	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333251-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)