

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333257-830

Luminaire Tested: **S125DIP-S1090D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333257-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D365U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5380.6 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	55
3	86	76	69	62	82	73	66	60	67	61	57	61	57	53	56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	42	40
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	35	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	2.8
10°-20°	428.4	8.0
20°-30°	632.5	11.8
30°-40°	738.0	13.7
40°-50°	741.2	13.8
50°-60°	650.7	12.1
60°-70°	484.8	9.0
70°-80°	277.2	5.2
80°-90°	81.6	1.5
90°-100°	28.7	0.5
100°-110°	84.7	1.6
110°-120°	143.4	2.7
120°-130°	188.7	3.5
130°-140°	211.5	3.9
140°-150°	207.3	3.9
150°-160°	174.1	3.2
160°-170°	115.7	2.2
170°-180°	40.5	0.8
0°-30°	1212.5	22.5
0°-40°	1950.5	36.3
0°-60°	3342.4	62.1
0°-90°	4186.0	77.8
90°-120°	256.8	4.8
90°-150°	864.2	16.1
90°-180°	1195.0	22.2
0°-180°	5380.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	0	3	5	7	8	5
95°	22	22	26	28	29	23
105°	76	78	80	82	83	81
115°	144	145	146	145	145	142
125°	210	211	212	211	211	188
135°	272	274	275	275	274	210
145°	330	331	332	332	332	206
155°	378	378	378	379	378	174
165°	411	410	410	412	410	116
175°	427	426	426	427	425	41
180°	428	428	428	428	428	



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.5	27.7	27.8	27.9	28.0	28.0	27.9	27.8	27.6	27.5	27.6
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	8.1	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3
95°	21.7	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2
97.5°	36.0	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4
100°	46.7	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7
102.5°	58.1	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4
105°	76.0	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0
107.5°	95.7	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1
110°	109.2	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.1	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4
115°	143.5	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5
117.5°	164.1	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3
120°	176.9	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9
122.5°	190.8	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2
125°	209.5	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7
127.5°	229.5	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0
130°	241.5	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7
132.5°	253.5	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0
135°	272.5	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8
137.5°	290.4	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1
140°	301.8	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6
142.5°	313.3	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0
145°	330.2	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4
147.5°	345.7	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4
150°	356.1	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1
152.5°	364.7	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8
155°	377.8	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4
157.5°	389.5	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4
160°	396.4	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1
162.5°	402.6	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3
165°	410.8	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8
167.5°	417.6	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8
170°	421.4	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6
172.5°	424.0	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2
175°	427.1	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2
177.5°	428.6	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	27.7	27.7	27.8	27.6	27.2	26.9	26.4	26.0
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	13.8	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	26.7	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	41.8	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	52.3	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.1	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	80.5	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.3	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.4	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333257-830

CATALOG NUMBER: S125DIP-S1090D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.5	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.4	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.4	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.1	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.6	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.9	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.7	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	256.0	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.2	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.8	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.1	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.6	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.0	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	378.7	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	389.6	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.3	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.6	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.0	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.3	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	420.9	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	423.7	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	426.6	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.0	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)