

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332970-935

Luminaire Tested: **S124RDIP-S1020D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332970-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D810U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6378.8 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	95	91	88	92	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	68	64	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.0	2.3
10°-20°	407.3	6.4
20°-30°	588.1	9.2
30°-40°	666.6	10.5
40°-50°	643.7	10.1
50°-60°	535.3	8.4
60°-70°	369.6	5.8
70°-80°	187.4	2.9
80°-90°	50.7	0.8
90°-100°	30.8	0.5
100°-110°	196.3	3.1
110°-120°	375.5	5.9
120°-130°	476.7	7.5
130°-140°	510.0	8.0
140°-150°	476.9	7.5
150°-160°	384.6	6.0
160°-170°	248.0	3.9
170°-180°	85.5	1.3
0°-30°	1141.4	17.9
0°-40°	1808.0	28.3
0°-60°	2987.0	46.8
0°-90°	3594.6	56.4
90°-120°	602.6	9.4
90°-150°	2066.1	32.4
90°-180°	2784.0	43.6
0°-180°	6378.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	2	9	15	19	20	5
95°	37	15	15	19	20	48
105°	203	207	210	214	192	212
115°	378	380	380	381	381	372
125°	532	534	533	535	536	475
135°	660	659	662	663	664	508
145°	761	763	763	763	765	475
155°	834	835	833	835	833	384
165°	880	877	876	881	876	249
175°	900	896	897	902	895	86
180°	900	900	900	900	900	



TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.3	20.9	19.5	18.3	16.9	16.2	16.2	16.3	16.3	16.3	16.3
90°	2.0	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7
92.5°	8.5	8.6	8.7	8.8	8.9	9.5	10.7	11.9	13.1	14.3	15.2
95°	37.0	31.9	26.9	21.8	16.7	14.2	14.4	14.6	14.6	14.8	15.7
97.5°	78.6	81.8	85.0	88.2	91.4	84.6	67.8	51.1	34.4	17.7	17.8
100°	110.4	113.1	115.8	118.5	121.1	112.2	91.5	70.9	50.3	29.6	27.0
102.5°	145.9	147.9	149.9	151.9	153.9	153.5	150.8	148.1	145.4	142.8	115.3
105°	202.6	203.5	204.4	205.3	206.2	207.1	207.8	208.5	209.3	210.0	211.4
107.5°	255.3	255.7	256.1	256.7	257.1	257.8	258.8	259.8	260.9	261.9	262.5
110°	290.8	291.3	291.7	292.1	292.7	293.3	294.2	295.1	296.0	296.9	297.2



TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.1	326.9	327.7	328.6	329.2	329.6	329.9	330.4	330.8	330.8
115°	378.3	378.8	379.3	379.7	380.1	380.3	380.1	380.0	379.9	379.7	380.0
117.5°	426.1	426.7	427.3	427.9	428.5	429.0	429.3	429.6	430.0	430.3	430.2
120°	458.5	459.1	459.7	460.3	460.8	461.1	460.9	460.8	460.6	460.5	460.8
122.5°	488.6	489.0	489.3	489.7	490.1	490.3	490.5	490.8	490.9	491.2	491.4
125°	531.8	532.4	533.0	533.6	534.3	534.3	534.1	533.8	533.5	533.2	533.6
127.5°	572.7	572.9	573.1	573.3	573.3	573.8	574.5	575.1	575.8	576.5	576.4
130°	599.2	599.3	599.4	599.6	599.8	600.0	600.5	601.0	601.4	601.8	602.0
132.5°	623.4	623.6	624.0	624.2	624.5	624.9	625.4	626.0	626.5	627.2	627.3
135°	659.8	659.6	659.4	659.3	659.2	659.4	660.0	660.6	661.2	661.8	662.0
137.5°	691.9	692.0	692.1	692.1	692.2	692.5	693.2	693.9	694.5	695.2	695.5
140°	712.9	713.3	713.5	713.9	714.1	714.5	714.7	715.1	715.3	715.6	716.1
142.5°	731.8	732.3	732.9	733.4	733.9	734.3	734.4	734.7	734.9	735.0	735.4
145°	760.7	761.2	761.6	762.1	762.5	762.8	762.8	762.8	762.8	762.8	762.9
147.5°	783.8	784.6	785.4	786.3	787.1	787.5	787.3	787.1	787.0	786.9	787.0
150°	800.5	801.1	801.7	802.3	802.8	803.1	802.9	802.8	802.6	802.5	802.5
152.5°	814.4	814.9	815.4	815.9	816.4	816.5	816.2	816.0	815.6	815.4	815.6
155°	834.1	834.2	834.4	834.6	834.7	834.6	834.1	833.6	833.2	832.8	833.4
157.5°	850.7	850.6	850.5	850.4	850.3	850.0	849.5	849.0	848.5	848.0	848.8
160°	860.4	859.9	859.5	859.0	858.6	858.2	858.2	858.0	857.8	857.6	858.6
162.5°	869.0	868.4	867.8	867.3	866.7	866.3	866.2	866.1	865.9	865.7	866.7
165°	879.9	879.2	878.4	877.6	876.9	876.5	876.5	876.5	876.5	876.5	877.7
167.5°	888.5	887.7	886.9	886.1	885.4	884.9	884.8	884.8	884.7	884.6	885.9
170°	893.4	892.4	891.6	890.6	889.8	889.4	889.5	889.7	889.8	890.0	891.1
172.5°	896.6	895.7	894.8	893.9	893.0	892.6	892.8	892.9	893.0	893.2	894.4
175°	900.1	899.1	898.3	897.4	896.5	896.1	896.3	896.4	896.6	896.7	898.0
177.5°	901.7	900.9	900.0	899.1	898.4	898.0	898.3	898.5	898.8	899.0	899.9
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	16.3	16.2	16.2	16.3	16.5	16.8	17.1	17.4
90°	16.6	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	16.1	17.0	17.8	18.3	18.4	18.4	18.5	18.6
95°	16.6	17.5	18.4	18.9	19.1	19.2	19.4	19.5
97.5°	18.0	18.1	18.2	18.3	18.4	18.5	18.7	18.9
100°	24.5	22.0	19.5	18.3	18.4	18.5	18.7	18.9
102.5°	87.8	60.4	33.0	19.3	19.3	19.3	19.4	19.4
105°	212.8	214.0	215.4	213.4	208.0	202.6	197.3	191.8
107.5°	263.2	263.8	264.5	265.1	265.7	266.2	266.8	267.4
110°	297.5	297.8	298.1	298.4	298.9	299.4	299.8	300.2





TEST NUMBER: P332970-935

CATALOG NUMBER: S124RDIP-S1020D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	330.7	330.6	330.5	330.8	331.4	332.0	332.5	333.1
115°	380.3	380.6	380.9	381.1	381.1	381.1	381.1	381.1
117.5°	430.2	430.2	430.1	430.0	430.0	429.9	429.8	429.8
120°	461.1	461.4	461.7	461.7	461.4	461.1	460.8	460.5
122.5°	491.5	491.7	491.9	491.8	491.5	491.2	490.9	490.6
125°	534.1	534.5	534.9	535.3	535.5	535.5	535.7	535.9
127.5°	576.4	576.3	576.2	576.1	575.9	575.8	575.8	575.6
130°	602.2	602.3	602.4	602.5	602.5	602.5	602.5	602.5
132.5°	627.5	627.6	627.8	627.8	627.7	627.5	627.4	627.3
135°	662.4	662.6	663.0	663.2	663.6	663.8	664.2	664.4
137.5°	695.8	696.1	696.5	696.5	696.5	696.4	696.3	696.2
140°	716.5	717.0	717.4	717.7	717.9	718.0	718.2	718.3
142.5°	735.6	736.0	736.3	736.5	736.5	736.6	736.6	736.6
145°	763.0	763.2	763.4	763.5	763.9	764.1	764.5	764.7
147.5°	787.1	787.2	787.3	787.5	787.6	787.7	787.9	788.1
150°	802.5	802.5	802.5	802.5	802.7	802.8	803.0	803.1
152.5°	815.9	816.1	816.3	816.4	816.3	816.2	816.1	816.1
155°	834.0	834.6	835.2	835.3	834.7	834.3	833.9	833.4
157.5°	849.5	850.3	851.1	851.1	850.3	849.5	848.8	848.0
160°	859.5	860.4	861.3	861.3	860.4	859.5	858.6	857.6
162.5°	867.5	868.4	869.4	869.3	868.2	867.2	866.3	865.2
165°	878.9	880.1	881.3	881.2	879.9	878.6	877.2	875.8
167.5°	887.3	888.6	889.8	889.8	888.3	886.7	885.3	883.8
170°	892.3	893.5	894.8	894.6	893.1	891.7	890.1	888.6
172.5°	895.6	896.8	898.0	897.8	896.2	894.6	892.9	891.3
175°	899.4	900.8	902.1	901.9	900.1	898.3	896.5	894.7
177.5°	901.0	901.9	902.8	902.6	901.1	899.7	898.3	896.8
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1

(END OF REPORT)