

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333337-830

Luminaire Tested: **S125DIP-S1270D1205U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333337-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1205U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9374.4 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69		62	60	58		51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57		54	51	49		45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		40	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41		43	39	35		35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35		38	34	31		32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31		35	30	27		29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27		31	27	24		26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22		27	22	19		22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.1	1.9
10°-20°	494.7	5.3
20°-30°	730.5	7.8
30°-40°	852.4	9.1
40°-50°	856.1	9.1
50°-60°	751.5	8.0
60°-70°	559.9	6.0
70°-80°	320.2	3.4
80°-90°	96.2	1.0
90°-100°	53.7	0.6
100°-110°	330.9	3.5
110°-120°	600.2	6.4
120°-130°	770.3	8.2
130°-140°	828.6	8.8
140°-150°	777.7	8.3
150°-160°	629.1	6.7
160°-170°	406.9	4.3
170°-180°	140.3	1.5
0°-30°	1400.3	14.9
0°-40°	2252.7	24.0
0°-60°	3860.3	41.2
0°-90°	4836.6	51.6
90°-120°	984.9	10.5
90°-150°	3361.5	35.9
90°-180°	4538.0	48.4
0°-180°	9374.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	10	18	23	26	7
95°	62	57	18	23	23	80
105°	322	326	326	326	325	341
115°	605	610	611	607	600	599
125°	860	867	868	863	860	768
135°	1072	1078	1077	1074	1068	826
145°	1243	1245	1246	1246	1240	777
155°	1369	1363	1365	1368	1359	631
165°	1445	1439	1439	1445	1437	408
175°	1478	1472	1472	1480	1471	141
180°	1478	1478	1478	1478	1478	



TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	32.0	32.3	32.7	33.1	33.6	33.7	33.8	33.9	34.0	34.0	34.3
90°	1.1	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8
92.5°	16.9	15.6	14.1	12.8	11.4	11.5	13.0	14.5	16.0	17.5	18.8
95°	62.4	61.7	61.0	60.2	59.5	54.6	45.2	36.0	26.8	17.5	18.8
97.5°	130.4	131.7	133.0	134.3	135.6	127.1	108.8	90.5	72.2	53.9	47.0
100°	182.9	183.7	184.4	185.1	185.9	186.7	187.7	188.7	189.6	190.6	154.3
102.5°	236.4	237.3	238.3	239.1	240.1	240.8	241.4	242.0	242.6	243.2	236.3
105°	322.1	323.0	324.0	325.0	325.9	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	411.0	411.0	411.0	411.0	411.0	411.2	411.7	412.2	412.7	413.2	413.2
110°	468.8	468.8	468.8	468.8	468.8	469.1	469.6	470.0	470.5	471.0	470.3



TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.2	523.8	524.3	524.9	525.5	525.9	526.2	526.5	526.8	527.1	526.2
115°	604.6	605.9	607.1	608.3	609.5	610.3	610.5	610.8	611.0	611.2	610.3
117.5°	689.0	689.0	688.9	688.9	688.8	689.3	690.2	691.1	692.0	693.0	691.7
120°	741.6	741.3	741.1	740.8	740.6	740.8	741.6	742.3	743.0	743.8	743.3
122.5°	788.1	789.0	789.9	790.8	791.7	792.4	792.7	793.1	793.4	793.7	793.2
125°	859.9	861.6	863.3	865.0	866.7	867.5	867.5	867.5	867.5	867.5	866.6
127.5°	928.5	929.7	930.9	932.1	933.3	933.9	933.7	933.6	933.4	933.3	932.7
130°	970.5	971.8	973.0	974.2	975.4	976.1	976.4	976.7	976.9	977.1	976.4
132.5°	1012.6	1014.0	1015.4	1016.8	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4
135°	1072.4	1073.8	1075.3	1076.8	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3
137.5°	1127.4	1128.7	1129.9	1131.1	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2
140°	1163.3	1163.9	1164.3	1164.8	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9
142.5°	1195.7	1196.0	1196.4	1196.7	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7
145°	1243.3	1243.8	1244.3	1244.7	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8
147.5°	1284.9	1284.8	1284.7	1284.6	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1
150°	1311.2	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6
152.5°	1336.6	1335.6	1334.5	1333.4	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5
155°	1369.2	1367.8	1366.3	1364.9	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6
157.5°	1394.5	1393.5	1392.7	1391.9	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5
160°	1412.0	1410.5	1409.1	1407.6	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5
162.5°	1426.0	1424.6	1423.1	1421.6	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9
165°	1444.8	1443.4	1441.9	1440.5	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9
167.5°	1458.9	1457.4	1455.9	1454.3	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9
170°	1466.8	1465.1	1463.3	1461.6	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2
172.5°	1472.0	1470.3	1468.6	1466.9	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1
175°	1477.7	1476.2	1474.8	1473.3	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1
177.5°	1480.4	1479.1	1478.0	1476.9	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	34.6	34.8	35.1	35.0	34.6	34.2	33.8	33.5
90°	20.0	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	20.0	21.2	22.4	23.2	23.5	23.8	24.2	24.5
95°	20.0	21.2	22.4	23.0	23.0	23.0	23.0	23.0
97.5°	40.2	33.3	26.4	23.0	23.0	23.0	23.0	23.0
100°	118.1	81.8	45.5	26.9	25.9	25.0	23.9	23.0
102.5°	229.4	222.6	215.7	204.1	187.5	170.9	154.4	137.8
105°	326.4	326.4	326.4	326.3	326.0	325.8	325.6	325.4
107.5°	413.3	413.3	413.4	413.0	412.3	411.6	410.9	410.1
110°	469.6	468.8	468.1	467.9	468.1	468.3	468.6	468.8





TEST NUMBER: P333337-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.3	524.3	523.4	522.7	522.5	522.1	521.8	521.4
115°	609.3	608.3	607.4	606.1	604.6	603.2	601.7	600.3
117.5°	690.4	689.2	687.9	686.9	686.3	685.7	685.0	684.4
120°	742.8	742.3	741.9	741.0	739.8	738.6	737.4	736.1
122.5°	792.8	792.3	791.8	790.8	789.4	788.0	786.6	785.2
125°	865.6	864.6	863.7	862.8	862.0	861.4	860.6	859.9
127.5°	932.2	931.7	931.1	930.0	928.2	926.3	924.5	922.7
130°	975.6	974.9	974.2	973.2	971.9	970.8	969.6	968.4
132.5°	1016.2	1016.1	1016.0	1015.3	1014.1	1012.9	1011.6	1010.4
135°	1075.8	1075.3	1074.9	1073.8	1072.4	1070.9	1069.5	1068.0
137.5°	1131.3	1131.4	1131.5	1131.0	1129.6	1128.4	1127.1	1125.9
140°	1165.4	1165.8	1166.4	1165.8	1164.4	1163.0	1161.5	1160.1
142.5°	1198.8	1198.9	1199.0	1198.3	1196.8	1195.4	1193.9	1192.5
145°	1245.9	1246.2	1246.4	1245.9	1244.3	1242.9	1241.4	1240.0
147.5°	1286.4	1286.7	1286.9	1286.2	1284.5	1282.7	1281.0	1279.2
150°	1312.2	1312.7	1313.2	1312.4	1310.5	1308.5	1306.6	1304.7
152.5°	1334.9	1335.5	1336.0	1335.3	1333.5	1331.8	1330.0	1328.3
155°	1366.3	1367.1	1367.8	1367.2	1365.3	1363.3	1361.3	1359.4
157.5°	1392.3	1393.1	1393.8	1393.3	1391.3	1389.4	1387.4	1385.4
160°	1408.4	1409.4	1410.4	1409.9	1408.0	1406.0	1404.1	1402.1
162.5°	1423.2	1424.7	1426.0	1425.6	1423.4	1421.3	1419.2	1417.0
165°	1442.3	1443.8	1445.2	1444.9	1443.0	1441.1	1439.1	1437.2
167.5°	1456.7	1458.4	1460.2	1460.0	1457.7	1455.6	1453.4	1451.2
170°	1464.1	1466.0	1468.0	1467.8	1465.7	1463.5	1461.3	1459.1
172.5°	1469.8	1471.6	1473.3	1473.1	1470.9	1468.8	1466.5	1464.3
175°	1476.1	1478.1	1480.0	1479.9	1477.7	1475.6	1473.3	1471.1
177.5°	1478.7	1480.1	1481.4	1481.3	1479.8	1478.2	1476.6	1475.1
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7

(END OF REPORT)