

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333338-830

Luminaire Tested: **S125DIP-S1270D1205U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333338-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8763.9 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.1	2.0
10°-20°	494.7	5.6
20°-30°	730.5	8.3
30°-40°	852.4	9.7
40°-50°	856.1	9.8
50°-60°	751.5	8.6
60°-70°	559.9	6.4
70°-80°	320.2	3.7
80°-90°	96.2	1.1
90°-100°	94.3	1.1
100°-110°	278.4	3.2
110°-120°	471.5	5.4
120°-130°	620.5	7.1
130°-140°	695.3	7.9
140°-150°	681.4	7.8
150°-160°	572.4	6.5
160°-170°	380.5	4.3
170°-180°	133.1	1.5
0°-30°	1400.3	16.0
0°-40°	2252.7	25.7
0°-60°	3860.3	44.0
0°-90°	4836.6	55.2
90°-120°	844.1	9.6
90°-150°	2841.4	32.4
90°-180°	3927.0	44.8
0°-180°	8763.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	10	18	23	26	8
95°	71	74	84	92	94	76
105°	250	255	262	268	272	267
115°	472	476	479	478	476	467
125°	689	695	697	694	693	617
135°	896	902	904	903	899	690
145°	1085	1090	1093	1093	1090	678
155°	1242	1242	1243	1247	1242	572
165°	1350	1348	1349	1353	1347	381
175°	1404	1400	1400	1406	1399	133
180°	1407	1407	1407	1407	1407	



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	32.0	32.3	32.7	33.1	33.6	33.7	33.8	33.9	34.0	34.0	34.3
90°	1.1	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8
92.5°	26.5	27.9	29.2	30.6	32.0	33.6	35.8	37.9	40.0	42.0	43.6
95°	71.2	71.6	72.2	72.7	73.1	74.6	77.0	79.5	81.9	84.4	86.1
97.5°	118.3	118.5	118.7	118.9	119.0	120.8	124.2	127.5	130.9	134.3	135.9
100°	153.4	153.4	153.4	153.4	153.4	155.0	158.1	161.3	164.4	167.6	169.8
102.5°	191.1	192.0	192.9	194.0	194.9	196.2	197.8	199.4	201.0	202.6	205.0
105°	249.7	250.9	252.1	253.4	254.6	255.9	257.4	258.8	260.3	261.7	263.3
107.5°	314.5	315.8	317.0	318.2	319.4	320.6	321.7	322.8	324.0	325.1	325.8
110°	359.3	360.4	361.7	362.9	364.1	365.0	365.8	366.6	367.3	368.0	368.7



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	404.8	405.5	406.0	406.7	407.4	408.1	409.1	410.0	410.9	411.8	412.2
115°	472.0	473.1	474.0	474.9	476.0	476.6	477.2	477.7	478.2	478.6	478.4
117.5°	539.5	540.0	540.5	540.8	541.3	541.7	542.2	542.6	543.0	543.5	543.7
120°	581.5	582.8	584.0	585.2	586.4	587.2	587.4	587.7	588.0	588.1	588.1
122.5°	627.2	627.6	628.0	628.5	628.9	629.4	630.1	630.7	631.3	632.0	631.8
125°	688.9	690.4	691.8	693.3	694.7	695.6	695.9	696.1	696.4	696.6	696.1
127.5°	754.7	755.4	756.3	757.1	758.0	758.6	758.8	759.1	759.4	759.7	759.4
130°	794.1	795.3	796.5	797.8	798.9	799.8	800.3	800.8	801.3	801.7	801.5
132.5°	833.5	835.5	837.5	839.5	841.5	842.4	842.4	842.3	842.2	842.1	841.8
135°	896.0	897.4	898.9	900.3	901.8	902.7	902.9	903.1	903.3	903.6	903.6
137.5°	954.6	956.0	957.4	958.8	960.3	961.3	961.8	962.3	962.9	963.4	963.7
140°	992.3	993.5	994.8	996.0	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5
142.5°	1030.0	1031.0	1032.1	1033.0	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1
145°	1085.4	1086.4	1087.4	1088.4	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1
147.5°	1136.7	1137.2	1137.7	1138.3	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3
150°	1170.8	1170.6	1170.4	1170.2	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1
152.5°	1198.9	1199.2	1199.6	1200.0	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8
155°	1242.1	1242.1	1242.1	1242.1	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2
157.5°	1280.6	1280.1	1279.5	1279.0	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3
160°	1303.3	1302.7	1301.9	1301.2	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1
162.5°	1323.5	1323.0	1322.5	1321.9	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5
165°	1350.5	1350.0	1349.5	1349.1	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4
167.5°	1373.3	1372.2	1371.3	1370.4	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4
170°	1385.5	1384.6	1383.6	1382.6	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6
172.5°	1394.3	1393.4	1392.3	1391.4	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4
175°	1404.1	1403.2	1402.2	1401.2	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2
177.5°	1409.2	1408.4	1407.6	1406.8	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	34.6	34.8	35.1	35.0	34.6	34.2	33.8	33.5
90°	20.0	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	45.2	46.8	48.4	49.6	50.0	50.6	51.2	51.7
95°	87.8	89.4	91.1	92.3	92.7	93.2	93.7	94.2
97.5°	137.5	139.1	140.7	141.7	141.9	142.2	142.5	142.8
100°	171.9	174.2	176.3	177.7	178.1	178.6	179.2	179.6
102.5°	207.4	209.8	212.2	213.7	214.4	215.1	215.7	216.4
105°	264.7	266.2	267.6	268.7	269.5	270.1	270.9	271.6
107.5°	326.5	327.3	328.0	328.4	328.3	328.3	328.2	328.1
110°	369.5	370.2	370.9	371.2	370.9	370.7	370.4	370.2



TEST NUMBER: P333338-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	412.6	412.8	413.2	413.1	412.7	412.3	411.8	411.4
115°	478.2	477.9	477.7	477.4	477.2	476.9	476.6	476.5
117.5°	543.8	544.0	544.2	543.8	542.9	542.0	540.9	540.0
120°	588.1	588.1	588.1	587.7	586.7	585.7	584.8	583.8
122.5°	631.6	631.4	631.2	630.7	629.9	629.1	628.4	627.6
125°	695.6	695.1	694.7	694.3	694.1	693.8	693.5	693.3
127.5°	759.2	758.9	758.7	758.4	757.9	757.3	756.9	756.4
130°	801.3	801.0	800.8	800.4	799.9	799.5	798.9	798.4
132.5°	841.6	841.3	841.0	840.7	839.9	839.2	838.6	837.9
135°	903.6	903.6	903.6	903.1	902.1	901.2	900.2	899.2
137.5°	964.0	964.3	964.6	964.1	962.9	961.7	960.5	959.2
140°	1002.0	1002.6	1003.1	1002.7	1001.5	1000.2	999.0	997.8
142.5°	1039.3	1039.6	1039.9	1039.4	1038.2	1037.1	1035.9	1034.6
145°	1093.1	1093.1	1093.1	1092.7	1092.0	1091.3	1090.5	1089.8
147.5°	1142.9	1143.5	1144.1	1143.5	1141.9	1140.2	1138.6	1136.9
150°	1174.1	1174.1	1174.1	1173.9	1173.4	1172.9	1172.4	1172.0
152.5°	1203.3	1203.9	1204.5	1204.4	1203.5	1202.6	1201.7	1200.9
155°	1245.1	1246.0	1247.1	1246.9	1245.7	1244.4	1243.3	1242.1
157.5°	1281.2	1282.2	1283.2	1282.9	1281.3	1279.7	1278.1	1276.5
160°	1303.2	1304.1	1305.0	1305.0	1303.7	1302.5	1301.3	1300.1
162.5°	1323.7	1324.8	1326.1	1325.9	1324.5	1323.0	1321.6	1320.2
165°	1351.3	1352.3	1353.3	1353.0	1351.6	1350.1	1348.7	1347.2
167.5°	1371.8	1373.3	1374.7	1374.7	1373.2	1371.7	1370.2	1368.7
170°	1384.0	1385.5	1387.0	1386.9	1385.2	1383.5	1381.8	1380.1
172.5°	1392.8	1394.3	1395.7	1395.7	1394.2	1392.7	1391.2	1389.7
175°	1402.7	1404.1	1405.6	1405.5	1403.8	1402.1	1400.3	1398.6
177.5°	1407.1	1408.3	1409.5	1409.4	1408.1	1406.7	1405.3	1403.9
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4

(END OF REPORT)