

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333303-830

Luminaire Tested: **S125DIP-S1270D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333303-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6073.5 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	114	114	114	114	109	109	109	109	100	100	100		91	91	91		83	83	83	80
1	104	100	96	92	100	96	92	89	88	85	82		80	78	76		74	72	70	67
2	95	87	81	75	91	84	78	73	77	72	68		70	67	63		65	62	59	56
3	87	77	69	63	83	74	66	61	68	62	57		62	58	54		57	54	50	47
4	79	68	60	53	76	65	58	52	60	54	49		56	50	46		51	47	43	41
5	73	61	52	46	70	58	50	45	54	47	42		50	44	40		46	42	38	35
6	67	55	46	40	64	53	45	39	49	42	37		45	40	35		42	37	33	31
7	62	50	41	35	60	48	40	34	44	38	33		41	35	31		38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29		38	32	28		35	30	27	25
9	54	41	33	28	52	40	33	28	37	31	26		35	29	25		33	28	24	22
10	51	38	31	25	49	37	30	25	35	28	24		32	27	23		30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.1	2.9
10°-20°	494.7	8.1
20°-30°	730.5	12.0
30°-40°	852.4	14.0
40°-50°	856.1	14.1
50°-60°	751.5	12.4
60°-70°	559.9	9.2
70°-80°	320.2	5.3
80°-90°	94.1	1.5
90°-100°	119.8	2.0
100°-110°	257.4	4.2
110°-120°	241.6	4.0
120°-130°	195.8	3.2
130°-140°	157.1	2.6
140°-150°	118.6	2.0
150°-160°	83.5	1.4
160°-170°	49.2	0.8
170°-180°	16.0	0.3
0°-30°	1400.3	23.1
0°-40°	2252.7	37.1
0°-60°	3860.3	63.6
0°-90°	4834.4	79.6
90°-120°	618.8	10.2
90°-150°	1090.3	18.0
90°-180°	1239.0	20.4
0°-180°	6073.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	0	3	5	7	8	5
95°	11	32	295	134	78	12
105°	38	53	242	476	441	40
115°	67	81	194	418	492	66
125°	93	109	186	332	387	83
135°	109	131	184	279	322	85
145°	127	146	185	231	254	80
155°	145	156	181	204	213	67
165°	158	163	173	184	186	45
175°	165	165	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	31.8	31.9	32.0	32.1	32.2	32.2	32.0	32.0	31.8	31.7	31.7
90°	0.4	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7
92.5°	4.1	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9
95°	11.0	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8
97.5°	18.3	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4
100°	23.3	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1
102.5°	28.9	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9
105°	37.6	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1
107.5°	46.2	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6
110°	52.3	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	58.4	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4
115°	67.3	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5
117.5°	75.3	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4
120°	80.6	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9
122.5°	86.2	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1
125°	93.3	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6
127.5°	98.8	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5
130°	102.3	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6
132.5°	104.9	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4
135°	109.2	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5
137.5°	114.7	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1
140°	117.9	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5
142.5°	121.7	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2
145°	127.2	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2
147.5°	133.1	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1
150°	136.6	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5
152.5°	140.3	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6
155°	145.2	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5
157.5°	149.7	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6
160°	152.6	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3
162.5°	155.0	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1
165°	158.5	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9
167.5°	161.0	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8
170°	162.6	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9
172.5°	163.6	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0
175°	164.9	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5
177.5°	165.5	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	31.8	31.9	31.9	31.8	31.3	30.7	30.3	29.8
90°	6.0	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	59.0	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	239.5	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	356.7	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	409.7	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	427.5	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	417.1	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	379.5	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	351.8	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333303-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.9	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	302.5	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	284.7	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	275.1	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	268.0	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	257.5	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	246.9	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	240.2	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	233.5	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	224.9	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	217.5	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	213.5	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	210.1	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	205.6	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	201.2	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	198.9	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	196.2	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	192.2	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	188.2	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	185.6	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	182.6	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	178.5	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	174.7	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	172.6	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	170.1	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	165.8	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)