

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332881-935

Luminaire Tested: **S124RDIP-S350D810U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332881-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3647.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	79	69	62	57	71	63	57	52	51	46	43	39	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.4
10°-20°	139.4	3.8
20°-30°	201.3	5.5
30°-40°	228.2	6.3
40°-50°	220.4	6.0
50°-60°	183.2	5.0
60°-70°	126.5	3.5
70°-80°	64.1	1.8
80°-90°	19.0	0.5
90°-100°	57.4	1.6
100°-110°	170.1	4.7
110°-120°	288.6	7.9
120°-130°	380.6	10.4
130°-140°	427.4	11.7
140°-150°	420.0	11.5
150°-160°	353.3	9.7
160°-170°	235.0	6.4
170°-180°	82.3	2.3
0°-30°	390.7	10.7
0°-40°	619.0	17.0
0°-60°	1022.6	28.0
0°-90°	1232.3	33.8
90°-120°	516.1	14.2
90°-150°	1744.1	47.8
90°-180°	2415.0	66.2
0°-180°	3647.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	2	9	15	19	20	4
95°	40	46	51	53	53	45
105°	157	158	160	162	164	166
115°	294	293	292	291	291	289
125°	427	427	427	425	424	381
135°	551	555	555	554	552	426
145°	670	672	673	672	670	419
155°	767	767	767	769	767	353
165°	835	833	832	836	833	235
175°	869	866	865	869	865	82
180°	870	870	870	870	870	



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.9	7.7	7.4	7.1	6.9	6.9	7.1	7.2	7.3	7.5	7.7
90°	2.0	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7
92.5°	14.4	16.3	18.2	20.1	22.0	23.3	24.1	25.0	25.8	26.7	27.2
95°	40.4	41.8	43.0	44.4	45.8	47.0	48.0	49.1	50.1	51.1	51.6
97.5°	70.5	71.6	72.7	73.8	74.8	76.0	77.2	78.4	79.6	80.9	81.5
100°	94.3	94.8	95.4	96.0	96.6	97.6	98.9	100.3	101.6	103.0	103.3
102.5°	119.0	119.2	119.5	119.8	119.9	120.7	121.9	123.1	124.4	125.6	126.1
105°	156.9	157.0	157.1	157.3	157.5	157.8	158.4	159.0	159.6	160.2	160.7
107.5°	196.6	196.7	196.9	197.1	197.3	197.4	197.5	197.6	197.7	197.8	198.2
110°	223.5	223.8	224.0	224.4	224.6	224.7	224.6	224.5	224.3	224.1	223.9



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	251.5	251.5	251.6	251.7	251.8	251.6	251.3	251.1	250.8	250.6	250.5
115°	293.5	293.5	293.5	293.5	293.5	293.3	293.0	292.7	292.4	292.1	292.0
117.5°	333.0	333.2	333.3	333.4	333.6	333.5	333.3	333.0	332.9	332.7	332.2
120°	359.5	360.1	360.7	361.3	361.9	361.9	361.4	361.0	360.6	360.2	359.4
122.5°	386.9	387.1	387.4	387.6	387.9	387.9	387.7	387.4	387.3	387.0	386.5
125°	427.4	427.4	427.4	427.4	427.4	427.3	427.2	427.1	426.9	426.8	426.5
127.5°	464.2	464.6	465.1	465.5	466.0	466.1	465.8	465.6	465.4	465.1	464.9
130°	490.0	490.5	490.9	491.4	491.8	492.1	492.1	492.1	492.1	492.1	491.7
132.5°	516.4	516.8	517.1	517.4	517.7	517.8	517.7	517.6	517.5	517.4	517.0
135°	551.3	552.2	553.1	554.0	554.9	555.3	555.3	555.3	555.3	555.3	555.0
137.5°	589.3	589.7	590.0	590.5	590.9	591.2	591.5	591.8	591.9	592.2	591.9
140°	614.6	614.8	615.2	615.4	615.8	615.9	615.9	615.9	615.9	615.9	615.8
142.5°	637.7	638.0	638.3	638.6	638.9	639.0	638.9	638.8	638.6	638.5	638.5
145°	669.8	670.4	671.0	671.6	672.2	672.5	672.7	672.8	673.0	673.1	673.0
147.5°	701.5	702.2	702.9	703.7	704.4	704.7	704.6	704.5	704.3	704.2	704.1
150°	720.9	721.5	722.1	722.7	723.3	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	739.3	739.6	739.9	740.3	740.6	740.9	741.0	741.1	741.2	741.4	741.8
155°	767.3	767.3	767.3	767.3	767.3	767.2	767.2	767.0	766.8	766.7	767.2
157.5°	791.1	790.7	790.5	790.2	790.0	789.8	789.8	789.8	789.7	789.7	790.1
160°	805.0	804.9	804.8	804.6	804.4	804.3	804.2	804.0	803.8	803.7	804.2
162.5°	817.9	817.6	817.2	816.8	816.4	816.1	816.0	815.9	815.7	815.5	816.4
165°	835.3	834.9	834.5	834.0	833.5	833.2	832.8	832.6	832.2	832.0	832.8
167.5°	848.7	848.0	847.4	846.8	846.2	845.8	845.8	845.9	845.9	845.9	846.9
170°	856.2	855.5	854.7	853.9	853.3	852.9	853.1	853.3	853.3	853.5	854.4
172.5°	861.6	861.0	860.3	859.7	859.1	858.8	858.8	858.8	858.8	858.9	859.9
175°	869.0	868.2	867.5	866.8	866.0	865.6	865.4	865.2	865.1	865.0	866.0
177.5°	871.4	870.8	870.2	869.6	869.0	868.7	868.7	868.7	868.7	868.7	869.5
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	7.7	7.8	7.9	8.1	8.2	8.4	8.4	8.6
90°	16.6	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	27.7	28.2	28.8	29.2	29.4	29.5	29.7	29.9
95°	52.1	52.5	53.0	53.2	53.2	53.2	53.2	53.2
97.5°	82.0	82.5	83.1	83.3	83.3	83.3	83.3	83.3
100°	103.6	103.9	104.2	104.4	104.4	104.4	104.4	104.4
102.5°	126.5	126.8	127.3	127.5	127.7	127.8	127.9	128.0
105°	161.1	161.5	162.0	162.5	162.9	163.3	163.8	164.3
107.5°	198.6	199.0	199.4	199.7	199.6	199.6	199.6	199.5
110°	223.5	223.3	222.9	223.0	223.5	223.9	224.4	224.8



TEST NUMBER: P332881-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	250.4	250.4	250.3	250.3	250.4	250.5	250.6	250.6
115°	291.8	291.7	291.5	291.4	291.3	291.1	290.9	290.8
117.5°	331.7	331.1	330.6	330.2	329.9	329.6	329.3	329.0
120°	358.6	357.8	357.1	356.9	357.2	357.5	357.8	358.1
122.5°	386.0	385.6	385.0	384.5	383.9	383.4	382.9	382.4
125°	426.2	425.9	425.6	425.2	425.0	424.6	424.4	424.0
127.5°	464.5	464.3	463.9	463.6	463.4	463.2	463.0	462.7
130°	491.5	491.1	490.9	490.4	489.8	489.2	488.6	488.0
132.5°	516.8	516.4	516.2	515.9	515.7	515.4	515.1	515.0
135°	554.7	554.4	554.1	553.7	553.3	552.8	552.4	552.0
137.5°	591.4	591.1	590.6	590.5	590.6	590.6	590.7	590.9
140°	615.6	615.4	615.3	615.2	615.0	614.8	614.7	614.6
142.5°	638.4	638.4	638.4	638.3	638.3	638.3	638.3	638.3
145°	672.8	672.7	672.5	672.2	671.8	671.3	670.9	670.5
147.5°	704.0	703.9	703.7	703.6	703.4	703.3	703.2	703.0
150°	723.6	723.6	723.6	723.5	723.4	723.2	723.1	722.9
152.5°	742.1	742.4	742.8	742.8	742.4	742.0	741.7	741.2
155°	767.8	768.4	769.0	769.0	768.4	767.8	767.2	766.7
157.5°	790.6	791.1	791.5	791.4	791.0	790.5	790.0	789.5
160°	804.6	805.0	805.5	805.4	804.6	803.8	803.1	802.4
162.5°	817.2	817.9	818.8	818.8	818.0	817.3	816.6	815.8
165°	833.8	834.7	835.6	835.7	835.1	834.5	833.9	833.4
167.5°	847.7	848.7	849.5	849.5	848.6	847.7	846.8	845.8
170°	855.3	856.2	857.1	857.0	856.0	855.0	853.9	852.8
172.5°	860.9	861.9	863.0	863.0	861.9	860.8	859.8	858.8
175°	867.0	868.1	869.2	869.2	868.1	867.0	866.0	865.0
177.5°	870.4	871.2	872.1	872.0	871.1	870.1	869.2	868.1
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3

(END OF REPORT)