

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333150-830

Luminaire Tested: **S125DIP-S375D1035U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333150-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1035U830-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4935.2 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	33	32	31
2	85	78	72	67	76	70	65	60	55	51	48	41	39	37	29	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	34	31	25	24	22
4	71	60	52	47	63	54	48	43	43	38	34	32	29	27	23	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	17
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	15
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	15	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	1.1
10°-20°	146.6	3.0
20°-30°	216.5	4.4
30°-40°	252.7	5.1
40°-50°	253.8	5.1
50°-60°	222.8	4.5
60°-70°	166.0	3.4
70°-80°	94.9	1.9
80°-90°	30.2	0.6
90°-100°	338.3	6.9
100°-110°	727.2	14.7
110°-120°	682.5	13.8
120°-130°	553.1	11.2
130°-140°	443.9	9.0
140°-150°	334.9	6.8
150°-160°	235.8	4.8
160°-170°	139.0	2.8
170°-180°	45.2	0.9
0°-30°	415.1	8.4
0°-40°	667.8	13.5
0°-60°	1144.3	23.2
0°-90°	1435.4	29.1
90°-120°	1747.9	35.4
90°-150°	3079.8	62.4
90°-180°	3500.0	70.9
0°-180°	4935.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	1	8	15	20	22	3
95°	31	92	834	378	221	33
105°	106	149	682	1343	1247	112
115°	190	229	548	1180	1389	187
125°	263	309	525	939	1094	234
135°	309	371	521	787	909	240
145°	359	412	523	652	717	225
155°	410	441	510	576	601	189
165°	448	460	489	519	527	126
175°	466	466	470	475	473	44
180°	467	467	467	467	467	



TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.6	9.8	10.2	10.6	10.9	11.2	11.4	11.7	11.8	12.1	12.3
90°	0.9	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0
92.5°	11.5	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5
95°	31.0	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8
97.5°	51.6	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2
100°	65.9	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9
102.5°	81.7	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3
105°	106.3	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3
107.5°	130.4	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0
110°	147.7	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3



TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.0	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7
115°	190.1	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1
117.5°	212.6	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7
120°	227.7	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9
122.5°	243.6	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3
125°	263.4	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9
127.5°	279.1	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0
130°	288.9	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7
132.5°	296.4	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6
135°	308.6	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9
137.5°	324.0	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3
140°	333.1	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8
142.5°	343.7	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0
145°	359.4	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4
147.5°	376.0	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5
150°	385.8	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0
152.5°	396.3	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7
155°	410.2	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9
157.5°	422.6	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6
160°	430.9	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9
162.5°	437.7	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9
165°	447.9	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8
167.5°	454.7	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0
170°	459.2	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7
172.5°	462.2	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4
175°	465.7	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4
177.5°	467.4	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	12.4	12.6	12.8	13.1	13.0	12.8	12.8	12.7
90°	17.0	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	166.7	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	676.6	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	1007.6	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1157.3	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1207.8	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1178.0	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1071.9	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	993.6	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8





TEST NUMBER: P333150-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	931.9	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	854.3	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	804.3	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	777.2	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	756.9	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	727.4	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	697.2	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	678.4	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	659.6	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	635.1	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	614.4	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	603.1	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	593.3	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	580.5	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	568.5	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	561.8	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	554.2	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	542.9	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	531.6	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	524.1	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	515.9	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	504.4	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	493.4	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	487.4	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	480.6	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.2	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)