

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332912-935

Luminaire Tested: **S124RDIP-S575D810U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332912-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D810U935-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4515.8 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45																				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38																				
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	41	39	37	32																				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																				
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24																				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21																				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18																				
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16																				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13																				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.2	1.8
10°-20°	229.2	5.1
20°-30°	331.0	7.3
30°-40°	375.2	8.3
40°-50°	362.3	8.0
50°-60°	301.3	6.7
60°-70°	208.0	4.6
70°-80°	105.4	2.3
80°-90°	28.9	0.6
90°-100°	247.5	5.5
100°-110°	515.1	11.4
110°-120°	461.4	10.2
120°-130°	388.1	8.6
130°-140°	323.6	7.2
140°-150°	247.2	5.5
150°-160°	173.8	3.8
160°-170°	102.2	2.3
170°-180°	33.3	0.7
0°-30°	642.4	14.2
0°-40°	1017.6	22.5
0°-60°	1681.1	37.2
0°-90°	2023.5	44.8
90°-120°	1224.0	27.1
90°-150°	2183.0	48.3
90°-180°	2492.0	55.2
0°-180°	4515.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	1	5	12	13	14	3
95°	22	70	549	272	164	25
105°	79	114	442	951	947	84
115°	139	174	394	757	910	138
125°	193	230	392	644	726	172
135°	230	273	388	572	649	177
145°	265	303	386	482	530	166
155°	301	325	376	426	444	139
165°	328	338	360	381	387	93
175°	342	343	345	350	349	32
180°	343	343	343	343	343	



TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.5	11.8	11.2	10.4	9.6	9.0	9.7	9.6	9.8	9.9	9.6
90°	0.7	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5
92.5°	7.7	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9
95°	22.2	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2
97.5°	39.9	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8
100°	51.1	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6
102.5°	61.9	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2
105°	78.8	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9
107.5°	97.4	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6
110°	109.8	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0



TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3
115°	138.7	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6
117.5°	156.4	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7
120°	168.3	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9
122.5°	179.1	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6
125°	193.2	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4
127.5°	205.8	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9
130°	212.8	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0
132.5°	219.7	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6
135°	229.5	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5
137.5°	239.4	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5
140°	246.4	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7
142.5°	253.9	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5
145°	264.6	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9
147.5°	276.6	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0
150°	284.1	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2
152.5°	291.1	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9
155°	300.9	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5
157.5°	310.5	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9
160°	316.4	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0
162.5°	321.8	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7
165°	327.9	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6
167.5°	333.9	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1
170°	336.7	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8
172.5°	339.3	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0
175°	342.0	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7
177.5°	343.2	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	9.7	9.7	9.7	9.7	10.0	10.2	10.2	10.3
90°	12.1	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	132.2	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	498.9	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	737.0	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	811.9	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	808.1	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	754.1	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	677.2	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	630.9	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2





TEST NUMBER: P332912-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	596.9	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	562.8	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	546.1	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	538.6	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	532.1	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	521.1	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	507.6	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	496.9	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	485.5	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	469.9	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	455.8	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	447.7	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	440.1	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	429.6	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	420.8	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	415.3	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	409.5	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	400.5	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	391.0	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	385.1	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	379.2	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	370.9	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	363.0	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	358.2	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	353.9	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.1	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.3	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)