

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332949-935

Luminaire Tested: **S124RDIP-S795D1205U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332949-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D1205U935-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7014.3 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	23
5	68	56	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	16
8	53	42	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	1.6
10°-20°	332.2	4.7
20°-30°	519.5	7.4
30°-40°	577.6	8.2
40°-50°	512.4	7.3
50°-60°	399.3	5.7
60°-70°	261.4	3.7
70°-80°	128.6	1.8
80°-90°	35.6	0.5
90°-100°	45.8	0.7
100°-110°	291.7	4.2
110°-120°	558.0	8.0
120°-130°	708.4	10.1
130°-140°	757.9	10.8
140°-150°	708.7	10.1
150°-160°	571.5	8.1
160°-170°	368.6	5.3
170°-180°	127.0	1.8
0°-30°	961.8	13.7
0°-40°	1539.4	21.9
0°-60°	2451.2	34.9
0°-90°	2876.8	41.0
90°-120°	895.4	12.8
90°-150°	3070.4	43.8
90°-180°	4138.0	59.0
0°-180°	7014.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	27
90°	30	3	30	3	30	14
95°	29	55	29	55	29	23
105°	285	301	285	301	285	249
115°	566	562	566	562	566	561
125°	796	790	796	790	796	709
135°	987	980	987	980	987	760
145°	1136	1130	1136	1130	1136	710
155°	1238	1240	1238	1240	1238	571
165°	1302	1308	1302	1308	1302	368
175°	1330	1338	1330	1338	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	14.0	13.6	13.9	13.8	14.0	13.5	13.6	14.1	13.1	13.2	12.8
90°	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7	23.3	22.0	20.2
92.5°	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8	22.6	21.2	19.5
95°	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7	23.3	22.0	21.8
97.5°	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7	26.5	26.4	51.2
100°	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4	40.2	44.0	74.7
102.5°	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5	171.3	212.1	216.1
105°	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2	314.2	312.1	311.0
107.5°	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2	390.1	389.2	387.6
110°	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1	441.6	441.2	439.9



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5	491.5	491.6	491.0
115°	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2	564.7	564.2	564.5
117.5°	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3	639.4	639.5	639.0
120°	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3	684.5
122.5°	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5	730.2	730.0	729.6
125°	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7	793.0	792.4	792.8
127.5°	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5	856.6	856.8	855.7
130°	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8	894.6	894.4	893.7
132.5°	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5	932.2	932.0	931.2
135°	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3	983.9	983.4	982.6
137.5°	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1	1033.5	1033.0	1032.1
140°	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8	1064.1	1063.5	1063.0
142.5°	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3	1092.8	1092.3	1092.0
145°	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9	1133.8	1133.5	1133.5
147.5°	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7	1169.5	1169.3	1169.5
150°	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5	1212.1	1211.8	1212.1
155°	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3	1238.5	1237.5	1238.2
157.5°	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2	1260.9
160°	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5	1274.8
162.5°	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3	1287.9	1286.6	1286.8
165°	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1	1304.3	1302.6	1302.6
167.5°	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5	1316.6	1314.6	1314.7
170°	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1	1324.4	1322.6	1322.3
172.5°	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9	1329.1	1327.4	1327.1
175°	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6	1334.6	1332.6	1332.4
177.5°	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9	1337.4	1336.0	1335.7
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	12.5	11.8	12.1	11.7	11.6	12.6	13.2	13.1	12.5	11.8	11.2
90°	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6	12.7	12.9	13.0
95°	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0	47.4	39.9	32.4
97.5°	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8	121.6	126.3	131.0
100°	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1	168.1	172.1	176.1
102.5°	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9	219.8	222.7	225.7
105°	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1	302.5	303.8	305.1
107.5°	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4	380.0	380.7	381.3
110°	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2	432.8	433.5	434.2





TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5	484.7	485.8	487.0
115°	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2	562.9	563.6	564.2
117.5°	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3	634.1	635.1	635.9
120°	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3	682.2	683.1	684.0
122.5°	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1	726.7	727.2	727.7
125°	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3	791.3	792.1	793.0
127.5°	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2	851.4	851.6	851.9
130°	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4	890.6	890.9	891.0
132.5°	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4	926.8	927.2	927.6
135°	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4	980.2	980.0	979.7
137.5°	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3	1028.4	1028.5	1028.6
140°	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5	1059.9	1060.3	1060.8
142.5°	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4	1088.3	1089.1	1089.9
145°	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5	1131.2	1131.9	1132.5
147.5°	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7	1166.0	1167.2	1168.5
150°	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6	1190.4	1191.3	1192.2
152.5°	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3	1211.1	1211.8	1212.5
155°	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6	1239.8	1240.0	1240.2
157.5°	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1	1264.0	1263.9	1263.8
160°	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6	1277.9	1277.2	1276.6
162.5°	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3	1290.6	1289.7	1288.8
165°	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6	1306.5	1305.4	1304.2
167.5°	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3	1319.2	1318.1	1316.9
170°	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6	1326.3	1324.9	1323.6
172.5°	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4	1331.0	1329.7	1328.4
175°	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6	1336.3	1334.9	1333.6
177.5°	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0	1338.8	1337.5	1336.3
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	11.7	11.8	12.1	11.7	12.5	12.8	12.7	13.0	13.6	13.2	13.3
90°	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7	26.0	27.4	28.2
92.5°	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8	25.2	26.5	27.3
95°	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7	26.0	27.4	28.2
97.5°	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7	26.8	26.9	27.1
100°	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4	32.7	28.9	27.1
102.5°	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5	89.8	49.0	28.7
105°	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2	318.1	320.1	317.1
107.5°	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2	392.1	393.0	394.0
110°	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1	442.6	443.0	443.5



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5	491.4	491.3	491.6
115°	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2	565.6	566.0	566.3
117.5°	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3	639.2	639.1	639.0
120°	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2	685.6	686.0	686.0
122.5°	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5	730.7	731.0	730.9
125°	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7	794.4	795.0	795.5
127.5°	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5	856.4	856.3	856.1
130°	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8	895.1	895.3	895.4
132.5°	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5	932.7	932.9	932.9
135°	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3	984.7	985.2	985.7
137.5°	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1	1034.5	1035.0	1035.2
140°	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8	1065.5	1066.2	1066.6
142.5°	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3	1093.7	1094.2	1094.5
145°	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9	1134.2	1134.4	1134.7
147.5°	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7	1169.8	1170.0	1170.2
150°	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5	1212.8	1213.1	1213.2
155°	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3	1240.2	1241.1	1241.2
157.5°	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8
160°	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9
162.5°	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3	1290.6	1291.9	1291.8
165°	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1	1307.9	1309.7	1309.6
167.5°	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5	1320.4	1322.4	1322.2
170°	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1	1327.9	1329.7	1329.5
172.5°	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9	1332.7	1334.5	1334.2
175°	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6	1338.6	1340.6	1340.2
177.5°	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9	1340.2	1341.7	1341.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	14.1	13.9	13.6	14.0	13.6	13.9	14.1	13.3	13.2	13.6	13.0
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7
92.5°	27.4	27.5	27.6	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8
95°	28.3	28.6	28.8	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7
97.5°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7
100°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4
102.5°	28.7	28.8	28.8	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5
105°	309.1	301.1	293.2	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2
107.5°	394.9	395.7	396.5	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2
110°	444.2	444.9	445.6	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.5	493.4	494.2	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5
115°	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2
117.5°	638.9	638.9	638.8	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3
120°	685.6	685.2	684.8	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2
122.5°	730.5	730.0	729.5	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5
125°	795.7	795.9	796.2	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7
127.5°	855.9	855.7	855.6	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5
130°	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8
132.5°	932.7	932.5	932.4	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5
135°	986.1	986.5	987.0	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3
137.5°	1035.1	1034.9	1034.7	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1
140°	1066.8	1067.0	1067.2	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8
142.5°	1094.6	1094.6	1094.7	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3
145°	1135.1	1135.6	1136.1	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9
147.5°	1170.4	1170.7	1170.9	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7
150°	1192.8	1193.1	1193.3	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5
152.5°	1213.1	1213.0	1212.9	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5
155°	1240.5	1239.8	1239.2	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3
157.5°	1263.6	1262.5	1261.3	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5
160°	1278.6	1277.2	1275.9	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2
162.5°	1290.3	1288.8	1287.3	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3
165°	1307.6	1305.5	1303.6	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1
167.5°	1320.1	1317.8	1315.6	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5
170°	1327.2	1325.0	1322.8	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1
172.5°	1331.8	1329.4	1327.0	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9
175°	1337.6	1334.9	1332.2	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6
177.5°	1339.2	1337.0	1334.9	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	12.7	12.8	12.5	11.7	12.1	11.8	11.7	11.2	11.8	12.5	13.1
90°	23.3	22.0	20.2	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0
92.5°	22.6	21.2	19.5	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6
95°	23.3	22.0	21.8	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0
97.5°	26.5	26.4	51.2	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8
100°	40.2	44.0	74.7	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1
102.5°	171.3	212.1	216.1	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9
105°	314.2	312.1	311.0	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1
107.5°	390.1	389.2	387.6	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4
110°	441.6	441.2	439.9	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	491.6	491.0	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5
115°	564.7	564.2	564.5	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2
117.5°	639.4	639.5	639.0	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3
120°	684.8	684.3	684.5	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3
122.5°	730.2	730.0	729.6	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1
125°	793.0	792.4	792.8	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3
127.5°	856.6	856.8	855.7	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2
130°	894.6	894.4	893.7	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4
132.5°	932.2	932.0	931.2	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4
135°	983.9	983.4	982.6	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4
137.5°	1033.5	1033.0	1032.1	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3
140°	1064.1	1063.5	1063.0	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5
142.5°	1092.8	1092.3	1092.0	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4
145°	1133.8	1133.5	1133.5	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5
147.5°	1169.5	1169.3	1169.5	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7
150°	1192.5	1192.5	1192.7	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6
152.5°	1212.1	1211.8	1212.1	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3
155°	1238.5	1237.5	1238.2	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6
157.5°	1261.3	1260.2	1260.9	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1
160°	1275.9	1274.5	1274.8	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6
162.5°	1287.9	1286.6	1286.8	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3
165°	1304.3	1302.6	1302.6	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6
167.5°	1316.6	1314.6	1314.7	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3
170°	1324.4	1322.6	1322.3	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6
172.5°	1329.1	1327.4	1327.1	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4
175°	1334.6	1332.6	1332.4	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6
177.5°	1337.4	1336.0	1335.7	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	13.2	12.6	11.6	11.7	12.1	11.8	12.5	12.8	13.2	13.1	14.1
90°	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7
92.5°	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8
95°	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7
97.5°	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7
100°	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4
102.5°	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5
105°	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2
107.5°	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2
110°	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1





TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5
115°	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2
117.5°	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3
120°	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2
122.5°	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5
125°	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7
127.5°	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5
130°	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8
132.5°	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5
135°	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3
137.5°	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1
140°	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8
142.5°	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3
145°	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9
147.5°	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7
150°	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5
152.5°	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5
155°	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3
157.5°	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5
160°	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2
162.5°	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3
165°	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1
167.5°	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5
170°	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1
172.5°	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9
175°	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6
177.5°	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	13.6	13.5	14.0	13.8	13.9	13.6	14.0
90°	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.6	443.0	443.5	444.2	444.9	445.6	446.2



TEST NUMBER: P332949-935

CATALOG NUMBER: S124RDIP-S795D1205U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)