

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333140-830

Luminaire Tested: **S125DIP-S375D810U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333140-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4077.6 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	75	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	39	36	34	29	27	26	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	1.3
10°-20°	146.6	3.6
20°-30°	216.5	5.3
30°-40°	252.7	6.2
40°-50°	253.8	6.2
50°-60°	222.8	5.5
60°-70°	166.0	4.1
70°-80°	94.9	2.3
80°-90°	29.7	0.7
90°-100°	63.4	1.6
100°-110°	187.3	4.6
110°-120°	317.3	7.8
120°-130°	417.5	10.2
130°-140°	467.9	11.5
140°-150°	458.6	11.2
150°-160°	385.1	9.4
160°-170°	256.0	6.3
170°-180°	89.6	2.2
0°-30°	415.1	10.2
0°-40°	667.8	16.4
0°-60°	1144.3	28.1
0°-90°	1434.8	35.2
90°-120°	568.0	13.9
90°-150°	1912.0	46.9
90°-180°	2643.0	64.8
0°-180°	4077.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	1	7	12	15	18	4
95°	48	50	57	62	63	51
105°	168	172	176	180	183	180
115°	318	320	322	321	321	314
125°	464	468	469	467	467	415
135°	603	607	608	608	605	465
145°	730	733	736	735	733	456
155°	836	836	836	839	836	385
165°	909	907	908	911	906	256
175°	945	942	942	946	941	90
180°	947	947	947	947	947	



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.5	9.8	10.1	10.4	10.7	10.8	10.9	11.1	11.3	11.4	11.6
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	17.8	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4
95°	47.9	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9
97.5°	79.6	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4
100°	103.2	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2
102.5°	128.6	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0
105°	168.1	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1
107.5°	211.7	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2
110°	241.8	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.4	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4
115°	317.6	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9
117.5°	363.1	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8
120°	391.3	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8
122.5°	422.0	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1
125°	463.5	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4
127.5°	507.8	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0
130°	534.3	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3
132.5°	560.9	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5
135°	602.9	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0
137.5°	642.4	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5
140°	667.8	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0
142.5°	693.1	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2
145°	730.4	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6
147.5°	764.9	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6
150°	787.9	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1
152.5°	806.7	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4
155°	835.8	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2
157.5°	861.8	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5
160°	877.0	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3
162.5°	890.6	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9
165°	908.8	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7
167.5°	924.1	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1
170°	932.4	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4
172.5°	938.2	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2
175°	944.9	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9
177.5°	948.3	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	11.8	11.9	12.1	12.2	12.1	12.0	12.0	11.9
90°	13.4	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	30.4	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	59.0	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	92.6	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	115.7	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	139.6	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	178.1	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	219.7	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	248.6	249.1	249.6	249.8	249.6	249.4	249.3	249.1



TEST NUMBER: P333140-830

CATALOG NUMBER: S125DIP-S375D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.6	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.8	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.0	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	425.0	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	468.1	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.9	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.1	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.3	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.7	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.3	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.4	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.0	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	809.7	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	837.8	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.1	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	876.9	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	890.7	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	909.4	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	923.1	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	931.3	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	937.3	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	943.9	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	946.9	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)