

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333193-830

Luminaire Tested: **S125DIP-S610D1035U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333193-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1035U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6256.6 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32
2	86	79	73	68	78	72	67	62	59	55	52	46	44	41	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5846	5846	5846
5°	5859	5803	5841
10°	5823	5762	5795
15°	5760	5693	5717
20°	5670	5597	5606
25°	5573	5481	5476
30°	5452	5357	5330
35°	5324	5222	5149
40°	5193	5078	5005
45°	5050	4945	4847
50°	4893	4786	4641
55°	4741	4604	4476
60°	4561	4421	4265
65°	4345	4202	4060
70°	4137	3950	3814
75°	3770	3646	3521
80°	3355	3303	3221
85°	2920	2971	2816



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	1.4
10°-20°	241.1	3.9
20°-30°	356.0	5.7
30°-40°	415.4	6.6
40°-50°	417.2	6.7
50°-60°	366.2	5.9
60°-70°	272.9	4.4
70°-80°	156.0	2.5
80°-90°	48.0	0.8
90°-100°	46.1	0.7
100°-110°	284.3	4.5
110°-120°	515.7	8.2
120°-130°	661.8	10.6
130°-140°	711.8	11.4
140°-150°	668.2	10.7
150°-160°	540.5	8.6
160°-170°	349.6	5.6
170°-180°	120.6	1.9
0°-30°	682.4	10.9
0°-40°	1097.8	17.5
0°-60°	1881.2	30.1
0°-90°	2358.1	37.7
90°-120°	846.1	13.5
90°-150°	2887.9	46.2
90°-180°	3899.0	62.3
0°-180°	6256.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	904	902	895	901	901	86
15°	862	859	852	855	855	243
25°	782	778	769	770	768	360
35°	675	672	662	659	653	422
45°	553	550	541	533	531	426
55°	421	418	409	403	398	376
65°	284	282	275	269	266	282
75°	151	150	146	144	141	161
85°	39	40	40	39	38	44
90°	1	8	15	20	23	4
95°	54	49	15	20	20	68
105°	277	280	280	280	280	293
115°	520	524	525	521	516	515
125°	739	745	745	742	739	660
135°	921	927	925	923	918	710
145°	1068	1070	1070	1071	1065	668
155°	1176	1171	1173	1175	1168	542
165°	1241	1236	1237	1242	1235	351
175°	1270	1264	1265	1271	1264	121
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	907.5	907.1	906.7	906.3	906.0	905.1	903.9	902.6	901.4	900.0	901.4
5°	903.8	903.4	903.1	902.8	902.5	901.5	899.9	898.3	896.7	895.1	896.6
7.5°	895.4	895.1	894.8	894.5	894.2	893.2	891.4	889.7	887.9	886.2	887.5
10°	888.0	887.7	887.4	887.0	886.7	885.7	883.9	882.2	880.4	878.7	880.0
12.5°	878.8	878.3	877.7	877.1	876.6	875.4	873.8	872.2	870.5	868.9	870.0
15°	861.5	861.0	860.5	860.1	859.6	858.5	856.8	855.0	853.2	851.5	852.2
17.5°	841.6	840.9	840.2	839.5	838.8	837.5	835.8	833.9	832.1	830.3	831.2
20°	825.0	824.6	824.3	824.1	823.7	822.6	820.5	818.4	816.3	814.3	815.4
22.5°	808.3	807.8	807.2	806.6	806.1	804.8	802.9	801.0	799.0	797.0	797.8
25°	782.0	781.2	780.4	779.7	778.8	777.4	775.3	773.3	771.2	769.1	769.5
27.5°	751.2	750.7	750.3	749.8	749.3	748.0	745.8	743.8	741.6	739.5	739.5
30°	731.1	730.7	730.2	729.7	729.2	727.8	725.5	723.0	720.7	718.3	717.9
32.5°	709.4	708.7	707.9	707.2	706.4	705.0	702.9	700.8	698.6	696.5	696.0
35°	675.3	674.7	674.0	673.4	672.8	671.4	669.1	666.8	664.7	662.4	661.7
37.5°	639.9	639.1	638.4	637.5	636.8	635.3	633.2	631.1	629.0	626.9	625.8
40°	615.9	615.1	614.3	613.5	612.7	611.1	609.0	606.7	604.5	602.3	600.9
42.5°	590.1	589.5	588.7	588.1	587.4	586.0	583.7	581.5	579.3	577.0	575.8
45°	552.9	552.2	551.6	550.9	550.4	549.0	547.1	545.3	543.3	541.4	539.5
47.5°	512.7	512.7	512.8	512.8	512.8	511.7	509.4	507.2	504.9	502.6	500.7
50°	487.0	486.4	486.0	485.5	485.0	483.9	481.9	480.0	478.2	476.3	474.2
52.5°	460.6	460.2	460.0	459.6	459.2	458.0	456.0	453.9	451.9	449.9	448.1
55°	421.1	420.6	420.1	419.6	419.1	417.8	415.6	413.4	411.1	408.9	407.5
57.5°	379.4	379.2	378.9	378.6	378.4	377.3	375.4	373.5	371.6	369.9	368.0
60°	353.1	352.4	351.8	351.1	350.5	349.3	347.6	345.8	344.0	342.3	340.7
62.5°	325.6	325.1	324.5	324.0	323.5	322.5	321.0	319.5	318.0	316.5	314.8
65°	284.3	284.0	283.7	283.3	283.0	282.0	280.2	278.5	276.7	275.0	273.5
67.5°	244.3	243.6	243.0	242.3	241.7	240.7	239.4	238.1	236.8	235.4	234.2
70°	219.1	218.4	217.5	216.8	215.9	214.8	213.4	212.0	210.6	209.2	208.1
72.5°	191.6	191.1	190.6	190.0	189.5	188.7	187.8	186.9	186.0	185.0	184.0
75°	151.1	150.8	150.4	150.1	149.9	149.3	148.5	147.7	146.8	146.1	145.6
77.5°	113.8	113.6	113.5	113.3	113.2	112.9	112.4	112.1	111.6	111.1	110.8
80°	90.2	90.2	90.2	90.2	90.2	90.1	89.7	89.4	89.2	88.8	88.6
82.5°	69.7	69.4	69.1	68.8	68.6	68.4	68.3	68.3	68.2	68.1	67.9
85°	39.4	39.6	39.7	39.9	40.1	40.1	40.1	40.1	40.1	40.1	40.0
87.5°	15.6	16.0	16.3	16.7	17.0	17.2	17.4	17.5	17.7	17.9	18.1
90°	0.9	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1
92.5°	14.5	13.3	12.2	10.9	9.8	9.9	11.1	12.4	13.8	15.1	16.1
95°	53.6	53.0	52.4	51.7	51.2	46.8	38.9	30.9	23.0	15.1	16.1
97.5°	112.0	113.1	114.2	115.4	116.5	109.2	93.5	77.8	62.0	46.3	40.4
100°	157.1	157.8	158.4	159.0	159.7	160.4	161.3	162.1	162.9	163.7	132.6
102.5°	203.1	203.9	204.7	205.5	206.2	206.9	207.5	207.9	208.4	209.0	203.0
105°	276.6	277.5	278.3	279.2	280.0	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	353.1	353.1	353.1	353.1	353.1	353.3	353.7	354.1	354.6	355.0	355.1
110°	402.7	402.7	402.7	402.7	402.7	403.0	403.4	403.9	404.3	404.6	404.1



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.5	450.0	450.4	451.0	451.5	451.9	452.1	452.3	452.6	452.9	452.0
115°	519.5	520.6	521.6	522.6	523.7	524.3	524.5	524.7	524.9	525.1	524.3
117.5°	591.9	591.9	591.8	591.8	591.8	592.2	593.0	593.7	594.6	595.3	594.3
120°	637.2	636.9	636.7	636.5	636.3	636.5	637.2	637.7	638.4	639.0	638.6
122.5°	677.0	677.8	678.6	679.4	680.2	680.7	681.1	681.4	681.6	681.9	681.5
125°	738.8	740.2	741.7	743.2	744.6	745.4	745.4	745.4	745.4	745.4	744.5
127.5°	797.7	798.7	799.7	800.8	801.8	802.3	802.2	802.1	801.9	801.8	801.3
130°	833.8	834.9	835.9	837.0	838.0	838.6	838.9	839.1	839.2	839.4	838.9
132.5°	870.0	871.2	872.4	873.5	874.8	875.2	874.7	874.3	873.8	873.4	873.2
135°	921.3	922.6	923.9	925.1	926.3	926.8	926.3	926.0	925.5	925.1	924.6
137.5°	968.6	969.7	970.7	971.9	972.9	973.3	972.9	972.5	972.1	971.8	971.9
140°	999.5	999.8	1000.3	1000.7	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8
142.5°	1027.3	1027.6	1027.8	1028.0	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8
145°	1068.2	1068.6	1068.9	1069.4	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3
147.5°	1103.9	1103.8	1103.7	1103.6	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9
150°	1126.5	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9
152.5°	1148.3	1147.5	1146.5	1145.6	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5
155°	1176.4	1175.2	1173.8	1172.6	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3
157.5°	1198.0	1197.2	1196.6	1195.8	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5
160°	1213.1	1211.8	1210.6	1209.3	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2
162.5°	1225.1	1223.9	1222.6	1221.3	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6
165°	1241.3	1240.0	1238.8	1237.6	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8
167.5°	1253.4	1252.1	1250.8	1249.4	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0
170°	1260.1	1258.7	1257.2	1255.7	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1
172.5°	1264.6	1263.2	1261.7	1260.3	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2
175°	1269.5	1268.3	1267.1	1265.7	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5
177.5°	1271.8	1270.8	1269.8	1268.8	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	902.6	903.9	905.1	905.7	905.6	905.4	905.3	905.2
5°	898.1	899.5	900.9	901.5	901.4	901.3	901.1	900.9
7.5°	888.9	890.3	891.7	892.4	892.2	892.0	891.9	891.7
10°	881.3	882.5	883.8	884.4	884.2	884.0	883.8	883.7
12.5°	871.0	872.0	873.0	873.5	873.5	873.5	873.5	873.4
15°	853.1	853.8	854.7	855.1	855.1	855.1	855.1	855.1
17.5°	832.3	833.2	834.2	834.3	833.5	832.7	832.0	831.1
20°	816.4	817.6	818.7	818.9	818.0	817.3	816.4	815.7
22.5°	798.5	799.3	800.0	800.1	799.6	799.0	798.4	798.0
25°	769.8	770.1	770.4	770.3	769.9	769.4	768.9	768.5
27.5°	739.6	739.7	739.7	739.5	739.0	738.6	738.1	737.6
30°	717.7	717.4	717.0	716.6	716.1	715.7	715.2	714.7
32.5°	695.4	694.7	694.2	693.5	692.7	691.8	690.9	690.0
35°	660.8	660.1	659.2	658.2	657.0	655.6	654.4	653.1
37.5°	624.5	623.4	622.2	621.2	620.5	619.8	619.1	618.3
40°	599.4	597.9	596.5	595.6	595.1	594.7	594.2	593.7
42.5°	574.5	573.2	571.8	570.8	570.0	569.4	568.6	567.9
45°	537.5	535.6	533.8	532.5	532.1	531.6	531.1	530.7
47.5°	498.7	496.7	494.8	493.3	492.2	491.1	489.9	488.8
50°	472.1	470.0	468.0	466.4	465.2	464.1	463.0	461.9
52.5°	446.2	444.4	442.6	441.1	439.9	438.6	437.3	436.1
55°	406.0	404.6	403.2	401.9	400.8	399.6	398.6	397.5
57.5°	366.1	364.3	362.4	361.2	360.6	360.0	359.4	358.8
60°	339.1	337.5	335.9	334.6	333.5	332.3	331.2	330.2
62.5°	313.1	311.4	309.6	308.4	307.6	306.6	305.8	304.9
65°	272.1	270.7	269.3	268.2	267.6	266.9	266.4	265.7
67.5°	233.1	231.9	230.6	229.8	229.4	229.0	228.7	228.3
70°	207.2	206.2	205.3	204.5	203.9	203.2	202.6	202.0
72.5°	182.9	181.8	180.7	179.8	179.2	178.6	178.0	177.3
75°	145.2	144.7	144.2	143.6	143.0	142.3	141.8	141.1
77.5°	110.6	110.3	110.0	109.6	109.1	108.8	108.3	107.8
80°	88.5	88.3	88.1	87.9	87.6	87.3	87.0	86.6
82.5°	67.6	67.3	67.0	66.8	66.8	66.7	66.6	66.6
85°	39.8	39.6	39.5	39.2	38.9	38.5	38.3	38.0
87.5°	18.3	18.6	18.8	18.8	18.7	18.6	18.4	18.3
90°	17.2	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	17.2	18.2	19.2	19.9	20.2	20.5	20.8	21.1
95°	17.2	18.2	19.2	19.8	19.8	19.8	19.8	19.8
97.5°	34.5	28.7	22.7	19.8	19.8	19.8	19.8	19.8
100°	101.4	70.3	39.1	23.1	22.2	21.4	20.6	19.8
102.5°	197.1	191.2	185.3	175.3	161.1	146.8	132.6	118.4
105°	280.4	280.4	280.4	280.3	280.1	279.9	279.7	279.5
107.5°	355.1	355.2	355.2	354.9	354.2	353.6	353.0	352.3
110°	403.4	402.7	402.2	402.0	402.2	402.4	402.6	402.7



TEST NUMBER: P333193-830

CATALOG NUMBER: S125DIP-S610D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.3	450.4	449.7	449.1	448.8	448.6	448.3	448.0
115°	523.5	522.6	521.8	520.8	519.5	518.2	517.0	515.8
117.5°	593.1	592.1	591.0	590.1	589.7	589.1	588.5	588.0
120°	638.2	637.7	637.3	636.6	635.6	634.5	633.5	632.4
122.5°	681.1	680.7	680.2	679.4	678.3	677.0	675.8	674.6
125°	743.7	742.8	742.0	741.3	740.6	740.0	739.4	738.8
127.5°	800.9	800.4	799.9	799.0	797.4	795.9	794.4	792.8
130°	838.2	837.5	837.0	836.1	835.1	834.1	833.0	831.9
132.5°	873.1	873.0	872.8	872.2	871.2	870.2	869.1	868.1
135°	924.3	923.9	923.4	922.6	921.3	920.1	918.8	917.6
137.5°	971.9	972.0	972.1	971.6	970.5	969.4	968.4	967.2
140°	1001.3	1001.6	1002.0	1001.6	1000.4	999.1	997.9	996.6
142.5°	1029.9	1030.0	1030.1	1029.5	1028.2	1027.0	1025.8	1024.4
145°	1070.4	1070.6	1070.8	1070.4	1069.1	1067.8	1066.6	1065.4
147.5°	1105.1	1105.4	1105.7	1105.0	1103.5	1102.0	1100.5	1099.0
150°	1127.4	1127.8	1128.1	1127.6	1125.9	1124.2	1122.5	1120.9
152.5°	1146.9	1147.4	1147.7	1147.2	1145.7	1144.2	1142.6	1141.1
155°	1173.8	1174.5	1175.2	1174.6	1172.9	1171.2	1169.6	1167.9
157.5°	1196.2	1196.8	1197.5	1197.0	1195.3	1193.6	1191.9	1190.3
160°	1210.0	1210.9	1211.7	1211.3	1209.7	1208.0	1206.3	1204.6
162.5°	1222.8	1223.9	1225.1	1224.7	1222.9	1221.1	1219.3	1217.4
165°	1239.1	1240.4	1241.6	1241.4	1239.7	1238.0	1236.4	1234.7
167.5°	1251.5	1253.0	1254.5	1254.3	1252.5	1250.6	1248.7	1246.8
170°	1257.8	1259.5	1261.2	1261.0	1259.1	1257.4	1255.5	1253.6
172.5°	1262.7	1264.2	1265.7	1265.6	1263.7	1261.8	1259.9	1258.1
175°	1268.2	1269.9	1271.5	1271.4	1269.5	1267.6	1265.7	1263.9
177.5°	1270.4	1271.6	1272.7	1272.6	1271.3	1270.0	1268.7	1267.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5

(END OF REPORT)