

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333197-830

Luminaire Tested: **S125DIP-S610D1205U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333197-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1205U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6310.8 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	72	62	54	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5448	5448	5448	5448
5°	6309	5466	4786	5466
10°	7340	5438	4194	5438
15°	8125	5398	3869	5398
20°	9095	5335	3608	5335
25°	10655	5264	3480	5264
30°	11508	5193	3370	5193
35°	9462	5062	3297	5062
40°	6726	4878	3217	4878
45°	5167	4631	3172	4631
50°	4410	4324	3166	4324
55°	3926	4023	3193	4023
60°	3543	3695	3274	3695
65°	3272	3365	3359	3365
70°	2974	3021	3408	3021
75°	2628	2662	3376	2662
80°	2213	2168	3087	2168
85°	1756	1564	2490	1564



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.3
10°-20°	241.8	3.8
20°-30°	392.6	6.2
30°-40°	478.9	7.6
40°-50°	435.7	6.9
50°-60°	347.0	5.5
60°-70°	241.7	3.8
70°-80°	128.9	2.0
80°-90°	35.6	0.6
90°-100°	94.3	1.5
100°-110°	278.4	4.4
110°-120°	471.5	7.5
120°-130°	620.5	9.8
130°-140°	695.3	11.0
140°-150°	681.4	10.8
150°-160°	572.4	9.1
160°-170°	380.5	6.0
170°-180°	133.1	2.1
0°-30°	715.6	11.3
0°-40°	1194.5	18.9
0°-60°	1977.3	31.3
0°-90°	2383.5	37.8
90°-120°	844.1	13.4
90°-150°	2841.4	45.0
90°-180°	3927.0	62.2
0°-180°	6310.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	844	844	844	844	844	
5°	973	843	738	843	973	98
15°	1215	807	579	807	1215	348
25°	1495	739	488	739	1495	683
35°	1200	642	418	642	1200	735
45°	566	507	347	507	566	453
55°	349	357	284	357	349	314
65°	214	220	220	220	214	212
75°	105	107	135	107	105	113
85°	24	21	34	21	24	28
90°	26	1	26	1	26	16
95°	94	71	94	71	94	96
105°	272	250	272	250	272	288
115°	476	472	476	472	476	471
125°	693	689	693	689	693	619
135°	899	896	899	896	899	694
145°	1090	1085	1090	1085	1090	680
155°	1242	1242	1242	1242	1242	572
165°	1347	1350	1347	1350	1347	380
175°	1399	1404	1399	1404	1399	133
180°	1407	1407	1407	1407	1407	



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	892.3	891.1	889.9	887.7	889.4	884.5	882.2	878.3	873.4	871.7	869.6
5°	973.2	975.0	976.8	969.2	970.0	965.0	953.5	944.1	936.7	927.0	920.2
7.5°	1070.5	1066.3	1066.0	1061.1	1052.7	1046.0	1034.0	1018.6	1003.8	986.9	973.0
10°	1119.3	1119.6	1116.4	1110.7	1101.7	1095.2	1079.5	1064.5	1046.2	1024.7	1009.4
12.5°	1155.9	1157.4	1153.4	1145.7	1141.2	1126.8	1114.5	1096.6	1074.9	1057.7	1034.3
15°	1215.2	1211.3	1208.4	1198.7	1191.2	1176.2	1156.5	1137.8	1114.3	1092.4	1070.5
17.5°	1272.3	1275.5	1270.2	1261.3	1238.0	1220.4	1194.0	1168.6	1139.1	1109.8	1083.7
20°	1323.3	1326.3	1318.0	1302.6	1274.7	1257.1	1222.4	1189.4	1155.5	1117.9	1089.2
22.5°	1387.0	1384.7	1373.6	1350.1	1326.0	1293.5	1255.9	1215.8	1173.2	1130.7	1092.6
25°	1495.2	1480.2	1473.4	1444.4	1412.5	1364.9	1313.3	1254.6	1201.6	1145.4	1096.7
27.5°	1555.2	1550.5	1542.9	1522.7	1489.2	1438.3	1377.5	1306.0	1231.1	1160.3	1096.5
30°	1543.2	1543.9	1544.6	1538.1	1516.7	1478.4	1417.9	1340.9	1252.1	1172.2	1098.5
32.5°	1436.6	1449.6	1462.2	1476.9	1482.9	1475.6	1437.7	1368.1	1276.8	1186.0	1097.3
35°	1200.1	1204.1	1244.6	1284.7	1339.1	1381.4	1409.7	1378.8	1301.8	1197.7	1096.0
37.5°	935.8	955.2	983.2	1028.5	1107.0	1177.3	1267.8	1309.4	1284.5	1201.5	1093.4
40°	797.8	815.7	833.9	880.1	946.3	1031.5	1134.3	1222.0	1242.5	1189.4	1084.9
42.5°	691.2	705.4	725.7	760.3	815.7	891.2	989.4	1104.0	1174.5	1154.5	1066.9
45°	565.7	574.7	590.4	618.0	658.1	717.2	803.8	929.2	1038.3	1074.5	1024.0
47.5°	484.2	484.2	496.4	515.5	544.4	594.6	658.6	756.9	873.5	959.8	955.7
50°	438.9	437.2	446.9	463.4	486.3	519.5	580.8	659.2	771.3	869.0	896.2
52.5°	400.0	400.2	406.1	418.3	437.5	466.0	511.7	582.4	678.2	778.4	829.7
55°	348.7	347.3	354.1	362.3	376.4	394.9	427.9	481.9	559.6	658.5	725.0
57.5°	301.8	305.7	308.4	314.1	325.7	338.2	366.0	405.7	467.3	552.1	622.5
60°	274.3	278.2	280.3	286.1	295.4	306.1	327.6	359.9	411.8	484.8	554.6
62.5°	249.6	252.7	253.4	258.5	266.2	276.6	293.5	320.6	361.7	425.5	493.9
65°	214.1	214.1	215.6	220.9	224.5	233.8	246.7	266.4	299.4	349.1	407.5
67.5°	179.8	181.6	181.3	183.6	186.9	194.2	203.4	219.6	244.0	280.3	327.1
70°	157.5	159.0	158.6	160.4	164.0	168.6	176.2	191.5	209.1	240.3	280.3
72.5°	137.5	138.1	137.1	139.5	141.7	145.7	154.1	162.3	178.7	205.0	238.0
75°	105.3	105.9	106.7	108.1	110.3	112.4	116.7	125.0	135.7	155.4	176.5
77.5°	78.9	77.6	79.3	79.1	80.3	81.9	85.7	90.1	98.9	111.3	127.7
80°	59.5	59.8	59.8	60.1	61.9	63.1	66.3	69.5	76.3	85.6	97.0
82.5°	43.4	44.3	43.7	44.4	45.9	46.7	48.4	51.1	55.0	62.4	70.7
85°	23.7	21.9	22.5	23.3	23.3	23.7	25.1	26.1	28.3	31.1	34.4
87.5°	12.2	12.5	12.7	12.5	12.7	12.5	13.4	13.2	13.8	14.4	15.2
90°	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0	18.8	17.5	15.8
92.5°	51.7	51.2	50.6	50.0	49.6	48.4	46.8	45.2	43.6	42.0	40.0
95°	94.2	93.7	93.2	92.7	92.3	91.1	89.4	87.8	86.1	84.4	81.9
97.5°	142.8	142.5	142.2	141.9	141.7	140.7	139.1	137.5	135.9	134.3	130.9
100°	179.6	179.2	178.6	178.1	177.7	176.3	174.2	171.9	169.8	167.6	164.4
102.5°	216.4	215.7	215.1	214.4	213.7	212.2	209.8	207.4	205.0	202.6	201.0
105°	271.6	270.9	270.1	269.5	268.7	267.6	266.2	264.7	263.3	261.7	260.3
107.5°	328.1	328.2	328.3	328.3	328.4	328.0	327.3	326.5	325.8	325.1	324.0
110°	370.2	370.4	370.7	370.9	371.2	370.9	370.2	369.5	368.7	368.0	367.3



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	411.4	411.8	412.3	412.7	413.1	413.2	412.8	412.6	412.2	411.8	410.9
115°	476.5	476.6	476.9	477.2	477.4	477.7	477.9	478.2	478.4	478.6	478.2
117.5°	540.0	540.9	542.0	542.9	543.8	544.2	544.0	543.8	543.7	543.5	543.0
120°	583.8	584.8	585.7	586.7	587.7	588.1	588.1	588.1	588.1	588.1	588.0
122.5°	627.6	628.4	629.1	629.9	630.7	631.2	631.4	631.6	631.8	632.0	631.3
125°	693.3	693.5	693.8	694.1	694.3	694.7	695.1	695.6	696.1	696.6	696.4
127.5°	756.4	756.9	757.3	757.9	758.4	758.7	758.9	759.2	759.4	759.7	759.4
130°	798.4	798.9	799.5	799.9	800.4	800.8	801.0	801.3	801.5	801.7	801.3
132.5°	837.9	838.6	839.2	839.9	840.7	841.0	841.3	841.6	841.8	842.1	842.2
135°	899.2	900.2	901.2	902.1	903.1	903.6	903.6	903.6	903.6	903.6	903.3
137.5°	959.2	960.5	961.7	962.9	964.1	964.6	964.3	964.0	963.7	963.4	962.9
140°	997.8	999.0	1000.2	1001.5	1002.7	1003.1	1002.6	1002.0	1001.5	1001.1	1000.3
142.5°	1034.6	1035.9	1037.1	1038.2	1039.4	1039.9	1039.6	1039.3	1039.1	1038.8	1037.8
145°	1089.8	1090.5	1091.3	1092.0	1092.7	1093.1	1093.1	1093.1	1093.1	1093.1	1092.3
147.5°	1136.9	1138.6	1140.2	1141.9	1143.5	1144.1	1143.5	1142.9	1142.3	1141.7	1141.1
150°	1172.0	1172.4	1172.9	1173.4	1173.9	1174.1	1174.1	1174.1	1174.1	1174.1	1173.2
152.5°	1200.9	1201.7	1202.6	1203.5	1204.4	1204.5	1203.9	1203.3	1202.8	1202.2	1201.8
155°	1242.1	1243.3	1244.4	1245.7	1246.9	1247.1	1246.0	1245.1	1244.2	1243.1	1242.9
157.5°	1276.5	1278.1	1279.7	1281.3	1282.9	1283.2	1282.2	1281.2	1280.3	1279.3	1279.0
160°	1300.1	1301.3	1302.5	1303.7	1305.0	1305.0	1304.1	1303.2	1302.1	1301.2	1301.0
162.5°	1320.2	1321.6	1323.0	1324.5	1325.9	1326.1	1324.8	1323.7	1322.5	1321.4	1321.3
165°	1347.2	1348.7	1350.1	1351.6	1353.0	1353.3	1352.3	1351.3	1350.4	1349.3	1349.2
167.5°	1368.7	1370.2	1371.7	1373.2	1374.7	1374.7	1373.3	1371.8	1370.4	1368.9	1368.9
170°	1380.1	1381.8	1383.5	1385.2	1386.9	1387.0	1385.5	1384.0	1382.6	1381.1	1381.1
172.5°	1389.7	1391.2	1392.7	1394.2	1395.7	1395.7	1394.3	1392.8	1391.4	1389.9	1389.9
175°	1398.6	1400.3	1402.1	1403.8	1405.5	1405.6	1404.1	1402.7	1401.2	1399.8	1399.8
177.5°	1403.9	1405.3	1406.7	1408.1	1409.4	1409.5	1408.3	1407.1	1406.0	1404.8	1405.0
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	867.9	865.9	863.7	859.6	854.7	852.2	848.2	845.6	840.4	836.1	831.5
5°	911.9	902.7	894.1	883.0	870.8	862.9	853.6	843.2	832.5	821.3	809.2
7.5°	957.5	941.1	923.2	903.9	885.1	867.8	851.2	835.0	819.8	801.4	785.9
10°	988.3	967.4	945.3	919.1	893.7	871.5	848.9	829.2	809.2	787.7	768.7
12.5°	1018.9	991.2	959.9	931.1	900.6	873.8	847.3	822.1	796.9	773.1	751.0
15°	1040.5	1016.2	987.1	946.3	911.9	875.1	840.0	807.4	776.9	750.5	722.6
17.5°	1054.7	1023.4	992.2	953.1	908.0	866.8	827.0	789.8	755.4	721.8	694.9
20°	1057.3	1025.1	992.5	954.2	908.0	860.7	821.0	776.3	739.3	704.6	671.7
22.5°	1056.5	1019.9	984.5	945.0	900.0	856.5	808.4	762.8	722.7	688.6	654.2
25°	1048.4	1009.4	965.0	925.2	880.8	834.6	785.9	738.7	697.9	658.8	624.8
27.5°	1041.6	991.0	940.8	894.4	851.5	809.2	762.6	714.2	668.9	629.3	597.3
30°	1033.3	977.8	921.2	872.9	828.9	787.7	743.7	696.4	649.1	610.5	576.1
32.5°	1025.9	961.2	901.5	848.9	802.3	762.2	721.6	676.7	630.3	591.0	556.7
35°	1011.5	936.7	868.3	808.8	759.0	717.9	683.9	642.0	599.4	561.4	528.5
37.5°	993.3	904.5	831.0	768.7	714.2	670.8	639.1	607.0	566.1	529.5	499.7
40°	978.9	881.6	803.8	740.1	683.5	638.4	609.1	578.6	544.6	510.6	479.1
42.5°	960.8	860.9	776.3	707.8	651.8	607.8	576.9	551.1	521.1	489.4	460.1
45°	927.7	823.5	731.9	658.1	601.5	558.2	526.3	507.0	484.5	454.4	429.7
47.5°	878.9	778.6	683.8	607.7	549.3	509.2	479.3	460.7	444.9	422.5	400.1
50°	835.7	745.1	649.1	573.6	515.2	474.8	447.2	430.4	416.8	399.5	380.6
52.5°	787.3	702.9	615.1	540.4	482.6	442.7	415.7	400.9	389.6	377.2	358.5
55°	710.4	638.8	557.1	486.3	432.9	393.9	370.2	357.3	348.0	338.7	327.3
57.5°	625.7	569.7	497.3	432.5	383.4	347.9	325.8	313.3	306.0	301.2	294.5
60°	566.1	518.1	455.8	396.7	348.7	317.3	295.8	286.1	280.0	276.1	271.1
62.5°	510.8	471.4	413.7	359.8	317.8	288.0	268.8	259.5	253.6	251.8	247.5
65°	429.3	398.9	351.3	306.5	270.7	245.2	229.1	220.2	216.6	214.4	214.8
67.5°	349.0	330.5	292.3	254.1	225.5	204.2	191.2	184.4	182.6	179.7	179.6
70°	300.0	286.1	253.8	220.6	195.1	178.7	167.2	160.0	158.3	156.8	156.5
72.5°	256.7	244.6	216.6	189.9	167.1	152.6	143.2	138.8	135.9	135.1	135.0
75°	193.0	186.2	164.0	142.9	127.1	117.1	110.7	106.7	104.5	104.2	104.5
77.5°	137.2	131.3	117.2	102.2	92.3	84.6	79.2	77.9	75.4	75.5	75.1
80°	103.1	99.2	90.2	78.4	70.2	63.7	60.9	58.3	57.7	56.6	57.7
82.5°	74.7	70.5	64.5	56.9	50.1	46.3	43.4	42.6	42.1	41.7	41.8
85°	36.9	37.2	33.6	27.9	25.1	22.9	21.1	21.1	20.7	20.5	20.7
87.5°	15.5	14.5	13.0	11.8	10.0	8.8	8.0	7.9	7.4	7.5	8.3
90°	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1	3.0	5.0	7.0
92.5°	37.9	35.8	33.6	32.0	30.6	29.2	27.9	26.5	27.9	29.2	30.6
95°	79.5	77.0	74.6	73.1	72.7	72.2	71.6	71.2	71.6	72.2	72.7
97.5°	127.5	124.2	120.8	119.0	118.9	118.7	118.5	118.3	118.5	118.7	118.9
100°	161.3	158.1	155.0	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4
102.5°	199.4	197.8	196.2	194.9	194.0	192.9	192.0	191.1	192.0	192.9	194.0
105°	258.8	257.4	255.9	254.6	253.4	252.1	250.9	249.7	250.9	252.1	253.4
107.5°	322.8	321.7	320.6	319.4	318.2	317.0	315.8	314.5	315.8	317.0	318.2
110°	366.6	365.8	365.0	364.1	362.9	361.7	360.4	359.3	360.4	361.7	362.9



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.0	409.1	408.1	407.4	406.7	406.0	405.5	404.8	405.5	406.0	406.7
115°	477.7	477.2	476.6	476.0	474.9	474.0	473.1	472.0	473.1	474.0	474.9
117.5°	542.6	542.2	541.7	541.3	540.8	540.5	540.0	539.5	540.0	540.5	540.8
120°	587.7	587.4	587.2	586.4	585.2	584.0	582.8	581.5	582.8	584.0	585.2
122.5°	630.7	630.1	629.4	628.9	628.5	628.0	627.6	627.2	627.6	628.0	628.5
125°	696.1	695.9	695.6	694.7	693.3	691.8	690.4	688.9	690.4	691.8	693.3
127.5°	759.1	758.8	758.6	758.0	757.1	756.3	755.4	754.7	755.4	756.3	757.1
130°	800.8	800.3	799.8	798.9	797.8	796.5	795.3	794.1	795.3	796.5	797.8
132.5°	842.3	842.4	842.4	841.5	839.5	837.5	835.5	833.5	835.5	837.5	839.5
135°	903.1	902.9	902.7	901.8	900.3	898.9	897.4	896.0	897.4	898.9	900.3
137.5°	962.3	961.8	961.3	960.3	958.8	957.4	956.0	954.6	956.0	957.4	958.8
140°	999.7	998.9	998.2	997.2	996.0	994.8	993.5	992.3	993.5	994.8	996.0
142.5°	1036.9	1035.9	1035.1	1034.1	1033.0	1032.1	1031.0	1030.0	1031.0	1032.1	1033.0
145°	1091.7	1090.9	1090.1	1089.3	1088.4	1087.4	1086.4	1085.4	1086.4	1087.4	1088.4
147.5°	1140.6	1140.0	1139.3	1138.8	1138.3	1137.7	1137.2	1136.7	1137.2	1137.7	1138.3
150°	1172.1	1171.2	1170.3	1169.9	1170.2	1170.4	1170.6	1170.8	1170.6	1170.4	1170.2
152.5°	1201.4	1201.0	1200.6	1200.2	1200.0	1199.6	1199.2	1198.9	1199.2	1199.6	1200.0
155°	1242.6	1242.5	1242.2	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1
157.5°	1278.8	1278.6	1278.3	1278.5	1279.0	1279.5	1280.1	1280.6	1280.1	1279.5	1279.0
160°	1300.7	1300.4	1300.2	1300.4	1301.2	1301.9	1302.7	1303.3	1302.7	1301.9	1301.2
162.5°	1321.3	1321.2	1321.2	1321.4	1321.9	1322.5	1323.0	1323.5	1323.0	1322.5	1321.9
165°	1348.9	1348.7	1348.4	1348.5	1349.1	1349.5	1350.0	1350.5	1350.0	1349.5	1349.1
167.5°	1368.9	1368.9	1368.9	1369.3	1370.4	1371.3	1372.2	1373.3	1372.2	1371.3	1370.4
170°	1381.1	1381.1	1381.1	1381.7	1382.6	1383.6	1384.6	1385.5	1384.6	1383.6	1382.6
172.5°	1389.9	1389.9	1389.9	1390.4	1391.4	1392.3	1393.4	1394.3	1393.4	1392.3	1391.4
175°	1399.8	1399.8	1399.8	1400.2	1401.2	1402.2	1403.2	1404.1	1403.2	1402.2	1401.2
177.5°	1405.2	1405.4	1405.6	1406.1	1406.8	1407.6	1408.4	1409.2	1408.4	1407.6	1406.8
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	829.0	825.8	823.2	817.5	814.4	810.0	806.6	810.3	806.3	808.0	805.5
5°	803.1	793.1	785.9	775.5	766.6	758.4	752.2	751.2	748.3	746.9	742.6
7.5°	772.0	759.5	747.2	733.6	722.1	710.5	702.9	696.8	692.8	687.4	683.7
10°	753.7	736.9	722.6	706.1	691.7	679.2	669.2	664.2	659.5	652.7	650.3
12.5°	731.0	713.7	696.2	678.5	664.9	650.8	642.2	634.7	631.5	623.8	623.0
15°	703.9	677.8	660.6	642.7	623.7	612.3	605.1	596.9	593.3	588.0	584.0
17.5°	671.6	648.2	626.7	608.2	591.9	582.3	573.3	567.7	561.6	558.1	551.6
20°	648.1	625.8	604.4	584.7	572.1	561.1	553.9	548.6	542.1	540.3	533.9
22.5°	628.3	603.8	583.2	566.7	553.0	540.5	532.7	529.0	524.6	519.1	517.8
25°	596.2	570.7	553.2	536.7	524.5	513.1	507.7	503.0	498.8	494.8	493.4
27.5°	568.4	545.6	524.8	509.9	499.4	488.9	484.2	478.5	475.3	472.2	468.3
30°	548.9	525.7	507.4	493.0	481.5	472.3	467.2	463.4	460.4	457.6	455.4
32.5°	528.9	507.3	489.6	475.6	464.1	457.1	452.6	449.9	446.7	443.3	440.5
35°	502.4	478.7	461.6	449.3	440.4	435.0	430.0	427.5	424.0	424.0	421.0
37.5°	472.5	452.0	436.9	425.7	417.7	412.9	407.6	405.9	403.5	402.0	401.1
40°	454.7	435.7	421.4	410.3	401.7	397.8	393.5	390.6	389.2	387.4	386.7
42.5°	436.4	418.3	404.5	394.3	386.8	383.4	379.5	377.5	374.6	372.2	371.8
45°	408.5	391.0	378.4	370.2	363.8	359.9	357.3	353.1	351.6	348.7	348.4
47.5°	382.1	365.2	353.0	346.2	340.5	337.3	333.4	329.1	327.4	326.0	325.9
50°	362.3	346.9	335.5	329.0	323.7	319.1	315.1	312.3	311.1	311.1	311.9
52.5°	342.3	329.2	319.4	311.6	306.5	301.5	297.9	296.1	294.5	296.2	297.6
55°	312.9	299.7	292.6	285.0	280.0	274.3	272.5	271.7	270.7	273.5	274.9
57.5°	281.8	272.6	264.2	256.7	252.2	248.9	246.5	246.1	248.1	249.4	254.1
60°	262.1	251.4	243.8	238.1	232.7	230.5	229.9	229.1	230.5	234.5	240.6
62.5°	240.3	231.6	223.5	219.2	215.3	211.7	211.5	212.0	214.8	219.3	225.5
65°	208.4	200.9	195.5	190.5	187.3	185.1	185.9	187.3	190.5	196.6	203.4
67.5°	176.0	170.8	166.0	161.9	158.8	158.8	159.6	161.7	165.5	172.5	178.7
70°	155.0	149.3	145.3	143.5	141.1	139.7	141.8	145.3	148.5	155.0	160.4
72.5°	134.1	129.2	126.2	125.0	123.9	122.7	123.5	127.3	131.7	138.2	144.4
75°	103.1	101.3	99.2	97.7	96.7	97.4	98.1	101.7	105.3	112.1	119.2
77.5°	75.3	73.4	72.1	71.7	71.2	71.5	73.5	76.2	79.7	84.6	90.1
80°	56.9	56.2	55.5	55.1	55.1	55.5	58.3	60.1	63.3	68.1	72.3
82.5°	41.5	41.0	40.9	40.8	41.1	41.2	42.9	45.2	47.9	51.5	55.1
85°	21.9	21.1	22.2	22.5	21.9	22.9	23.7	25.1	26.1	27.9	29.7
87.5°	9.0	9.9	9.9	10.6	10.9	11.8	11.8	13.2	13.9	14.8	14.7
90°	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0	21.2	22.4	23.4
92.5°	32.0	33.6	35.8	37.9	40.0	42.0	43.6	45.2	46.8	48.4	49.6
95°	73.1	74.6	77.0	79.5	81.9	84.4	86.1	87.8	89.4	91.1	92.3
97.5°	119.0	120.8	124.2	127.5	130.9	134.3	135.9	137.5	139.1	140.7	141.7
100°	153.4	155.0	158.1	161.3	164.4	167.6	169.8	171.9	174.2	176.3	177.7
102.5°	194.9	196.2	197.8	199.4	201.0	202.6	205.0	207.4	209.8	212.2	213.7
105°	254.6	255.9	257.4	258.8	260.3	261.7	263.3	264.7	266.2	267.6	268.7
107.5°	319.4	320.6	321.7	322.8	324.0	325.1	325.8	326.5	327.3	328.0	328.4
110°	364.1	365.0	365.8	366.6	367.3	368.0	368.7	369.5	370.2	370.9	371.2



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	407.4	408.1	409.1	410.0	410.9	411.8	412.2	412.6	412.8	413.2	413.1
115°	476.0	476.6	477.2	477.7	478.2	478.6	478.4	478.2	477.9	477.7	477.4
117.5°	541.3	541.7	542.2	542.6	543.0	543.5	543.7	543.8	544.0	544.2	543.8
120°	586.4	587.2	587.4	587.7	588.0	588.1	588.1	588.1	588.1	588.1	587.7
122.5°	628.9	629.4	630.1	630.7	631.3	632.0	631.8	631.6	631.4	631.2	630.7
125°	694.7	695.6	695.9	696.1	696.4	696.6	696.1	695.6	695.1	694.7	694.3
127.5°	758.0	758.6	758.8	759.1	759.4	759.7	759.4	759.2	758.9	758.7	758.4
130°	798.9	799.8	800.3	800.8	801.3	801.7	801.5	801.3	801.0	800.8	800.4
132.5°	841.5	842.4	842.4	842.3	842.2	842.1	841.8	841.6	841.3	841.0	840.7
135°	901.8	902.7	902.9	903.1	903.3	903.6	903.6	903.6	903.6	903.6	903.1
137.5°	960.3	961.3	961.8	962.3	962.9	963.4	963.7	964.0	964.3	964.6	964.1
140°	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5	1002.0	1002.6	1003.1	1002.7
142.5°	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1	1039.3	1039.6	1039.9	1039.4
145°	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1	1093.1	1093.1	1093.1	1092.7
147.5°	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3	1142.9	1143.5	1144.1	1143.5
150°	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1	1174.1	1174.1	1174.1	1173.9
152.5°	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8	1203.3	1203.9	1204.5	1204.4
155°	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2	1245.1	1246.0	1247.1	1246.9
157.5°	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3	1281.2	1282.2	1283.2	1282.9
160°	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1	1303.2	1304.1	1305.0	1305.0
162.5°	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5	1323.7	1324.8	1326.1	1325.9
165°	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4	1351.3	1352.3	1353.3	1353.0
167.5°	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4	1371.8	1373.3	1374.7	1374.7
170°	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6	1384.0	1385.5	1387.0	1386.9
172.5°	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4	1392.8	1394.3	1395.7	1395.7
175°	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2	1402.7	1404.1	1405.6	1405.5
177.5°	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0	1407.1	1408.3	1409.5	1409.4
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	803.7	805.8	804.1	806.3	804.1	805.8	803.7	805.5	808.0	806.3	810.3
5°	740.8	737.5	739.7	738.3	739.7	737.5	740.8	742.6	746.9	748.3	751.2
7.5°	682.7	679.6	676.1	674.4	676.1	679.6	682.7	683.7	687.4	692.8	696.8
10°	646.3	642.3	642.0	639.5	642.0	642.3	646.3	650.3	652.7	659.5	664.2
12.5°	619.6	616.0	611.9	610.9	611.9	616.0	619.6	623.0	623.8	631.5	634.7
15°	581.8	579.0	576.5	578.6	576.5	579.0	581.8	584.0	588.0	593.3	596.9
17.5°	550.4	548.0	547.6	545.0	547.6	548.0	550.4	551.6	558.1	561.6	567.7
20°	530.7	528.9	529.5	524.9	529.5	528.9	530.7	533.9	540.3	542.1	548.6
22.5°	514.9	511.3	511.0	510.0	511.0	511.3	514.9	517.8	519.1	524.6	529.0
25°	490.2	488.4	486.6	488.4	486.6	488.4	490.2	493.4	494.8	498.8	503.0
27.5°	468.6	466.5	466.0	466.2	466.0	466.5	468.6	468.3	472.2	475.3	478.5
30°	455.4	451.9	452.2	451.9	452.2	451.9	455.4	455.4	457.6	460.4	463.4
32.5°	441.1	438.7	438.2	437.5	438.2	438.7	441.1	440.5	443.3	446.7	449.9
35°	420.0	420.0	418.2	418.2	418.2	420.0	420.0	421.0	424.0	424.0	427.5
37.5°	400.1	399.8	398.7	398.9	398.7	399.8	400.1	401.1	402.0	403.5	405.9
40°	385.2	384.9	383.8	381.6	383.8	384.9	385.2	386.7	387.4	389.2	390.6
42.5°	371.0	369.8	369.2	368.5	369.2	369.8	371.0	371.8	372.2	374.6	377.5
45°	348.4	348.4	347.7	347.3	347.7	348.4	348.4	348.4	348.7	351.6	353.1
47.5°	326.5	327.2	328.5	328.3	328.5	327.2	326.5	325.9	326.0	327.4	329.1
50°	313.3	313.7	314.7	315.1	314.7	313.7	313.3	311.9	311.1	311.1	312.3
52.5°	298.7	300.8	302.1	301.9	302.1	300.8	298.7	297.6	296.2	294.5	296.1
55°	278.2	280.7	283.2	283.6	283.2	280.7	278.2	274.9	273.5	270.7	271.7
57.5°	258.0	261.5	264.1	264.9	264.1	261.5	258.0	254.1	249.4	248.1	246.1
60°	244.2	248.8	252.0	253.5	252.0	248.8	244.2	240.6	234.5	230.5	229.1
62.5°	231.0	236.2	239.5	239.8	239.5	236.2	231.0	225.5	219.3	214.8	212.0
65°	209.4	214.8	217.7	219.8	217.7	214.8	209.4	203.4	196.6	190.5	187.3
67.5°	186.2	191.6	194.8	196.5	194.8	191.6	186.2	178.7	172.5	165.5	161.7
70°	169.4	174.7	179.0	180.5	179.0	174.7	169.4	160.4	155.0	148.5	145.3
72.5°	152.8	157.5	161.0	162.7	161.0	157.5	152.8	144.4	138.2	131.7	127.3
75°	123.9	130.4	133.6	135.3	133.6	130.4	123.9	119.2	112.1	105.3	101.7
77.5°	95.6	101.4	103.3	104.2	103.3	101.4	95.6	90.1	84.6	79.7	76.2
80°	76.6	80.2	82.8	83.0	82.8	80.2	76.6	72.3	68.1	63.3	60.1
82.5°	58.9	61.8	62.7	63.6	62.7	61.8	58.9	55.1	51.5	47.9	45.2
85°	32.2	33.6	34.0	33.6	34.0	33.6	32.2	29.7	27.9	26.1	25.1
87.5°	15.5	15.3	15.5	16.1	15.5	15.3	15.5	14.7	14.8	13.9	13.2
90°	24.1	24.8	25.5	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0
92.5°	50.0	50.6	51.2	51.7	51.2	50.6	50.0	49.6	48.4	46.8	45.2
95°	92.7	93.2	93.7	94.2	93.7	93.2	92.7	92.3	91.1	89.4	87.8
97.5°	141.9	142.2	142.5	142.8	142.5	142.2	141.9	141.7	140.7	139.1	137.5
100°	178.1	178.6	179.2	179.6	179.2	178.6	178.1	177.7	176.3	174.2	171.9
102.5°	214.4	215.1	215.7	216.4	215.7	215.1	214.4	213.7	212.2	209.8	207.4
105°	269.5	270.1	270.9	271.6	270.9	270.1	269.5	268.7	267.6	266.2	264.7
107.5°	328.3	328.3	328.2	328.1	328.2	328.3	328.3	328.4	328.0	327.3	326.5
110°	370.9	370.7	370.4	370.2	370.4	370.7	370.9	371.2	370.9	370.2	369.5



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.7	412.3	411.8	411.4	411.8	412.3	412.7	413.1	413.2	412.8	412.6
115°	477.2	476.9	476.6	476.5	476.6	476.9	477.2	477.4	477.7	477.9	478.2
117.5°	542.9	542.0	540.9	540.0	540.9	542.0	542.9	543.8	544.2	544.0	543.8
120°	586.7	585.7	584.8	583.8	584.8	585.7	586.7	587.7	588.1	588.1	588.1
122.5°	629.9	629.1	628.4	627.6	628.4	629.1	629.9	630.7	631.2	631.4	631.6
125°	694.1	693.8	693.5	693.3	693.5	693.8	694.1	694.3	694.7	695.1	695.6
127.5°	757.9	757.3	756.9	756.4	756.9	757.3	757.9	758.4	758.7	758.9	759.2
130°	799.9	799.5	798.9	798.4	798.9	799.5	799.9	800.4	800.8	801.0	801.3
132.5°	839.9	839.2	838.6	837.9	838.6	839.2	839.9	840.7	841.0	841.3	841.6
135°	902.1	901.2	900.2	899.2	900.2	901.2	902.1	903.1	903.6	903.6	903.6
137.5°	962.9	961.7	960.5	959.2	960.5	961.7	962.9	964.1	964.6	964.3	964.0
140°	1001.5	1000.2	999.0	997.8	999.0	1000.2	1001.5	1002.7	1003.1	1002.6	1002.0
142.5°	1038.2	1037.1	1035.9	1034.6	1035.9	1037.1	1038.2	1039.4	1039.9	1039.6	1039.3
145°	1092.0	1091.3	1090.5	1089.8	1090.5	1091.3	1092.0	1092.7	1093.1	1093.1	1093.1
147.5°	1141.9	1140.2	1138.6	1136.9	1138.6	1140.2	1141.9	1143.5	1144.1	1143.5	1142.9
150°	1173.4	1172.9	1172.4	1172.0	1172.4	1172.9	1173.4	1173.9	1174.1	1174.1	1174.1
152.5°	1203.5	1202.6	1201.7	1200.9	1201.7	1202.6	1203.5	1204.4	1204.5	1203.9	1203.3
155°	1245.7	1244.4	1243.3	1242.1	1243.3	1244.4	1245.7	1246.9	1247.1	1246.0	1245.1
157.5°	1281.3	1279.7	1278.1	1276.5	1278.1	1279.7	1281.3	1282.9	1283.2	1282.2	1281.2
160°	1303.7	1302.5	1301.3	1300.1	1301.3	1302.5	1303.7	1305.0	1305.0	1304.1	1303.2
162.5°	1324.5	1323.0	1321.6	1320.2	1321.6	1323.0	1324.5	1325.9	1326.1	1324.8	1323.7
165°	1351.6	1350.1	1348.7	1347.2	1348.7	1350.1	1351.6	1353.0	1353.3	1352.3	1351.3
167.5°	1373.2	1371.7	1370.2	1368.7	1370.2	1371.7	1373.2	1374.7	1374.7	1373.3	1371.8
170°	1385.2	1383.5	1381.8	1380.1	1381.8	1383.5	1385.2	1386.9	1387.0	1385.5	1384.0
172.5°	1394.2	1392.7	1391.2	1389.7	1391.2	1392.7	1394.2	1395.7	1395.7	1394.3	1392.8
175°	1403.8	1402.1	1400.3	1398.6	1400.3	1402.1	1403.8	1405.5	1405.6	1404.1	1402.7
177.5°	1408.1	1406.7	1405.3	1403.9	1405.3	1406.7	1408.1	1409.4	1409.5	1408.3	1407.1
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	806.6	810.0	814.4	817.5	823.2	825.8	829.0	831.5	836.1	840.4	845.6
5°	752.2	758.4	766.6	775.5	785.9	793.1	803.1	809.2	821.3	832.5	843.2
7.5°	702.9	710.5	722.1	733.6	747.2	759.5	772.0	785.9	801.4	819.8	835.0
10°	669.2	679.2	691.7	706.1	722.6	736.9	753.7	768.7	787.7	809.2	829.2
12.5°	642.2	650.8	664.9	678.5	696.2	713.7	731.0	751.0	773.1	796.9	822.1
15°	605.1	612.3	623.7	642.7	660.6	677.8	703.9	722.6	750.5	776.9	807.4
17.5°	573.3	582.3	591.9	608.2	626.7	648.2	671.6	694.9	721.8	755.4	789.8
20°	553.9	561.1	572.1	584.7	604.4	625.8	648.1	671.7	704.6	739.3	776.3
22.5°	532.7	540.5	553.0	566.7	583.2	603.8	628.3	654.2	688.6	722.7	762.8
25°	507.7	513.1	524.5	536.7	553.2	570.7	596.2	624.8	658.8	697.9	738.7
27.5°	484.2	488.9	499.4	509.9	524.8	545.6	568.4	597.3	629.3	668.9	714.2
30°	467.2	472.3	481.5	493.0	507.4	525.7	548.9	576.1	610.5	649.1	696.4
32.5°	452.6	457.1	464.1	475.6	489.6	507.3	528.9	556.7	591.0	630.3	676.7
35°	430.0	435.0	440.4	449.3	461.6	478.7	502.4	528.5	561.4	599.4	642.0
37.5°	407.6	412.9	417.7	425.7	436.9	452.0	472.5	499.7	529.5	566.1	607.0
40°	393.5	397.8	401.7	410.3	421.4	435.7	454.7	479.1	510.6	544.6	578.6
42.5°	379.5	383.4	386.8	394.3	404.5	418.3	436.4	460.1	489.4	521.1	551.1
45°	357.3	359.9	363.8	370.2	378.4	391.0	408.5	429.7	454.4	484.5	507.0
47.5°	333.4	337.3	340.5	346.2	353.0	365.2	382.1	400.1	422.5	444.9	460.7
50°	315.1	319.1	323.7	329.0	335.5	346.9	362.3	380.6	399.5	416.8	430.4
52.5°	297.9	301.5	306.5	311.6	319.4	329.2	342.3	358.5	377.2	389.6	400.9
55°	272.5	274.3	280.0	285.0	292.6	299.7	312.9	327.3	338.7	348.0	357.3
57.5°	246.5	248.9	252.2	256.7	264.2	272.6	281.8	294.5	301.2	306.0	313.3
60°	229.9	230.5	232.7	238.1	243.8	251.4	262.1	271.1	276.1	280.0	286.1
62.5°	211.5	211.7	215.3	219.2	223.5	231.6	240.3	247.5	251.8	253.6	259.5
65°	185.9	185.1	187.3	190.5	195.5	200.9	208.4	214.8	214.4	216.6	220.2
67.5°	159.6	158.8	158.8	161.9	166.0	170.8	176.0	179.6	179.7	182.6	184.4
70°	141.8	139.7	141.1	143.5	145.3	149.3	155.0	156.5	156.8	158.3	160.0
72.5°	123.5	122.7	123.9	125.0	126.2	129.2	134.1	135.0	135.1	135.9	138.8
75°	98.1	97.4	96.7	97.7	99.2	101.3	103.1	104.5	104.2	104.5	106.7
77.5°	73.5	71.5	71.2	71.7	72.1	73.4	75.3	75.1	75.5	75.4	77.9
80°	58.3	55.5	55.1	55.1	55.5	56.2	56.9	57.7	56.6	57.7	58.3
82.5°	42.9	41.2	41.1	40.8	40.9	41.0	41.5	41.8	41.7	42.1	42.6
85°	23.7	22.9	21.9	22.5	22.2	21.1	21.9	20.7	20.5	20.7	21.1
87.5°	11.8	11.8	10.9	10.6	9.9	9.9	9.0	8.3	7.5	7.4	7.9
90°	18.8	17.5	15.8	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1
92.5°	43.6	42.0	40.0	37.9	35.8	33.6	32.0	30.6	29.2	27.9	26.5
95°	86.1	84.4	81.9	79.5	77.0	74.6	73.1	72.7	72.2	71.6	71.2
97.5°	135.9	134.3	130.9	127.5	124.2	120.8	119.0	118.9	118.7	118.5	118.3
100°	169.8	167.6	164.4	161.3	158.1	155.0	153.4	153.4	153.4	153.4	153.4
102.5°	205.0	202.6	201.0	199.4	197.8	196.2	194.9	194.0	192.9	192.0	191.1
105°	263.3	261.7	260.3	258.8	257.4	255.9	254.6	253.4	252.1	250.9	249.7
107.5°	325.8	325.1	324.0	322.8	321.7	320.6	319.4	318.2	317.0	315.8	314.5
110°	368.7	368.0	367.3	366.6	365.8	365.0	364.1	362.9	361.7	360.4	359.3



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	412.2	411.8	410.9	410.0	409.1	408.1	407.4	406.7	406.0	405.5	404.8
115°	478.4	478.6	478.2	477.7	477.2	476.6	476.0	474.9	474.0	473.1	472.0
117.5°	543.7	543.5	543.0	542.6	542.2	541.7	541.3	540.8	540.5	540.0	539.5
120°	588.1	588.1	588.0	587.7	587.4	587.2	586.4	585.2	584.0	582.8	581.5
122.5°	631.8	632.0	631.3	630.7	630.1	629.4	628.9	628.5	628.0	627.6	627.2
125°	696.1	696.6	696.4	696.1	695.9	695.6	694.7	693.3	691.8	690.4	688.9
127.5°	759.4	759.7	759.4	759.1	758.8	758.6	758.0	757.1	756.3	755.4	754.7
130°	801.5	801.7	801.3	800.8	800.3	799.8	798.9	797.8	796.5	795.3	794.1
132.5°	841.8	842.1	842.2	842.3	842.4	842.4	841.5	839.5	837.5	835.5	833.5
135°	903.6	903.6	903.3	903.1	902.9	902.7	901.8	900.3	898.9	897.4	896.0
137.5°	963.7	963.4	962.9	962.3	961.8	961.3	960.3	958.8	957.4	956.0	954.6
140°	1001.5	1001.1	1000.3	999.7	998.9	998.2	997.2	996.0	994.8	993.5	992.3
142.5°	1039.1	1038.8	1037.8	1036.9	1035.9	1035.1	1034.1	1033.0	1032.1	1031.0	1030.0
145°	1093.1	1093.1	1092.3	1091.7	1090.9	1090.1	1089.3	1088.4	1087.4	1086.4	1085.4
147.5°	1142.3	1141.7	1141.1	1140.6	1140.0	1139.3	1138.8	1138.3	1137.7	1137.2	1136.7
150°	1174.1	1174.1	1173.2	1172.1	1171.2	1170.3	1169.9	1170.2	1170.4	1170.6	1170.8
152.5°	1202.8	1202.2	1201.8	1201.4	1201.0	1200.6	1200.2	1200.0	1199.6	1199.2	1198.9
155°	1244.2	1243.1	1242.9	1242.6	1242.5	1242.2	1242.1	1242.1	1242.1	1242.1	1242.1
157.5°	1280.3	1279.3	1279.0	1278.8	1278.6	1278.3	1278.5	1279.0	1279.5	1280.1	1280.6
160°	1302.1	1301.2	1301.0	1300.7	1300.4	1300.2	1300.4	1301.2	1301.9	1302.7	1303.3
162.5°	1322.5	1321.4	1321.3	1321.3	1321.2	1321.2	1321.4	1321.9	1322.5	1323.0	1323.5
165°	1350.4	1349.3	1349.2	1348.9	1348.7	1348.4	1348.5	1349.1	1349.5	1350.0	1350.5
167.5°	1370.4	1368.9	1368.9	1368.9	1368.9	1368.9	1369.3	1370.4	1371.3	1372.2	1373.3
170°	1382.6	1381.1	1381.1	1381.1	1381.1	1381.1	1381.7	1382.6	1383.6	1384.6	1385.5
172.5°	1391.4	1389.9	1389.9	1389.9	1389.9	1389.9	1390.4	1391.4	1392.3	1393.4	1394.3
175°	1401.2	1399.8	1399.8	1399.8	1399.8	1399.8	1400.2	1401.2	1402.2	1403.2	1404.1
177.5°	1406.0	1404.8	1405.0	1405.2	1405.4	1405.6	1406.1	1406.8	1407.6	1408.4	1409.2
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	848.2	852.2	854.7	859.6	863.7	865.9	867.9	869.6	871.7	873.4	878.3
5°	853.6	862.9	870.8	883.0	894.1	902.7	911.9	920.2	927.0	936.7	944.1
7.5°	851.2	867.8	885.1	903.9	923.2	941.1	957.5	973.0	986.9	1003.8	1018.6
10°	848.9	871.5	893.7	919.1	945.3	967.4	988.3	1009.4	1024.7	1046.2	1064.5
12.5°	847.3	873.8	900.6	931.1	959.9	991.2	1018.9	1034.3	1057.7	1074.9	1096.6
15°	840.0	875.1	911.9	946.3	987.1	1016.2	1040.5	1070.5	1092.4	1114.3	1137.8
17.5°	827.0	866.8	908.0	953.1	992.2	1023.4	1054.7	1083.7	1109.8	1139.1	1168.6
20°	821.0	860.7	908.0	954.2	992.5	1025.1	1057.3	1089.2	1117.9	1155.5	1189.4
22.5°	808.4	856.5	900.0	945.0	984.5	1019.9	1056.5	1092.6	1130.7	1173.2	1215.8
25°	785.9	834.6	880.8	925.2	965.0	1009.4	1048.4	1096.7	1145.4	1201.6	1254.6
27.5°	762.6	809.2	851.5	894.4	940.8	991.0	1041.6	1096.5	1160.3	1231.1	1306.0
30°	743.7	787.7	828.9	872.9	921.2	977.8	1033.3	1098.5	1172.2	1252.1	1340.9
32.5°	721.6	762.2	802.3	848.9	901.5	961.2	1025.9	1097.3	1186.0	1276.8	1368.1
35°	683.9	717.9	759.0	808.8	868.3	936.7	1011.5	1096.0	1197.7	1301.8	1378.8
37.5°	639.1	670.8	714.2	768.7	831.0	904.5	993.3	1093.4	1201.5	1284.5	1309.4
40°	609.1	638.4	683.5	740.1	803.8	881.6	978.9	1084.9	1189.4	1242.5	1222.0
42.5°	576.9	607.8	651.8	707.8	776.3	860.9	960.8	1066.9	1154.5	1174.5	1104.0
45°	526.3	558.2	601.5	658.1	731.9	823.5	927.7	1024.0	1074.5	1038.3	929.2
47.5°	479.3	509.2	549.3	607.7	683.8	778.6	878.9	955.7	959.8	873.5	756.9
50°	447.2	474.8	515.2	573.6	649.1	745.1	835.7	896.2	869.0	771.3	659.2
52.5°	415.7	442.7	482.6	540.4	615.1	702.9	787.3	829.7	778.4	678.2	582.4
55°	370.2	393.9	432.9	486.3	557.1	638.8	710.4	725.0	658.5	559.6	481.9
57.5°	325.8	347.9	383.4	432.5	497.3	569.7	625.7	622.5	552.1	467.3	405.7
60°	295.8	317.3	348.7	396.7	455.8	518.1	566.1	554.6	484.8	411.8	359.9
62.5°	268.8	288.0	317.8	359.8	413.7	471.4	510.8	493.9	425.5	361.7	320.6
65°	229.1	245.2	270.7	306.5	351.3	398.9	429.3	407.5	349.1	299.4	266.4
67.5°	191.2	204.2	225.5	254.1	292.3	330.5	349.0	327.1	280.3	244.0	219.6
70°	167.2	178.7	195.1	220.6	253.8	286.1	300.0	280.3	240.3	209.1	191.5
72.5°	143.2	152.6	167.1	189.9	216.6	244.6	256.7	238.0	205.0	178.7	162.3
75°	110.7	117.1	127.1	142.9	164.0	186.2	193.0	176.5	155.4	135.7	125.0
77.5°	79.2	84.6	92.3	102.2	117.2	131.3	137.2	127.7	111.3	98.9	90.1
80°	60.9	63.7	70.2	78.4	90.2	99.2	103.1	97.0	85.6	76.3	69.5
82.5°	43.4	46.3	50.1	56.9	64.5	70.5	74.7	70.7	62.4	55.0	51.1
85°	21.1	22.9	25.1	27.9	33.6	37.2	36.9	34.4	31.1	28.3	26.1
87.5°	8.0	8.8	10.0	11.8	13.0	14.5	15.5	15.2	14.4	13.8	13.2
90°	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0
92.5°	27.9	29.2	30.6	32.0	33.6	35.8	37.9	40.0	42.0	43.6	45.2
95°	71.6	72.2	72.7	73.1	74.6	77.0	79.5	81.9	84.4	86.1	87.8
97.5°	118.5	118.7	118.9	119.0	120.8	124.2	127.5	130.9	134.3	135.9	137.5
100°	153.4	153.4	153.4	153.4	155.0	158.1	161.3	164.4	167.6	169.8	171.9
102.5°	192.0	192.9	194.0	194.9	196.2	197.8	199.4	201.0	202.6	205.0	207.4
105°	250.9	252.1	253.4	254.6	255.9	257.4	258.8	260.3	261.7	263.3	264.7
107.5°	315.8	317.0	318.2	319.4	320.6	321.7	322.8	324.0	325.1	325.8	326.5
110°	360.4	361.7	362.9	364.1	365.0	365.8	366.6	367.3	368.0	368.7	369.5



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	405.5	406.0	406.7	407.4	408.1	409.1	410.0	410.9	411.8	412.2	412.6
115°	473.1	474.0	474.9	476.0	476.6	477.2	477.7	478.2	478.6	478.4	478.2
117.5°	540.0	540.5	540.8	541.3	541.7	542.2	542.6	543.0	543.5	543.7	543.8
120°	582.8	584.0	585.2	586.4	587.2	587.4	587.7	588.0	588.1	588.1	588.1
122.5°	627.6	628.0	628.5	628.9	629.4	630.1	630.7	631.3	632.0	631.8	631.6
125°	690.4	691.8	693.3	694.7	695.6	695.9	696.1	696.4	696.6	696.1	695.6
127.5°	755.4	756.3	757.1	758.0	758.6	758.8	759.1	759.4	759.7	759.4	759.2
130°	795.3	796.5	797.8	798.9	799.8	800.3	800.8	801.3	801.7	801.5	801.3
132.5°	835.5	837.5	839.5	841.5	842.4	842.4	842.3	842.2	842.1	841.8	841.6
135°	897.4	898.9	900.3	901.8	902.7	902.9	903.1	903.3	903.6	903.6	903.6
137.5°	956.0	957.4	958.8	960.3	961.3	961.8	962.3	962.9	963.4	963.7	964.0
140°	993.5	994.8	996.0	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5	1002.0
142.5°	1031.0	1032.1	1033.0	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1	1039.3
145°	1086.4	1087.4	1088.4	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1	1093.1
147.5°	1137.2	1137.7	1138.3	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3	1142.9
150°	1170.6	1170.4	1170.2	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1	1174.1
152.5°	1199.2	1199.6	1200.0	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8	1203.3
155°	1242.1	1242.1	1242.1	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2	1245.1
157.5°	1280.1	1279.5	1279.0	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3	1281.2
160°	1302.7	1301.9	1301.2	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1	1303.2
162.5°	1323.0	1322.5	1321.9	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5	1323.7
165°	1350.0	1349.5	1349.1	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4	1351.3
167.5°	1372.2	1371.3	1370.4	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4	1371.8
170°	1384.6	1383.6	1382.6	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6	1384.0
172.5°	1393.4	1392.3	1391.4	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4	1392.8
175°	1403.2	1402.2	1401.2	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2	1402.7
177.5°	1408.4	1407.6	1406.8	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0	1407.1
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	882.2	884.5	889.4	887.7	889.9	891.1	892.3
5°	953.5	965.0	970.0	969.2	976.8	975.0	973.2
7.5°	1034.0	1046.0	1052.7	1061.1	1066.0	1066.3	1070.5
10°	1079.5	1095.2	1101.7	1110.7	1116.4	1119.6	1119.3
12.5°	1114.5	1126.8	1141.2	1145.7	1153.4	1157.4	1155.9
15°	1156.5	1176.2	1191.2	1198.7	1208.4	1211.3	1215.2
17.5°	1194.0	1220.4	1238.0	1261.3	1270.2	1275.5	1272.3
20°	1222.4	1257.1	1274.7	1302.6	1318.0	1326.3	1323.3
22.5°	1255.9	1293.5	1326.0	1350.1	1373.6	1384.7	1387.0
25°	1313.3	1364.9	1412.5	1444.4	1473.4	1480.2	1495.2
27.5°	1377.5	1438.3	1489.2	1522.7	1542.9	1550.5	1555.2
30°	1417.9	1478.4	1516.7	1538.1	1544.6	1543.9	1543.2
32.5°	1437.7	1475.6	1482.9	1476.9	1462.2	1449.6	1436.6
35°	1409.7	1381.4	1339.1	1284.7	1244.6	1204.1	1200.1
37.5°	1267.8	1177.3	1107.0	1028.5	983.2	955.2	935.8
40°	1134.3	1031.5	946.3	880.1	833.9	815.7	797.8
42.5°	989.4	891.2	815.7	760.3	725.7	705.4	691.2
45°	803.8	717.2	658.1	618.0	590.4	574.7	565.7
47.5°	658.6	594.6	544.4	515.5	496.4	484.2	484.2
50°	580.8	519.5	486.3	463.4	446.9	437.2	438.9
52.5°	511.7	466.0	437.5	418.3	406.1	400.2	400.0
55°	427.9	394.9	376.4	362.3	354.1	347.3	348.7
57.5°	366.0	338.2	325.7	314.1	308.4	305.7	301.8
60°	327.6	306.1	295.4	286.1	280.3	278.2	274.3
62.5°	293.5	276.6	266.2	258.5	253.4	252.7	249.6
65°	246.7	233.8	224.5	220.9	215.6	214.1	214.1
67.5°	203.4	194.2	186.9	183.6	181.3	181.6	179.8
70°	176.2	168.6	164.0	160.4	158.6	159.0	157.5
72.5°	154.1	145.7	141.7	139.5	137.1	138.1	137.5
75°	116.7	112.4	110.3	108.1	106.7	105.9	105.3
77.5°	85.7	81.9	80.3	79.1	79.3	77.6	78.9
80°	66.3	63.1	61.9	60.1	59.8	59.8	59.5
82.5°	48.4	46.7	45.9	44.4	43.7	44.3	43.4
85°	25.1	23.7	23.3	23.3	22.5	21.9	23.7
87.5°	13.4	12.5	12.7	12.5	12.7	12.5	12.2
90°	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	46.8	48.4	49.6	50.0	50.6	51.2	51.7
95°	89.4	91.1	92.3	92.7	93.2	93.7	94.2
97.5°	139.1	140.7	141.7	141.9	142.2	142.5	142.8
100°	174.2	176.3	177.7	178.1	178.6	179.2	179.6
102.5°	209.8	212.2	213.7	214.4	215.1	215.7	216.4
105°	266.2	267.6	268.7	269.5	270.1	270.9	271.6
107.5°	327.3	328.0	328.4	328.3	328.3	328.2	328.1
110°	370.2	370.9	371.2	370.9	370.7	370.4	370.2



TEST NUMBER: P333197-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	412.8	413.2	413.1	412.7	412.3	411.8	411.4
115°	477.9	477.7	477.4	477.2	476.9	476.6	476.5
117.5°	544.0	544.2	543.8	542.9	542.0	540.9	540.0
120°	588.1	588.1	587.7	586.7	585.7	584.8	583.8
122.5°	631.4	631.2	630.7	629.9	629.1	628.4	627.6
125°	695.1	694.7	694.3	694.1	693.8	693.5	693.3
127.5°	758.9	758.7	758.4	757.9	757.3	756.9	756.4
130°	801.0	800.8	800.4	799.9	799.5	798.9	798.4
132.5°	841.3	841.0	840.7	839.9	839.2	838.6	837.9
135°	903.6	903.6	903.1	902.1	901.2	900.2	899.2
137.5°	964.3	964.6	964.1	962.9	961.7	960.5	959.2
140°	1002.6	1003.1	1002.7	1001.5	1000.2	999.0	997.8
142.5°	1039.6	1039.9	1039.4	1038.2	1037.1	1035.9	1034.6
145°	1093.1	1093.1	1092.7	1092.0	1091.3	1090.5	1089.8
147.5°	1143.5	1144.1	1143.5	1141.9	1140.2	1138.6	1136.9
150°	1174.1	1174.1	1173.9	1173.4	1172.9	1172.4	1172.0
152.5°	1203.9	1204.5	1204.4	1203.5	1202.6	1201.7	1200.9
155°	1246.0	1247.1	1246.9	1245.7	1244.4	1243.3	1242.1
157.5°	1282.2	1283.2	1282.9	1281.3	1279.7	1278.1	1276.5
160°	1304.1	1305.0	1305.0	1303.7	1302.5	1301.3	1300.1
162.5°	1324.8	1326.1	1325.9	1324.5	1323.0	1321.6	1320.2
165°	1352.3	1353.3	1353.0	1351.6	1350.1	1348.7	1347.2
167.5°	1373.3	1374.7	1374.7	1373.2	1371.7	1370.2	1368.7
170°	1385.5	1387.0	1386.9	1385.2	1383.5	1381.8	1380.1
172.5°	1394.3	1395.7	1395.7	1394.2	1392.7	1391.2	1389.7
175°	1404.1	1405.6	1405.5	1403.8	1402.1	1400.3	1398.6
177.5°	1408.3	1409.5	1409.4	1408.1	1406.7	1405.3	1403.9
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4

(END OF REPORT)