

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333203-830

Luminaire Tested: **S125DIP-S610D1205U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333203-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D1205U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6285.9 lumens  
Efficiency: N/A  
Efficacy: 127.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	62	53	51	50	39	38	38	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5846	5846	5846
5°	5859	5803	5841
10°	5823	5762	5795
15°	5760	5693	5717
20°	5670	5597	5606
25°	5573	5481	5476
30°	5452	5357	5330
35°	5324	5222	5149
40°	5193	5078	5005
45°	5050	4945	4847
50°	4893	4786	4641
55°	4741	4604	4476
60°	4561	4421	4265
65°	4345	4202	4060
70°	4137	3950	3814
75°	3770	3646	3521
80°	3355	3303	3221
85°	2920	2971	2816



TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.3	1.4
10°-20°	241.1	3.8
20°-30°	356.0	5.7
30°-40°	415.4	6.6
40°-50°	417.2	6.6
50°-60°	366.2	5.8
60°-70°	272.9	4.3
70°-80°	156.0	2.5
80°-90°	48.5	0.8
90°-100°	94.3	1.5
100°-110°	278.4	4.4
110°-120°	471.5	7.5
120°-130°	620.5	9.9
130°-140°	695.3	11.1
140°-150°	681.4	10.8
150°-160°	572.4	9.1
160°-170°	380.5	6.1
170°-180°	133.1	2.1
0°-30°	682.4	10.9
0°-40°	1097.8	17.5
0°-60°	1881.2	29.9
0°-90°	2358.5	37.5
90°-120°	844.1	13.4
90°-150°	2841.4	45.2
90°-180°	3927.0	62.5
0°-180°	6285.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	904	902	895	901	901	86
15°	862	859	852	855	855	243
25°	782	778	769	770	768	360
35°	675	672	662	659	653	422
45°	553	550	541	533	531	426
55°	421	418	409	403	398	376
65°	284	282	275	269	266	282
75°	151	150	146	144	141	161
85°	39	40	40	39	38	44
90°	1	10	18	23	26	6
95°	71	74	84	92	94	76
105°	250	255	262	268	272	267
115°	472	476	479	478	476	467
125°	689	695	697	694	693	617
135°	896	902	904	903	899	690
145°	1085	1090	1093	1093	1090	678
155°	1242	1242	1243	1247	1242	572
165°	1350	1348	1349	1353	1347	381
175°	1404	1400	1400	1406	1399	133
180°	1407	1407	1407	1407	1407	



TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	907.5	907.1	906.7	906.3	906.0	905.1	903.9	902.6	901.4	900.0	901.4
5°	903.8	903.4	903.1	902.8	902.5	901.5	899.9	898.3	896.7	895.1	896.6
7.5°	895.4	895.1	894.8	894.5	894.2	893.2	891.4	889.7	887.9	886.2	887.5
10°	888.0	887.7	887.4	887.0	886.7	885.7	883.9	882.2	880.4	878.7	880.0
12.5°	878.8	878.3	877.7	877.1	876.6	875.4	873.8	872.2	870.5	868.9	870.0
15°	861.5	861.0	860.5	860.1	859.6	858.5	856.8	855.0	853.2	851.5	852.2
17.5°	841.6	840.9	840.2	839.5	838.8	837.5	835.8	833.9	832.1	830.3	831.2
20°	825.0	824.6	824.3	824.1	823.7	822.6	820.5	818.4	816.3	814.3	815.4
22.5°	808.3	807.8	807.2	806.6	806.1	804.8	802.9	801.0	799.0	797.0	797.8
25°	782.0	781.2	780.4	779.7	778.8	777.4	775.3	773.3	771.2	769.1	769.5
27.5°	751.2	750.7	750.3	749.8	749.3	748.0	745.8	743.8	741.6	739.5	739.5
30°	731.1	730.7	730.2	729.7	729.2	727.8	725.5	723.0	720.7	718.3	717.9
32.5°	709.4	708.7	707.9	707.2	706.4	705.0	702.9	700.8	698.6	696.5	696.0
35°	675.3	674.7	674.0	673.4	672.8	671.4	669.1	666.8	664.7	662.4	661.7
37.5°	639.9	639.1	638.4	637.5	636.8	635.3	633.2	631.1	629.0	626.9	625.8
40°	615.9	615.1	614.3	613.5	612.7	611.1	609.0	606.7	604.5	602.3	600.9
42.5°	590.1	589.5	588.7	588.1	587.4	586.0	583.7	581.5	579.3	577.0	575.8
45°	552.9	552.2	551.6	550.9	550.4	549.0	547.1	545.3	543.3	541.4	539.5
47.5°	512.7	512.7	512.8	512.8	512.8	511.7	509.4	507.2	504.9	502.6	500.7
50°	487.0	486.4	486.0	485.5	485.0	483.9	481.9	480.0	478.2	476.3	474.2
52.5°	460.6	460.2	460.0	459.6	459.2	458.0	456.0	453.9	451.9	449.9	448.1
55°	421.1	420.6	420.1	419.6	419.1	417.8	415.6	413.4	411.1	408.9	407.5
57.5°	379.4	379.2	378.9	378.6	378.4	377.3	375.4	373.5	371.6	369.9	368.0
60°	353.1	352.4	351.8	351.1	350.5	349.3	347.6	345.8	344.0	342.3	340.7
62.5°	325.6	325.1	324.5	324.0	323.5	322.5	321.0	319.5	318.0	316.5	314.8
65°	284.3	284.0	283.7	283.3	283.0	282.0	280.2	278.5	276.7	275.0	273.5
67.5°	244.3	243.6	243.0	242.3	241.7	240.7	239.4	238.1	236.8	235.4	234.2
70°	219.1	218.4	217.5	216.8	215.9	214.8	213.4	212.0	210.6	209.2	208.1
72.5°	191.6	191.1	190.6	190.0	189.5	188.7	187.8	186.9	186.0	185.0	184.0
75°	151.1	150.8	150.4	150.1	149.9	149.3	148.5	147.7	146.8	146.1	145.6
77.5°	113.8	113.6	113.5	113.3	113.2	112.9	112.4	112.1	111.6	111.1	110.8
80°	90.2	90.2	90.2	90.2	90.2	90.1	89.7	89.4	89.2	88.8	88.6
82.5°	69.7	69.4	69.1	68.8	68.6	68.4	68.3	68.3	68.2	68.1	67.9
85°	39.4	39.6	39.7	39.9	40.1	40.1	40.1	40.1	40.1	40.1	40.0
87.5°	15.6	16.1	16.5	16.9	17.2	17.5	17.7	18.0	18.2	18.4	18.7
90°	1.1	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8
92.5°	26.5	27.9	29.2	30.6	32.0	33.6	35.8	37.9	40.0	42.0	43.6
95°	71.2	71.6	72.2	72.7	73.1	74.6	77.0	79.5	81.9	84.4	86.1
97.5°	118.3	118.5	118.7	118.9	119.0	120.8	124.2	127.5	130.9	134.3	135.9
100°	153.4	153.4	153.4	153.4	153.4	155.0	158.1	161.3	164.4	167.6	169.8
102.5°	191.1	192.0	192.9	194.0	194.9	196.2	197.8	199.4	201.0	202.6	205.0
105°	249.7	250.9	252.1	253.4	254.6	255.9	257.4	258.8	260.3	261.7	263.3
107.5°	314.5	315.8	317.0	318.2	319.4	320.6	321.7	322.8	324.0	325.1	325.8
110°	359.3	360.4	361.7	362.9	364.1	365.0	365.8	366.6	367.3	368.0	368.7



TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	404.8	405.5	406.0	406.7	407.4	408.1	409.1	410.0	410.9	411.8	412.2
115°	472.0	473.1	474.0	474.9	476.0	476.6	477.2	477.7	478.2	478.6	478.4
117.5°	539.5	540.0	540.5	540.8	541.3	541.7	542.2	542.6	543.0	543.5	543.7
120°	581.5	582.8	584.0	585.2	586.4	587.2	587.4	587.7	588.0	588.1	588.1
122.5°	627.2	627.6	628.0	628.5	628.9	629.4	630.1	630.7	631.3	632.0	631.8
125°	688.9	690.4	691.8	693.3	694.7	695.6	695.9	696.1	696.4	696.6	696.1
127.5°	754.7	755.4	756.3	757.1	758.0	758.6	758.8	759.1	759.4	759.7	759.4
130°	794.1	795.3	796.5	797.8	798.9	799.8	800.3	800.8	801.3	801.7	801.5
132.5°	833.5	835.5	837.5	839.5	841.5	842.4	842.4	842.3	842.2	842.1	841.8
135°	896.0	897.4	898.9	900.3	901.8	902.7	902.9	903.1	903.3	903.6	903.6
137.5°	954.6	956.0	957.4	958.8	960.3	961.3	961.8	962.3	962.9	963.4	963.7
140°	992.3	993.5	994.8	996.0	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5
142.5°	1030.0	1031.0	1032.1	1033.0	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1
145°	1085.4	1086.4	1087.4	1088.4	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1
147.5°	1136.7	1137.2	1137.7	1138.3	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3
150°	1170.8	1170.6	1170.4	1170.2	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1
152.5°	1198.9	1199.2	1199.6	1200.0	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8
155°	1242.1	1242.1	1242.1	1242.1	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2
157.5°	1280.6	1280.1	1279.5	1279.0	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3
160°	1303.3	1302.7	1301.9	1301.2	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1
162.5°	1323.5	1323.0	1322.5	1321.9	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5
165°	1350.5	1350.0	1349.5	1349.1	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4
167.5°	1373.3	1372.2	1371.3	1370.4	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4
170°	1385.5	1384.6	1383.6	1382.6	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6
172.5°	1394.3	1393.4	1392.3	1391.4	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4
175°	1404.1	1403.2	1402.2	1401.2	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2
177.5°	1409.2	1408.4	1407.6	1406.8	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	902.6	903.9	905.1	905.7	905.6	905.4	905.3	905.2
5°	898.1	899.5	900.9	901.5	901.4	901.3	901.1	900.9
7.5°	888.9	890.3	891.7	892.4	892.2	892.0	891.9	891.7
10°	881.3	882.5	883.8	884.4	884.2	884.0	883.8	883.7
12.5°	871.0	872.0	873.0	873.5	873.5	873.5	873.5	873.4
15°	853.1	853.8	854.7	855.1	855.1	855.1	855.1	855.1
17.5°	832.3	833.2	834.2	834.3	833.5	832.7	832.0	831.1
20°	816.4	817.6	818.7	818.9	818.0	817.3	816.4	815.7
22.5°	798.5	799.3	800.0	800.1	799.6	799.0	798.4	798.0
25°	769.8	770.1	770.4	770.3	769.9	769.4	768.9	768.5
27.5°	739.6	739.7	739.7	739.5	739.0	738.6	738.1	737.6
30°	717.7	717.4	717.0	716.6	716.1	715.7	715.2	714.7
32.5°	695.4	694.7	694.2	693.5	692.7	691.8	690.9	690.0
35°	660.8	660.1	659.2	658.2	657.0	655.6	654.4	653.1
37.5°	624.5	623.4	622.2	621.2	620.5	619.8	619.1	618.3
40°	599.4	597.9	596.5	595.6	595.1	594.7	594.2	593.7
42.5°	574.5	573.2	571.8	570.8	570.0	569.4	568.6	567.9
45°	537.5	535.6	533.8	532.5	532.1	531.6	531.1	530.7
47.5°	498.7	496.7	494.8	493.3	492.2	491.1	489.9	488.8
50°	472.1	470.0	468.0	466.4	465.2	464.1	463.0	461.9
52.5°	446.2	444.4	442.6	441.1	439.9	438.6	437.3	436.1
55°	406.0	404.6	403.2	401.9	400.8	399.6	398.6	397.5
57.5°	366.1	364.3	362.4	361.2	360.6	360.0	359.4	358.8
60°	339.1	337.5	335.9	334.6	333.5	332.3	331.2	330.2
62.5°	313.1	311.4	309.6	308.4	307.6	306.6	305.8	304.9
65°	272.1	270.7	269.3	268.2	267.6	266.9	266.4	265.7
67.5°	233.1	231.9	230.6	229.8	229.4	229.0	228.7	228.3
70°	207.2	206.2	205.3	204.5	203.9	203.2	202.6	202.0
72.5°	182.9	181.8	180.7	179.8	179.2	178.6	178.0	177.3
75°	145.2	144.7	144.2	143.6	143.0	142.3	141.8	141.1
77.5°	110.6	110.3	110.0	109.6	109.1	108.8	108.3	107.8
80°	88.5	88.3	88.1	87.9	87.6	87.3	87.0	86.6
82.5°	67.6	67.3	67.0	66.8	66.8	66.7	66.6	66.6
85°	39.8	39.6	39.5	39.2	38.9	38.5	38.3	38.0
87.5°	18.9	19.1	19.4	19.4	19.3	19.2	19.1	19.0
90°	20.0	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	45.2	46.8	48.4	49.6	50.0	50.6	51.2	51.7
95°	87.8	89.4	91.1	92.3	92.7	93.2	93.7	94.2
97.5°	137.5	139.1	140.7	141.7	141.9	142.2	142.5	142.8
100°	171.9	174.2	176.3	177.7	178.1	178.6	179.2	179.6
102.5°	207.4	209.8	212.2	213.7	214.4	215.1	215.7	216.4
105°	264.7	266.2	267.6	268.7	269.5	270.1	270.9	271.6
107.5°	326.5	327.3	328.0	328.4	328.3	328.3	328.2	328.1
110°	369.5	370.2	370.9	371.2	370.9	370.7	370.4	370.2





TEST NUMBER: P333203-830

CATALOG NUMBER: S125DIP-S610D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	412.6	412.8	413.2	413.1	412.7	412.3	411.8	411.4
115°	478.2	477.9	477.7	477.4	477.2	476.9	476.6	476.5
117.5°	543.8	544.0	544.2	543.8	542.9	542.0	540.9	540.0
120°	588.1	588.1	588.1	587.7	586.7	585.7	584.8	583.8
122.5°	631.6	631.4	631.2	630.7	629.9	629.1	628.4	627.6
125°	695.6	695.1	694.7	694.3	694.1	693.8	693.5	693.3
127.5°	759.2	758.9	758.7	758.4	757.9	757.3	756.9	756.4
130°	801.3	801.0	800.8	800.4	799.9	799.5	798.9	798.4
132.5°	841.6	841.3	841.0	840.7	839.9	839.2	838.6	837.9
135°	903.6	903.6	903.6	903.1	902.1	901.2	900.2	899.2
137.5°	964.0	964.3	964.6	964.1	962.9	961.7	960.5	959.2
140°	1002.0	1002.6	1003.1	1002.7	1001.5	1000.2	999.0	997.8
142.5°	1039.3	1039.6	1039.9	1039.4	1038.2	1037.1	1035.9	1034.6
145°	1093.1	1093.1	1093.1	1092.7	1092.0	1091.3	1090.5	1089.8
147.5°	1142.9	1143.5	1144.1	1143.5	1141.9	1140.2	1138.6	1136.9
150°	1174.1	1174.1	1174.1	1173.9	1173.4	1172.9	1172.4	1172.0
152.5°	1203.3	1203.9	1204.5	1204.4	1203.5	1202.6	1201.7	1200.9
155°	1245.1	1246.0	1247.1	1246.9	1245.7	1244.4	1243.3	1242.1
157.5°	1281.2	1282.2	1283.2	1282.9	1281.3	1279.7	1278.1	1276.5
160°	1303.2	1304.1	1305.0	1305.0	1303.7	1302.5	1301.3	1300.1
162.5°	1323.7	1324.8	1326.1	1325.9	1324.5	1323.0	1321.6	1320.2
165°	1351.3	1352.3	1353.3	1353.0	1351.6	1350.1	1348.7	1347.2
167.5°	1371.8	1373.3	1374.7	1374.7	1373.2	1371.7	1370.2	1368.7
170°	1384.0	1385.5	1387.0	1386.9	1385.2	1383.5	1381.8	1380.1
172.5°	1392.8	1394.3	1395.7	1395.7	1394.2	1392.7	1391.2	1389.7
175°	1402.7	1404.1	1405.6	1405.5	1403.8	1402.1	1400.3	1398.6
177.5°	1407.1	1408.3	1409.5	1409.4	1408.1	1406.7	1405.3	1403.9
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4

(END OF REPORT)