

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332669-840

Luminaire Tested: **S124DIP-S1020D1205U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332669-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1205U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8818.9 lumens  
Efficiency: N/A  
Efficacy: 134.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.1	1.9
10°-20°	462.4	5.2
20°-30°	680.5	7.7
30°-40°	791.1	9.0
40°-50°	791.2	9.0
50°-60°	692.1	7.8
60°-70°	514.0	5.8
70°-80°	292.0	3.3
80°-90°	87.6	1.0
90°-100°	431.4	4.9
100°-110°	897.9	10.2
110°-120°	804.2	9.1
120°-130°	676.5	7.7
130°-140°	564.1	6.4
140°-150°	430.9	4.9
150°-160°	302.9	3.4
160°-170°	178.2	2.0
170°-180°	58.0	0.7
0°-30°	1307.0	14.8
0°-40°	2098.1	23.8
0°-60°	3581.3	40.6
0°-90°	4474.8	50.7
90°-120°	2133.5	24.2
90°-150°	3805.0	43.1
90°-180°	4344.0	49.3
0°-180°	8818.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	1	9	21	23	25	6
95°	39	122	956	474	286	43
105°	137	199	770	1658	1651	146
115°	242	303	686	1319	1585	240
125°	337	400	683	1122	1265	300
135°	400	476	677	996	1131	309
145°	461	528	674	840	924	289
155°	524	566	655	742	773	242
165°	572	589	628	665	675	161
175°	596	597	602	610	608	57
180°	597	597	597	597	597	



TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.3	29.5	30.0	29.9	29.9	29.7	30.8	30.6	30.8	31.0	30.8
90°	1.2	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0
92.5°	13.3	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0
95°	38.7	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4
97.5°	69.5	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5
100°	89.2	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9
102.5°	108.0	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5
105°	137.3	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5
107.5°	169.7	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3
110°	191.3	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7



TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.0	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5
115°	241.8	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4
117.5°	272.7	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1
120°	293.4	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6
122.5°	312.1	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1
125°	336.8	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6
127.5°	358.6	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9
130°	370.8	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6
132.5°	383.0	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2
135°	400.1	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2
137.5°	417.3	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0
140°	429.5	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4
142.5°	442.6	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7
145°	461.2	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1
147.5°	482.0	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5
150°	495.2	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9
152.5°	507.4	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3
155°	524.5	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1
157.5°	541.2	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6
160°	551.5	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1
162.5°	560.9	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6
165°	571.5	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2
167.5°	582.1	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9
170°	586.7	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4
172.5°	591.4	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9
175°	596.1	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3
177.5°	598.2	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	31.0	31.3	31.5	31.5	31.7	32.0	31.7	31.7
90°	21.1	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	230.5	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	869.5	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1284.8	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1415.2	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1408.7	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1314.2	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1180.2	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1099.5	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1





TEST NUMBER: P332669-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1040.4	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	981.0	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	951.9	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	938.8	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	927.5	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	908.3	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	884.7	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	866.1	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	846.3	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	819.1	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	794.5	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	780.3	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	767.2	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	748.7	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	733.5	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	724.1	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	713.7	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	698.2	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	681.6	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	671.3	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	660.9	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	646.6	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	632.8	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	624.3	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	616.7	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	606.7	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	600.1	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)