

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333216-830

Luminaire Tested: **S125DIP-S850D590U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333216-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D590U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5255.1 lumens  
Efficiency: N/A  
Efficacy: 130.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	32	29
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.0	2.1
10°-20°	330.5	6.3
20°-30°	536.7	10.2
30°-40°	654.6	12.5
40°-50°	595.5	11.3
50°-60°	474.4	9.0
60°-70°	330.4	6.3
70°-80°	176.2	3.4
80°-90°	45.9	0.9
90°-100°	193.3	3.7
100°-110°	415.5	7.9
110°-120°	390.0	7.4
120°-130°	316.0	6.0
130°-140°	253.6	4.8
140°-150°	191.4	3.6
150°-160°	134.7	2.6
160°-170°	79.4	1.5
170°-180°	25.8	0.5
0°-30°	978.2	18.6
0°-40°	1632.8	31.1
0°-60°	2702.7	51.4
0°-90°	3255.2	61.9
90°-120°	998.8	19.0
90°-150°	1759.9	33.5
90°-180°	2000.0	38.1
0°-180°	5255.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	38
90°	12	1	12	1	12	10
95°	126	18	126	18	126	179
105°	712	61	712	61	712	708
115°	794	109	794	109	794	775
125°	625	150	625	150	625	566
135°	519	176	519	176	519	402
145°	410	205	410	205	410	260
155°	344	234	344	234	344	160
165°	301	256	301	256	301	86
175°	270	266	270	266	270	26
180°	267	267	267	267	267	



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	11.9	12.6	12.9	12.9	13.3	13.1	14.6	14.4	15.6	16.6	17.9
90°	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7	9.1	8.6	7.5
92.5°	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3	140.3	173.3	176.2
95°	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5	466.2	476.4	388.7
97.5°	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7	589.8	508.7	347.1
100°	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3	619.9	485.5	309.7
102.5°	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1	601.8	444.6	281.3
105°	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2	544.1	389.8	253.7
107.5°	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5	485.2	352.0	242.1
110°	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8	451.7	334.4	238.7



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5	426.7	324.1	238.7
115°	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1	399.4	312.9	240.3
117.5°	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6	383.2	307.5	243.8
120°	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1	374.2	304.8	247.3
122.5°	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5	366.5	302.7	250.3
125°	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6	355.9	300.0	255.4
127.5°	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4	346.3	298.7	261.1
130°	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7	339.8	297.8	264.6
132.5°	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9	334.6	297.8	268.4
135°	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9	328.5	297.8	273.6
137.5°	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1	323.0	298.5	278.5
140°	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6	320.5	299.0	280.7
142.5°	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0	318.3	299.4	281.9
145°	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8	315.1	299.0	283.3
147.5°	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9	311.7	297.6	283.9
150°	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9	309.2	296.2	283.9
152.5°	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7	306.1	294.5	283.4
155°	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2	301.0	291.4	282.3
157.5°	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8	296.3	288.1	280.9
160°	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4	292.5	286.1	279.6
162.5°	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7	289.1	283.4	278.3
165°	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1	283.9	279.6	276.4
167.5°	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9	278.8	275.8	273.3
170°	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5	275.8	273.6	272.0
172.5°	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7	272.8	271.1	270.3
175°	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4	268.8	268.2	268.2
177.5°	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5	267.1	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	18.7	17.6	15.9	14.6	12.3	11.0	10.4	10.7	9.6	9.4	10.1
90°	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6	1.0	2.2	3.2
92.5°	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6	7.9	12.4	19.1
95°	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7	18.3	22.6	28.5
97.5°	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5	30.1	33.1	39.0
100°	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6	38.7	40.9	46.8
102.5°	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7	47.3	49.0	55.4
105°	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8	60.8	63.4	68.8
107.5°	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6	75.6	78.1	82.6
110°	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5	85.5	87.7	92.5





TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3	95.4	97.1	102.0
115°	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6	109.7	111.3	116.1
117.5°	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5	123.1	124.9	129.7
120°	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1	131.8	133.8	138.7
122.5°	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1	140.3	142.0	146.8
125°	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5	151.7	154.3	159.1
127.5°	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5	161.1	164.6	170.7
130°	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0	166.6	171.0	178.0
132.5°	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4	171.4	176.5	184.5
135°	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3	178.5	184.9	193.6
137.5°	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2	186.8	192.8	201.4
140°	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3	191.9	198.4	207.0
142.5°	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3	197.6	203.6	212.2
145°	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4	206.4	211.8	219.3
147.5°	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8	215.5	220.1	227.1
150°	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5	221.5	225.3	232.2
152.5°	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5	227.1	230.5	236.6
155°	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4	234.4	237.6	243.0
157.5°	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5	241.4	244.0	248.6
160°	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3	245.7	247.9	251.7
162.5°	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2	249.6	251.8	255.1
165°	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9	254.9	256.5	259.1
167.5°	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8	259.3	260.2	261.7
170°	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4	261.8	262.4	263.4
172.5°	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1	263.2	263.6	264.8
175°	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2	265.0	265.6	266.2
177.5°	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1	266.3	266.3	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	10.7	11.7	11.4	12.0	12.1	13.1	12.8	14.4	15.4	16.2	16.0
90°	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7	10.2	10.7	11.8
92.5°	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3	69.2	52.0	44.1
95°	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5	304.8	238.7	193.6
97.5°	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7	518.4	454.0	391.2
100°	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3	635.0	579.6	523.7
102.5°	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1	706.3	679.8	642.0
105°	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2	746.8	770.4	764.5
107.5°	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5	710.8	771.6	799.6
110°	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8	670.0	745.7	791.5



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5	629.5	706.2	760.1
115°	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1	571.6	645.2	703.8
117.5°	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6	531.4	594.8	648.7
120°	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1	508.6	567.8	615.1
122.5°	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5	492.3	545.0	589.3
125°	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6	470.4	517.3	555.9
127.5°	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4	449.6	493.2	529.5
130°	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7	435.0	476.9	511.8
132.5°	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9	421.2	459.3	492.9
135°	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9	400.0	434.4	465.1
137.5°	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1	381.1	409.7	435.7
140°	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6	369.9	394.6	417.3
142.5°	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0	360.4	381.7	401.3
145°	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8	348.4	365.0	379.6
147.5°	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9	338.4	351.2	362.1
150°	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9	332.8	343.0	352.7
152.5°	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7	327.3	336.6	344.1
155°	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2	318.9	326.3	332.2
157.5°	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8	310.9	316.7	321.3
160°	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4	304.8	310.2	314.0
162.5°	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7	299.7	304.2	307.6
165°	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1	291.9	295.2	297.8
167.5°	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9	284.5	286.9	288.8
170°	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5	280.1	281.7	282.8
172.5°	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7	276.3	277.4	278.1
175°	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4	270.4	271.5	271.5
177.5°	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5	268.0	268.0	268.0
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	16.9	16.5	16.6	17.3	16.6	16.5	16.9	16.0	16.2	15.4	14.4
90°	11.8	11.8	12.3	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7
92.5°	37.2	35.9	35.2	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3
95°	155.4	139.2	135.0	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5
97.5°	358.0	327.8	312.3	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7
100°	486.5	447.9	428.0	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3
102.5°	602.3	574.8	553.2	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1
105°	747.3	729.6	718.9	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2
107.5°	808.3	808.2	804.6	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5
110°	815.6	825.9	829.6	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	795.4	812.9	822.3	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5
115°	745.7	771.6	786.6	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1
117.5°	690.6	717.3	732.2	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6
120°	654.9	680.7	695.2	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1
122.5°	624.7	648.4	662.9	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5
125°	586.1	608.1	619.9	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6
127.5°	556.8	576.3	587.4	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4
130°	538.8	556.5	567.2	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7
132.5°	519.8	537.5	547.4	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9
135°	488.7	506.4	516.1	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9
137.5°	456.9	473.1	481.9	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1
140°	437.2	451.1	459.1	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6
142.5°	418.2	430.0	437.6	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0
145°	392.5	401.6	407.6	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8
147.5°	372.4	379.7	383.1	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9
150°	360.8	367.2	369.4	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9
152.5°	350.9	356.0	358.2	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7
155°	337.6	341.4	343.0	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2
157.5°	325.5	328.6	330.1	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8
160°	317.7	320.5	321.5	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4
162.5°	310.5	312.7	312.9	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7
165°	300.0	301.0	301.0	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1
167.5°	289.9	290.9	290.4	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9
170°	283.9	284.5	284.5	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5
172.5°	278.3	279.3	278.4	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7
175°	271.5	272.0	271.0	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4
177.5°	267.5	268.0	266.6	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	12.8	13.1	12.1	12.0	11.4	11.7	10.7	10.1	9.4	9.6	10.7
90°	9.1	8.6	7.5	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6
92.5°	140.3	173.3	176.2	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6
95°	466.2	476.4	388.7	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7
97.5°	589.8	508.7	347.1	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5
100°	619.9	485.5	309.7	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6
102.5°	601.8	444.6	281.3	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7
105°	544.1	389.8	253.7	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8
107.5°	485.2	352.0	242.1	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6
110°	451.7	334.4	238.7	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	426.7	324.1	238.7	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3
115°	399.4	312.9	240.3	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6
117.5°	383.2	307.5	243.8	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5
120°	374.2	304.8	247.3	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1
122.5°	366.5	302.7	250.3	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1
125°	355.9	300.0	255.4	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5
127.5°	346.3	298.7	261.1	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5
130°	339.8	297.8	264.6	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0
132.5°	334.6	297.8	268.4	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4
135°	328.5	297.8	273.6	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3
137.5°	323.0	298.5	278.5	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2
140°	320.5	299.0	280.7	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3
142.5°	318.3	299.4	281.9	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3
145°	315.1	299.0	283.3	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4
147.5°	311.7	297.6	283.9	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8
150°	309.2	296.2	283.9	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5
152.5°	306.1	294.5	283.4	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5
155°	301.0	291.4	282.3	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4
157.5°	296.3	288.1	280.9	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5
160°	292.5	286.1	279.6	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3
162.5°	289.1	283.4	278.3	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2
165°	283.9	279.6	276.4	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9
167.5°	278.8	275.8	273.3	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8
170°	275.8	273.6	272.0	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4
172.5°	272.8	271.1	270.3	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1
175°	268.8	268.2	268.2	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2
177.5°	267.1	266.6	266.6	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.4	11.0	12.3	14.6	15.9	17.6	18.7	17.9	16.6	15.6	14.4
90°	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7
92.5°	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3
95°	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5
97.5°	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7
100°	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3
102.5°	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1
105°	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2
107.5°	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5
110°	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8





TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5
115°	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1
117.5°	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6
120°	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1
122.5°	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5
125°	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6
127.5°	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4
130°	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7
132.5°	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9
135°	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9
137.5°	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1
140°	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6
142.5°	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0
145°	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8
147.5°	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9
150°	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9
152.5°	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7
155°	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2
157.5°	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8
160°	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4
162.5°	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7
165°	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1
167.5°	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9
170°	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5
172.5°	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7
175°	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4
177.5°	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	14.6	13.1	13.3	12.9	12.9	12.6	11.9
90°	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333216-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)