

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332649-840

Luminaire Tested: **S124DIP-S1020D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332649-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D810U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7740.2 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58																			
1	99	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53	49																			
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45	41																			
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	44	41	38	34																			
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30																			
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	32	29	26																			
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	23																			
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23	20																			
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18																			
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16																			
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.1
10°-20°	462.4	6.0
20°-30°	680.5	8.8
30°-40°	791.1	10.2
40°-50°	791.2	10.2
50°-60°	692.1	8.9
60°-70°	514.0	6.6
70°-80°	292.0	3.8
80°-90°	87.3	1.1
90°-100°	36.1	0.5
100°-110°	230.2	3.0
110°-120°	440.4	5.7
120°-130°	559.1	7.2
130°-140°	598.2	7.7
140°-150°	559.3	7.2
150°-160°	451.1	5.8
160°-170°	290.9	3.8
170°-180°	100.3	1.3
0°-30°	1307.0	16.9
0°-40°	2098.1	27.1
0°-60°	3581.3	46.3
0°-90°	4474.6	57.8
90°-120°	706.7	9.1
90°-150°	2423.3	31.3
90°-180°	3266.0	42.2
0°-180°	7740.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	2	11	17	22	24	6
95°	43	18	17	22	23	56
105°	238	242	246	252	225	249
115°	444	446	445	447	447	437
125°	624	627	625	628	628	557
135°	774	773	776	778	779	596
145°	892	894	895	895	897	557
155°	978	979	977	980	978	451
165°	1032	1028	1028	1034	1027	292
175°	1056	1051	1052	1058	1049	100
180°	1056	1056	1056	1056	1056	



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.5	29.7	29.8	29.9	30.1	30.2	30.2	30.2	30.3	30.3	30.5
90°	2.3	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4
92.5°	10.0	10.1	10.2	10.3	10.4	11.1	12.5	13.9	15.3	16.8	17.8
95°	43.4	37.5	31.5	25.5	19.6	16.7	16.9	17.1	17.2	17.4	18.4
97.5°	92.2	95.9	99.7	103.4	107.1	99.2	79.6	60.0	40.4	20.8	20.9
100°	129.5	132.7	135.8	139.0	142.1	131.6	107.3	83.2	59.0	34.7	31.7
102.5°	171.2	173.5	175.8	178.1	180.5	180.1	176.8	173.7	170.6	167.4	135.2
105°	237.6	238.7	239.7	240.9	241.9	242.9	243.7	244.6	245.5	246.3	247.9
107.5°	299.4	299.9	300.4	301.0	301.5	302.4	303.6	304.8	306.0	307.2	307.9
110°	341.1	341.6	342.1	342.6	343.3	344.0	345.1	346.1	347.2	348.2	348.6



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.4	383.4	384.4	385.4	386.1	386.6	387.0	387.5	388.0	388.0
115°	443.7	444.2	444.8	445.4	445.9	446.1	445.9	445.7	445.6	445.4	445.7
117.5°	499.8	500.5	501.2	501.9	502.6	503.2	503.5	503.9	504.3	504.7	504.6
120°	537.8	538.5	539.2	539.9	540.5	540.8	540.6	540.5	540.3	540.1	540.5
122.5°	573.1	573.5	573.9	574.3	574.8	575.1	575.3	575.6	575.8	576.1	576.3
125°	623.8	624.5	625.2	625.9	626.6	626.7	626.4	626.1	625.7	625.4	625.9
127.5°	671.8	672.0	672.2	672.4	672.5	673.0	673.8	674.6	675.4	676.2	676.1
130°	702.8	703.0	703.1	703.3	703.5	703.8	704.3	704.9	705.4	705.9	706.1
132.5°	731.1	731.4	731.8	732.2	732.5	733.0	733.6	734.3	734.9	735.6	735.8
135°	773.9	773.7	773.5	773.3	773.2	773.4	774.1	774.8	775.5	776.2	776.5
137.5°	811.5	811.6	811.7	811.7	811.8	812.2	813.0	813.9	814.6	815.4	815.8
140°	836.2	836.6	836.9	837.3	837.6	838.0	838.3	838.7	839.0	839.3	839.9
142.5°	858.3	858.9	859.6	860.2	860.8	861.2	861.4	861.7	861.9	862.1	862.5
145°	892.2	892.8	893.3	893.8	894.3	894.6	894.6	894.6	894.6	894.6	894.8
147.5°	919.3	920.3	921.2	922.2	923.2	923.6	923.4	923.2	923.0	922.9	923.0
150°	938.9	939.6	940.3	941.0	941.6	941.9	941.7	941.6	941.4	941.2	941.2
152.5°	955.2	955.8	956.3	956.9	957.6	957.7	957.4	957.0	956.6	956.3	956.6
155°	978.4	978.5	978.7	978.9	979.1	978.9	978.4	977.8	977.2	976.7	977.4
157.5°	997.7	997.6	997.5	997.4	997.3	996.9	996.3	995.8	995.2	994.6	995.5
160°	1009.2	1008.6	1008.0	1007.5	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0
162.5°	1019.3	1018.5	1017.8	1017.2	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5
165°	1032.0	1031.2	1030.3	1029.4	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5
167.5°	1042.1	1041.2	1040.3	1039.4	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1
170°	1047.8	1046.7	1045.7	1044.6	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2
172.5°	1051.6	1050.6	1049.5	1048.4	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0
175°	1055.7	1054.6	1053.6	1052.6	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3
177.5°	1057.6	1056.6	1055.6	1054.6	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	30.7	30.9	31.1	31.3	31.3	31.4	31.5	31.5
90°	19.5	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	18.9	19.9	20.9	21.5	21.6	21.6	21.7	21.8
95°	19.5	20.5	21.6	22.2	22.4	22.5	22.7	22.9
97.5°	21.1	21.2	21.3	21.4	21.6	21.7	21.9	22.1
100°	28.8	25.8	22.8	21.4	21.6	21.7	21.9	22.1
102.5°	103.0	70.9	38.7	22.6	22.6	22.6	22.7	22.7
105°	249.5	251.1	252.7	250.3	244.0	237.6	231.4	225.0
107.5°	308.7	309.4	310.2	310.9	311.6	312.3	313.0	313.7
110°	348.9	349.3	349.6	350.0	350.6	351.1	351.6	352.1



TEST NUMBER: P332649-840

CATALOG NUMBER: S124DIP-S1020D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.9	387.8	387.7	388.0	388.7	389.4	390.0	390.7
115°	446.1	446.4	446.8	447.0	447.0	447.0	447.0	447.0
117.5°	504.5	504.5	504.4	504.3	504.3	504.2	504.1	504.1
120°	540.8	541.2	541.5	541.5	541.2	540.8	540.5	540.1
122.5°	576.5	576.7	576.9	576.8	576.5	576.1	575.8	575.4
125°	626.4	626.9	627.4	627.8	628.0	628.1	628.3	628.5
127.5°	676.0	675.9	675.8	675.7	675.5	675.4	675.3	675.1
130°	706.3	706.4	706.6	706.7	706.7	706.7	706.7	706.7
132.5°	736.0	736.1	736.3	736.3	736.2	736.0	735.9	735.8
135°	776.9	777.2	777.6	777.9	778.3	778.6	779.0	779.3
137.5°	816.1	816.5	816.9	817.0	816.9	816.8	816.7	816.6
140°	840.4	840.9	841.4	841.8	842.0	842.1	842.3	842.5
142.5°	862.8	863.2	863.6	863.8	863.8	863.9	863.9	863.9
145°	894.9	895.1	895.3	895.5	896.0	896.3	896.7	897.0
147.5°	923.2	923.3	923.4	923.6	923.8	923.9	924.1	924.3
150°	941.2	941.2	941.2	941.3	941.5	941.6	941.8	942.0
152.5°	956.9	957.3	957.5	957.6	957.5	957.4	957.3	957.2
155°	978.2	978.9	979.6	979.7	979.1	978.6	978.1	977.5
157.5°	996.4	997.3	998.3	998.3	997.3	996.4	995.5	994.6
160°	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9
162.5°	1017.5	1018.5	1019.7	1019.6	1018.3	1017.1	1016.0	1014.8
165°	1030.9	1032.3	1033.7	1033.6	1032.0	1030.5	1028.9	1027.2
167.5°	1040.7	1042.2	1043.7	1043.6	1041.9	1040.1	1038.3	1036.6
170°	1046.6	1048.0	1049.5	1049.2	1047.5	1045.8	1044.0	1042.3
172.5°	1050.5	1051.9	1053.3	1053.0	1051.2	1049.2	1047.3	1045.4
175°	1054.9	1056.5	1058.0	1057.8	1055.7	1053.6	1051.5	1049.4
177.5°	1056.7	1057.8	1058.9	1058.6	1056.9	1055.3	1053.6	1051.9
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7

(END OF REPORT)