

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333229-830

Luminaire Tested: **S125DIP-S850D810U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333229-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6275.3 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69		62	60	58		51	49	48	43
2	89	82	76	70	82	76	70	66	64	60	57		54	51	49		44	42	41	36
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		39	37	35	30
4	74	64	56	50	68	59	52	47	50	45	41		43	38	35		35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35		38	34	30		32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31		35	30	27		29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27		31	27	24		26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	21		26	22	19		22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	1.9
10°-20°	329.6	5.3
20°-30°	486.6	7.8
30°-40°	567.8	9.0
40°-50°	570.3	9.1
50°-60°	500.6	8.0
60°-70°	373.0	5.9
70°-80°	213.3	3.4
80°-90°	64.1	1.0
90°-100°	36.1	0.6
100°-110°	222.7	3.5
110°-120°	403.9	6.4
120°-130°	518.4	8.3
130°-140°	557.5	8.9
140°-150°	523.3	8.3
150°-160°	423.3	6.7
160°-170°	273.8	4.4
170°-180°	94.4	1.5
0°-30°	932.8	14.9
0°-40°	1500.6	23.9
0°-60°	2571.4	41.0
0°-90°	3221.8	51.3
90°-120°	662.7	10.6
90°-150°	2262.0	36.0
90°-180°	3054.0	48.7
0°-180°	6275.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	7	12	15	18	5
95°	42	38	12	15	16	54
105°	217	219	220	220	219	230
115°	407	410	411	408	404	403
125°	579	584	584	581	579	517
135°	722	726	725	723	719	556
145°	837	838	838	839	834	523
155°	921	917	918	920	915	424
165°	972	968	969	972	967	275
175°	994	990	991	996	990	95
180°	994	994	994	994	994	



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.3	21.6	21.8	22.1	22.3	22.5	22.5	22.6	22.6	22.7	22.9
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	11.3	10.5	9.5	8.6	7.7	7.7	8.8	9.8	10.7	11.8	12.6
95°	42.0	41.6	41.0	40.5	40.1	36.7	30.4	24.2	18.0	11.8	12.6
97.5°	87.8	88.6	89.4	90.4	91.2	85.6	73.2	60.9	48.5	36.3	31.7
100°	123.1	123.6	124.0	124.6	125.1	125.6	126.3	127.0	127.6	128.3	103.9
102.5°	159.1	159.7	160.3	160.9	161.6	162.0	162.5	162.9	163.2	163.6	159.0
105°	216.7	217.4	218.0	218.7	219.3	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.5	276.5	276.5	276.5	276.5	276.7	277.0	277.4	277.7	278.1	278.1
110°	315.5	315.5	315.5	315.5	315.5	315.7	315.9	316.3	316.6	317.0	316.5



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.0	352.4	352.8	353.3	353.6	353.9	354.1	354.3	354.5	354.7	354.1
115°	406.9	407.7	408.5	409.3	410.2	410.7	410.9	410.9	411.1	411.3	410.7
117.5°	463.6	463.6	463.5	463.5	463.5	463.8	464.4	465.1	465.7	466.3	465.4
120°	499.0	498.9	498.7	498.5	498.3	498.5	499.0	499.5	500.0	500.5	500.2
122.5°	530.3	530.9	531.5	532.2	532.7	533.2	533.4	533.7	533.9	534.1	533.8
125°	578.6	579.8	580.9	582.1	583.2	583.8	583.8	583.8	583.8	583.8	583.2
127.5°	624.8	625.6	626.4	627.3	628.0	628.4	628.3	628.2	628.1	628.0	627.6
130°	653.1	653.9	654.7	655.5	656.4	656.9	657.0	657.1	657.3	657.5	657.0
132.5°	681.4	682.3	683.2	684.2	685.2	685.5	685.1	684.8	684.4	684.0	683.9
135°	721.6	722.6	723.6	724.6	725.6	725.9	725.6	725.2	724.9	724.6	724.2
137.5°	758.7	759.5	760.3	761.2	762.0	762.3	762.0	761.8	761.5	761.1	761.2
140°	782.8	783.2	783.4	783.8	784.1	784.2	784.0	783.9	783.7	783.5	783.9
142.5°	804.6	804.8	805.0	805.2	805.4	805.6	805.9	806.1	806.3	806.5	806.6
145°	836.6	837.0	837.3	837.6	837.9	838.1	838.1	838.1	838.1	838.1	838.3
147.5°	864.6	864.6	864.5	864.4	864.4	864.4	864.6	864.8	865.1	865.3	865.4
150°	882.3	882.0	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3	882.7
152.5°	899.5	898.7	898.0	897.3	896.5	896.4	896.6	897.0	897.3	897.7	898.0
155°	921.4	920.4	919.5	918.4	917.5	917.1	917.5	917.8	918.1	918.4	918.9
157.5°	938.3	937.7	937.2	936.6	935.9	935.7	935.8	935.8	935.8	935.9	936.3
160°	950.2	949.1	948.2	947.2	946.2	945.8	945.9	946.1	946.3	946.4	947.1
162.5°	959.6	958.6	957.6	956.6	955.6	955.3	955.4	955.5	955.7	955.9	956.8
165°	972.2	971.3	970.3	969.3	968.3	967.9	968.1	968.3	968.4	968.6	969.6
167.5°	981.7	980.7	979.7	978.6	977.6	977.2	977.3	977.5	977.7	977.9	979.0
170°	987.0	985.8	984.7	983.5	982.4	981.9	982.0	982.2	982.4	982.6	983.9
172.5°	990.5	989.4	988.3	987.1	985.9	985.5	985.8	986.1	986.4	986.7	987.9
175°	994.4	993.3	992.4	991.5	990.4	990.0	990.1	990.3	990.5	990.7	992.0
177.5°	996.2	995.3	994.6	993.8	993.0	992.7	992.8	992.9	993.1	993.2	994.1
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	23.1	23.2	23.4	23.4	23.1	22.8	22.6	22.3
90°	13.5	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	13.5	14.2	15.1	15.6	15.8	16.0	16.3	16.5
95°	13.5	14.2	15.1	15.5	15.5	15.5	15.5	15.5
97.5°	27.1	22.4	17.8	15.5	15.5	15.5	15.5	15.5
100°	79.5	55.0	30.6	18.1	17.4	16.8	16.1	15.5
102.5°	154.4	149.8	145.2	137.3	126.1	115.0	103.9	92.7
105°	219.6	219.6	219.6	219.6	219.4	219.2	219.0	219.0
107.5°	278.1	278.1	278.1	278.0	277.5	276.9	276.4	276.0
110°	315.9	315.5	315.0	314.8	315.0	315.2	315.3	315.5



TEST NUMBER: P333229-830

CATALOG NUMBER: S125DIP-S850D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	352.8	352.2	351.8	351.6	351.3	351.1	350.9
115°	410.0	409.3	408.7	407.8	406.9	405.9	404.9	404.0
117.5°	464.6	463.7	462.9	462.2	461.8	461.4	461.0	460.5
120°	499.8	499.5	499.2	498.6	497.8	497.0	496.2	495.3
122.5°	533.5	533.1	532.8	532.2	531.2	530.3	529.3	528.4
125°	582.5	581.8	581.2	580.6	580.1	579.6	579.1	578.6
127.5°	627.3	627.0	626.6	625.8	624.6	623.4	622.2	620.9
130°	656.5	656.0	655.5	654.9	654.0	653.3	652.4	651.6
132.5°	683.8	683.7	683.6	683.2	682.4	681.6	680.7	680.0
135°	724.0	723.6	723.3	722.6	721.6	720.7	719.6	718.7
137.5°	761.3	761.3	761.4	761.0	760.2	759.3	758.5	757.6
140°	784.2	784.6	784.9	784.6	783.5	782.6	781.6	780.6
142.5°	806.7	806.7	806.8	806.3	805.4	804.4	803.4	802.4
145°	838.4	838.6	838.8	838.3	837.4	836.4	835.4	834.4
147.5°	865.6	865.8	866.0	865.5	864.3	863.2	862.0	860.8
150°	883.0	883.4	883.6	883.2	881.8	880.5	879.2	877.9
152.5°	898.3	898.6	899.0	898.5	897.4	896.2	895.0	893.8
155°	919.5	919.9	920.4	920.0	918.7	917.4	916.1	914.7
157.5°	936.9	937.5	937.9	937.5	936.2	934.9	933.6	932.3
160°	947.7	948.4	949.0	948.8	947.4	946.1	944.8	943.5
162.5°	957.7	958.7	959.5	959.3	957.8	956.4	955.0	953.6
165°	970.5	971.5	972.5	972.3	971.0	969.7	968.4	967.0
167.5°	980.2	981.4	982.6	982.4	980.9	979.5	978.0	976.6
170°	985.1	986.5	987.8	987.7	986.3	984.8	983.3	981.8
172.5°	989.0	990.2	991.5	991.3	989.8	988.4	986.8	985.3
175°	993.3	994.6	995.9	995.8	994.4	992.9	991.5	990.0
177.5°	995.0	995.9	996.8	996.8	995.7	994.7	993.6	992.6
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4

(END OF REPORT)