

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332705-840

Luminaire Tested: **S124DIP-S1195D1035U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332705-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1035U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8899.2 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58																				
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54	49																				
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45	41																				
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38	35																				
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30																				
5	70	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29	26																				
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23																				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20																				
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18																				
9	51	39	31	26	48	37	30	25	32	27	23	29	24	21	25	21	18	16																				
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.1
10°-20°	534.0	6.0
20°-30°	786.0	8.8
30°-40°	913.7	10.3
40°-50°	913.7	10.3
50°-60°	799.3	9.0
60°-70°	593.6	6.7
70°-80°	337.2	3.8
80°-90°	100.1	1.1
90°-100°	370.6	4.2
100°-110°	771.4	8.7
110°-120°	690.9	7.8
120°-130°	581.2	6.5
130°-140°	484.6	5.4
140°-150°	370.2	4.2
150°-160°	260.2	2.9
160°-170°	153.1	1.7
170°-180°	49.8	0.6
0°-30°	1509.5	17.0
0°-40°	2423.2	27.2
0°-60°	4136.2	46.5
0°-90°	5167.2	58.1
90°-120°	1833.0	20.6
90°-150°	3269.0	36.7
90°-180°	3732.0	41.9
0°-180°	8899.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	1	8	18	20	21	6
95°	33	105	822	407	246	37
105°	118	171	661	1424	1418	126
115°	208	261	590	1133	1362	206
125°	289	344	587	964	1087	258
135°	344	409	582	856	972	266
145°	396	454	579	722	794	249
155°	451	486	563	637	664	208
165°	491	506	539	571	580	139
175°	512	513	517	524	522	49
180°	513	513	513	513	513	



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	33.7	33.8	34.1	34.1	34.0	33.7	34.6	34.3	34.4	34.6	34.4
90°	1.0	3.0	6.1	7.1	8.1	8.1	14.1	14.1	16.2	18.2	17.2
92.5°	11.5	16.8	26.3	38.5	53.2	74.2	125.4	203.7	279.8	319.8	266.4
95°	33.2	36.3	46.4	59.5	83.7	126.0	213.7	379.1	620.1	821.6	844.9
97.5°	59.7	59.7	68.4	80.5	101.2	136.7	204.3	340.7	580.3	865.4	1061.4
100°	76.6	76.6	83.7	95.7	114.9	147.2	206.7	320.6	526.2	810.5	1068.6
102.5°	92.7	94.3	100.6	111.9	130.3	160.9	214.7	315.0	490.0	742.0	1008.1
105°	118.0	121.0	126.0	138.1	156.2	185.5	233.9	317.6	458.7	661.4	898.3
107.5°	145.8	147.8	152.8	165.7	183.1	211.9	256.3	332.4	453.0	616.2	809.5
110°	164.3	166.3	171.4	183.5	201.7	228.8	273.2	343.8	454.6	600.9	765.2



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.1	184.1	190.0	201.3	219.3	246.6	289.3	355.9	459.5	593.6	740.2
115°	207.7	210.7	217.7	227.8	247.0	274.2	314.6	375.1	468.8	589.8	716.8
117.5°	234.3	237.1	243.4	254.5	272.4	300.6	338.9	394.6	478.7	588.8	706.3
120°	252.1	254.1	261.2	272.2	289.3	317.6	355.9	408.3	485.9	588.8	700.6
122.5°	268.2	270.1	277.2	287.5	306.3	333.7	372.0	421.2	493.2	587.9	694.2
125°	289.3	293.4	299.4	310.5	329.6	357.9	394.2	440.6	504.1	586.7	683.6
127.5°	308.1	311.3	318.6	331.2	351.2	379.7	414.8	457.3	512.7	584.5	669.2
130°	318.6	322.7	330.6	345.8	365.0	394.2	428.5	467.8	519.2	583.7	660.4
132.5°	329.0	332.2	342.7	357.1	377.9	405.5	439.8	478.3	524.8	582.9	652.3
135°	343.8	347.8	357.9	375.1	396.2	422.4	455.7	492.0	533.3	581.7	640.2
137.5°	358.5	362.3	373.4	389.7	411.7	436.8	467.8	501.7	538.4	581.5	629.7
140°	369.0	372.0	383.1	400.2	421.4	445.7	475.8	508.1	542.4	580.7	624.1
142.5°	380.3	383.3	393.5	409.9	430.3	453.6	483.1	512.9	545.6	580.7	619.2
145°	396.2	399.2	409.3	423.4	442.6	464.7	491.0	518.2	547.4	578.7	611.0
147.5°	414.1	415.2	424.0	438.6	454.4	474.4	499.1	522.8	548.5	575.0	603.5
150°	425.5	426.5	434.5	446.7	461.7	480.9	503.1	525.2	548.5	572.6	597.8
152.5°	436.0	436.2	444.2	455.4	469.0	486.6	506.3	526.8	546.8	568.6	591.4
155°	450.6	451.6	457.7	467.8	478.9	494.0	511.1	528.3	544.4	562.6	581.7
157.5°	464.9	464.9	470.6	478.5	488.2	500.1	514.5	528.3	541.8	556.3	571.8
160°	473.8	473.8	477.9	484.9	493.0	504.1	516.1	528.3	539.4	551.5	564.6
162.5°	481.9	481.1	484.3	490.6	497.9	506.5	517.8	528.3	536.9	546.6	558.2
165°	491.0	491.0	493.0	498.1	503.1	509.1	518.2	526.2	532.3	539.4	547.4
167.5°	500.1	499.1	500.1	503.9	506.8	511.3	518.0	523.8	527.5	532.1	537.8
170°	504.1	503.1	504.1	507.2	509.1	512.1	517.2	522.2	524.2	527.3	531.3
172.5°	508.1	507.2	507.3	509.5	510.7	512.9	516.3	520.6	521.0	522.4	525.6
175°	512.1	511.1	511.1	512.1	513.1	513.1	515.1	518.2	517.2	517.2	519.2
177.5°	513.9	513.1	512.3	513.1	513.1	513.1	513.9	515.5	513.9	513.9	514.7
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	34.6	34.8	35.0	35.0	35.2	35.4	35.2	35.2
90°	18.2	19.2	20.2	20.2	21.2	22.2	21.2	21.2
92.5°	198.0	149.1	118.6	98.4	86.5	81.1	77.7	77.7
95°	747.0	590.8	455.7	357.9	308.5	277.2	259.1	246.0
97.5°	1103.8	1045.6	947.1	841.8	769.4	708.7	678.5	657.5
100°	1215.9	1236.0	1186.6	1112.0	1024.3	962.8	932.5	924.5
102.5°	1210.2	1310.2	1324.5	1293.4	1239.6	1195.1	1163.3	1156.8
105°	1129.1	1303.5	1403.3	1444.7	1446.7	1438.7	1424.5	1418.5
107.5°	1014.0	1199.7	1340.3	1430.2	1480.0	1503.0	1513.1	1515.7
110°	944.6	1119.0	1265.3	1376.1	1447.7	1490.1	1508.2	1517.3



TEST NUMBER: P332705-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	893.8	1048.0	1186.2	1297.1	1378.4	1429.6	1455.0	1469.7
115°	842.8	966.8	1084.8	1181.5	1261.2	1321.7	1353.9	1362.0
117.5°	817.8	920.5	1013.2	1095.3	1163.3	1214.1	1246.7	1252.9
120°	806.5	900.3	981.0	1052.5	1109.9	1154.4	1180.5	1191.6
122.5°	796.9	887.4	960.8	1023.5	1072.1	1109.9	1132.2	1143.3
125°	780.3	867.0	936.5	992.0	1032.4	1061.6	1080.8	1086.8
127.5°	760.1	843.0	912.4	965.0	1005.5	1031.6	1047.6	1053.7
130°	744.1	823.6	892.2	945.6	986.9	1012.2	1028.3	1034.4
132.5°	727.1	801.9	868.8	922.3	962.8	991.2	1006.5	1012.6
135°	703.7	769.2	830.7	881.1	921.5	949.7	965.8	971.9
137.5°	682.6	738.0	789.8	835.4	873.0	900.9	914.2	921.5
140°	670.4	717.8	763.2	805.5	840.8	863.0	877.1	885.1
142.5°	659.1	700.8	739.8	776.5	807.7	828.3	840.8	846.5
145°	643.2	677.5	707.7	736.0	761.1	778.3	788.4	793.5
147.5°	630.1	657.3	681.6	703.7	722.3	737.0	744.7	746.4
150°	622.1	645.2	665.4	683.6	699.6	712.8	718.8	719.8
152.5°	613.2	633.1	651.7	666.6	680.3	690.9	694.6	695.6
155°	599.9	616.0	631.1	643.2	653.3	661.4	664.4	664.4
157.5°	585.5	599.1	611.8	621.5	629.0	635.1	636.9	636.9
160°	576.6	587.7	598.8	606.9	613.0	619.0	620.1	620.1
162.5°	567.7	577.2	585.9	593.2	597.6	603.7	604.7	603.9
165°	555.5	561.6	568.6	573.6	577.6	581.7	580.7	579.7
167.5°	543.6	548.3	553.9	556.9	559.0	561.6	561.4	560.6
170°	536.3	539.4	543.4	546.4	548.5	549.5	548.5	548.5
172.5°	529.9	532.1	534.5	536.7	538.0	539.0	538.0	536.3
175°	521.2	522.2	524.2	524.2	524.2	526.2	524.2	522.2
177.5°	515.5	516.3	516.3	517.2	516.3	517.2	515.5	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1

(END OF REPORT)