

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333598-830

Luminaire Tested: **S125RDIP-S1090D1035U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333598-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7916.2 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



49% Up

51% Dn



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	43	40	38	36	32
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	32	28	32	28	25	27	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	1.9
10°-20°	435.5	5.5
20°-30°	690.5	8.7
30°-40°	832.7	10.5
40°-50°	743.6	9.4
50°-60°	570.3	7.2
60°-70°	370.6	4.7
70°-80°	180.2	2.3
80°-90°	45.6	0.6
90°-100°	46.1	0.6
100°-110°	284.3	3.6
110°-120°	515.7	6.5
120°-130°	661.8	8.4
130°-140°	711.8	9.0
140°-150°	668.2	8.4
150°-160°	540.5	6.8
160°-170°	349.6	4.4
170°-180°	120.6	1.5
0°-30°	1274.6	16.1
0°-40°	2107.3	26.6
0°-60°	3421.2	43.2
0°-90°	4017.6	50.8
90°-120°	846.1	10.7
90°-150°	2887.9	36.5
90°-180°	3899.0	49.3
0°-180°	7916.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	23	1	23	1	23	11
95°	20	54	20	54	20	16
105°	280	277	280	277	280	253
115°	516	520	516	520	516	512
125°	739	739	739	739	739	657
135°	918	921	918	921	918	708
145°	1065	1068	1065	1068	1065	665
155°	1168	1176	1168	1176	1168	538
165°	1235	1241	1235	1241	1235	348
175°	1264	1270	1264	1270	1264	120
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	15.7	15.1	14.4	14.3	14.7	15.6	14.8	14.1	13.9	13.7	13.9
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	21.1	20.8	20.5	20.2	19.9	19.2	18.2	17.2	16.1	15.1	13.8
95°	19.8	19.8	19.8	19.8	19.8	19.2	18.2	17.2	16.1	15.1	23.0
97.5°	19.8	19.8	19.8	19.8	19.8	22.7	28.7	34.5	40.4	46.3	62.0
100°	19.8	20.6	21.4	22.2	23.1	39.1	70.3	101.4	132.6	163.7	162.9
102.5°	118.4	132.6	146.8	161.1	175.3	185.3	191.2	197.1	203.0	209.0	208.4
105°	279.5	279.7	279.9	280.1	280.3	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	352.3	353.0	353.6	354.2	354.9	355.2	355.2	355.1	355.1	355.0	354.6
110°	402.7	402.6	402.4	402.2	402.0	402.2	402.7	403.4	404.1	404.6	404.3



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.0	448.3	448.6	448.8	449.1	449.7	450.4	451.3	452.0	452.9	452.6
115°	515.8	517.0	518.2	519.5	520.8	521.8	522.6	523.5	524.3	525.1	524.9
117.5°	588.0	588.5	589.1	589.7	590.1	591.0	592.1	593.1	594.3	595.3	594.6
120°	632.4	633.5	634.5	635.6	636.6	637.3	637.7	638.2	638.6	639.0	638.4
122.5°	674.6	675.8	677.0	678.3	679.4	680.2	680.7	681.1	681.5	681.9	681.6
125°	738.8	739.4	740.0	740.6	741.3	742.0	742.8	743.7	744.5	745.4	745.4
127.5°	792.8	794.4	795.9	797.4	799.0	799.9	800.4	800.9	801.3	801.8	801.9
130°	831.9	833.0	834.1	835.1	836.1	837.0	837.5	838.2	838.9	839.4	839.2
132.5°	868.1	869.1	870.2	871.2	872.2	872.8	873.0	873.1	873.2	873.4	873.8
135°	917.6	918.8	920.1	921.3	922.6	923.4	923.9	924.3	924.6	925.1	925.5
137.5°	967.2	968.4	969.4	970.5	971.6	972.1	972.0	971.9	971.9	971.8	972.1
140°	996.6	997.9	999.1	1000.4	1001.6	1002.0	1001.6	1001.3	1000.8	1000.4	1000.6
142.5°	1024.4	1025.8	1027.0	1028.2	1029.5	1030.1	1030.0	1029.9	1029.8	1029.7	1029.4
145°	1065.4	1066.6	1067.8	1069.1	1070.4	1070.8	1070.6	1070.4	1070.3	1070.1	1070.1
147.5°	1099.0	1100.5	1102.0	1103.5	1105.0	1105.7	1105.4	1105.1	1104.9	1104.7	1104.4
150°	1120.9	1122.5	1124.2	1125.9	1127.6	1128.1	1127.8	1127.4	1126.9	1126.5	1126.1
152.5°	1141.1	1142.6	1144.2	1145.7	1147.2	1147.7	1147.4	1146.9	1146.5	1146.0	1145.7
155°	1167.9	1169.6	1171.2	1172.9	1174.6	1175.2	1174.5	1173.8	1173.3	1172.6	1172.1
157.5°	1190.3	1191.9	1193.6	1195.3	1197.0	1197.5	1196.8	1196.2	1195.5	1194.9	1194.8
160°	1204.6	1206.3	1208.0	1209.7	1211.3	1211.7	1210.9	1210.0	1209.2	1208.3	1208.2
162.5°	1217.4	1219.3	1221.1	1222.9	1224.7	1225.1	1223.9	1222.8	1221.6	1220.4	1220.2
165°	1234.7	1236.4	1238.0	1239.7	1241.4	1241.6	1240.4	1239.1	1237.8	1236.6	1236.4
167.5°	1246.8	1248.7	1250.6	1252.5	1254.3	1254.5	1253.0	1251.5	1250.0	1248.5	1248.2
170°	1253.6	1255.5	1257.4	1259.1	1261.0	1261.2	1259.5	1257.8	1256.1	1254.5	1254.2
172.5°	1258.1	1259.9	1261.8	1263.7	1265.6	1265.7	1264.2	1262.7	1261.2	1259.7	1259.3
175°	1263.9	1265.7	1267.6	1269.5	1271.4	1271.5	1269.9	1268.2	1266.5	1264.8	1264.6
177.5°	1267.2	1268.7	1270.0	1271.3	1272.6	1272.7	1271.6	1270.4	1269.2	1268.0	1267.9
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	14.1	13.9	14.0	13.8	12.9	15.1	16.3	16.5	15.8	15.1	14.4
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	12.4	11.1	9.9	9.8	10.9	12.2	13.3	14.5	13.3	12.2	10.9
95°	30.9	38.9	46.8	51.2	51.7	52.4	53.0	53.6	53.0	52.4	51.7
97.5°	77.8	93.5	109.2	116.5	115.4	114.2	113.1	112.0	113.1	114.2	115.4
100°	162.1	161.3	160.4	159.7	159.0	158.4	157.8	157.1	157.8	158.4	159.0
102.5°	207.9	207.5	206.9	206.2	205.5	204.7	203.9	203.1	203.9	204.7	205.5
105°	280.4	280.4	280.4	280.0	279.2	278.3	277.5	276.6	277.5	278.3	279.2
107.5°	354.1	353.7	353.3	353.1	353.1	353.1	353.1	353.1	353.1	353.1	353.1
110°	403.9	403.4	403.0	402.7	402.7	402.7	402.7	402.7	402.7	402.7	402.7



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.3	452.1	451.9	451.5	451.0	450.4	450.0	449.5	450.0	450.4	451.0
115°	524.7	524.5	524.3	523.7	522.6	521.6	520.6	519.5	520.6	521.6	522.6
117.5°	593.7	593.0	592.2	591.8	591.8	591.8	591.9	591.9	591.9	591.8	591.8
120°	637.7	637.2	636.5	636.3	636.5	636.7	636.9	637.2	636.9	636.7	636.5
122.5°	681.4	681.1	680.7	680.2	679.4	678.6	677.8	677.0	677.8	678.6	679.4
125°	745.4	745.4	745.4	744.6	743.2	741.7	740.2	738.8	740.2	741.7	743.2
127.5°	802.1	802.2	802.3	801.8	800.8	799.7	798.7	797.7	798.7	799.7	800.8
130°	839.1	838.9	838.6	838.0	837.0	835.9	834.9	833.8	834.9	835.9	837.0
132.5°	874.3	874.7	875.2	874.8	873.5	872.4	871.2	870.0	871.2	872.4	873.5
135°	926.0	926.3	926.8	926.3	925.1	923.9	922.6	921.3	922.6	923.9	925.1
137.5°	972.5	972.9	973.3	972.9	971.9	970.7	969.7	968.6	969.7	970.7	971.9
140°	1000.8	1001.0	1001.3	1001.1	1000.7	1000.3	999.8	999.5	999.8	1000.3	1000.7
142.5°	1029.2	1028.9	1028.6	1028.3	1028.0	1027.8	1027.6	1027.3	1027.6	1027.8	1028.0
145°	1070.1	1070.1	1070.1	1069.8	1069.4	1068.9	1068.6	1068.2	1068.6	1068.9	1069.4
147.5°	1104.2	1103.9	1103.6	1103.5	1103.6	1103.7	1103.8	1103.9	1103.8	1103.7	1103.6
150°	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.1	1125.7	1125.2
152.5°	1145.2	1144.8	1144.4	1144.6	1145.6	1146.5	1147.5	1148.3	1147.5	1146.5	1145.6
155°	1171.8	1171.4	1170.9	1171.4	1172.6	1173.8	1175.2	1176.4	1175.2	1173.8	1172.6
157.5°	1194.8	1194.7	1194.7	1195.0	1195.8	1196.6	1197.2	1198.0	1197.2	1196.6	1195.8
160°	1208.0	1207.8	1207.5	1208.1	1209.3	1210.6	1211.8	1213.1	1211.8	1210.6	1209.3
162.5°	1220.0	1219.7	1219.6	1220.1	1221.3	1222.6	1223.9	1225.1	1223.9	1222.6	1221.3
165°	1236.1	1236.0	1235.8	1236.3	1237.6	1238.8	1240.0	1241.3	1240.0	1238.8	1237.6
167.5°	1248.0	1247.8	1247.6	1248.2	1249.4	1250.8	1252.1	1253.4	1252.1	1250.8	1249.4
170°	1254.1	1253.9	1253.7	1254.2	1255.7	1257.2	1258.7	1260.1	1258.7	1257.2	1255.7
172.5°	1259.0	1258.6	1258.3	1258.8	1260.3	1261.7	1263.2	1264.6	1263.2	1261.7	1260.3
175°	1264.4	1264.2	1264.0	1264.5	1265.7	1267.1	1268.3	1269.5	1268.3	1267.1	1265.7
177.5°	1267.7	1267.5	1267.3	1267.8	1268.8	1269.8	1270.8	1271.8	1270.8	1269.8	1268.8
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	14.2	14.6	14.3	15.6	14.4	15.3	15.5	15.2	15.4	15.6	15.2
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	9.8	9.9	11.1	12.4	13.8	15.1	16.1	17.2	18.2	19.2	19.9
95°	51.2	46.8	38.9	30.9	23.0	15.1	16.1	17.2	18.2	19.2	19.8
97.5°	116.5	109.2	93.5	77.8	62.0	46.3	40.4	34.5	28.7	22.7	19.8
100°	159.7	160.4	161.3	162.1	162.9	163.7	132.6	101.4	70.3	39.1	23.1
102.5°	206.2	206.9	207.5	207.9	208.4	209.0	203.0	197.1	191.2	185.3	175.3
105°	280.0	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.3
107.5°	353.1	353.3	353.7	354.1	354.6	355.0	355.1	355.1	355.2	355.2	354.9
110°	402.7	403.0	403.4	403.9	404.3	404.6	404.1	403.4	402.7	402.2	402.0



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	451.5	451.9	452.1	452.3	452.6	452.9	452.0	451.3	450.4	449.7	449.1
115°	523.7	524.3	524.5	524.7	524.9	525.1	524.3	523.5	522.6	521.8	520.8
117.5°	591.8	592.2	593.0	593.7	594.6	595.3	594.3	593.1	592.1	591.0	590.1
120°	636.3	636.5	637.2	637.7	638.4	639.0	638.6	638.2	637.7	637.3	636.6
122.5°	680.2	680.7	681.1	681.4	681.6	681.9	681.5	681.1	680.7	680.2	679.4
125°	744.6	745.4	745.4	745.4	745.4	745.4	744.5	743.7	742.8	742.0	741.3
127.5°	801.8	802.3	802.2	802.1	801.9	801.8	801.3	800.9	800.4	799.9	799.0
130°	838.0	838.6	838.9	839.1	839.2	839.4	838.9	838.2	837.5	837.0	836.1
132.5°	874.8	875.2	874.7	874.3	873.8	873.4	873.2	873.1	873.0	872.8	872.2
135°	926.3	926.8	926.3	926.0	925.5	925.1	924.6	924.3	923.9	923.4	922.6
137.5°	972.9	973.3	972.9	972.5	972.1	971.8	971.9	971.9	972.0	972.1	971.6
140°	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8	1001.3	1001.6	1002.0	1001.6
142.5°	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8	1029.9	1030.0	1030.1	1029.5
145°	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3	1070.4	1070.6	1070.8	1070.4
147.5°	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9	1105.1	1105.4	1105.7	1105.0
150°	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9	1127.4	1127.8	1128.1	1127.6
152.5°	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5	1146.9	1147.4	1147.7	1147.2
155°	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3	1173.8	1174.5	1175.2	1174.6
157.5°	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5	1196.2	1196.8	1197.5	1197.0
160°	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2	1210.0	1210.9	1211.7	1211.3
162.5°	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6	1222.8	1223.9	1225.1	1224.7
165°	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8	1239.1	1240.4	1241.6	1241.4
167.5°	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0	1251.5	1253.0	1254.5	1254.3
170°	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1	1257.8	1259.5	1261.2	1261.0
172.5°	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2	1262.7	1264.2	1265.7	1265.6
175°	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5	1268.2	1269.9	1271.5	1271.4
177.5°	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2	1270.4	1271.6	1272.7	1272.6
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	15.8	15.5	15.6	15.7	15.6	15.5	15.8	15.2	15.6	15.4	15.2
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	20.2	20.5	20.8	21.1	20.8	20.5	20.2	19.9	19.2	18.2	17.2
95°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.2	18.2	17.2
97.5°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8	22.7	28.7	34.5
100°	22.2	21.4	20.6	19.8	20.6	21.4	22.2	23.1	39.1	70.3	101.4
102.5°	161.1	146.8	132.6	118.4	132.6	146.8	161.1	175.3	185.3	191.2	197.1
105°	280.1	279.9	279.7	279.5	279.7	279.9	280.1	280.3	280.4	280.4	280.4
107.5°	354.2	353.6	353.0	352.3	353.0	353.6	354.2	354.9	355.2	355.2	355.1
110°	402.2	402.4	402.6	402.7	402.6	402.4	402.2	402.0	402.2	402.7	403.4



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.8	448.6	448.3	448.0	448.3	448.6	448.8	449.1	449.7	450.4	451.3
115°	519.5	518.2	517.0	515.8	517.0	518.2	519.5	520.8	521.8	522.6	523.5
117.5°	589.7	589.1	588.5	588.0	588.5	589.1	589.7	590.1	591.0	592.1	593.1
120°	635.6	634.5	633.5	632.4	633.5	634.5	635.6	636.6	637.3	637.7	638.2
122.5°	678.3	677.0	675.8	674.6	675.8	677.0	678.3	679.4	680.2	680.7	681.1
125°	740.6	740.0	739.4	738.8	739.4	740.0	740.6	741.3	742.0	742.8	743.7
127.5°	797.4	795.9	794.4	792.8	794.4	795.9	797.4	799.0	799.9	800.4	800.9
130°	835.1	834.1	833.0	831.9	833.0	834.1	835.1	836.1	837.0	837.5	838.2
132.5°	871.2	870.2	869.1	868.1	869.1	870.2	871.2	872.2	872.8	873.0	873.1
135°	921.3	920.1	918.8	917.6	918.8	920.1	921.3	922.6	923.4	923.9	924.3
137.5°	970.5	969.4	968.4	967.2	968.4	969.4	970.5	971.6	972.1	972.0	971.9
140°	1000.4	999.1	997.9	996.6	997.9	999.1	1000.4	1001.6	1002.0	1001.6	1001.3
142.5°	1028.2	1027.0	1025.8	1024.4	1025.8	1027.0	1028.2	1029.5	1030.1	1030.0	1029.9
145°	1069.1	1067.8	1066.6	1065.4	1066.6	1067.8	1069.1	1070.4	1070.8	1070.6	1070.4
147.5°	1103.5	1102.0	1100.5	1099.0	1100.5	1102.0	1103.5	1105.0	1105.7	1105.4	1105.1
150°	1125.9	1124.2	1122.5	1120.9	1122.5	1124.2	1125.9	1127.6	1128.1	1127.8	1127.4
152.5°	1145.7	1144.2	1142.6	1141.1	1142.6	1144.2	1145.7	1147.2	1147.7	1147.4	1146.9
155°	1172.9	1171.2	1169.6	1167.9	1169.6	1171.2	1172.9	1174.6	1175.2	1174.5	1173.8
157.5°	1195.3	1193.6	1191.9	1190.3	1191.9	1193.6	1195.3	1197.0	1197.5	1196.8	1196.2
160°	1209.7	1208.0	1206.3	1204.6	1206.3	1208.0	1209.7	1211.3	1211.7	1210.9	1210.0
162.5°	1222.9	1221.1	1219.3	1217.4	1219.3	1221.1	1222.9	1224.7	1225.1	1223.9	1222.8
165°	1239.7	1238.0	1236.4	1234.7	1236.4	1238.0	1239.7	1241.4	1241.6	1240.4	1239.1
167.5°	1252.5	1250.6	1248.7	1246.8	1248.7	1250.6	1252.5	1254.3	1254.5	1253.0	1251.5
170°	1259.1	1257.4	1255.5	1253.6	1255.5	1257.4	1259.1	1261.0	1261.2	1259.5	1257.8
172.5°	1263.7	1261.8	1259.9	1258.1	1259.9	1261.8	1263.7	1265.6	1265.7	1264.2	1262.7
175°	1269.5	1267.6	1265.7	1263.9	1265.7	1267.6	1269.5	1271.4	1271.5	1269.9	1268.2
177.5°	1271.3	1270.0	1268.7	1267.2	1268.7	1270.0	1271.3	1272.6	1272.7	1271.6	1270.4
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	15.5	15.3	14.4	15.6	14.3	14.6	14.2	14.4	15.1	15.8	16.5
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	16.1	15.1	13.8	12.4	11.1	9.9	9.8	10.9	12.2	13.3	14.5
95°	16.1	15.1	23.0	30.9	38.9	46.8	51.2	51.7	52.4	53.0	53.6
97.5°	40.4	46.3	62.0	77.8	93.5	109.2	116.5	115.4	114.2	113.1	112.0
100°	132.6	163.7	162.9	162.1	161.3	160.4	159.7	159.0	158.4	157.8	157.1
102.5°	203.0	209.0	208.4	207.9	207.5	206.9	206.2	205.5	204.7	203.9	203.1
105°	280.4	280.4	280.4	280.4	280.4	280.4	280.0	279.2	278.3	277.5	276.6
107.5°	355.1	355.0	354.6	354.1	353.7	353.3	353.1	353.1	353.1	353.1	353.1
110°	404.1	404.6	404.3	403.9	403.4	403.0	402.7	402.7	402.7	402.7	402.7



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.0	452.9	452.6	452.3	452.1	451.9	451.5	451.0	450.4	450.0	449.5
115°	524.3	525.1	524.9	524.7	524.5	524.3	523.7	522.6	521.6	520.6	519.5
117.5°	594.3	595.3	594.6	593.7	593.0	592.2	591.8	591.8	591.8	591.9	591.9
120°	638.6	639.0	638.4	637.7	637.2	636.5	636.3	636.5	636.7	636.9	637.2
122.5°	681.5	681.9	681.6	681.4	681.1	680.7	680.2	679.4	678.6	677.8	677.0
125°	744.5	745.4	745.4	745.4	745.4	745.4	744.6	743.2	741.7	740.2	738.8
127.5°	801.3	801.8	801.9	802.1	802.2	802.3	801.8	800.8	799.7	798.7	797.7
130°	838.9	839.4	839.2	839.1	838.9	838.6	838.0	837.0	835.9	834.9	833.8
132.5°	873.2	873.4	873.8	874.3	874.7	875.2	874.8	873.5	872.4	871.2	870.0
135°	924.6	925.1	925.5	926.0	926.3	926.8	926.3	925.1	923.9	922.6	921.3
137.5°	971.9	971.8	972.1	972.5	972.9	973.3	972.9	971.9	970.7	969.7	968.6
140°	1000.8	1000.4	1000.6	1000.8	1001.0	1001.3	1001.1	1000.7	1000.3	999.8	999.5
142.5°	1029.8	1029.7	1029.4	1029.2	1028.9	1028.6	1028.3	1028.0	1027.8	1027.6	1027.3
145°	1070.3	1070.1	1070.1	1070.1	1070.1	1070.1	1069.8	1069.4	1068.9	1068.6	1068.2
147.5°	1104.9	1104.7	1104.4	1104.2	1103.9	1103.6	1103.5	1103.6	1103.7	1103.8	1103.9
150°	1126.9	1126.5	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5
152.5°	1146.5	1146.0	1145.7	1145.2	1144.8	1144.4	1144.6	1145.6	1146.5	1147.5	1148.3
155°	1173.3	1172.6	1172.1	1171.8	1171.4	1170.9	1171.4	1172.6	1173.8	1175.2	1176.4
157.5°	1195.5	1194.9	1194.8	1194.8	1194.7	1194.7	1195.0	1195.8	1196.6	1197.2	1198.0
160°	1209.2	1208.3	1208.2	1208.0	1207.8	1207.5	1208.1	1209.3	1210.6	1211.8	1213.1
162.5°	1221.6	1220.4	1220.2	1220.0	1219.7	1219.6	1220.1	1221.3	1222.6	1223.9	1225.1
165°	1237.8	1236.6	1236.4	1236.1	1236.0	1235.8	1236.3	1237.6	1238.8	1240.0	1241.3
167.5°	1250.0	1248.5	1248.2	1248.0	1247.8	1247.6	1248.2	1249.4	1250.8	1252.1	1253.4
170°	1256.1	1254.5	1254.2	1254.1	1253.9	1253.7	1254.2	1255.7	1257.2	1258.7	1260.1
172.5°	1261.2	1259.7	1259.3	1259.0	1258.6	1258.3	1258.8	1260.3	1261.7	1263.2	1264.6
175°	1266.5	1264.8	1264.6	1264.4	1264.2	1264.0	1264.5	1265.7	1267.1	1268.3	1269.5
177.5°	1269.2	1268.0	1267.9	1267.7	1267.5	1267.3	1267.8	1268.8	1269.8	1270.8	1271.8
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.3	15.1	12.9	13.8	14.0	13.9	14.1	13.9	13.7	13.9	14.1
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	13.3	12.2	10.9	9.8	9.9	11.1	12.4	13.8	15.1	16.1	17.2
95°	53.0	52.4	51.7	51.2	46.8	38.9	30.9	23.0	15.1	16.1	17.2
97.5°	113.1	114.2	115.4	116.5	109.2	93.5	77.8	62.0	46.3	40.4	34.5
100°	157.8	158.4	159.0	159.7	160.4	161.3	162.1	162.9	163.7	132.6	101.4
102.5°	203.9	204.7	205.5	206.2	206.9	207.5	207.9	208.4	209.0	203.0	197.1
105°	277.5	278.3	279.2	280.0	280.4	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	353.1	353.1	353.1	353.1	353.3	353.7	354.1	354.6	355.0	355.1	355.1
110°	402.7	402.7	402.7	402.7	403.0	403.4	403.9	404.3	404.6	404.1	403.4



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	450.0	450.4	451.0	451.5	451.9	452.1	452.3	452.6	452.9	452.0	451.3
115°	520.6	521.6	522.6	523.7	524.3	524.5	524.7	524.9	525.1	524.3	523.5
117.5°	591.9	591.8	591.8	591.8	592.2	593.0	593.7	594.6	595.3	594.3	593.1
120°	636.9	636.7	636.5	636.3	636.5	637.2	637.7	638.4	639.0	638.6	638.2
122.5°	677.8	678.6	679.4	680.2	680.7	681.1	681.4	681.6	681.9	681.5	681.1
125°	740.2	741.7	743.2	744.6	745.4	745.4	745.4	745.4	745.4	744.5	743.7
127.5°	798.7	799.7	800.8	801.8	802.3	802.2	802.1	801.9	801.8	801.3	800.9
130°	834.9	835.9	837.0	838.0	838.6	838.9	839.1	839.2	839.4	838.9	838.2
132.5°	871.2	872.4	873.5	874.8	875.2	874.7	874.3	873.8	873.4	873.2	873.1
135°	922.6	923.9	925.1	926.3	926.8	926.3	926.0	925.5	925.1	924.6	924.3
137.5°	969.7	970.7	971.9	972.9	973.3	972.9	972.5	972.1	971.8	971.9	971.9
140°	999.8	1000.3	1000.7	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8	1001.3
142.5°	1027.6	1027.8	1028.0	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8	1029.9
145°	1068.6	1068.9	1069.4	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3	1070.4
147.5°	1103.8	1103.7	1103.6	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9	1105.1
150°	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9	1127.4
152.5°	1147.5	1146.5	1145.6	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5	1146.9
155°	1175.2	1173.8	1172.6	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3	1173.8
157.5°	1197.2	1196.6	1195.8	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5	1196.2
160°	1211.8	1210.6	1209.3	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2	1210.0
162.5°	1223.9	1222.6	1221.3	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6	1222.8
165°	1240.0	1238.8	1237.6	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8	1239.1
167.5°	1252.1	1250.8	1249.4	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0	1251.5
170°	1258.7	1257.2	1255.7	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1	1257.8
172.5°	1263.2	1261.7	1260.3	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2	1262.7
175°	1268.3	1267.1	1265.7	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5	1268.2
177.5°	1270.8	1269.8	1268.8	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2	1270.4
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	14.8	15.6	14.7	14.3	14.4	15.1	15.7
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	18.2	19.2	19.9	20.2	20.5	20.8	21.1
95°	18.2	19.2	19.8	19.8	19.8	19.8	19.8
97.5°	28.7	22.7	19.8	19.8	19.8	19.8	19.8
100°	70.3	39.1	23.1	22.2	21.4	20.6	19.8
102.5°	191.2	185.3	175.3	161.1	146.8	132.6	118.4
105°	280.4	280.4	280.3	280.1	279.9	279.7	279.5
107.5°	355.2	355.2	354.9	354.2	353.6	353.0	352.3
110°	402.7	402.2	402.0	402.2	402.4	402.6	402.7



TEST NUMBER: P333598-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.1	448.8	448.6	448.3	448.0
115°	522.6	521.8	520.8	519.5	518.2	517.0	515.8
117.5°	592.1	591.0	590.1	589.7	589.1	588.5	588.0
120°	637.7	637.3	636.6	635.6	634.5	633.5	632.4
122.5°	680.7	680.2	679.4	678.3	677.0	675.8	674.6
125°	742.8	742.0	741.3	740.6	740.0	739.4	738.8
127.5°	800.4	799.9	799.0	797.4	795.9	794.4	792.8
130°	837.5	837.0	836.1	835.1	834.1	833.0	831.9
132.5°	873.0	872.8	872.2	871.2	870.2	869.1	868.1
135°	923.9	923.4	922.6	921.3	920.1	918.8	917.6
137.5°	972.0	972.1	971.6	970.5	969.4	968.4	967.2
140°	1001.6	1002.0	1001.6	1000.4	999.1	997.9	996.6
142.5°	1030.0	1030.1	1029.5	1028.2	1027.0	1025.8	1024.4
145°	1070.6	1070.8	1070.4	1069.1	1067.8	1066.6	1065.4
147.5°	1105.4	1105.7	1105.0	1103.5	1102.0	1100.5	1099.0
150°	1127.8	1128.1	1127.6	1125.9	1124.2	1122.5	1120.9
152.5°	1147.4	1147.7	1147.2	1145.7	1144.2	1142.6	1141.1
155°	1174.5	1175.2	1174.6	1172.9	1171.2	1169.6	1167.9
157.5°	1196.8	1197.5	1197.0	1195.3	1193.6	1191.9	1190.3
160°	1210.9	1211.7	1211.3	1209.7	1208.0	1206.3	1204.6
162.5°	1223.9	1225.1	1224.7	1222.9	1221.1	1219.3	1217.4
165°	1240.4	1241.6	1241.4	1239.7	1238.0	1236.4	1234.7
167.5°	1253.0	1254.5	1254.3	1252.5	1250.6	1248.7	1246.8
170°	1259.5	1261.2	1261.0	1259.1	1257.4	1255.5	1253.6
172.5°	1264.2	1265.7	1265.6	1263.7	1261.8	1259.9	1258.1
175°	1269.9	1271.5	1271.4	1269.5	1267.6	1265.7	1263.9
177.5°	1271.6	1272.7	1272.6	1271.3	1270.0	1268.7	1267.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5

(END OF REPORT)