

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333603-830

Luminaire Tested: **S125RDIP-S1090D1035U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333603-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7482.3 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.1
10°-20°	442.7	5.9
20°-30°	642.0	8.6
30°-40°	731.6	9.8
40°-50°	713.2	9.5
50°-60°	600.3	8.0
60°-70°	420.8	5.6
70°-80°	216.3	2.9
80°-90°	57.2	0.8
90°-100°	338.3	4.5
100°-110°	727.2	9.7
110°-120°	682.5	9.1
120°-130°	553.1	7.4
130°-140°	443.9	5.9
140°-150°	334.9	4.5
150°-160°	235.8	3.2
160°-170°	139.0	1.9
170°-180°	45.2	0.6
0°-30°	1243.1	16.6
0°-40°	1974.7	26.4
0°-60°	3288.2	43.9
0°-90°	3982.5	53.2
90°-120°	1747.9	23.4
90°-150°	3079.8	41.2
90°-180°	3500.0	46.8
0°-180°	7482.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	8	15	20	22	5
95°	31	92	834	378	221	33
105°	106	149	682	1343	1247	112
115°	190	229	548	1180	1389	187
125°	263	309	525	939	1094	234
135°	309	371	521	787	909	240
145°	359	412	523	652	717	225
155°	410	441	510	576	601	189
165°	448	460	489	519	527	126
175°	466	466	470	475	473	44
180°	467	467	467	467	467	



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.2	21.0	19.8	18.6	18.1	18.0	18.2	18.1	18.3	18.5
90°	0.9	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0
92.5°	11.5	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5
95°	31.0	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8
97.5°	51.6	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2
100°	65.9	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9
102.5°	81.7	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3
105°	106.3	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3
107.5°	130.4	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0
110°	147.7	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.0	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7
115°	190.1	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1
117.5°	212.6	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7
120°	227.7	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9
122.5°	243.6	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3
125°	263.4	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9
127.5°	279.1	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0
130°	288.9	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7
132.5°	296.4	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6
135°	308.6	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9
137.5°	324.0	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3
140°	333.1	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8
142.5°	343.7	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0
145°	359.4	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4
147.5°	376.0	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5
150°	385.8	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0
152.5°	396.3	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7
155°	410.2	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9
157.5°	422.6	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6
160°	430.9	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9
162.5°	437.7	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9
165°	447.9	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8
167.5°	454.7	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0
170°	459.2	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7
172.5°	462.2	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4
175°	465.7	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4
177.5°	467.4	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	18.7	18.9	19.0	19.3	19.0	18.9	18.9	18.6
90°	17.0	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	166.7	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	676.6	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	1007.6	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1157.3	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1207.8	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1178.0	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1071.9	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	993.6	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333603-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	931.9	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	854.3	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	804.3	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	777.2	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	756.9	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	727.4	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	697.2	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	678.4	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	659.6	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	635.1	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	614.4	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	603.1	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	593.3	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	580.5	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	568.5	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	561.8	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	554.2	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	542.9	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	531.6	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	524.1	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	515.9	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	504.4	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	493.4	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	487.4	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	480.6	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.2	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)