

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333613-830

Luminaire Tested: **S125RDIP-S1270D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333613-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D365U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5977.6 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	88	81	76	90	84	78	73	77	72	68	70	66	63	64	61	59	55
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50	47
4	80	69	61	54	76	66	59	53	61	54	50	56	51	47	51	47	44	41
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38	36
6	68	56	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34	31
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	38	34	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.0	3.1
10°-20°	511.3	8.6
20°-30°	741.4	12.4
30°-40°	845.0	14.1
40°-50°	823.6	13.8
50°-60°	693.3	11.6
60°-70°	486.0	8.1
70°-80°	249.8	4.2
80°-90°	64.0	1.1
90°-100°	16.3	0.3
100°-110°	100.7	1.7
110°-120°	182.6	3.1
120°-130°	234.3	3.9
130°-140°	252.0	4.2
140°-150°	236.5	4.0
150°-160°	191.3	3.2
160°-170°	123.8	2.1
170°-180°	42.7	0.7
0°-30°	1435.7	24.0
0°-40°	2280.6	38.2
0°-60°	3797.6	63.5
0°-90°	4597.5	76.9
90°-120°	299.6	5.0
90°-150°	1022.4	17.1
90°-180°	1380.0	23.1
0°-180°	5977.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	0	3	5	7	8	5
95°	19	17	5	7	7	24
105°	98	99	99	99	99	104
115°	184	186	186	185	183	182
125°	262	264	264	263	262	234
135°	326	328	328	327	325	251
145°	378	379	379	379	377	236
155°	416	415	415	416	414	192
165°	439	438	438	440	437	124
175°	449	448	448	450	447	43
180°	449	449	449	449	449	



TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.4	23.7	22.0	20.3	19.3	19.1	19.0	18.9	18.7	18.8
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	5.1	4.7	4.3	3.9	3.5	3.5	4.0	4.4	4.9	5.4	5.7
95°	18.9	18.8	18.6	18.3	18.1	16.6	13.8	10.9	8.1	5.4	5.7
97.5°	39.7	40.1	40.4	40.8	41.3	38.6	33.1	27.5	22.0	16.4	14.3
100°	55.6	55.9	56.1	56.3	56.6	56.7	57.1	57.4	57.7	58.0	46.9
102.5°	71.9	72.2	72.5	72.8	73.0	73.2	73.4	73.6	73.8	74.0	71.9
105°	97.9	98.2	98.6	98.9	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	125.0	125.0	125.0	125.0	125.0	125.1	125.3	125.4	125.5	125.6	125.6
110°	142.6	142.6	142.6	142.6	142.6	142.7	142.8	143.0	143.1	143.3	143.1



TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.1	159.3	159.5	159.7	159.9	159.9	160.0	160.1	160.2	160.3	160.0
115°	183.9	184.3	184.6	185.0	185.4	185.6	185.7	185.8	185.9	185.9	185.6
117.5°	209.5	209.5	209.5	209.5	209.5	209.6	209.9	210.2	210.5	210.8	210.4
120°	225.6	225.5	225.5	225.4	225.3	225.4	225.6	225.7	226.0	226.2	226.1
122.5°	239.7	240.0	240.3	240.5	240.8	241.0	241.1	241.2	241.3	241.4	241.3
125°	261.6	262.0	262.6	263.1	263.6	263.9	263.9	263.9	263.9	263.9	263.5
127.5°	282.4	282.8	283.1	283.5	283.9	284.1	284.0	284.0	283.9	283.9	283.7
130°	295.2	295.6	296.0	296.3	296.7	296.9	297.0	297.0	297.1	297.2	297.0
132.5°	308.0	308.4	308.9	309.2	309.7	309.8	309.7	309.5	309.3	309.2	309.2
135°	326.2	326.6	327.1	327.5	327.9	328.1	327.9	327.8	327.6	327.5	327.3
137.5°	342.9	343.3	343.7	344.0	344.4	344.6	344.4	344.3	344.1	344.0	344.0
140°	353.8	354.0	354.1	354.3	354.4	354.5	354.4	354.3	354.2	354.2	354.3
142.5°	363.7	363.8	363.9	363.9	364.0	364.1	364.3	364.4	364.5	364.6	364.6
145°	378.1	378.3	378.4	378.6	378.7	378.8	378.8	378.8	378.8	378.8	378.9
147.5°	390.8	390.8	390.8	390.7	390.7	390.7	390.8	390.9	391.0	391.1	391.2
150°	398.8	398.7	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8	399.0
152.5°	406.5	406.2	405.9	405.6	405.2	405.1	405.3	405.5	405.6	405.8	405.9
155°	416.5	416.0	415.6	415.1	414.7	414.5	414.7	414.8	415.0	415.1	415.4
157.5°	424.1	423.9	423.6	423.3	423.1	422.9	422.9	423.0	423.0	423.0	423.2
160°	429.4	429.0	428.6	428.1	427.7	427.5	427.5	427.6	427.7	427.8	428.1
162.5°	433.8	433.3	432.8	432.3	432.0	431.8	431.9	431.9	432.0	432.1	432.4
165°	439.4	439.0	438.6	438.1	437.7	437.5	437.5	437.6	437.7	437.8	438.2
167.5°	443.7	443.3	442.8	442.3	441.9	441.7	441.8	441.9	442.0	442.0	442.5
170°	446.1	445.6	445.1	444.6	444.0	443.8	443.9	443.9	444.0	444.1	444.7
172.5°	447.7	447.2	446.7	446.2	445.6	445.4	445.5	445.7	445.8	446.0	446.5
175°	449.4	449.0	448.6	448.1	447.7	447.5	447.5	447.6	447.7	447.8	448.4
177.5°	450.3	449.9	449.5	449.2	448.8	448.7	448.7	448.8	448.8	448.9	449.3
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	18.9	18.9	19.0	18.9	18.7	18.5	18.3	18.1
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	6.0	6.4	6.8	7.1	7.2	7.3	7.4	7.4
95°	6.0	6.4	6.8	7.0	7.0	7.0	7.0	7.0
97.5°	12.3	10.1	8.0	7.0	7.0	7.0	7.0	7.0
100°	35.9	24.9	13.9	8.2	7.9	7.6	7.3	7.0
102.5°	69.7	67.7	65.6	62.0	57.0	52.0	46.9	41.9
105°	99.2	99.2	99.2	99.2	99.2	99.1	99.1	99.0
107.5°	125.7	125.7	125.7	125.6	125.5	125.2	125.0	124.7
110°	142.8	142.6	142.4	142.3	142.4	142.4	142.5	142.6





TEST NUMBER: P333613-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.8	159.5	159.2	159.0	158.9	158.8	158.7	158.6
115°	185.3	185.0	184.7	184.4	183.9	183.5	183.0	182.6
117.5°	210.0	209.6	209.2	209.0	208.8	208.6	208.4	208.2
120°	225.9	225.7	225.6	225.4	225.0	224.6	224.2	223.9
122.5°	241.1	241.0	240.8	240.5	240.1	239.7	239.2	238.8
125°	263.3	263.0	262.7	262.4	262.2	262.0	261.7	261.6
127.5°	283.5	283.3	283.2	282.9	282.3	281.7	281.3	280.7
130°	296.7	296.5	296.3	296.0	295.7	295.3	294.9	294.5
132.5°	309.1	309.1	309.0	308.8	308.4	308.0	307.6	307.4
135°	327.3	327.1	326.9	326.6	326.2	325.7	325.3	324.8
137.5°	344.1	344.1	344.1	343.9	343.6	343.2	342.8	342.4
140°	354.5	354.6	354.8	354.6	354.2	353.7	353.3	352.8
142.5°	364.6	364.7	364.7	364.5	364.0	363.5	363.2	362.7
145°	379.0	379.0	379.1	378.9	378.5	378.1	377.6	377.1
147.5°	391.2	391.3	391.4	391.2	390.7	390.1	389.6	389.1
150°	399.1	399.3	399.4	399.2	398.6	398.0	397.4	396.8
152.5°	406.0	406.1	406.3	406.1	405.6	405.1	404.5	404.0
155°	415.6	415.8	416.0	415.8	415.3	414.6	414.1	413.5
157.5°	423.5	423.7	424.0	423.8	423.2	422.5	422.0	421.4
160°	428.4	428.7	429.0	428.9	428.2	427.6	427.1	426.5
162.5°	432.9	433.3	433.8	433.6	432.9	432.3	431.7	431.0
165°	438.7	439.1	439.6	439.5	438.9	438.3	437.7	437.2
167.5°	443.1	443.6	444.1	444.0	443.4	442.7	442.1	441.4
170°	445.3	445.9	446.5	446.5	445.8	445.2	444.4	443.7
172.5°	447.0	447.6	448.1	448.1	447.4	446.7	446.0	445.4
175°	448.9	449.6	450.2	450.2	449.4	448.7	448.1	447.4
177.5°	449.8	450.2	450.5	450.5	450.1	449.6	449.1	448.7
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4

(END OF REPORT)