

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333616-830

Luminaire Tested: **S125RDIP-S1270D590U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333616-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6866.2 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	98	94	91	96	93	89	86	83	80	78	73	72	70	65	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	55	53	50
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	52	48	46	43
4	79	68	60	54	74	64	57	52	58	52	48	52	47	44	46	43	40	37
5	72	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	32
6	67	55	47	41	63	52	45	39	47	41	36	43	38	34	38	34	31	28
7	62	50	42	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	28	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	2.5
10°-20°	503.0	7.3
20°-30°	797.5	11.6
30°-40°	961.7	14.0
40°-50°	858.8	12.5
50°-60°	658.6	9.6
60°-70°	428.0	6.2
70°-80°	208.1	3.0
80°-90°	51.2	0.7
90°-100°	26.4	0.4
100°-110°	162.5	2.4
110°-120°	294.7	4.3
120°-130°	378.2	5.5
130°-140°	406.7	5.9
140°-150°	381.8	5.6
150°-160°	308.8	4.5
160°-170°	199.7	2.9
170°-180°	68.9	1.0
0°-30°	1472.1	21.4
0°-40°	2433.8	35.4
0°-60°	3951.3	57.5
0°-90°	4638.6	67.6
90°-120°	483.5	7.0
90°-150°	1650.2	24.0
90°-180°	2228.0	32.4
0°-180°	6866.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	13	1	13	1	13	7
95°	11	31	11	31	11	9
105°	160	158	160	158	160	144
115°	295	297	295	297	295	293
125°	422	422	422	422	422	376
135°	524	526	524	526	524	405
145°	609	610	609	610	609	380
155°	667	672	667	672	667	308
165°	706	709	706	709	706	199
175°	722	726	722	726	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	15.6	14.9	14.2	14.1	14.6	15.7	15.0	14.3	14.1	14.0	14.5
90°	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8	9.2	8.6	7.7
92.5°	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8	9.2	8.6	7.8
95°	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8	9.2	8.6	13.1
97.5°	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7	23.1	26.5	35.4
100°	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0	75.8	93.6	93.1
102.5°	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6	116.0	119.4	119.1
105°	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9	202.8	202.8	202.6
110°	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5	230.9	231.2	231.0



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9	258.4	258.7	258.6
115°	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1	299.6	300.1	299.9
117.5°	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9	339.6	340.2	339.7
120°	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7	364.9	365.1	364.8
122.5°	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2	389.5	389.6	389.5
125°	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0	425.5	425.9	425.9
127.5°	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6	457.9	458.2	458.3
130°	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0	479.3	479.7	479.6
132.5°	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9	499.0	499.1	499.3
135°	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1	528.4	528.6	528.9
137.5°	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3	555.3	555.3	555.5
140°	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1	571.8	571.7	571.7
142.5°	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5	588.4	588.4	588.2
145°	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7	611.5	611.4	611.4
147.5°	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5	631.4	631.2	631.0
150°	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1	643.9	643.7	643.5
152.5°	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3	655.2	654.9	654.6
155°	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8	670.4	670.1	669.8
157.5°	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5	683.2	682.8	682.7
160°	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4	691.0	690.5	690.3
162.5°	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7	698.0	697.4	697.2
165°	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0	707.3	706.6	706.5
167.5°	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1	714.3	713.4	713.2
170°	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8	717.7	716.8	716.7
172.5°	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5	720.7	719.8	719.6
175°	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6	723.7	722.7	722.6
177.5°	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9	725.3	724.5	724.4
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	14.9	14.7	15.2	15.0	14.2	17.0	18.5	18.9	17.9	17.0	15.9
90°	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6	1.5	2.5	3.4
92.5°	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3	7.6	7.0	6.3
95°	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6	30.3	30.0	29.6
97.5°	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0	64.7	65.3	65.9
100°	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8	90.2	90.5	90.9
102.5°	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0	116.5	117.0	117.4
105°	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1	158.5	159.1	159.6
107.5°	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8	201.8	201.8	201.8
110°	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8	257.1	257.4	257.7
115°	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8	297.5	298.0	298.6
117.5°	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3	338.2	338.2	338.2
120°	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1	363.9	363.8	363.7
122.5°	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8	387.3	387.8	388.2
125°	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2	423.0	423.8	424.6
127.5°	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8	456.4	457.0	457.6
130°	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5	477.0	477.7	478.2
132.5°	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1	497.8	498.5	499.2
135°	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5	527.2	527.9	528.6
137.5°	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5	554.1	554.7	555.3
140°	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1	571.4	571.6	571.8
142.5°	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0	587.2	587.3	587.5
145°	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4	610.6	610.9	611.1
147.5°	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7	630.7	630.7	630.7
150°	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.5	643.2	643.0
152.5°	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2	655.6	655.2	654.6
155°	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2	671.5	670.8	670.1
157.5°	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6	684.1	683.7	683.2
160°	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1	692.5	691.7	691.0
162.5°	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0	699.4	698.6	697.9
165°	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3	708.6	707.8	707.2
167.5°	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1	715.5	714.7	714.0
170°	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1	719.3	718.4	717.6
172.5°	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6	721.8	721.0	720.1
175°	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5	724.7	724.0	723.3
177.5°	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7	726.1	725.6	725.0
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	15.6	15.7	15.4	16.7	15.1	15.8	15.9	15.5	15.6	15.7	15.3
90°	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8	10.4	11.0	11.5
92.5°	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8	10.4	11.0	11.4
95°	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8	10.4	11.0	11.3
97.5°	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7	16.3	13.0	11.3
100°	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0	40.2	22.3	13.2
102.5°	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6	109.2	105.9	100.2
105°	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9	202.9	202.9	202.7
110°	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5	230.2	229.8	229.7



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9	257.4	256.9	256.7
115°	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1	298.6	298.1	297.6
117.5°	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9	338.3	337.7	337.2
120°	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7	364.4	364.2	363.7
122.5°	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2	389.0	388.7	388.2
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0	424.4	424.0	423.6
127.5°	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6	457.4	457.1	456.6
130°	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0	478.6	478.2	477.8
132.5°	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9	498.8	498.8	498.4
135°	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1	527.9	527.6	527.2
137.5°	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3	555.4	555.4	555.2
140°	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1	572.3	572.6	572.3
142.5°	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5	588.5	588.6	588.2
145°	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7	611.8	611.9	611.6
147.5°	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5	631.7	631.8	631.4
150°	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1	644.4	644.6	644.3
152.5°	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3	655.6	655.8	655.5
155°	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8	671.1	671.5	671.2
157.5°	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5	683.9	684.3	684.0
160°	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4	691.9	692.4	692.1
162.5°	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7	699.4	700.0	699.8
165°	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0	708.8	709.5	709.4
167.5°	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1	716.0	716.8	716.7
170°	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8	719.7	720.7	720.6
172.5°	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5	722.5	723.3	723.2
175°	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6	725.6	726.6	726.5
177.5°	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9	726.6	727.3	727.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	15.9	15.4	15.5	15.6	15.5	15.4	15.9	15.3	15.7	15.6	15.5
90°	11.9	12.2	12.5	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8
92.5°	11.5	11.7	11.9	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8
95°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8
97.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7
100°	12.7	12.3	11.8	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0
102.5°	92.0	83.9	75.8	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6
105°	160.0	159.9	159.9	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2
107.5°	202.5	202.1	201.7	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9
110°	229.8	229.9	230.1	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	256.5	256.3	256.2	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9
115°	296.8	296.1	295.4	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1
117.5°	337.0	336.6	336.3	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9
120°	363.2	362.6	361.9	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7
122.5°	387.6	386.8	386.2	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2
125°	423.2	422.8	422.5	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0
127.5°	455.6	454.8	453.9	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6
130°	477.2	476.5	476.0	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0
132.5°	497.9	497.2	496.6	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9
135°	526.5	525.8	525.0	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1
137.5°	554.6	553.9	553.4	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3
140°	571.7	570.9	570.2	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1
142.5°	587.6	586.8	586.1	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5
145°	610.9	610.2	609.4	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7
147.5°	630.6	629.7	628.9	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5
150°	643.4	642.3	641.4	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1
152.5°	654.7	653.8	652.9	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3
155°	670.2	669.3	668.4	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8
157.5°	683.1	682.0	681.1	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5
160°	691.2	690.2	689.3	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4
162.5°	698.8	697.8	696.7	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7
165°	708.4	707.5	706.5	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0
167.5°	715.7	714.5	713.5	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1
170°	719.5	718.4	717.4	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8
172.5°	722.1	721.0	719.9	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5
175°	725.5	724.3	723.3	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6
177.5°	726.4	725.7	724.9	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	15.9	15.8	15.1	16.7	15.4	15.7	15.6	15.9	17.0	17.9	18.9
90°	9.2	8.6	7.7	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6
92.5°	9.2	8.6	7.8	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3
95°	9.2	8.6	13.1	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6
97.5°	23.1	26.5	35.4	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0
100°	75.8	93.6	93.1	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8
102.5°	116.0	119.4	119.1	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0
105°	160.2	160.2	160.2	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1
107.5°	202.8	202.8	202.6	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8
110°	230.9	231.2	231.0	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	258.4	258.7	258.6	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8
115°	299.6	300.1	299.9	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8
117.5°	339.6	340.2	339.7	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3
120°	364.9	365.1	364.8	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1
122.5°	389.5	389.6	389.5	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2
127.5°	457.9	458.2	458.3	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8
130°	479.3	479.7	479.6	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5
132.5°	499.0	499.1	499.3	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1
135°	528.4	528.6	528.9	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5
137.5°	555.3	555.3	555.5	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5
140°	571.8	571.7	571.7	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1
142.5°	588.4	588.4	588.2	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0
145°	611.5	611.4	611.4	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4
147.5°	631.4	631.2	631.0	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7
150°	643.9	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7
152.5°	655.2	654.9	654.6	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2
155°	670.4	670.1	669.8	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2
157.5°	683.2	682.8	682.7	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6
160°	691.0	690.5	690.3	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1
162.5°	698.0	697.4	697.2	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0
165°	707.3	706.6	706.5	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3
167.5°	714.3	713.4	713.2	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1
170°	717.7	716.8	716.7	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1
172.5°	720.7	719.8	719.6	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6
175°	723.7	722.7	722.6	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5
177.5°	725.3	724.5	724.4	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.5	17.0	14.2	15.0	15.2	14.7	14.9	14.5	14.0	14.1	14.3
90°	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8
92.5°	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8
95°	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8
97.5°	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7
100°	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0
102.5°	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6
105°	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9
110°	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9
115°	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1
117.5°	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9
120°	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7
122.5°	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2
125°	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0
127.5°	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6
130°	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0
132.5°	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9
135°	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1
137.5°	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3
140°	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1
142.5°	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5
145°	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7
147.5°	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5
150°	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1
152.5°	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3
155°	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8
157.5°	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5
160°	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4
162.5°	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7
165°	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0
167.5°	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1
170°	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8
172.5°	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5
175°	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6
177.5°	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	15.0	15.7	14.6	14.1	14.2	14.9	15.6
90°	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333616-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)