

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333623-830

Luminaire Tested: **S125RDIP-S1270D810U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333623-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7281.9 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	86	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	76	68	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	64	56	51	57	51	47	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	32	54	42	35	30	38	32	28	34	29	26	30	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.6	2.4
10°-20°	503.0	6.9
20°-30°	797.5	11.0
30°-40°	961.7	13.2
40°-50°	858.8	11.8
50°-60°	658.6	9.0
60°-70°	428.0	5.9
70°-80°	208.1	2.9
80°-90°	51.7	0.7
90°-100°	63.4	0.9
100°-110°	187.3	2.6
110°-120°	317.3	4.4
120°-130°	417.5	5.7
130°-140°	467.9	6.4
140°-150°	458.6	6.3
150°-160°	385.1	5.3
160°-170°	256.0	3.5
170°-180°	89.6	1.2
0°-30°	1472.1	20.2
0°-40°	2433.8	33.4
0°-60°	3951.3	54.3
0°-90°	4639.1	63.7
90°-120°	568.0	7.8
90°-150°	1912.0	26.3
90°-180°	2643.0	36.3
0°-180°	7281.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	18	1	18	1	18	12
95°	63	48	63	48	63	65
105°	183	168	183	168	183	194
115°	321	318	321	318	321	317
125°	467	464	467	464	467	417
135°	605	603	605	603	605	467
145°	733	730	733	730	733	458
155°	836	836	836	836	836	385
165°	906	909	906	909	906	256
175°	941	945	941	945	941	89
180°	947	947	947	947	947	



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	16.5	15.7	15.1	15.0	15.5	16.5	15.7	15.0	14.9	14.7	15.1
90°	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.4	12.6	11.8	10.7
92.5°	34.8	34.4	34.0	33.7	33.4	32.6	31.6	30.4	29.4	28.3	26.9
95°	63.3	63.1	62.8	62.4	62.1	61.4	60.2	59.0	57.9	56.7	55.1
97.5°	96.1	96.0	95.7	95.5	95.3	94.7	93.6	92.6	91.4	90.4	88.1
100°	120.8	120.6	120.2	119.9	119.6	118.7	117.2	115.7	114.2	112.7	110.7
102.5°	145.6	145.2	144.7	144.3	143.8	142.8	141.2	139.6	138.0	136.4	135.3
105°	182.8	182.3	181.8	181.3	180.8	180.1	179.1	178.1	177.1	176.2	175.1
107.5°	220.8	220.8	220.8	220.9	220.9	220.7	220.2	219.7	219.2	218.8	218.0
110°	249.1	249.3	249.4	249.6	249.8	249.6	249.1	248.6	248.2	247.6	247.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.8	277.1	277.4	277.7	278.1	278.1	277.8	277.6	277.4	277.1	276.5
115°	320.7	320.7	320.9	321.1	321.2	321.4	321.6	321.8	321.9	322.1	321.8
117.5°	363.4	364.0	364.7	365.3	366.0	366.3	366.1	366.0	365.8	365.7	365.4
120°	392.9	393.5	394.2	394.8	395.5	395.8	395.8	395.8	395.8	395.8	395.6
122.5°	422.4	422.8	423.4	423.9	424.4	424.7	424.9	425.0	425.1	425.3	424.8
125°	466.6	466.7	466.8	467.0	467.2	467.4	467.8	468.1	468.4	468.7	468.5
127.5°	509.0	509.3	509.6	510.0	510.3	510.6	510.7	510.9	511.0	511.2	511.0
130°	537.2	537.6	537.9	538.3	538.6	538.9	539.0	539.1	539.3	539.5	539.1
132.5°	563.8	564.3	564.8	565.2	565.6	566.0	566.1	566.3	566.5	566.7	566.7
135°	605.1	605.8	606.4	607.1	607.8	608.0	608.0	608.0	608.0	608.0	607.8
137.5°	645.5	646.3	647.1	647.9	648.8	649.0	648.8	648.7	648.5	648.3	647.9
140°	671.5	672.2	673.1	673.9	674.7	675.0	674.6	674.3	674.0	673.6	673.2
142.5°	696.2	697.0	697.9	698.6	699.5	699.7	699.6	699.4	699.2	699.0	698.3
145°	733.3	733.9	734.3	734.8	735.3	735.6	735.6	735.6	735.6	735.6	735.1
147.5°	765.1	766.2	767.2	768.4	769.5	769.9	769.5	769.0	768.6	768.3	767.9
150°	788.6	788.9	789.3	789.6	789.9	790.1	790.1	790.1	790.1	790.1	789.5
152.5°	808.0	808.7	809.3	809.8	810.4	810.5	810.1	809.7	809.4	809.0	808.7
155°	835.8	836.6	837.4	838.2	839.1	839.1	838.5	837.8	837.2	836.5	836.3
157.5°	858.9	860.0	861.1	862.1	863.3	863.5	862.8	862.1	861.5	860.8	860.6
160°	874.9	875.6	876.5	877.3	878.2	878.2	877.5	876.9	876.3	875.6	875.4
162.5°	888.4	889.4	890.3	891.3	892.2	892.3	891.6	890.7	889.9	889.2	889.1
165°	906.5	907.5	908.5	909.5	910.5	910.6	910.0	909.4	908.7	908.0	907.9
167.5°	921.0	922.0	923.0	924.1	925.0	925.1	924.1	923.1	922.1	921.1	921.1
170°	928.7	929.8	930.9	932.1	933.2	933.3	932.4	931.3	930.4	929.3	929.3
172.5°	935.1	936.1	937.2	938.2	939.2	939.2	938.2	937.3	936.2	935.3	935.3
175°	941.2	942.4	943.5	944.6	945.7	945.8	944.9	943.9	942.9	941.9	941.9
177.5°	944.7	945.7	946.6	947.4	948.4	948.5	947.6	946.9	946.1	945.3	945.5
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	15.5	15.2	15.6	15.3	14.4	17.2	18.7	18.9	18.0	17.2	16.2
90°	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8	2.1	3.4	4.7
92.5°	25.4	24.0	22.6	21.5	20.5	19.7	18.8	17.8	18.8	19.7	20.5
95°	53.4	51.8	50.2	49.2	48.9	48.5	48.3	47.9	48.3	48.5	48.9
97.5°	85.9	83.6	81.3	80.1	80.0	79.8	79.7	79.6	79.7	79.8	80.0
100°	108.5	106.4	104.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2
102.5°	134.2	133.1	132.1	131.2	130.5	129.9	129.2	128.6	129.2	129.9	130.5
105°	174.2	173.2	172.2	171.4	170.5	169.7	168.9	168.1	168.9	169.7	170.5
107.5°	217.3	216.5	215.7	215.0	214.1	213.3	212.4	211.7	212.4	213.3	214.1
110°	246.7	246.2	245.7	245.1	244.2	243.4	242.6	241.8	242.6	243.4	244.2





TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.9	275.2	274.7	274.1	273.7	273.2	272.9	272.4	272.9	273.2	273.7
115°	321.4	321.1	320.7	320.3	319.6	319.0	318.3	317.6	318.3	319.0	319.6
117.5°	365.1	364.9	364.6	364.2	363.9	363.6	363.4	363.1	363.4	363.6	363.9
120°	395.5	395.3	395.1	394.6	393.8	393.0	392.2	391.3	392.2	393.0	393.8
122.5°	424.4	424.0	423.6	423.2	422.9	422.6	422.4	422.0	422.4	422.6	422.9
125°	468.4	468.3	468.1	467.5	466.6	465.5	464.6	463.5	464.6	465.5	466.6
127.5°	510.8	510.6	510.4	510.0	509.4	508.9	508.4	507.8	508.4	508.9	509.4
130°	538.9	538.5	538.2	537.6	536.8	536.0	535.2	534.3	535.2	536.0	536.8
132.5°	566.8	566.8	566.8	566.3	564.9	563.5	562.2	560.9	562.2	563.5	564.9
135°	607.8	607.6	607.4	606.8	605.9	604.8	603.9	602.9	603.9	604.8	605.9
137.5°	647.5	647.2	646.9	646.2	645.3	644.3	643.4	642.4	643.4	644.3	645.3
140°	672.7	672.1	671.7	671.0	670.2	669.4	668.5	667.8	668.5	669.4	670.2
142.5°	697.8	697.1	696.5	695.9	695.1	694.5	693.8	693.1	693.8	694.5	695.1
145°	734.5	734.1	733.6	733.0	732.4	731.7	731.0	730.4	731.0	731.7	732.4
147.5°	767.5	767.1	766.7	766.3	766.0	765.6	765.3	764.9	765.3	765.6	766.0
150°	788.8	788.2	787.5	787.2	787.4	787.6	787.7	787.9	787.7	787.6	787.4
152.5°	808.4	808.1	807.9	807.7	807.5	807.2	807.0	806.7	807.0	807.2	807.5
155°	836.2	836.0	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8
157.5°	860.5	860.4	860.2	860.3	860.6	861.0	861.4	861.8	861.4	861.0	860.6
160°	875.2	875.1	875.0	875.1	875.6	876.1	876.6	877.0	876.6	876.1	875.6
162.5°	889.1	889.0	889.0	889.2	889.6	889.9	890.2	890.6	890.2	889.9	889.6
165°	907.7	907.5	907.4	907.5	907.8	908.1	908.4	908.8	908.4	908.1	907.8
167.5°	921.1	921.1	921.1	921.4	922.1	922.7	923.4	924.1	923.4	922.7	922.1
170°	929.3	929.3	929.3	929.7	930.4	931.0	931.7	932.4	931.7	931.0	930.4
172.5°	935.3	935.3	935.3	935.6	936.2	936.9	937.5	938.2	937.5	936.9	936.2
175°	941.9	941.9	941.9	942.3	942.9	943.6	944.2	944.9	944.2	943.6	942.9
177.5°	945.6	945.7	945.8	946.1	946.7	947.3	947.7	948.3	947.7	947.3	946.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	15.9	16.1	15.7	17.2	15.6	16.5	16.6	16.2	16.4	16.5	16.1
90°	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.4	14.2	15.1	15.7
92.5°	21.5	22.6	24.0	25.4	26.9	28.3	29.4	30.4	31.6	32.6	33.4
95°	49.2	50.2	51.8	53.4	55.1	56.7	57.9	59.0	60.2	61.4	62.1
97.5°	80.1	81.3	83.6	85.9	88.1	90.4	91.4	92.6	93.6	94.7	95.3
100°	103.2	104.2	106.4	108.5	110.7	112.7	114.2	115.7	117.2	118.7	119.6
102.5°	131.2	132.1	133.1	134.2	135.3	136.4	138.0	139.6	141.2	142.8	143.8
105°	171.4	172.2	173.2	174.2	175.1	176.2	177.1	178.1	179.1	180.1	180.8
107.5°	215.0	215.7	216.5	217.3	218.0	218.8	219.2	219.7	220.2	220.7	220.9
110°	245.1	245.7	246.2	246.7	247.1	247.6	248.2	248.6	249.1	249.6	249.8



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	274.1	274.7	275.2	275.9	276.5	277.1	277.4	277.6	277.8	278.1	278.1
115°	320.3	320.7	321.1	321.4	321.8	322.1	321.9	321.8	321.6	321.4	321.2
117.5°	364.2	364.6	364.9	365.1	365.4	365.7	365.8	366.0	366.1	366.3	366.0
120°	394.6	395.1	395.3	395.5	395.6	395.8	395.8	395.8	395.8	395.8	395.5
122.5°	423.2	423.6	424.0	424.4	424.8	425.3	425.1	425.0	424.9	424.7	424.4
125°	467.5	468.1	468.3	468.4	468.5	468.7	468.4	468.1	467.8	467.4	467.2
127.5°	510.0	510.4	510.6	510.8	511.0	511.2	511.0	510.9	510.7	510.6	510.3
130°	537.6	538.2	538.5	538.9	539.1	539.5	539.3	539.1	539.0	538.9	538.6
132.5°	566.3	566.8	566.8	566.8	566.7	566.7	566.5	566.3	566.1	566.0	565.6
135°	606.8	607.4	607.6	607.8	607.8	608.0	608.0	608.0	608.0	608.0	607.8
137.5°	646.2	646.9	647.2	647.5	647.9	648.3	648.5	648.7	648.8	649.0	648.8
140°	671.0	671.7	672.1	672.7	673.2	673.6	674.0	674.3	674.6	675.0	674.7
142.5°	695.9	696.5	697.1	697.8	698.3	699.0	699.2	699.4	699.6	699.7	699.5
145°	733.0	733.6	734.1	734.5	735.1	735.6	735.6	735.6	735.6	735.6	735.3
147.5°	766.3	766.7	767.1	767.5	767.9	768.3	768.6	769.0	769.5	769.9	769.5
150°	787.2	787.5	788.2	788.8	789.5	790.1	790.1	790.1	790.1	790.1	789.9
152.5°	807.7	807.9	808.1	808.4	808.7	809.0	809.4	809.7	810.1	810.5	810.4
155°	835.8	835.8	836.0	836.2	836.3	836.5	837.2	837.8	838.5	839.1	839.1
157.5°	860.3	860.2	860.4	860.5	860.6	860.8	861.5	862.1	862.8	863.5	863.3
160°	875.1	875.0	875.1	875.2	875.4	875.6	876.3	876.9	877.5	878.2	878.2
162.5°	889.2	889.0	889.0	889.1	889.1	889.2	889.9	890.7	891.6	892.3	892.2
165°	907.5	907.4	907.5	907.7	907.9	908.0	908.7	909.4	910.0	910.6	910.5
167.5°	921.4	921.1	921.1	921.1	921.1	921.1	922.1	923.1	924.1	925.1	925.0
170°	929.7	929.3	929.3	929.3	929.3	929.3	930.4	931.3	932.4	933.3	933.2
172.5°	935.6	935.3	935.3	935.3	935.3	935.3	936.2	937.3	938.2	939.2	939.2
175°	942.3	941.9	941.9	941.9	941.9	941.9	942.9	943.9	944.9	945.8	945.7
177.5°	946.1	945.8	945.7	945.6	945.5	945.3	946.1	946.9	947.6	948.5	948.4
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	16.8	16.3	16.4	16.5	16.4	16.3	16.8	16.1	16.5	16.4	16.2
90°	16.2	16.7	17.2	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.4
92.5°	33.7	34.0	34.4	34.8	34.4	34.0	33.7	33.4	32.6	31.6	30.4
95°	62.4	62.8	63.1	63.3	63.1	62.8	62.4	62.1	61.4	60.2	59.0
97.5°	95.5	95.7	96.0	96.1	96.0	95.7	95.5	95.3	94.7	93.6	92.6
100°	119.9	120.2	120.6	120.8	120.6	120.2	119.9	119.6	118.7	117.2	115.7
102.5°	144.3	144.7	145.2	145.6	145.2	144.7	144.3	143.8	142.8	141.2	139.6
105°	181.3	181.8	182.3	182.8	182.3	181.8	181.3	180.8	180.1	179.1	178.1
107.5°	220.9	220.8	220.8	220.8	220.8	220.8	220.9	220.9	220.7	220.2	219.7
110°	249.6	249.4	249.3	249.1	249.3	249.4	249.6	249.8	249.6	249.1	248.6



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	277.7	277.4	277.1	276.8	277.1	277.4	277.7	278.1	278.1	277.8	277.6
115°	321.1	320.9	320.7	320.7	320.7	320.9	321.1	321.2	321.4	321.6	321.8
117.5°	365.3	364.7	364.0	363.4	364.0	364.7	365.3	366.0	366.3	366.1	366.0
120°	394.8	394.2	393.5	392.9	393.5	394.2	394.8	395.5	395.8	395.8	395.8
122.5°	423.9	423.4	422.8	422.4	422.8	423.4	423.9	424.4	424.7	424.9	425.0
125°	467.0	466.8	466.7	466.6	466.7	466.8	467.0	467.2	467.4	467.8	468.1
127.5°	510.0	509.6	509.3	509.0	509.3	509.6	510.0	510.3	510.6	510.7	510.9
130°	538.3	537.9	537.6	537.2	537.6	537.9	538.3	538.6	538.9	539.0	539.1
132.5°	565.2	564.8	564.3	563.8	564.3	564.8	565.2	565.6	566.0	566.1	566.3
135°	607.1	606.4	605.8	605.1	605.8	606.4	607.1	607.8	608.0	608.0	608.0
137.5°	647.9	647.1	646.3	645.5	646.3	647.1	647.9	648.8	649.0	648.8	648.7
140°	673.9	673.1	672.2	671.5	672.2	673.1	673.9	674.7	675.0	674.6	674.3
142.5°	698.6	697.9	697.0	696.2	697.0	697.9	698.6	699.5	699.7	699.6	699.4
145°	734.8	734.3	733.9	733.3	733.9	734.3	734.8	735.3	735.6	735.6	735.6
147.5°	768.4	767.2	766.2	765.1	766.2	767.2	768.4	769.5	769.9	769.5	769.0
150°	789.6	789.3	788.9	788.6	788.9	789.3	789.6	789.9	790.1	790.1	790.1
152.5°	809.8	809.3	808.7	808.0	808.7	809.3	809.8	810.4	810.5	810.1	809.7
155°	838.2	837.4	836.6	835.8	836.6	837.4	838.2	839.1	839.1	838.5	837.8
157.5°	862.1	861.1	860.0	858.9	860.0	861.1	862.1	863.3	863.5	862.8	862.1
160°	877.3	876.5	875.6	874.9	875.6	876.5	877.3	878.2	878.2	877.5	876.9
162.5°	891.3	890.3	889.4	888.4	889.4	890.3	891.3	892.2	892.3	891.6	890.7
165°	909.5	908.5	907.5	906.5	907.5	908.5	909.5	910.5	910.6	910.0	909.4
167.5°	924.1	923.0	922.0	921.0	922.0	923.0	924.1	925.0	925.1	924.1	923.1
170°	932.1	930.9	929.8	928.7	929.8	930.9	932.1	933.2	933.3	932.4	931.3
172.5°	938.2	937.2	936.1	935.1	936.1	937.2	938.2	939.2	939.2	938.2	937.3
175°	944.6	943.5	942.4	941.2	942.4	943.5	944.6	945.7	945.8	944.9	943.9
177.5°	947.4	946.6	945.7	944.7	945.7	946.6	947.4	948.4	948.5	947.6	946.9
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	16.6	16.5	15.6	17.2	15.7	16.1	15.9	16.2	17.2	18.0	18.9
90°	12.6	11.8	10.7	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8
92.5°	29.4	28.3	26.9	25.4	24.0	22.6	21.5	20.5	19.7	18.8	17.8
95°	57.9	56.7	55.1	53.4	51.8	50.2	49.2	48.9	48.5	48.3	47.9
97.5°	91.4	90.4	88.1	85.9	83.6	81.3	80.1	80.0	79.8	79.7	79.6
100°	114.2	112.7	110.7	108.5	106.4	104.2	103.2	103.2	103.2	103.2	103.2
102.5°	138.0	136.4	135.3	134.2	133.1	132.1	131.2	130.5	129.9	129.2	128.6
105°	177.1	176.2	175.1	174.2	173.2	172.2	171.4	170.5	169.7	168.9	168.1
107.5°	219.2	218.8	218.0	217.3	216.5	215.7	215.0	214.1	213.3	212.4	211.7
110°	248.2	247.6	247.1	246.7	246.2	245.7	245.1	244.2	243.4	242.6	241.8



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	277.4	277.1	276.5	275.9	275.2	274.7	274.1	273.7	273.2	272.9	272.4
115°	321.9	322.1	321.8	321.4	321.1	320.7	320.3	319.6	319.0	318.3	317.6
117.5°	365.8	365.7	365.4	365.1	364.9	364.6	364.2	363.9	363.6	363.4	363.1
120°	395.8	395.8	395.6	395.5	395.3	395.1	394.6	393.8	393.0	392.2	391.3
122.5°	425.1	425.3	424.8	424.4	424.0	423.6	423.2	422.9	422.6	422.4	422.0
125°	468.4	468.7	468.5	468.4	468.3	468.1	467.5	466.6	465.5	464.6	463.5
127.5°	511.0	511.2	511.0	510.8	510.6	510.4	510.0	509.4	508.9	508.4	507.8
130°	539.3	539.5	539.1	538.9	538.5	538.2	537.6	536.8	536.0	535.2	534.3
132.5°	566.5	566.7	566.7	566.8	566.8	566.8	566.3	564.9	563.5	562.2	560.9
135°	608.0	608.0	607.8	607.8	607.6	607.4	606.8	605.9	604.8	603.9	602.9
137.5°	648.5	648.3	647.9	647.5	647.2	646.9	646.2	645.3	644.3	643.4	642.4
140°	674.0	673.6	673.2	672.7	672.1	671.7	671.0	670.2	669.4	668.5	667.8
142.5°	699.2	699.0	698.3	697.8	697.1	696.5	695.9	695.1	694.5	693.8	693.1
145°	735.6	735.6	735.1	734.5	734.1	733.6	733.0	732.4	731.7	731.0	730.4
147.5°	768.6	768.3	767.9	767.5	767.1	766.7	766.3	766.0	765.6	765.3	764.9
150°	790.1	790.1	789.5	788.8	788.2	787.5	787.2	787.4	787.6	787.7	787.9
152.5°	809.4	809.0	808.7	808.4	808.1	807.9	807.7	807.5	807.2	807.0	806.7
155°	837.2	836.5	836.3	836.2	836.0	835.8	835.8	835.8	835.8	835.8	835.8
157.5°	861.5	860.8	860.6	860.5	860.4	860.2	860.3	860.6	861.0	861.4	861.8
160°	876.3	875.6	875.4	875.2	875.1	875.0	875.1	875.6	876.1	876.6	877.0
162.5°	889.9	889.2	889.1	889.1	889.0	889.0	889.2	889.6	889.9	890.2	890.6
165°	908.7	908.0	907.9	907.7	907.5	907.4	907.5	907.8	908.1	908.4	908.8
167.5°	922.1	921.1	921.1	921.1	921.1	921.1	921.4	922.1	922.7	923.4	924.1
170°	930.4	929.3	929.3	929.3	929.3	929.3	929.7	930.4	931.0	931.7	932.4
172.5°	936.2	935.3	935.3	935.3	935.3	935.3	935.6	936.2	936.9	937.5	938.2
175°	942.9	941.9	941.9	941.9	941.9	941.9	942.3	942.9	943.6	944.2	944.9
177.5°	946.1	945.3	945.5	945.6	945.7	945.8	946.1	946.7	947.3	947.7	948.3
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.7	17.2	14.4	15.3	15.6	15.2	15.5	15.1	14.7	14.9	15.0
90°	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.4
92.5°	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4	30.4
95°	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9	59.0
97.5°	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4	92.6
100°	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2	115.7
102.5°	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0	139.6
105°	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1	178.1
107.5°	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2	219.7
110°	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2	248.6





TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4	277.6
115°	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9	321.8
117.5°	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8	366.0
120°	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8	395.8
122.5°	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1	425.0
125°	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4	468.1
127.5°	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0	510.9
130°	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3	539.1
132.5°	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5	566.3
135°	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0	608.0
137.5°	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5	648.7
140°	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0	674.3
142.5°	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2	699.4
145°	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6	735.6
147.5°	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6	769.0
150°	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1	790.1
152.5°	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4	809.7
155°	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2	837.8
157.5°	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5	862.1
160°	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3	876.9
162.5°	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9	890.7
165°	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7	909.4
167.5°	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1	923.1
170°	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4	931.3
172.5°	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2	937.3
175°	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9	943.9
177.5°	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1	946.9
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	15.7	16.5	15.5	15.0	15.1	15.7	16.5
90°	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	249.1	249.6	249.8	249.6	249.4	249.3	249.1



TEST NUMBER: P333623-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)