

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332518-840

Luminaire Tested: **S124DIP-S350D1035U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332518-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D1035U840-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5211.7 lumens  
Efficiency: N/A  
Efficacy: 139.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	38	38	38	31	
1	94	89	86	82	84	80	77	74	64	62	60	48	47	46	34	33	33	33	33	33	26	
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	28	28	28	28	22	
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	24	24	24	19	
4	71	61	53	48	64	55	48	43	44	39	36	34	30	28	24	22	20	20	20	20	16	
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	18	18	18	14	
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	16	16	16	13	
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	14	14	14	11	
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	13	13	13	10	
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	11	11	11	9	
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	10	8	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4657	4657	4657	4657
5°	5485	4669	4122	4669
10°	6567	4649	3710	4649
15°	7770	4603	3408	4603
20°	8652	4554	3137	4554
25°	8792	4483	2950	4483
30°	7481	4416	2892	4416
35°	5752	4306	2893	4306
40°	4484	4176	2947	4176
45°	3738	3981	2997	3981
50°	3291	3743	3097	3743
55°	3015	3458	3222	3458
60°	2824	3202	3371	3202
65°	2628	2917	3498	2917
70°	2403	2634	3576	2634
75°	2149	2318	3534	2318
80°	1799	1901	3422	1901
85°	1325	1371	3270	1371



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	1.1
10°-20°	173.3	3.3
20°-30°	274.7	5.3
30°-40°	305.7	5.9
40°-50°	278.3	5.3
50°-60°	227.4	4.4
60°-70°	162.4	3.1
70°-80°	89.4	1.7
80°-90°	28.3	0.5
90°-100°	86.0	1.6
100°-110°	254.7	4.9
110°-120°	432.2	8.3
120°-130°	569.9	10.9
130°-140°	640.1	12.3
140°-150°	629.0	12.1
150°-160°	529.0	10.2
160°-170°	352.0	6.8
170°-180°	123.2	2.4
0°-30°	504.2	9.7
0°-40°	809.9	15.5
0°-60°	1315.6	25.2
0°-90°	1595.7	30.6
90°-120°	772.9	14.8
90°-150°	2611.8	50.1
90°-180°	3616.0	69.4
0°-180°	5211.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	577	577	577	577	577	
5°	677	576	509	576	677	69
15°	930	551	408	551	930	263
25°	987	503	331	503	987	435
35°	584	437	294	437	584	370
45°	327	349	262	349	327	258
55°	214	246	229	246	214	193
65°	138	153	183	153	138	136
75°	69	74	113	74	69	73
85°	14	15	35	15	14	18
90°	30	3	30	3	30	16
95°	80	60	80	60	80	83
105°	246	235	246	235	246	259
115°	436	440	436	440	436	430
125°	635	640	635	640	635	566
135°	827	826	827	826	827	638
145°	1004	1003	1004	1003	1004	628
155°	1148	1149	1148	1149	1148	528
165°	1248	1251	1248	1251	1248	351
175°	1295	1301	1295	1301	1295	123
180°	1303	1303	1303	1303	1303	



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	614.0	613.9	612.0	611.6	610.3	608.5	608.1	605.0	599.0	596.0	595.3
5°	676.8	681.7	675.4	674.2	673.5	665.6	661.6	656.8	645.8	639.3	634.3
7.5°	751.8	752.3	749.6	747.5	741.3	734.5	724.2	713.2	700.0	686.5	676.2
10°	801.1	803.0	799.9	799.5	787.3	779.6	764.4	751.4	736.6	720.1	705.1
12.5°	853.1	850.5	848.9	838.7	836.4	822.4	804.7	791.4	768.5	749.5	729.5
15°	929.7	924.4	921.1	907.1	900.1	880.7	861.8	847.3	817.4	788.9	767.4
17.5°	974.6	979.9	972.2	966.3	948.5	934.8	915.5	884.9	861.6	826.3	799.1
20°	1007.1	1007.6	1003.3	997.3	983.3	966.0	945.0	911.6	883.6	848.5	811.1
22.5°	1015.9	1016.0	1014.2	1008.7	997.9	984.0	962.8	934.8	901.0	862.8	825.5
25°	987.0	986.1	988.3	994.5	990.5	986.1	973.9	953.1	921.6	881.2	841.0
27.5°	879.8	886.5	898.6	913.8	928.6	939.8	942.9	938.7	919.2	886.0	843.8
30°	802.5	810.7	819.8	835.1	864.7	881.7	900.3	914.4	906.6	880.0	840.8
32.5°	717.7	719.7	733.2	750.5	777.7	810.3	839.9	868.6	878.1	864.1	831.4
35°	583.6	587.0	601.6	618.7	652.0	692.0	736.4	776.1	808.8	821.9	805.2
37.5°	476.3	485.8	496.1	514.6	543.9	579.9	626.0	677.4	726.2	758.9	764.5
40°	425.5	431.4	438.8	452.9	477.8	513.1	552.8	611.6	663.5	710.3	725.6
42.5°	385.3	388.8	393.3	406.1	425.0	460.2	496.4	548.2	600.2	656.2	681.9
45°	327.4	331.0	338.7	346.1	360.4	384.8	418.5	461.0	513.4	567.3	614.7
47.5°	285.7	287.9	292.5	300.4	312.7	328.7	356.1	391.6	440.1	492.6	543.0
50°	262.0	263.9	267.4	274.6	284.0	298.3	320.7	354.0	391.9	444.7	494.2
52.5°	243.2	244.0	246.6	251.5	258.9	270.9	289.4	316.9	352.2	399.3	448.6
55°	214.2	215.1	217.5	221.1	227.5	235.2	249.2	269.8	300.6	341.5	384.4
57.5°	190.3	191.0	192.9	194.3	199.7	205.8	216.7	231.4	254.7	289.4	327.6
60°	174.9	174.5	176.8	178.0	181.7	186.9	195.3	209.3	229.6	257.6	292.8
62.5°	160.1	159.4	161.4	163.0	165.0	169.5	176.3	187.3	203.9	229.1	259.5
65°	137.6	136.7	137.9	139.9	141.7	144.1	149.2	159.0	172.1	190.3	213.4
67.5°	115.2	116.2	116.4	117.3	118.5	121.7	125.1	132.1	141.4	155.9	175.5
70°	101.8	102.1	103.0	103.0	103.7	106.6	109.5	113.5	122.6	136.0	152.0
72.5°	88.5	89.5	89.1	89.8	90.4	92.3	94.3	98.3	105.9	115.9	129.5
75°	68.9	69.6	69.6	69.8	70.5	71.2	72.9	75.7	81.3	88.7	98.0
77.5°	50.2	50.3	50.6	51.5	51.5	52.6	53.8	56.1	58.9	63.9	69.7
80°	38.7	39.2	39.0	39.5	39.5	40.4	40.9	43.7	44.9	48.3	52.8
82.5°	28.4	28.9	28.8	29.5	29.9	30.1	30.7	31.9	33.1	36.1	37.9
85°	14.3	14.8	14.3	14.8	15.6	15.8	16.5	16.8	17.7	18.4	20.1
87.5°	10.3	10.7	10.6	10.7	11.0	11.0	11.0	10.5	11.0	10.9	11.3
90°	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8	23.5	22.2	20.4
92.5°	44.7	44.5	44.2	43.9	43.7	43.1	42.3	41.5	40.7	39.9	38.7
95°	79.7	79.7	79.7	79.7	79.7	79.3	78.7	78.0	77.3	76.6	75.0
97.5°	124.8	124.8	124.8	124.8	124.8	124.4	123.6	122.8	122.0	121.2	119.4
100°	156.2	156.2	156.2	156.2	156.2	156.0	155.5	155.1	154.7	154.2	152.2
102.5°	191.7	191.6	191.4	191.2	191.0	190.6	190.0	189.3	188.7	188.1	186.2
105°	245.9	245.3	244.6	243.9	243.3	242.6	242.0	241.3	240.5	239.9	239.0
107.5°	298.7	298.8	298.8	298.9	298.9	298.6	298.0	297.4	296.8	296.2	296.0
110°	336.7	336.0	335.3	334.7	334.0	333.9	334.3	334.8	335.2	335.7	335.9



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.4	375.3	375.1	375.0	374.9	374.9	374.9	375.0	375.1	375.2	375.6
115°	435.5	435.7	435.9	436.2	436.4	436.6	436.8	437.0	437.3	437.5	437.9
117.5°	492.7	493.1	493.6	494.0	494.5	495.1	495.8	496.7	497.4	498.2	498.5
120°	536.2	535.8	535.3	534.9	534.4	534.8	535.9	537.0	538.2	539.3	540.0
122.5°	572.5	573.3	574.1	574.9	575.7	576.5	577.3	578.0	578.9	579.6	579.9
125°	635.0	635.5	635.9	636.4	636.8	637.2	637.7	638.1	638.6	639.0	639.2
127.5°	692.9	693.3	693.6	694.0	694.3	694.7	695.2	695.6	696.1	696.5	696.9
130°	730.7	731.6	732.6	733.5	734.4	735.1	735.5	736.0	736.4	736.8	736.8
132.5°	771.1	771.4	771.8	772.1	772.5	773.0	773.4	773.9	774.3	774.8	774.9
135°	826.6	827.2	827.9	828.6	829.2	829.8	830.2	830.7	831.1	831.6	831.6
137.5°	884.8	884.6	884.5	884.4	884.2	884.5	885.0	885.7	886.3	886.9	886.5
140°	920.3	920.5	920.7	921.0	921.2	921.4	921.6	921.9	922.1	922.3	922.3
142.5°	955.7	955.8	955.8	955.9	955.9	956.0	956.0	956.0	956.1	956.1	956.3
145°	1003.9	1004.6	1005.3	1005.9	1006.6	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7
147.5°	1052.8	1053.0	1053.2	1053.4	1053.6	1053.8	1054.0	1054.2	1054.4	1054.6	1054.7
150°	1082.6	1082.8	1083.0	1083.3	1083.5	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6
152.5°	1109.9	1110.5	1111.2	1111.8	1112.4	1112.4	1111.8	1111.3	1110.8	1110.1	1110.0
155°	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7	1150.7	1149.9	1149.0	1148.1	1148.3
157.5°	1182.1	1183.0	1183.7	1184.5	1185.2	1185.3	1184.6	1183.9	1183.3	1182.6	1182.7
160°	1201.5	1202.6	1203.8	1204.9	1206.0	1206.2	1205.6	1204.9	1204.2	1203.6	1203.8
162.5°	1221.6	1222.8	1224.0	1225.1	1226.2	1226.1	1224.9	1223.7	1222.4	1221.2	1221.5
165°	1247.9	1248.8	1249.7	1250.6	1251.4	1251.2	1249.9	1248.6	1247.2	1245.9	1246.3
167.5°	1266.7	1268.0	1269.4	1270.8	1272.2	1272.2	1270.9	1269.5	1268.2	1266.9	1266.8
170°	1277.1	1278.7	1280.2	1281.8	1283.3	1283.5	1282.1	1280.8	1279.5	1278.1	1277.9
172.5°	1286.0	1287.6	1289.1	1290.7	1292.2	1292.3	1290.7	1289.2	1287.7	1286.2	1286.2
175°	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5	1300.0	1298.4	1296.9	1295.3	1295.5
177.5°	1300.1	1301.5	1302.9	1304.4	1305.9	1306.0	1304.6	1303.4	1302.1	1300.9	1300.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	595.5	592.8	590.9	589.4	585.2	582.7	580.8	578.1	575.0	571.8	567.7
5°	629.2	621.2	615.2	606.1	597.5	590.4	582.9	576.2	568.2	559.3	552.8
7.5°	664.8	652.7	637.2	623.8	608.6	595.5	583.8	571.8	559.3	547.0	535.9
10°	687.4	671.9	654.6	634.3	615.2	598.2	582.5	567.1	552.3	537.6	524.8
12.5°	711.7	692.3	666.8	643.1	621.7	599.0	580.0	561.2	543.3	527.8	513.0
15°	744.3	716.3	686.9	655.1	626.9	600.4	574.3	550.7	530.6	510.0	495.6
17.5°	764.3	729.6	696.1	662.9	628.7	595.2	567.1	539.9	514.7	494.3	476.3
20°	777.5	743.1	701.3	668.0	627.4	593.0	560.5	530.1	503.8	482.1	463.4
22.5°	788.9	749.2	707.3	663.6	623.2	586.6	551.1	520.6	493.7	470.8	452.9
25°	795.2	749.5	704.1	660.6	614.7	571.5	539.2	503.3	474.6	450.5	431.4
27.5°	795.9	747.0	695.6	647.3	600.0	559.7	519.0	486.9	457.2	431.6	413.2
30°	793.8	742.9	687.6	635.3	587.7	544.0	508.6	473.7	443.3	418.0	398.9
32.5°	787.0	734.1	677.3	621.9	572.6	529.8	493.3	460.1	430.5	405.6	385.5
35°	767.7	715.3	654.9	597.2	546.8	503.6	470.6	436.9	407.3	383.6	364.3
37.5°	737.4	690.1	628.6	569.1	519.5	476.1	443.3	412.9	386.2	362.1	342.3
40°	711.0	669.4	607.7	549.7	496.1	454.8	424.2	396.3	369.7	347.0	328.1
42.5°	680.6	644.4	587.5	526.0	474.3	432.8	403.0	377.9	352.9	331.9	313.1
45°	626.4	602.5	549.0	492.1	438.3	399.1	370.7	348.7	327.7	307.1	291.3
47.5°	564.1	552.2	507.2	453.1	402.1	363.5	338.8	318.5	300.0	282.7	268.7
50°	522.2	516.4	477.6	425.5	376.7	340.3	315.5	298.0	282.3	267.0	253.8
52.5°	480.9	480.7	445.6	397.9	352.7	317.8	293.1	276.8	263.2	250.7	238.9
55°	417.8	424.4	397.0	354.5	314.1	282.5	260.2	245.7	236.1	225.9	217.0
57.5°	359.8	370.9	348.2	310.7	277.0	248.0	228.6	217.7	207.5	201.3	194.8
60°	321.9	332.4	314.8	283.3	251.5	226.6	208.1	198.3	189.6	185.2	180.7
62.5°	288.3	297.6	284.6	255.3	227.7	203.8	188.2	178.8	172.9	168.2	165.2
65°	240.2	248.1	236.8	215.6	191.9	172.8	160.2	152.7	147.0	145.1	141.7
67.5°	194.2	201.4	195.3	177.2	158.2	143.7	133.8	126.7	123.3	121.7	119.3
70°	166.8	174.0	167.5	151.8	137.1	125.0	115.6	111.6	108.1	107.3	104.0
72.5°	143.7	148.6	142.1	129.8	117.3	107.0	99.8	95.5	93.7	92.4	90.6
75°	107.8	112.1	107.8	98.3	89.4	82.2	76.0	74.3	72.2	71.5	70.3
77.5°	76.2	80.0	76.7	70.8	64.1	58.6	55.2	53.1	52.6	51.4	52.0
80°	58.3	60.7	57.6	53.5	48.3	44.4	42.1	40.9	39.5	39.0	39.9
82.5°	41.9	42.9	41.3	38.6	34.7	32.2	30.6	29.2	28.9	29.0	29.0
85°	21.7	21.5	21.3	18.9	17.7	16.1	15.0	14.8	14.5	15.0	15.6
87.5°	11.0	10.8	10.3	9.1	8.0	7.0	6.3	5.6	6.3	7.0	7.7
90°	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0	5.5	8.0	10.4
92.5°	37.4	36.2	34.9	32.8	30.0	27.2	24.4	21.6	24.4	27.2	30.0
95°	73.5	71.9	70.3	68.6	66.6	64.5	62.5	60.5	62.5	64.5	66.6
97.5°	117.4	115.6	113.8	112.1	110.5	108.9	107.2	105.6	107.2	108.9	110.5
100°	150.2	148.1	146.1	144.7	143.8	142.9	142.0	141.1	142.0	142.9	143.8
102.5°	184.4	182.6	180.8	179.7	179.3	178.9	178.5	178.2	178.5	178.9	179.3
105°	238.1	237.2	236.3	235.8	235.5	235.3	235.1	234.9	235.1	235.3	235.5
107.5°	295.9	295.8	295.6	295.4	295.2	294.9	294.6	294.4	294.6	294.9	295.2
110°	336.1	336.3	336.6	336.5	336.0	335.6	335.1	334.7	335.1	335.6	336.0





TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	376.0	376.4	376.8	377.0	376.9	376.8	376.7	376.6	376.7	376.8	376.9
115°	438.4	438.8	439.3	439.5	439.5	439.5	439.5	439.5	439.5	439.5	439.5
117.5°	498.8	499.1	499.4	499.5	499.3	499.1	499.0	498.8	499.0	499.1	499.3
120°	540.6	541.3	542.0	541.9	541.0	540.1	539.2	538.3	539.2	540.1	541.0
122.5°	580.2	580.6	580.9	580.8	580.5	580.1	579.8	579.4	579.8	580.1	580.5
125°	639.5	639.7	640.0	640.1	640.1	640.1	640.1	640.1	640.1	640.1	640.1
127.5°	697.2	697.6	697.9	697.8	697.1	696.4	695.8	695.1	695.8	696.4	697.1
130°	736.8	736.8	736.8	736.5	735.8	735.2	734.5	733.8	734.5	735.2	735.8
132.5°	775.1	775.3	775.5	775.3	774.8	774.3	773.9	773.4	773.9	774.3	774.8
135°	831.6	831.6	831.6	830.9	829.6	828.2	826.9	825.6	826.9	828.2	829.6
137.5°	886.2	885.8	885.3	884.9	884.2	883.6	883.0	882.4	883.0	883.6	884.2
140°	922.3	922.3	922.3	922.1	921.6	921.2	920.7	920.3	920.7	921.2	921.6
142.5°	956.5	956.7	956.8	956.7	956.3	955.8	955.4	954.9	955.4	955.8	956.3
145°	1007.5	1007.3	1007.0	1006.5	1005.6	1004.7	1003.8	1002.9	1003.8	1004.7	1005.6
147.5°	1054.9	1055.1	1055.3	1054.8	1053.8	1052.7	1051.6	1050.6	1051.6	1052.7	1053.8
150°	1083.6	1083.6	1083.6	1083.2	1082.3	1081.4	1080.5	1079.5	1080.5	1081.4	1082.3
152.5°	1109.8	1109.6	1109.4	1109.1	1108.6	1108.0	1107.5	1107.0	1107.5	1108.0	1108.6
155°	1148.5	1148.7	1149.0	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1
157.5°	1182.7	1182.7	1182.8	1183.0	1183.4	1183.8	1184.2	1184.6	1184.2	1183.8	1183.4
160°	1204.0	1204.2	1204.5	1204.7	1204.9	1205.1	1205.3	1205.6	1205.3	1205.1	1204.9
162.5°	1221.7	1221.9	1222.1	1222.5	1223.1	1223.8	1224.4	1224.9	1224.4	1223.8	1223.1
165°	1246.8	1247.2	1247.7	1248.2	1248.9	1249.6	1250.2	1250.9	1250.2	1249.6	1248.9
167.5°	1266.8	1266.7	1266.7	1267.1	1268.1	1269.0	1269.9	1270.9	1269.9	1269.0	1268.1
170°	1277.7	1277.5	1277.2	1277.7	1278.8	1279.9	1281.0	1282.1	1281.0	1279.9	1278.8
172.5°	1286.1	1286.1	1286.0	1286.5	1287.4	1288.4	1289.3	1290.2	1289.3	1288.4	1287.4
175°	1295.7	1296.0	1296.2	1296.9	1298.0	1299.1	1300.2	1301.3	1300.2	1299.1	1298.0
177.5°	1300.9	1300.9	1300.9	1301.3	1302.2	1303.1	1304.0	1304.9	1304.0	1303.1	1302.2
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	565.8	564.1	561.7	558.3	555.3	552.3	551.5	550.4	552.7	550.8	550.2
5°	547.3	542.3	535.8	528.5	524.1	518.0	516.7	514.3	511.9	511.7	509.3
7.5°	527.7	520.3	511.8	504.3	497.4	490.5	486.0	485.1	481.6	479.5	477.2
10°	515.0	505.9	496.1	489.0	480.9	473.7	468.7	465.9	463.4	460.8	458.4
12.5°	500.2	490.5	482.4	474.6	465.0	459.6	451.3	446.4	445.9	445.9	439.7
15°	482.8	473.2	460.8	449.8	444.5	434.0	429.5	423.7	420.2	416.6	413.7
17.5°	462.9	451.0	441.3	428.7	418.7	410.3	404.3	400.9	395.5	390.4	386.8
20°	450.5	437.9	427.6	414.1	403.2	392.9	387.9	383.1	379.1	374.8	370.7
22.5°	437.9	424.6	412.1	399.1	388.9	378.0	373.1	366.7	362.8	360.4	356.4
25°	418.0	403.6	389.3	376.9	366.4	356.8	350.4	345.4	341.0	339.1	336.5
27.5°	396.4	382.1	368.3	354.2	342.2	335.3	330.1	326.4	323.9	321.3	320.1
30°	382.6	367.8	353.0	339.8	328.9	321.9	317.2	314.6	312.7	311.4	310.2
32.5°	368.7	354.1	338.5	326.5	316.6	310.4	306.8	304.2	303.3	302.9	302.4
35°	346.3	331.5	317.2	306.4	297.1	294.7	291.5	290.1	289.6	291.3	292.1
37.5°	324.7	310.9	297.7	287.3	281.1	277.7	276.6	276.7	278.4	279.8	281.6
40°	310.7	297.3	284.9	275.8	270.0	267.9	267.4	268.6	270.5	272.3	274.2
42.5°	297.1	284.0	272.7	264.2	260.1	258.1	258.4	259.6	262.4	264.4	267.2
45°	276.1	265.1	254.1	247.1	243.8	244.3	244.3	246.4	249.0	252.2	255.3
47.5°	256.2	245.1	236.1	230.2	228.5	228.1	229.4	232.3	236.0	239.8	244.2
50°	242.9	232.3	224.4	219.1	217.2	217.9	219.8	222.5	227.0	231.9	236.4
52.5°	229.2	219.6	212.4	207.5	206.1	207.4	209.3	213.5	217.5	222.7	228.1
55°	208.1	200.1	194.3	190.8	190.3	191.0	193.1	197.6	203.4	209.8	215.1
57.5°	187.2	180.4	175.1	172.7	172.9	173.6	177.1	182.5	188.6	195.5	202.3
60°	173.0	166.8	162.5	160.6	160.9	162.3	166.6	171.6	179.3	185.9	193.1
62.5°	159.7	154.2	150.1	148.3	148.0	151.2	155.3	160.5	168.1	175.6	183.4
65°	138.1	133.8	130.5	129.6	130.3	132.7	137.9	144.8	151.3	159.2	167.3
67.5°	117.1	113.6	111.3	111.7	112.6	116.1	120.5	126.4	133.8	142.0	150.0
70°	103.7	100.4	98.5	98.7	100.2	104.4	108.3	114.2	122.1	130.5	137.1
72.5°	90.0	87.8	86.0	87.1	88.5	91.4	96.2	102.2	109.2	116.9	124.0
75°	69.1	69.1	68.2	68.9	71.0	73.8	77.5	83.6	90.6	96.8	102.5
77.5°	51.2	50.7	51.3	52.2	53.4	56.9	61.0	65.4	70.6	76.9	81.6
80°	39.2	39.5	40.6	42.1	42.5	45.1	49.5	53.5	57.6	62.8	67.4
82.5°	29.5	29.7	30.3	32.1	32.6	35.4	38.2	42.2	45.9	49.5	53.2
85°	16.1	16.1	17.2	18.0	19.1	21.0	22.7	25.1	28.5	30.8	34.4
87.5°	8.7	9.1	10.2	11.0	11.9	13.2	13.8	16.3	17.3	18.5	20.4
90°	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8	26.3	27.6	28.5
92.5°	32.8	34.9	36.2	37.4	38.7	39.9	40.7	41.5	42.3	43.1	43.7
95°	68.6	70.3	71.9	73.5	75.0	76.6	77.3	78.0	78.7	79.3	79.7
97.5°	112.1	113.8	115.6	117.4	119.4	121.2	122.0	122.8	123.6	124.4	124.8
100°	144.7	146.1	148.1	150.2	152.2	154.2	154.7	155.1	155.5	156.0	156.2
102.5°	179.7	180.8	182.6	184.4	186.2	188.1	188.7	189.3	190.0	190.6	191.0
105°	235.8	236.3	237.2	238.1	239.0	239.9	240.5	241.3	242.0	242.6	243.3
107.5°	295.4	295.6	295.8	295.9	296.0	296.2	296.8	297.4	298.0	298.6	298.9
110°	336.5	336.6	336.3	336.1	335.9	335.7	335.2	334.8	334.3	333.9	334.0



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	377.0	376.8	376.4	376.0	375.6	375.2	375.1	375.0	374.9	374.9	374.9
115°	439.5	439.3	438.8	438.4	437.9	437.5	437.3	437.0	436.8	436.6	436.4
117.5°	499.5	499.4	499.1	498.8	498.5	498.2	497.4	496.7	495.8	495.1	494.5
120°	541.9	542.0	541.3	540.6	540.0	539.3	538.2	537.0	535.9	534.8	534.4
122.5°	580.8	580.9	580.6	580.2	579.9	579.6	578.9	578.0	577.3	576.5	575.7
125°	640.1	640.0	639.7	639.5	639.2	639.0	638.6	638.1	637.7	637.2	636.8
127.5°	697.8	697.9	697.6	697.2	696.9	696.5	696.1	695.6	695.2	694.7	694.3
130°	736.5	736.8	736.8	736.8	736.8	736.8	736.4	736.0	735.5	735.1	734.4
132.5°	775.3	775.5	775.3	775.1	774.9	774.8	774.3	773.9	773.4	773.0	772.5
135°	830.9	831.6	831.6	831.6	831.6	831.6	831.1	830.7	830.2	829.8	829.2
137.5°	884.9	885.3	885.8	886.2	886.5	886.9	886.3	885.7	885.0	884.5	884.2
140°	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.9	921.6	921.4	921.2
142.5°	956.7	956.8	956.7	956.5	956.3	956.1	956.1	956.0	956.0	956.0	955.9
145°	1006.5	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7	1007.5	1007.3	1007.0	1006.6
147.5°	1054.8	1055.3	1055.1	1054.9	1054.7	1054.6	1054.4	1054.2	1054.0	1053.8	1053.6
150°	1083.2	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.5
152.5°	1109.1	1109.4	1109.6	1109.8	1110.0	1110.1	1110.8	1111.3	1111.8	1112.4	1112.4
155°	1149.1	1149.0	1148.7	1148.5	1148.3	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7
157.5°	1183.0	1182.8	1182.7	1182.7	1182.7	1182.6	1183.3	1183.9	1184.6	1185.3	1185.2
160°	1204.7	1204.5	1204.2	1204.0	1203.8	1203.6	1204.2	1204.9	1205.6	1206.2	1206.0
162.5°	1222.5	1222.1	1221.9	1221.7	1221.5	1221.2	1222.4	1223.7	1224.9	1226.1	1226.2
165°	1248.2	1247.7	1247.2	1246.8	1246.3	1245.9	1247.2	1248.6	1249.9	1251.2	1251.4
167.5°	1267.1	1266.7	1266.7	1266.8	1266.8	1266.9	1268.2	1269.5	1270.9	1272.2	1272.2
170°	1277.7	1277.2	1277.5	1277.7	1277.9	1278.1	1279.5	1280.8	1282.1	1283.5	1283.3
172.5°	1286.5	1286.0	1286.1	1286.1	1286.2	1286.2	1287.7	1289.2	1290.7	1292.3	1292.2
175°	1296.9	1296.2	1296.0	1295.7	1295.5	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5
177.5°	1301.3	1300.9	1300.9	1300.9	1300.9	1300.9	1302.1	1303.4	1304.6	1306.0	1305.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	549.8	549.5	548.1	547.9	548.1	549.5	549.8	550.2	550.8	552.7	550.4
5°	507.9	506.6	505.9	508.6	505.9	506.6	507.9	509.3	511.7	511.9	514.3
7.5°	476.3	475.3	473.2	472.5	473.2	475.3	476.3	477.2	479.5	481.6	485.1
10°	456.1	455.0	453.1	452.6	453.1	455.0	456.1	458.4	460.8	463.4	465.9
12.5°	436.5	434.6	434.2	434.7	434.2	434.6	436.5	439.7	445.9	445.9	446.4
15°	410.6	409.6	407.0	407.8	407.0	409.6	410.6	413.7	416.6	420.2	423.7
17.5°	385.1	384.0	380.7	383.5	380.7	384.0	385.1	386.8	390.4	395.5	400.9
20°	369.0	367.1	365.5	365.2	365.5	367.1	369.0	370.7	374.8	379.1	383.1
22.5°	353.8	352.0	351.8	350.3	351.8	352.0	353.8	356.4	360.4	362.8	366.7
25°	334.6	333.0	332.4	331.2	332.4	333.0	334.6	336.5	339.1	341.0	345.4
27.5°	319.9	319.1	318.2	318.6	318.2	319.1	319.9	320.1	321.3	323.9	326.4
30°	310.9	310.7	310.2	310.2	310.2	310.7	310.9	310.2	311.4	312.7	314.6
32.5°	303.5	303.5	303.8	303.8	303.8	303.5	303.5	302.4	302.9	303.3	304.2
35°	293.1	293.8	294.2	293.5	294.2	293.8	293.1	292.1	291.3	289.6	290.1
37.5°	283.6	284.3	285.0	285.8	285.0	284.3	283.6	281.6	279.8	278.4	276.7
40°	276.3	277.9	278.4	279.6	278.4	277.9	276.3	274.2	272.3	270.5	268.6
42.5°	269.4	271.2	272.5	272.8	272.5	271.2	269.4	267.2	264.4	262.4	259.6
45°	258.8	260.7	262.5	262.5	262.5	260.7	258.8	255.3	252.2	249.0	246.4
47.5°	247.9	250.6	252.4	252.8	252.4	250.6	247.9	244.2	239.8	236.0	232.3
50°	240.4	243.8	245.5	246.6	245.5	243.8	240.4	236.4	231.9	227.0	222.5
52.5°	233.2	236.5	238.7	239.3	238.7	236.5	233.2	228.1	222.7	217.5	213.5
55°	220.6	225.4	228.0	228.9	228.0	225.4	220.6	215.1	209.8	203.4	197.6
57.5°	208.7	213.2	216.2	216.9	216.2	213.2	208.7	202.3	195.5	188.6	182.5
60°	199.5	204.4	208.1	208.8	208.1	204.4	199.5	193.1	185.9	179.3	171.6
62.5°	190.2	195.2	198.6	200.5	198.6	195.2	190.2	183.4	175.6	168.1	160.5
65°	174.0	179.0	182.4	183.1	182.4	179.0	174.0	167.3	159.2	151.3	144.8
67.5°	156.3	161.4	163.5	164.9	163.5	161.4	156.3	150.0	142.0	133.8	126.4
70°	143.9	147.9	150.4	151.5	150.4	147.9	143.9	137.1	130.5	122.1	114.2
72.5°	129.8	134.0	136.7	137.0	136.7	134.0	129.8	124.0	116.9	109.2	102.2
75°	108.1	111.9	113.3	113.3	113.3	111.9	108.1	102.5	96.8	90.6	83.6
77.5°	85.5	87.5	89.3	89.7	89.3	87.5	85.5	81.6	76.9	70.6	65.4
80°	71.0	72.2	73.6	73.6	73.6	72.2	71.0	67.4	62.8	57.6	53.5
82.5°	56.0	57.1	58.5	58.3	58.5	57.1	56.0	53.2	49.5	45.9	42.2
85°	33.9	36.1	35.9	35.3	35.9	36.1	33.9	34.4	30.8	28.5	25.1
87.5°	21.1	21.3	22.0	22.5	22.0	21.3	21.1	20.4	18.5	17.3	16.3
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8
92.5°	43.9	44.2	44.5	44.7	44.5	44.2	43.9	43.7	43.1	42.3	41.5
95°	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.3	78.7	78.0
97.5°	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.4	123.6	122.8
100°	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.0	155.5	155.1
102.5°	191.2	191.4	191.6	191.7	191.6	191.4	191.2	191.0	190.6	190.0	189.3
105°	243.9	244.6	245.3	245.9	245.3	244.6	243.9	243.3	242.6	242.0	241.3
107.5°	298.9	298.8	298.8	298.7	298.8	298.8	298.9	298.9	298.6	298.0	297.4
110°	334.7	335.3	336.0	336.7	336.0	335.3	334.7	334.0	333.9	334.3	334.8



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	375.0	375.1	375.3	375.4	375.3	375.1	375.0	374.9	374.9	374.9	375.0
115°	436.2	435.9	435.7	435.5	435.7	435.9	436.2	436.4	436.6	436.8	437.0
117.5°	494.0	493.6	493.1	492.7	493.1	493.6	494.0	494.5	495.1	495.8	496.7
120°	534.9	535.3	535.8	536.2	535.8	535.3	534.9	534.4	534.8	535.9	537.0
122.5°	574.9	574.1	573.3	572.5	573.3	574.1	574.9	575.7	576.5	577.3	578.0
125°	636.4	635.9	635.5	635.0	635.5	635.9	636.4	636.8	637.2	637.7	638.1
127.5°	694.0	693.6	693.3	692.9	693.3	693.6	694.0	694.3	694.7	695.2	695.6
130°	733.5	732.6	731.6	730.7	731.6	732.6	733.5	734.4	735.1	735.5	736.0
132.5°	772.1	771.8	771.4	771.1	771.4	771.8	772.1	772.5	773.0	773.4	773.9
135°	828.6	827.9	827.2	826.6	827.2	827.9	828.6	829.2	829.8	830.2	830.7
137.5°	884.4	884.5	884.6	884.8	884.6	884.5	884.4	884.2	884.5	885.0	885.7
140°	921.0	920.7	920.5	920.3	920.5	920.7	921.0	921.2	921.4	921.6	921.9
142.5°	955.9	955.8	955.8	955.7	955.8	955.8	955.9	955.9	956.0	956.0	956.0
145°	1005.9	1005.3	1004.6	1003.9	1004.6	1005.3	1005.9	1006.6	1007.0	1007.3	1007.5
147.5°	1053.4	1053.2	1053.0	1052.8	1053.0	1053.2	1053.4	1053.6	1053.8	1054.0	1054.2
150°	1083.3	1083.0	1082.8	1082.6	1082.8	1083.0	1083.3	1083.5	1083.6	1083.6	1083.6
152.5°	1111.8	1111.2	1110.5	1109.9	1110.5	1111.2	1111.8	1112.4	1112.4	1111.8	1111.3
155°	1150.7	1149.9	1149.0	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7	1150.7	1149.9
157.5°	1184.5	1183.7	1183.0	1182.1	1183.0	1183.7	1184.5	1185.2	1185.3	1184.6	1183.9
160°	1204.9	1203.8	1202.6	1201.5	1202.6	1203.8	1204.9	1206.0	1206.2	1205.6	1204.9
162.5°	1225.1	1224.0	1222.8	1221.6	1222.8	1224.0	1225.1	1226.2	1226.1	1224.9	1223.7
165°	1250.6	1249.7	1248.8	1247.9	1248.8	1249.7	1250.6	1251.4	1251.2	1249.9	1248.6
167.5°	1270.8	1269.4	1268.0	1266.7	1268.0	1269.4	1270.8	1272.2	1272.2	1270.9	1269.5
170°	1281.8	1280.2	1278.7	1277.1	1278.7	1280.2	1281.8	1283.3	1283.5	1282.1	1280.8
172.5°	1290.7	1289.1	1287.6	1286.0	1287.6	1289.1	1290.7	1292.2	1292.3	1290.7	1289.2
175°	1300.0	1298.4	1296.9	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5	1300.0	1298.4
177.5°	1304.4	1302.9	1301.5	1300.1	1301.5	1302.9	1304.4	1305.9	1306.0	1304.6	1303.4
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	551.5	552.3	555.3	558.3	561.7	564.1	565.8	567.7	571.8	575.0	578.1
5°	516.7	518.0	524.1	528.5	535.8	542.3	547.3	552.8	559.3	568.2	576.2
7.5°	486.0	490.5	497.4	504.3	511.8	520.3	527.7	535.9	547.0	559.3	571.8
10°	468.7	473.7	480.9	489.0	496.1	505.9	515.0	524.8	537.6	552.3	567.1
12.5°	451.3	459.6	465.0	474.6	482.4	490.5	500.2	513.0	527.8	543.3	561.2
15°	429.5	434.0	444.5	449.8	460.8	473.2	482.8	495.6	510.0	530.6	550.7
17.5°	404.3	410.3	418.7	428.7	441.3	451.0	462.9	476.3	494.3	514.7	539.9
20°	387.9	392.9	403.2	414.1	427.6	437.9	450.5	463.4	482.1	503.8	530.1
22.5°	373.1	378.0	388.9	399.1	412.1	424.6	437.9	452.9	470.8	493.7	520.6
25°	350.4	356.8	366.4	376.9	389.3	403.6	418.0	431.4	450.5	474.6	503.3
27.5°	330.1	335.3	342.2	354.2	368.3	382.1	396.4	413.2	431.6	457.2	486.9
30°	317.2	321.9	328.9	339.8	353.0	367.8	382.6	398.9	418.0	443.3	473.7
32.5°	306.8	310.4	316.6	326.5	338.5	354.1	368.7	385.5	405.6	430.5	460.1
35°	291.5	294.7	297.1	306.4	317.2	331.5	346.3	364.3	383.6	407.3	436.9
37.5°	276.6	277.7	281.1	287.3	297.7	310.9	324.7	342.3	362.1	386.2	412.9
40°	267.4	267.9	270.0	275.8	284.9	297.3	310.7	328.1	347.0	369.7	396.3
42.5°	258.4	258.1	260.1	264.2	272.7	284.0	297.1	313.1	331.9	352.9	377.9
45°	244.3	244.3	243.8	247.1	254.1	265.1	276.1	291.3	307.1	327.7	348.7
47.5°	229.4	228.1	228.5	230.2	236.1	245.1	256.2	268.7	282.7	300.0	318.5
50°	219.8	217.9	217.2	219.1	224.4	232.3	242.9	253.8	267.0	282.3	298.0
52.5°	209.3	207.4	206.1	207.5	212.4	219.6	229.2	238.9	250.7	263.2	276.8
55°	193.1	191.0	190.3	190.8	194.3	200.1	208.1	217.0	225.9	236.1	245.7
57.5°	177.1	173.6	172.9	172.7	175.1	180.4	187.2	194.8	201.3	207.5	217.7
60°	166.6	162.3	160.9	160.6	162.5	166.8	173.0	180.7	185.2	189.6	198.3
62.5°	155.3	151.2	148.0	148.3	150.1	154.2	159.7	165.2	168.2	172.9	178.8
65°	137.9	132.7	130.3	129.6	130.5	133.8	138.1	141.7	145.1	147.0	152.7
67.5°	120.5	116.1	112.6	111.7	111.3	113.6	117.1	119.3	121.7	123.3	126.7
70°	108.3	104.4	100.2	98.7	98.5	100.4	103.7	104.0	107.3	108.1	111.6
72.5°	96.2	91.4	88.5	87.1	86.0	87.8	90.0	90.6	92.4	93.7	95.5
75°	77.5	73.8	71.0	68.9	68.2	69.1	69.1	70.3	71.5	72.2	74.3
77.5°	61.0	56.9	53.4	52.2	51.3	50.7	51.2	52.0	51.4	52.6	53.1
80°	49.5	45.1	42.5	42.1	40.6	39.5	39.2	39.9	39.0	39.5	40.9
82.5°	38.2	35.4	32.6	32.1	30.3	29.7	29.5	29.0	29.0	28.9	29.2
85°	22.7	21.0	19.1	18.0	17.2	16.1	16.1	15.6	15.0	14.5	14.8
87.5°	13.8	13.2	11.9	11.0	10.2	9.1	8.7	7.7	7.0	6.3	5.6
90°	23.5	22.2	20.4	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0
92.5°	40.7	39.9	38.7	37.4	36.2	34.9	32.8	30.0	27.2	24.4	21.6
95°	77.3	76.6	75.0	73.5	71.9	70.3	68.6	66.6	64.5	62.5	60.5
97.5°	122.0	121.2	119.4	117.4	115.6	113.8	112.1	110.5	108.9	107.2	105.6
100°	154.7	154.2	152.2	150.2	148.1	146.1	144.7	143.8	142.9	142.0	141.1
102.5°	188.7	188.1	186.2	184.4	182.6	180.8	179.7	179.3	178.9	178.5	178.2
105°	240.5	239.9	239.0	238.1	237.2	236.3	235.8	235.5	235.3	235.1	234.9
107.5°	296.8	296.2	296.0	295.9	295.8	295.6	295.4	295.2	294.9	294.6	294.4
110°	335.2	335.7	335.9	336.1	336.3	336.6	336.5	336.0	335.6	335.1	334.7



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.1	375.2	375.6	376.0	376.4	376.8	377.0	376.9	376.8	376.7	376.6
115°	437.3	437.5	437.9	438.4	438.8	439.3	439.5	439.5	439.5	439.5	439.5
117.5°	497.4	498.2	498.5	498.8	499.1	499.4	499.5	499.3	499.1	499.0	498.8
120°	538.2	539.3	540.0	540.6	541.3	542.0	541.9	541.0	540.1	539.2	538.3
122.5°	578.9	579.6	579.9	580.2	580.6	580.9	580.8	580.5	580.1	579.8	579.4
125°	638.6	639.0	639.2	639.5	639.7	640.0	640.1	640.1	640.1	640.1	640.1
127.5°	696.1	696.5	696.9	697.2	697.6	697.9	697.8	697.1	696.4	695.8	695.1
130°	736.4	736.8	736.8	736.8	736.8	736.8	736.5	735.8	735.2	734.5	733.8
132.5°	774.3	774.8	774.9	775.1	775.3	775.5	775.3	774.8	774.3	773.9	773.4
135°	831.1	831.6	831.6	831.6	831.6	831.6	830.9	829.6	828.2	826.9	825.6
137.5°	886.3	886.9	886.5	886.2	885.8	885.3	884.9	884.2	883.6	883.0	882.4
140°	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.6	921.2	920.7	920.3
142.5°	956.1	956.1	956.3	956.5	956.7	956.8	956.7	956.3	955.8	955.4	954.9
145°	1007.7	1007.9	1007.7	1007.5	1007.3	1007.0	1006.5	1005.6	1004.7	1003.8	1002.9
147.5°	1054.4	1054.6	1054.7	1054.9	1055.1	1055.3	1054.8	1053.8	1052.7	1051.6	1050.6
150°	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.2	1082.3	1081.4	1080.5	1079.5
152.5°	1110.8	1110.1	1110.0	1109.8	1109.6	1109.4	1109.1	1108.6	1108.0	1107.5	1107.0
155°	1149.0	1148.1	1148.3	1148.5	1148.7	1149.0	1149.1	1149.1	1149.1	1149.1	1149.1
157.5°	1183.3	1182.6	1182.7	1182.7	1182.7	1182.8	1183.0	1183.4	1183.8	1184.2	1184.6
160°	1204.2	1203.6	1203.8	1204.0	1204.2	1204.5	1204.7	1204.9	1205.1	1205.3	1205.6
162.5°	1222.4	1221.2	1221.5	1221.7	1221.9	1222.1	1222.5	1223.1	1223.8	1224.4	1224.9
165°	1247.2	1245.9	1246.3	1246.8	1247.2	1247.7	1248.2	1248.9	1249.6	1250.2	1250.9
167.5°	1268.2	1266.9	1266.8	1266.8	1266.7	1266.7	1267.1	1268.1	1269.0	1269.9	1270.9
170°	1279.5	1278.1	1277.9	1277.7	1277.5	1277.2	1277.7	1278.8	1279.9	1281.0	1282.1
172.5°	1287.7	1286.2	1286.2	1286.1	1286.1	1286.0	1286.5	1287.4	1288.4	1289.3	1290.2
175°	1296.9	1295.3	1295.5	1295.7	1296.0	1296.2	1296.9	1298.0	1299.1	1300.2	1301.3
177.5°	1302.1	1300.9	1300.9	1300.9	1300.9	1300.9	1301.3	1302.2	1303.1	1304.0	1304.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	580.8	582.7	585.2	589.4	590.9	592.8	595.5	595.3	596.0	599.0	605.0
5°	582.9	590.4	597.5	606.1	615.2	621.2	629.2	634.3	639.3	645.8	656.8
7.5°	583.8	595.5	608.6	623.8	637.2	652.7	664.8	676.2	686.5	700.0	713.2
10°	582.5	598.2	615.2	634.3	654.6	671.9	687.4	705.1	720.1	736.6	751.4
12.5°	580.0	599.0	621.7	643.1	666.8	692.3	711.7	729.5	749.5	768.5	791.4
15°	574.3	600.4	626.9	655.1	686.9	716.3	744.3	767.4	788.9	817.4	847.3
17.5°	567.1	595.2	628.7	662.9	696.1	729.6	764.3	799.1	826.3	861.6	884.9
20°	560.5	593.0	627.4	668.0	701.3	743.1	777.5	811.1	848.5	883.6	911.6
22.5°	551.1	586.6	623.2	663.6	707.3	749.2	788.9	825.5	862.8	901.0	934.8
25°	539.2	571.5	614.7	660.6	704.1	749.5	795.2	841.0	881.2	921.6	953.1
27.5°	519.0	559.7	600.0	647.3	695.6	747.0	795.9	843.8	886.0	919.2	938.7
30°	508.6	544.0	587.7	635.3	687.6	742.9	793.8	840.8	880.0	906.6	914.4
32.5°	493.3	529.8	572.6	621.9	677.3	734.1	787.0	831.4	864.1	878.1	868.6
35°	470.6	503.6	546.8	597.2	654.9	715.3	767.7	805.2	821.9	808.8	776.1
37.5°	443.3	476.1	519.5	569.1	628.6	690.1	737.4	764.5	758.9	726.2	677.4
40°	424.2	454.8	496.1	549.7	607.7	669.4	711.0	725.6	710.3	663.5	611.6
42.5°	403.0	432.8	474.3	526.0	587.5	644.4	680.6	681.9	656.2	600.2	548.2
45°	370.7	399.1	438.3	492.1	549.0	602.5	626.4	614.7	567.3	513.4	461.0
47.5°	338.8	363.5	402.1	453.1	507.2	552.2	564.1	543.0	492.6	440.1	391.6
50°	315.5	340.3	376.7	425.5	477.6	516.4	522.2	494.2	444.7	391.9	354.0
52.5°	293.1	317.8	352.7	397.9	445.6	480.7	480.9	448.6	399.3	352.2	316.9
55°	260.2	282.5	314.1	354.5	397.0	424.4	417.8	384.4	341.5	300.6	269.8
57.5°	228.6	248.0	277.0	310.7	348.2	370.9	359.8	327.6	289.4	254.7	231.4
60°	208.1	226.6	251.5	283.3	314.8	332.4	321.9	292.8	257.6	229.6	209.3
62.5°	188.2	203.8	227.7	255.3	284.6	297.6	288.3	259.5	229.1	203.9	187.3
65°	160.2	172.8	191.9	215.6	236.8	248.1	240.2	213.4	190.3	172.1	159.0
67.5°	133.8	143.7	158.2	177.2	195.3	201.4	194.2	175.5	155.9	141.4	132.1
70°	115.6	125.0	137.1	151.8	167.5	174.0	166.8	152.0	136.0	122.6	113.5
72.5°	99.8	107.0	117.3	129.8	142.1	148.6	143.7	129.5	115.9	105.9	98.3
75°	76.0	82.2	89.4	98.3	107.8	112.1	107.8	98.0	88.7	81.3	75.7
77.5°	55.2	58.6	64.1	70.8	76.7	80.0	76.2	69.7	63.9	58.9	56.1
80°	42.1	44.4	48.3	53.5	57.6	60.7	58.3	52.8	48.3	44.9	43.7
82.5°	30.6	32.2	34.7	38.6	41.3	42.9	41.9	37.9	36.1	33.1	31.9
85°	15.0	16.1	17.7	18.9	21.3	21.5	21.7	20.1	18.4	17.7	16.8
87.5°	6.3	7.0	8.0	9.1	10.3	10.8	11.0	11.3	10.9	11.0	10.5
90°	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8
92.5°	24.4	27.2	30.0	32.8	34.9	36.2	37.4	38.7	39.9	40.7	41.5
95°	62.5	64.5	66.6	68.6	70.3	71.9	73.5	75.0	76.6	77.3	78.0
97.5°	107.2	108.9	110.5	112.1	113.8	115.6	117.4	119.4	121.2	122.0	122.8
100°	142.0	142.9	143.8	144.7	146.1	148.1	150.2	152.2	154.2	154.7	155.1
102.5°	178.5	178.9	179.3	179.7	180.8	182.6	184.4	186.2	188.1	188.7	189.3
105°	235.1	235.3	235.5	235.8	236.3	237.2	238.1	239.0	239.9	240.5	241.3
107.5°	294.6	294.9	295.2	295.4	295.6	295.8	295.9	296.0	296.2	296.8	297.4
110°	335.1	335.6	336.0	336.5	336.6	336.3	336.1	335.9	335.7	335.2	334.8





TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	376.7	376.8	376.9	377.0	376.8	376.4	376.0	375.6	375.2	375.1	375.0
115°	439.5	439.5	439.5	439.5	439.3	438.8	438.4	437.9	437.5	437.3	437.0
117.5°	499.0	499.1	499.3	499.5	499.4	499.1	498.8	498.5	498.2	497.4	496.7
120°	539.2	540.1	541.0	541.9	542.0	541.3	540.6	540.0	539.3	538.2	537.0
122.5°	579.8	580.1	580.5	580.8	580.9	580.6	580.2	579.9	579.6	578.9	578.0
125°	640.1	640.1	640.1	640.1	640.0	639.7	639.5	639.2	639.0	638.6	638.1
127.5°	695.8	696.4	697.1	697.8	697.9	697.6	697.2	696.9	696.5	696.1	695.6
130°	734.5	735.2	735.8	736.5	736.8	736.8	736.8	736.8	736.8	736.4	736.0
132.5°	773.9	774.3	774.8	775.3	775.5	775.3	775.1	774.9	774.8	774.3	773.9
135°	826.9	828.2	829.6	830.9	831.6	831.6	831.6	831.6	831.6	831.1	830.7
137.5°	883.0	883.6	884.2	884.9	885.3	885.8	886.2	886.5	886.9	886.3	885.7
140°	920.7	921.2	921.6	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.9
142.5°	955.4	955.8	956.3	956.7	956.8	956.7	956.5	956.3	956.1	956.1	956.0
145°	1003.8	1004.7	1005.6	1006.5	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7	1007.5
147.5°	1051.6	1052.7	1053.8	1054.8	1055.3	1055.1	1054.9	1054.7	1054.6	1054.4	1054.2
150°	1080.5	1081.4	1082.3	1083.2	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6
152.5°	1107.5	1108.0	1108.6	1109.1	1109.4	1109.6	1109.8	1110.0	1110.1	1110.8	1111.3
155°	1149.1	1149.1	1149.1	1149.1	1149.0	1148.7	1148.5	1148.3	1148.1	1149.0	1149.9
157.5°	1184.2	1183.8	1183.4	1183.0	1182.8	1182.7	1182.7	1182.7	1182.6	1183.3	1183.9
160°	1205.3	1205.1	1204.9	1204.7	1204.5	1204.2	1204.0	1203.8	1203.6	1204.2	1204.9
162.5°	1224.4	1223.8	1223.1	1222.5	1222.1	1221.9	1221.7	1221.5	1221.2	1222.4	1223.7
165°	1250.2	1249.6	1248.9	1248.2	1247.7	1247.2	1246.8	1246.3	1245.9	1247.2	1248.6
167.5°	1269.9	1269.0	1268.1	1267.1	1266.7	1266.7	1266.8	1266.8	1266.9	1268.2	1269.5
170°	1281.0	1279.9	1278.8	1277.7	1277.2	1277.5	1277.7	1277.9	1278.1	1279.5	1280.8
172.5°	1289.3	1288.4	1287.4	1286.5	1286.0	1286.1	1286.1	1286.2	1286.2	1287.7	1289.2
175°	1300.2	1299.1	1298.0	1296.9	1296.2	1296.0	1295.7	1295.5	1295.3	1296.9	1298.4
177.5°	1304.0	1303.1	1302.2	1301.3	1300.9	1300.9	1300.9	1300.9	1300.9	1302.1	1303.4
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	608.1	608.5	610.3	611.6	612.0	613.9	614.0
5°	661.6	665.6	673.5	674.2	675.4	681.7	676.8
7.5°	724.2	734.5	741.3	747.5	749.6	752.3	751.8
10°	764.4	779.6	787.3	799.5	799.9	803.0	801.1
12.5°	804.7	822.4	836.4	838.7	848.9	850.5	853.1
15°	861.8	880.7	900.1	907.1	921.1	924.4	929.7
17.5°	915.5	934.8	948.5	966.3	972.2	979.9	974.6
20°	945.0	966.0	983.3	997.3	1003.3	1007.6	1007.1
22.5°	962.8	984.0	997.9	1008.7	1014.2	1016.0	1015.9
25°	973.9	986.1	990.5	994.5	988.3	986.1	987.0
27.5°	942.9	939.8	928.6	913.8	898.6	886.5	879.8
30°	900.3	881.7	864.7	835.1	819.8	810.7	802.5
32.5°	839.9	810.3	777.7	750.5	733.2	719.7	717.7
35°	736.4	692.0	652.0	618.7	601.6	587.0	583.6
37.5°	626.0	579.9	543.9	514.6	496.1	485.8	476.3
40°	552.8	513.1	477.8	452.9	438.8	431.4	425.5
42.5°	496.4	460.2	425.0	406.1	393.3	388.8	385.3
45°	418.5	384.8	360.4	346.1	338.7	331.0	327.4
47.5°	356.1	328.7	312.7	300.4	292.5	287.9	285.7
50°	320.7	298.3	284.0	274.6	267.4	263.9	262.0
52.5°	289.4	270.9	258.9	251.5	246.6	244.0	243.2
55°	249.2	235.2	227.5	221.1	217.5	215.1	214.2
57.5°	216.7	205.8	199.7	194.3	192.9	191.0	190.3
60°	195.3	186.9	181.7	178.0	176.8	174.5	174.9
62.5°	176.3	169.5	165.0	163.0	161.4	159.4	160.1
65°	149.2	144.1	141.7	139.9	137.9	136.7	137.6
67.5°	125.1	121.7	118.5	117.3	116.4	116.2	115.2
70°	109.5	106.6	103.7	103.0	103.0	102.1	101.8
72.5°	94.3	92.3	90.4	89.8	89.1	89.5	88.5
75°	72.9	71.2	70.5	69.8	69.6	69.6	68.9
77.5°	53.8	52.6	51.5	51.5	50.6	50.3	50.2
80°	40.9	40.4	39.5	39.5	39.0	39.2	38.7
82.5°	30.7	30.1	29.9	29.5	28.8	28.9	28.4
85°	16.5	15.8	15.6	14.8	14.3	14.8	14.3
87.5°	11.0	11.0	11.0	10.7	10.6	10.7	10.3
90°	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	42.3	43.1	43.7	43.9	44.2	44.5	44.7
95°	78.7	79.3	79.7	79.7	79.7	79.7	79.7
97.5°	123.6	124.4	124.8	124.8	124.8	124.8	124.8
100°	155.5	156.0	156.2	156.2	156.2	156.2	156.2
102.5°	190.0	190.6	191.0	191.2	191.4	191.6	191.7
105°	242.0	242.6	243.3	243.9	244.6	245.3	245.9
107.5°	298.0	298.6	298.9	298.9	298.8	298.8	298.7
110°	334.3	333.9	334.0	334.7	335.3	336.0	336.7



TEST NUMBER: P332518-840

CATALOG NUMBER: S124DIP-S350D1035U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.9	374.9	374.9	375.0	375.1	375.3	375.4
115°	436.8	436.6	436.4	436.2	435.9	435.7	435.5
117.5°	495.8	495.1	494.5	494.0	493.6	493.1	492.7
120°	535.9	534.8	534.4	534.9	535.3	535.8	536.2
122.5°	577.3	576.5	575.7	574.9	574.1	573.3	572.5
125°	637.7	637.2	636.8	636.4	635.9	635.5	635.0
127.5°	695.2	694.7	694.3	694.0	693.6	693.3	692.9
130°	735.5	735.1	734.4	733.5	732.6	731.6	730.7
132.5°	773.4	773.0	772.5	772.1	771.8	771.4	771.1
135°	830.2	829.8	829.2	828.6	827.9	827.2	826.6
137.5°	885.0	884.5	884.2	884.4	884.5	884.6	884.8
140°	921.6	921.4	921.2	921.0	920.7	920.5	920.3
142.5°	956.0	956.0	955.9	955.9	955.8	955.8	955.7
145°	1007.3	1007.0	1006.6	1005.9	1005.3	1004.6	1003.9
147.5°	1054.0	1053.8	1053.6	1053.4	1053.2	1053.0	1052.8
150°	1083.6	1083.6	1083.5	1083.3	1083.0	1082.8	1082.6
152.5°	1111.8	1112.4	1112.4	1111.8	1111.2	1110.5	1109.9
155°	1150.7	1151.7	1151.7	1150.7	1149.9	1149.0	1148.1
157.5°	1184.6	1185.3	1185.2	1184.5	1183.7	1183.0	1182.1
160°	1205.6	1206.2	1206.0	1204.9	1203.8	1202.6	1201.5
162.5°	1224.9	1226.1	1226.2	1225.1	1224.0	1222.8	1221.6
165°	1249.9	1251.2	1251.4	1250.6	1249.7	1248.8	1247.9
167.5°	1270.9	1272.2	1272.2	1270.8	1269.4	1268.0	1266.7
170°	1282.1	1283.5	1283.3	1281.8	1280.2	1278.7	1277.1
172.5°	1290.7	1292.3	1292.2	1290.7	1289.1	1287.6	1286.0
175°	1300.0	1301.5	1301.5	1300.0	1298.4	1296.9	1295.3
177.5°	1304.6	1306.0	1305.9	1304.4	1302.9	1301.5	1300.1
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3

(END OF REPORT)