

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332526-840

Luminaire Tested: **S124DIP-S350D1205U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332526-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D1205U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6449.3 lumens  
Efficiency: N/A  
Efficacy: 152.8 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	17	13
5	64	53	45	40	57	48	41	36	37	33	29	28	24	22	19	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4657	4657	4657	4657
5°	5485	4669	4122	4669
10°	6567	4649	3710	4649
15°	7770	4603	3408	4603
20°	8652	4554	3137	4554
25°	8792	4483	2950	4483
30°	7481	4416	2892	4416
35°	5752	4306	2893	4306
40°	4484	4176	2947	4176
45°	3738	3981	2997	3981
50°	3291	3743	3097	3743
55°	3015	3458	3222	3458
60°	2824	3202	3371	3202
65°	2628	2917	3498	2917
70°	2403	2634	3576	2634
75°	2149	2318	3534	2318
80°	1799	1901	3422	1901
85°	1325	1371	3270	1371



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	0.9
10°-20°	173.3	2.7
20°-30°	274.7	4.3
30°-40°	305.7	4.7
40°-50°	278.3	4.3
50°-60°	227.4	3.5
60°-70°	162.4	2.5
70°-80°	89.4	1.4
80°-90°	28.9	0.4
90°-100°	53.7	0.8
100°-110°	342.1	5.3
110°-120°	654.5	10.1
120°-130°	830.8	12.9
130°-140°	888.9	13.8
140°-150°	831.2	12.9
150°-160°	670.3	10.4
160°-170°	432.4	6.7
170°-180°	149.0	2.3
0°-30°	504.2	7.8
0°-40°	809.9	12.6
0°-60°	1315.6	20.4
0°-90°	1596.4	24.8
90°-120°	1050.3	16.3
90°-150°	3601.3	55.8
90°-180°	4853.0	75.2
0°-180°	6449.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	577	577	577	577	577	
5°	677	576	509	576	677	69
15°	930	551	408	551	930	263
25°	987	503	331	503	987	435
35°	584	437	294	437	584	370
45°	327	349	262	349	327	258
55°	214	246	229	246	214	193
65°	138	153	183	153	138	136
75°	69	74	113	74	69	73
85°	14	15	35	15	14	18
90°	35	4	35	4	35	16
95°	34	64	34	64	34	27
105°	334	353	334	353	334	292
115°	664	659	664	659	664	657
125°	934	927	934	927	934	832
135°	1158	1150	1158	1150	1158	891
145°	1333	1326	1333	1326	1333	833
155°	1453	1454	1453	1454	1453	670
165°	1527	1534	1527	1534	1527	431
175°	1559	1569	1559	1569	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	614.0	613.9	612.0	611.6	610.3	608.5	608.1	605.0	599.0	596.0	595.3
5°	676.8	681.7	675.4	674.2	673.5	665.6	661.6	656.8	645.8	639.3	634.3
7.5°	751.8	752.3	749.6	747.5	741.3	734.5	724.2	713.2	700.0	686.5	676.2
10°	801.1	803.0	799.9	799.5	787.3	779.6	764.4	751.4	736.6	720.1	705.1
12.5°	853.1	850.5	848.9	838.7	836.4	822.4	804.7	791.4	768.5	749.5	729.5
15°	929.7	924.4	921.1	907.1	900.1	880.7	861.8	847.3	817.4	788.9	767.4
17.5°	974.6	979.9	972.2	966.3	948.5	934.8	915.5	884.9	861.6	826.3	799.1
20°	1007.1	1007.6	1003.3	997.3	983.3	966.0	945.0	911.6	883.6	848.5	811.1
22.5°	1015.9	1016.0	1014.2	1008.7	997.9	984.0	962.8	934.8	901.0	862.8	825.5
25°	987.0	986.1	988.3	994.5	990.5	986.1	973.9	953.1	921.6	881.2	841.0
27.5°	879.8	886.5	898.6	913.8	928.6	939.8	942.9	938.7	919.2	886.0	843.8
30°	802.5	810.7	819.8	835.1	864.7	881.7	900.3	914.4	906.6	880.0	840.8
32.5°	717.7	719.7	733.2	750.5	777.7	810.3	839.9	868.6	878.1	864.1	831.4
35°	583.6	587.0	601.6	618.7	652.0	692.0	736.4	776.1	808.8	821.9	805.2
37.5°	476.3	485.8	496.1	514.6	543.9	579.9	626.0	677.4	726.2	758.9	764.5
40°	425.5	431.4	438.8	452.9	477.8	513.1	552.8	611.6	663.5	710.3	725.6
42.5°	385.3	388.8	393.3	406.1	425.0	460.2	496.4	548.2	600.2	656.2	681.9
45°	327.4	331.0	338.7	346.1	360.4	384.8	418.5	461.0	513.4	567.3	614.7
47.5°	285.7	287.9	292.5	300.4	312.7	328.7	356.1	391.6	440.1	492.6	543.0
50°	262.0	263.9	267.4	274.6	284.0	298.3	320.7	354.0	391.9	444.7	494.2
52.5°	243.2	244.0	246.6	251.5	258.9	270.9	289.4	316.9	352.2	399.3	448.6
55°	214.2	215.1	217.5	221.1	227.5	235.2	249.2	269.8	300.6	341.5	384.4
57.5°	190.3	191.0	192.9	194.3	199.7	205.8	216.7	231.4	254.7	289.4	327.6
60°	174.9	174.5	176.8	178.0	181.7	186.9	195.3	209.3	229.6	257.6	292.8
62.5°	160.1	159.4	161.4	163.0	165.0	169.5	176.3	187.3	203.9	229.1	259.5
65°	137.6	136.7	137.9	139.9	141.7	144.1	149.2	159.0	172.1	190.3	213.4
67.5°	115.2	116.2	116.4	117.3	118.5	121.7	125.1	132.1	141.4	155.9	175.5
70°	101.8	102.1	103.0	103.0	103.7	106.6	109.5	113.5	122.6	136.0	152.0
72.5°	88.5	89.5	89.1	89.8	90.4	92.3	94.3	98.3	105.9	115.9	129.5
75°	68.9	69.6	69.6	69.8	70.5	71.2	72.9	75.7	81.3	88.7	98.0
77.5°	50.2	50.3	50.6	51.5	51.5	52.6	53.8	56.1	58.9	63.9	69.7
80°	38.7	39.2	39.0	39.5	39.5	40.4	40.9	43.7	44.9	48.3	52.8
82.5°	28.4	28.9	28.8	29.5	29.9	30.1	30.7	31.9	33.1	36.1	37.9
85°	14.3	14.8	14.3	14.8	15.6	15.8	16.5	16.8	17.7	18.4	20.1
87.5°	11.2	11.7	11.6	11.7	12.0	11.9	11.8	11.3	11.8	11.6	12.0
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0	26.5	24.8	22.8
95°	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0	27.4	25.9	25.5
97.5°	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3	31.1	31.0	60.1
100°	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7	47.2	51.6	87.7
102.5°	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1	201.0	248.7	253.5
105°	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8	368.5	366.1	364.8
107.5°	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8	457.6	456.5	454.6
110°	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6	518.0	517.5	515.9



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4	576.5	576.6	575.9
115°	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9	662.4	661.8	662.1
117.5°	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8	749.9	750.0	749.5
120°	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6	802.8
122.5°	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8	856.5	856.2	855.8
125°	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9	930.1	929.4	929.9
127.5°	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.7	1004.9	1003.7
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6	1049.2	1049.0	1048.2
132.5°	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7	1093.4	1093.2	1092.2
135°	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5	1154.0	1153.5	1152.5
137.5°	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8	1212.2	1211.6	1210.5
140°	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9	1248.1	1247.4	1246.8
142.5°	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3	1281.7	1281.1	1280.8
145°	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0	1329.8	1329.5	1329.5
147.5°	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9	1371.7	1371.5	1371.7
150°	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7	1398.7	1398.7	1399.0
152.5°	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1	1421.7	1421.3	1421.7
155°	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6	1452.6	1451.5	1452.3
157.5°	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0	1478.9
160°	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9	1495.2
162.5°	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2	1510.6	1509.0	1509.2
165°	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0	1529.8	1527.8	1527.8
167.5°	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5	1544.2	1541.9	1542.1
170°	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4	1553.4	1551.3	1551.0
172.5°	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0	1558.9	1556.9	1556.6
175°	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7	1565.3	1563.0	1562.8
177.5°	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3	1568.6	1567.0	1566.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	595.5	592.8	590.9	589.4	585.2	582.7	580.8	578.1	575.0	571.8	567.7
5°	629.2	621.2	615.2	606.1	597.5	590.4	582.9	576.2	568.2	559.3	552.8
7.5°	664.8	652.7	637.2	623.8	608.6	595.5	583.8	571.8	559.3	547.0	535.9
10°	687.4	671.9	654.6	634.3	615.2	598.2	582.5	567.1	552.3	537.6	524.8
12.5°	711.7	692.3	666.8	643.1	621.7	599.0	580.0	561.2	543.3	527.8	513.0
15°	744.3	716.3	686.9	655.1	626.9	600.4	574.3	550.7	530.6	510.0	495.6
17.5°	764.3	729.6	696.1	662.9	628.7	595.2	567.1	539.9	514.7	494.3	476.3
20°	777.5	743.1	701.3	668.0	627.4	593.0	560.5	530.1	503.8	482.1	463.4
22.5°	788.9	749.2	707.3	663.6	623.2	586.6	551.1	520.6	493.7	470.8	452.9
25°	795.2	749.5	704.1	660.6	614.7	571.5	539.2	503.3	474.6	450.5	431.4
27.5°	795.9	747.0	695.6	647.3	600.0	559.7	519.0	486.9	457.2	431.6	413.2
30°	793.8	742.9	687.6	635.3	587.7	544.0	508.6	473.7	443.3	418.0	398.9
32.5°	787.0	734.1	677.3	621.9	572.6	529.8	493.3	460.1	430.5	405.6	385.5
35°	767.7	715.3	654.9	597.2	546.8	503.6	470.6	436.9	407.3	383.6	364.3
37.5°	737.4	690.1	628.6	569.1	519.5	476.1	443.3	412.9	386.2	362.1	342.3
40°	711.0	669.4	607.7	549.7	496.1	454.8	424.2	396.3	369.7	347.0	328.1
42.5°	680.6	644.4	587.5	526.0	474.3	432.8	403.0	377.9	352.9	331.9	313.1
45°	626.4	602.5	549.0	492.1	438.3	399.1	370.7	348.7	327.7	307.1	291.3
47.5°	564.1	552.2	507.2	453.1	402.1	363.5	338.8	318.5	300.0	282.7	268.7
50°	522.2	516.4	477.6	425.5	376.7	340.3	315.5	298.0	282.3	267.0	253.8
52.5°	480.9	480.7	445.6	397.9	352.7	317.8	293.1	276.8	263.2	250.7	238.9
55°	417.8	424.4	397.0	354.5	314.1	282.5	260.2	245.7	236.1	225.9	217.0
57.5°	359.8	370.9	348.2	310.7	277.0	248.0	228.6	217.7	207.5	201.3	194.8
60°	321.9	332.4	314.8	283.3	251.5	226.6	208.1	198.3	189.6	185.2	180.7
62.5°	288.3	297.6	284.6	255.3	227.7	203.8	188.2	178.8	172.9	168.2	165.2
65°	240.2	248.1	236.8	215.6	191.9	172.8	160.2	152.7	147.0	145.1	141.7
67.5°	194.2	201.4	195.3	177.2	158.2	143.7	133.8	126.7	123.3	121.7	119.3
70°	166.8	174.0	167.5	151.8	137.1	125.0	115.6	111.6	108.1	107.3	104.0
72.5°	143.7	148.6	142.1	129.8	117.3	107.0	99.8	95.5	93.7	92.4	90.6
75°	107.8	112.1	107.8	98.3	89.4	82.2	76.0	74.3	72.2	71.5	70.3
77.5°	76.2	80.0	76.7	70.8	64.1	58.6	55.2	53.1	52.6	51.4	52.0
80°	58.3	60.7	57.6	53.5	48.3	44.4	42.1	40.9	39.5	39.0	39.9
82.5°	41.9	42.9	41.3	38.6	34.7	32.2	30.6	29.2	28.9	29.0	29.0
85°	21.7	21.5	21.3	18.9	17.7	16.1	15.0	14.8	14.5	15.0	15.6
87.5°	11.6	11.4	10.8	9.5	8.4	7.2	6.5	5.7	6.5	7.2	8.0
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7	14.9	15.1	15.2
95°	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5	55.6	46.8	38.0
97.5°	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0	142.6	148.1	153.6
100°	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5	197.1	201.9	206.5
102.5°	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4	257.8	261.3	264.7
105°	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1	354.8	356.3	357.9
107.5°	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9	445.8	446.6	447.3
110°	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0	507.7	508.5	509.3





TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0	568.5	569.8	571.2
115°	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4	660.2	661.1	661.8
117.5°	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8	743.8	744.9	745.9
120°	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1	800.1	801.2	802.2
122.5°	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6	852.3	852.9	853.5
125°	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0	928.1	929.1	930.1
127.5°	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4	998.6	998.9	999.2
130°	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3	1044.6	1044.9	1045.1
132.5°	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6	1087.0	1087.5	1088.0
135°	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9	1149.7	1149.4	1149.1
137.5°	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1	1206.2	1206.3	1206.4
140°	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6	1243.1	1243.6	1244.3
142.5°	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5	1276.5	1277.4	1278.3
145°	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0	1326.8	1327.6	1328.3
147.5°	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0	1367.6	1369.0	1370.5
150°	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2	1396.2	1397.2	1398.4
152.5°	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6	1420.5	1421.3	1422.1
155°	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9	1454.1	1454.4	1454.6
157.5°	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7	1482.6	1482.4	1482.3
160°	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6	1498.8	1498.0	1497.3
162.5°	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6	1513.7	1512.7	1511.7
165°	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7	1532.4	1531.1	1529.7
167.5°	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6	1547.3	1546.0	1544.6
170°	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1	1555.6	1554.0	1552.5
172.5°	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8	1561.2	1559.6	1558.0
175°	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8	1567.3	1565.7	1564.2
177.5°	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7	1570.2	1568.7	1567.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	565.8	564.1	561.7	558.3	555.3	552.3	551.5	550.4	552.7	550.8	550.2
5°	547.3	542.3	535.8	528.5	524.1	518.0	516.7	514.3	511.9	511.7	509.3
7.5°	527.7	520.3	511.8	504.3	497.4	490.5	486.0	485.1	481.6	479.5	477.2
10°	515.0	505.9	496.1	489.0	480.9	473.7	468.7	465.9	463.4	460.8	458.4
12.5°	500.2	490.5	482.4	474.6	465.0	459.6	451.3	446.4	445.9	445.9	439.7
15°	482.8	473.2	460.8	449.8	444.5	434.0	429.5	423.7	420.2	416.6	413.7
17.5°	462.9	451.0	441.3	428.7	418.7	410.3	404.3	400.9	395.5	390.4	386.8
20°	450.5	437.9	427.6	414.1	403.2	392.9	387.9	383.1	379.1	374.8	370.7
22.5°	437.9	424.6	412.1	399.1	388.9	378.0	373.1	366.7	362.8	360.4	356.4
25°	418.0	403.6	389.3	376.9	366.4	356.8	350.4	345.4	341.0	339.1	336.5
27.5°	396.4	382.1	368.3	354.2	342.2	335.3	330.1	326.4	323.9	321.3	320.1
30°	382.6	367.8	353.0	339.8	328.9	321.9	317.2	314.6	312.7	311.4	310.2
32.5°	368.7	354.1	338.5	326.5	316.6	310.4	306.8	304.2	303.3	302.9	302.4
35°	346.3	331.5	317.2	306.4	297.1	294.7	291.5	290.1	289.6	291.3	292.1
37.5°	324.7	310.9	297.7	287.3	281.1	277.7	276.6	276.7	278.4	279.8	281.6
40°	310.7	297.3	284.9	275.8	270.0	267.9	267.4	268.6	270.5	272.3	274.2
42.5°	297.1	284.0	272.7	264.2	260.1	258.1	258.4	259.6	262.4	264.4	267.2
45°	276.1	265.1	254.1	247.1	243.8	244.3	244.3	246.4	249.0	252.2	255.3
47.5°	256.2	245.1	236.1	230.2	228.5	228.1	229.4	232.3	236.0	239.8	244.2
50°	242.9	232.3	224.4	219.1	217.2	217.9	219.8	222.5	227.0	231.9	236.4
52.5°	229.2	219.6	212.4	207.5	206.1	207.4	209.3	213.5	217.5	222.7	228.1
55°	208.1	200.1	194.3	190.8	190.3	191.0	193.1	197.6	203.4	209.8	215.1
57.5°	187.2	180.4	175.1	172.7	172.9	173.6	177.1	182.5	188.6	195.5	202.3
60°	173.0	166.8	162.5	160.6	160.9	162.3	166.6	171.6	179.3	185.9	193.1
62.5°	159.7	154.2	150.1	148.3	148.0	151.2	155.3	160.5	168.1	175.6	183.4
65°	138.1	133.8	130.5	129.6	130.3	132.7	137.9	144.8	151.3	159.2	167.3
67.5°	117.1	113.6	111.3	111.7	112.6	116.1	120.5	126.4	133.8	142.0	150.0
70°	103.7	100.4	98.5	98.7	100.2	104.4	108.3	114.2	122.1	130.5	137.1
72.5°	90.0	87.8	86.0	87.1	88.5	91.4	96.2	102.2	109.2	116.9	124.0
75°	69.1	69.1	68.2	68.9	71.0	73.8	77.5	83.6	90.6	96.8	102.5
77.5°	51.2	50.7	51.3	52.2	53.4	56.9	61.0	65.4	70.6	76.9	81.6
80°	39.2	39.5	40.6	42.1	42.5	45.1	49.5	53.5	57.6	62.8	67.4
82.5°	29.5	29.7	30.3	32.1	32.6	35.4	38.2	42.2	45.9	49.5	53.2
85°	16.1	16.1	17.2	18.0	19.1	21.0	22.7	25.1	28.5	30.8	34.4
87.5°	9.1	9.6	10.8	11.6	12.6	13.9	14.6	17.1	18.2	19.4	21.3
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0	29.6	31.1	32.0
95°	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0	30.5	32.1	33.0
97.5°	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3	31.4	31.6	31.8
100°	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7	38.4	33.9	31.8
102.5°	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1	105.3	57.5	33.6
105°	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8	373.1	375.5	371.9
107.5°	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8	459.9	461.0	462.1
110°	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6	519.1	519.6	520.2



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4	576.3	576.2	576.6
115°	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9	663.4	663.9	664.2
117.5°	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8	749.7	749.6	749.5
120°	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7	804.2	804.7	804.7
122.5°	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8	857.1	857.4	857.3
125°	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9	931.7	932.5	933.0
127.5°	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6	1004.4	1004.3	1004.1
130°	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6	1049.9	1050.1	1050.2
132.5°	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7	1094.0	1094.2	1094.2
135°	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5	1155.0	1155.6	1156.1
137.5°	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8	1213.4	1214.0	1214.2
140°	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9	1249.7	1250.5	1251.0
142.5°	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3	1282.8	1283.4	1283.7
145°	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0	1330.3	1330.5	1330.9
147.5°	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9	1372.1	1372.3	1372.5
150°	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7	1398.7	1398.7	1398.9
152.5°	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1	1422.5	1422.9	1423.0
155°	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6	1454.6	1455.7	1455.8
157.5°	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5
160°	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2
162.5°	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2	1513.7	1515.3	1515.2
165°	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0	1534.1	1536.1	1536.0
167.5°	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5	1548.7	1551.1	1550.8
170°	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4	1557.5	1559.6	1559.3
172.5°	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0	1563.2	1565.2	1564.9
175°	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7	1570.0	1572.4	1572.0
177.5°	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3	1572.0	1573.7	1573.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	549.8	549.5	548.1	547.9	548.1	549.5	549.8	550.2	550.8	552.7	550.4
5°	507.9	506.6	505.9	508.6	505.9	506.6	507.9	509.3	511.7	511.9	514.3
7.5°	476.3	475.3	473.2	472.5	473.2	475.3	476.3	477.2	479.5	481.6	485.1
10°	456.1	455.0	453.1	452.6	453.1	455.0	456.1	458.4	460.8	463.4	465.9
12.5°	436.5	434.6	434.2	434.7	434.2	434.6	436.5	439.7	445.9	445.9	446.4
15°	410.6	409.6	407.0	407.8	407.0	409.6	410.6	413.7	416.6	420.2	423.7
17.5°	385.1	384.0	380.7	383.5	380.7	384.0	385.1	386.8	390.4	395.5	400.9
20°	369.0	367.1	365.5	365.2	365.5	367.1	369.0	370.7	374.8	379.1	383.1
22.5°	353.8	352.0	351.8	350.3	351.8	352.0	353.8	356.4	360.4	362.8	366.7
25°	334.6	333.0	332.4	331.2	332.4	333.0	334.6	336.5	339.1	341.0	345.4
27.5°	319.9	319.1	318.2	318.6	318.2	319.1	319.9	320.1	321.3	323.9	326.4
30°	310.9	310.7	310.2	310.2	310.2	310.7	310.9	310.2	311.4	312.7	314.6
32.5°	303.5	303.5	303.8	303.8	303.8	303.5	303.5	302.4	302.9	303.3	304.2
35°	293.1	293.8	294.2	293.5	294.2	293.8	293.1	292.1	291.3	289.6	290.1
37.5°	283.6	284.3	285.0	285.8	285.0	284.3	283.6	281.6	279.8	278.4	276.7
40°	276.3	277.9	278.4	279.6	278.4	277.9	276.3	274.2	272.3	270.5	268.6
42.5°	269.4	271.2	272.5	272.8	272.5	271.2	269.4	267.2	264.4	262.4	259.6
45°	258.8	260.7	262.5	262.5	262.5	260.7	258.8	255.3	252.2	249.0	246.4
47.5°	247.9	250.6	252.4	252.8	252.4	250.6	247.9	244.2	239.8	236.0	232.3
50°	240.4	243.8	245.5	246.6	245.5	243.8	240.4	236.4	231.9	227.0	222.5
52.5°	233.2	236.5	238.7	239.3	238.7	236.5	233.2	228.1	222.7	217.5	213.5
55°	220.6	225.4	228.0	228.9	228.0	225.4	220.6	215.1	209.8	203.4	197.6
57.5°	208.7	213.2	216.2	216.9	216.2	213.2	208.7	202.3	195.5	188.6	182.5
60°	199.5	204.4	208.1	208.8	208.1	204.4	199.5	193.1	185.9	179.3	171.6
62.5°	190.2	195.2	198.6	200.5	198.6	195.2	190.2	183.4	175.6	168.1	160.5
65°	174.0	179.0	182.4	183.1	182.4	179.0	174.0	167.3	159.2	151.3	144.8
67.5°	156.3	161.4	163.5	164.9	163.5	161.4	156.3	150.0	142.0	133.8	126.4
70°	143.9	147.9	150.4	151.5	150.4	147.9	143.9	137.1	130.5	122.1	114.2
72.5°	129.8	134.0	136.7	137.0	136.7	134.0	129.8	124.0	116.9	109.2	102.2
75°	108.1	111.9	113.3	113.3	113.3	111.9	108.1	102.5	96.8	90.6	83.6
77.5°	85.5	87.5	89.3	89.7	89.3	87.5	85.5	81.6	76.9	70.6	65.4
80°	71.0	72.2	73.6	73.6	73.6	72.2	71.0	67.4	62.8	57.6	53.5
82.5°	56.0	57.1	58.5	58.3	58.5	57.1	56.0	53.2	49.5	45.9	42.2
85°	33.9	36.1	35.9	35.3	35.9	36.1	33.9	34.4	30.8	28.5	25.1
87.5°	22.0	22.3	23.0	23.5	23.0	22.3	22.0	21.3	19.4	18.2	17.1
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	32.1	32.2	32.3	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0
95°	33.2	33.5	33.7	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0
97.5°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3
100°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7
102.5°	33.6	33.7	33.7	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1
105°	362.5	353.1	343.9	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8
107.5°	463.1	464.1	465.0	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8
110°	521.0	521.8	522.6	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.6	578.7	579.7	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4
115°	664.2	664.2	664.2	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9
117.5°	749.4	749.3	749.2	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8
120°	804.2	803.7	803.1	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7
122.5°	856.8	856.3	855.7	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8
125°	933.2	933.5	933.8	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9
127.5°	1003.9	1003.7	1003.5	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6
132.5°	1094.0	1093.8	1093.6	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7
135°	1156.6	1157.1	1157.6	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5
137.5°	1214.1	1213.9	1213.7	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8
140°	1251.2	1251.5	1251.7	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9
142.5°	1283.8	1283.8	1283.9	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3
145°	1331.4	1331.9	1332.5	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0
147.5°	1372.8	1373.1	1373.3	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9
150°	1399.1	1399.4	1399.7	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7
152.5°	1422.9	1422.7	1422.6	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1
155°	1455.0	1454.2	1453.5	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6
157.5°	1482.1	1480.8	1479.4	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8
160°	1499.6	1498.0	1496.5	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0
162.5°	1513.4	1511.7	1509.8	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2
165°	1533.7	1531.3	1528.9	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0
167.5°	1548.3	1545.7	1543.1	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5
170°	1556.7	1554.1	1551.6	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4
172.5°	1562.1	1559.2	1556.4	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0
175°	1568.8	1565.7	1562.6	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7
177.5°	1570.7	1568.2	1565.7	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	551.5	552.3	555.3	558.3	561.7	564.1	565.8	567.7	571.8	575.0	578.1
5°	516.7	518.0	524.1	528.5	535.8	542.3	547.3	552.8	559.3	568.2	576.2
7.5°	486.0	490.5	497.4	504.3	511.8	520.3	527.7	535.9	547.0	559.3	571.8
10°	468.7	473.7	480.9	489.0	496.1	505.9	515.0	524.8	537.6	552.3	567.1
12.5°	451.3	459.6	465.0	474.6	482.4	490.5	500.2	513.0	527.8	543.3	561.2
15°	429.5	434.0	444.5	449.8	460.8	473.2	482.8	495.6	510.0	530.6	550.7
17.5°	404.3	410.3	418.7	428.7	441.3	451.0	462.9	476.3	494.3	514.7	539.9
20°	387.9	392.9	403.2	414.1	427.6	437.9	450.5	463.4	482.1	503.8	530.1
22.5°	373.1	378.0	388.9	399.1	412.1	424.6	437.9	452.9	470.8	493.7	520.6
25°	350.4	356.8	366.4	376.9	389.3	403.6	418.0	431.4	450.5	474.6	503.3
27.5°	330.1	335.3	342.2	354.2	368.3	382.1	396.4	413.2	431.6	457.2	486.9
30°	317.2	321.9	328.9	339.8	353.0	367.8	382.6	398.9	418.0	443.3	473.7
32.5°	306.8	310.4	316.6	326.5	338.5	354.1	368.7	385.5	405.6	430.5	460.1
35°	291.5	294.7	297.1	306.4	317.2	331.5	346.3	364.3	383.6	407.3	436.9
37.5°	276.6	277.7	281.1	287.3	297.7	310.9	324.7	342.3	362.1	386.2	412.9
40°	267.4	267.9	270.0	275.8	284.9	297.3	310.7	328.1	347.0	369.7	396.3
42.5°	258.4	258.1	260.1	264.2	272.7	284.0	297.1	313.1	331.9	352.9	377.9
45°	244.3	244.3	243.8	247.1	254.1	265.1	276.1	291.3	307.1	327.7	348.7
47.5°	229.4	228.1	228.5	230.2	236.1	245.1	256.2	268.7	282.7	300.0	318.5
50°	219.8	217.9	217.2	219.1	224.4	232.3	242.9	253.8	267.0	282.3	298.0
52.5°	209.3	207.4	206.1	207.5	212.4	219.6	229.2	238.9	250.7	263.2	276.8
55°	193.1	191.0	190.3	190.8	194.3	200.1	208.1	217.0	225.9	236.1	245.7
57.5°	177.1	173.6	172.9	172.7	175.1	180.4	187.2	194.8	201.3	207.5	217.7
60°	166.6	162.3	160.9	160.6	162.5	166.8	173.0	180.7	185.2	189.6	198.3
62.5°	155.3	151.2	148.0	148.3	150.1	154.2	159.7	165.2	168.2	172.9	178.8
65°	137.9	132.7	130.3	129.6	130.5	133.8	138.1	141.7	145.1	147.0	152.7
67.5°	120.5	116.1	112.6	111.7	111.3	113.6	117.1	119.3	121.7	123.3	126.7
70°	108.3	104.4	100.2	98.7	98.5	100.4	103.7	104.0	107.3	108.1	111.6
72.5°	96.2	91.4	88.5	87.1	86.0	87.8	90.0	90.6	92.4	93.7	95.5
75°	77.5	73.8	71.0	68.9	68.2	69.1	69.1	70.3	71.5	72.2	74.3
77.5°	61.0	56.9	53.4	52.2	51.3	50.7	51.2	52.0	51.4	52.6	53.1
80°	49.5	45.1	42.5	42.1	40.6	39.5	39.2	39.9	39.0	39.5	40.9
82.5°	38.2	35.4	32.6	32.1	30.3	29.7	29.5	29.0	29.0	28.9	29.2
85°	22.7	21.0	19.1	18.0	17.2	16.1	16.1	15.6	15.0	14.5	14.8
87.5°	14.6	13.9	12.6	11.6	10.8	9.6	9.1	8.0	7.2	6.5	5.7
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	26.5	24.8	22.8	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7
95°	27.4	25.9	25.5	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5
97.5°	31.1	31.0	60.1	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0
100°	47.2	51.6	87.7	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5
102.5°	201.0	248.7	253.5	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4
105°	368.5	366.1	364.8	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1
107.5°	457.6	456.5	454.6	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9
110°	518.0	517.5	515.9	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	576.5	576.6	575.9	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0
115°	662.4	661.8	662.1	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4
117.5°	749.9	750.0	749.5	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8
120°	803.1	802.6	802.8	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1
122.5°	856.5	856.2	855.8	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6
125°	930.1	929.4	929.9	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0
127.5°	1004.7	1004.9	1003.7	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4
130°	1049.2	1049.0	1048.2	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3
132.5°	1093.4	1093.2	1092.2	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6
135°	1154.0	1153.5	1152.5	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9
137.5°	1212.2	1211.6	1210.5	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1
140°	1248.1	1247.4	1246.8	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6
142.5°	1281.7	1281.1	1280.8	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5
145°	1329.8	1329.5	1329.5	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0
147.5°	1371.7	1371.5	1371.7	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0
150°	1398.7	1398.7	1399.0	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2
152.5°	1421.7	1421.3	1421.7	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6
155°	1452.6	1451.5	1452.3	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9
157.5°	1479.4	1478.0	1478.9	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7
160°	1496.5	1494.9	1495.2	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6
162.5°	1510.6	1509.0	1509.2	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6
165°	1529.8	1527.8	1527.8	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7
167.5°	1544.2	1541.9	1542.1	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6
170°	1553.4	1551.3	1551.0	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1
172.5°	1558.9	1556.9	1556.6	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8
175°	1565.3	1563.0	1562.8	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8
177.5°	1568.6	1567.0	1566.6	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	580.8	582.7	585.2	589.4	590.9	592.8	595.5	595.3	596.0	599.0	605.0
5°	582.9	590.4	597.5	606.1	615.2	621.2	629.2	634.3	639.3	645.8	656.8
7.5°	583.8	595.5	608.6	623.8	637.2	652.7	664.8	676.2	686.5	700.0	713.2
10°	582.5	598.2	615.2	634.3	654.6	671.9	687.4	705.1	720.1	736.6	751.4
12.5°	580.0	599.0	621.7	643.1	666.8	692.3	711.7	729.5	749.5	768.5	791.4
15°	574.3	600.4	626.9	655.1	686.9	716.3	744.3	767.4	788.9	817.4	847.3
17.5°	567.1	595.2	628.7	662.9	696.1	729.6	764.3	799.1	826.3	861.6	884.9
20°	560.5	593.0	627.4	668.0	701.3	743.1	777.5	811.1	848.5	883.6	911.6
22.5°	551.1	586.6	623.2	663.6	707.3	749.2	788.9	825.5	862.8	901.0	934.8
25°	539.2	571.5	614.7	660.6	704.1	749.5	795.2	841.0	881.2	921.6	953.1
27.5°	519.0	559.7	600.0	647.3	695.6	747.0	795.9	843.8	886.0	919.2	938.7
30°	508.6	544.0	587.7	635.3	687.6	742.9	793.8	840.8	880.0	906.6	914.4
32.5°	493.3	529.8	572.6	621.9	677.3	734.1	787.0	831.4	864.1	878.1	868.6
35°	470.6	503.6	546.8	597.2	654.9	715.3	767.7	805.2	821.9	808.8	776.1
37.5°	443.3	476.1	519.5	569.1	628.6	690.1	737.4	764.5	758.9	726.2	677.4
40°	424.2	454.8	496.1	549.7	607.7	669.4	711.0	725.6	710.3	663.5	611.6
42.5°	403.0	432.8	474.3	526.0	587.5	644.4	680.6	681.9	656.2	600.2	548.2
45°	370.7	399.1	438.3	492.1	549.0	602.5	626.4	614.7	567.3	513.4	461.0
47.5°	338.8	363.5	402.1	453.1	507.2	552.2	564.1	543.0	492.6	440.1	391.6
50°	315.5	340.3	376.7	425.5	477.6	516.4	522.2	494.2	444.7	391.9	354.0
52.5°	293.1	317.8	352.7	397.9	445.6	480.7	480.9	448.6	399.3	352.2	316.9
55°	260.2	282.5	314.1	354.5	397.0	424.4	417.8	384.4	341.5	300.6	269.8
57.5°	228.6	248.0	277.0	310.7	348.2	370.9	359.8	327.6	289.4	254.7	231.4
60°	208.1	226.6	251.5	283.3	314.8	332.4	321.9	292.8	257.6	229.6	209.3
62.5°	188.2	203.8	227.7	255.3	284.6	297.6	288.3	259.5	229.1	203.9	187.3
65°	160.2	172.8	191.9	215.6	236.8	248.1	240.2	213.4	190.3	172.1	159.0
67.5°	133.8	143.7	158.2	177.2	195.3	201.4	194.2	175.5	155.9	141.4	132.1
70°	115.6	125.0	137.1	151.8	167.5	174.0	166.8	152.0	136.0	122.6	113.5
72.5°	99.8	107.0	117.3	129.8	142.1	148.6	143.7	129.5	115.9	105.9	98.3
75°	76.0	82.2	89.4	98.3	107.8	112.1	107.8	98.0	88.7	81.3	75.7
77.5°	55.2	58.6	64.1	70.8	76.7	80.0	76.2	69.7	63.9	58.9	56.1
80°	42.1	44.4	48.3	53.5	57.6	60.7	58.3	52.8	48.3	44.9	43.7
82.5°	30.6	32.2	34.7	38.6	41.3	42.9	41.9	37.9	36.1	33.1	31.9
85°	15.0	16.1	17.7	18.9	21.3	21.5	21.7	20.1	18.4	17.7	16.8
87.5°	6.5	7.2	8.4	9.5	10.8	11.4	11.6	12.0	11.6	11.8	11.3
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0
95°	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0
97.5°	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3
100°	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7
102.5°	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1
105°	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8
107.5°	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8
110°	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6





TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4
115°	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9
117.5°	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8
120°	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7
122.5°	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8
125°	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9
127.5°	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6
130°	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6
132.5°	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7
135°	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5
137.5°	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8
140°	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9
142.5°	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3
145°	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0
147.5°	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9
150°	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7
152.5°	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1
155°	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6
157.5°	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8
160°	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0
162.5°	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2
165°	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0
167.5°	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5
170°	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4
172.5°	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0
175°	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7
177.5°	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	608.1	608.5	610.3	611.6	612.0	613.9	614.0
5°	661.6	665.6	673.5	674.2	675.4	681.7	676.8
7.5°	724.2	734.5	741.3	747.5	749.6	752.3	751.8
10°	764.4	779.6	787.3	799.5	799.9	803.0	801.1
12.5°	804.7	822.4	836.4	838.7	848.9	850.5	853.1
15°	861.8	880.7	900.1	907.1	921.1	924.4	929.7
17.5°	915.5	934.8	948.5	966.3	972.2	979.9	974.6
20°	945.0	966.0	983.3	997.3	1003.3	1007.6	1007.1
22.5°	962.8	984.0	997.9	1008.7	1014.2	1016.0	1015.9
25°	973.9	986.1	990.5	994.5	988.3	986.1	987.0
27.5°	942.9	939.8	928.6	913.8	898.6	886.5	879.8
30°	900.3	881.7	864.7	835.1	819.8	810.7	802.5
32.5°	839.9	810.3	777.7	750.5	733.2	719.7	717.7
35°	736.4	692.0	652.0	618.7	601.6	587.0	583.6
37.5°	626.0	579.9	543.9	514.6	496.1	485.8	476.3
40°	552.8	513.1	477.8	452.9	438.8	431.4	425.5
42.5°	496.4	460.2	425.0	406.1	393.3	388.8	385.3
45°	418.5	384.8	360.4	346.1	338.7	331.0	327.4
47.5°	356.1	328.7	312.7	300.4	292.5	287.9	285.7
50°	320.7	298.3	284.0	274.6	267.4	263.9	262.0
52.5°	289.4	270.9	258.9	251.5	246.6	244.0	243.2
55°	249.2	235.2	227.5	221.1	217.5	215.1	214.2
57.5°	216.7	205.8	199.7	194.3	192.9	191.0	190.3
60°	195.3	186.9	181.7	178.0	176.8	174.5	174.9
62.5°	176.3	169.5	165.0	163.0	161.4	159.4	160.1
65°	149.2	144.1	141.7	139.9	137.9	136.7	137.6
67.5°	125.1	121.7	118.5	117.3	116.4	116.2	115.2
70°	109.5	106.6	103.7	103.0	103.0	102.1	101.8
72.5°	94.3	92.3	90.4	89.8	89.1	89.5	88.5
75°	72.9	71.2	70.5	69.8	69.6	69.6	68.9
77.5°	53.8	52.6	51.5	51.5	50.6	50.3	50.2
80°	40.9	40.4	39.5	39.5	39.0	39.2	38.7
82.5°	30.7	30.1	29.9	29.5	28.8	28.9	28.4
85°	16.5	15.8	15.6	14.8	14.3	14.8	14.3
87.5°	11.8	11.9	12.0	11.7	11.6	11.7	11.2
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	519.1	519.6	520.2	521.0	521.8	522.6	523.3



TEST NUMBER: P332526-840

CATALOG NUMBER: S124DIP-S350D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)