

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333519-830

Luminaire Tested: **S125RDIP-S375D1205U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333519-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5439.2 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	19	17	15	14	12	9
8	50	39	31	26	45	35	28	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.0
10°-20°	151.6	2.8
20°-30°	219.8	4.0
30°-40°	250.5	4.6
40°-50°	244.1	4.5
50°-60°	205.5	3.8
60°-70°	144.1	2.6
70°-80°	74.1	1.4
80°-90°	21.7	0.4
90°-100°	393.7	7.2
100°-110°	846.4	15.6
110°-120°	794.4	14.6
120°-130°	643.8	11.8
130°-140°	516.6	9.5
140°-150°	389.9	7.2
150°-160°	274.4	5.0
160°-170°	161.8	3.0
170°-180°	52.6	1.0
0°-30°	425.6	7.8
0°-40°	676.0	12.4
0°-60°	1125.7	20.7
0°-90°	1365.6	25.1
90°-120°	2034.5	37.4
90°-150°	3584.8	65.9
90°-180°	4074.0	74.9
0°-180°	5439.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	1	10	18	23	25	3
95°	36	107	970	440	257	38
105°	124	173	794	1563	1451	130
115°	221	267	637	1374	1616	218
125°	307	359	611	1093	1274	272
135°	359	432	607	916	1058	279
145°	418	479	609	758	834	262
155°	478	514	594	671	700	220
165°	521	536	570	604	613	147
175°	542	542	546	553	551	51
180°	543	543	543	543	543	



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.2	7.9	7.8	7.7	7.6	7.7	7.8	8.2	8.4	8.8	9.0
90°	1.1	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7
92.5°	13.4	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9
95°	36.1	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5
97.5°	60.0	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5
100°	76.6	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7
102.5°	95.1	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0
105°	123.8	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3
107.5°	151.7	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4
110°	171.9	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.1	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1
115°	221.2	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7
117.5°	247.5	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6
120°	265.0	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2
122.5°	283.4	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5
125°	306.6	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0
127.5°	324.8	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3
130°	336.2	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2
132.5°	345.0	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6
135°	359.2	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2
137.5°	377.2	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0
140°	387.7	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7
142.5°	399.9	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4
145°	418.4	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8
147.5°	437.6	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0
150°	449.0	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7
152.5°	461.3	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6
155°	477.5	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3
157.5°	492.0	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7
160°	501.6	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8
162.5°	509.4	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8
165°	521.3	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2
167.5°	529.2	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0
170°	534.4	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8
172.5°	538.0	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7
175°	542.2	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6
177.5°	544.1	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	9.1	9.4	9.6	10.0	9.9	9.9	10.0	9.9
90°	19.7	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	194.1	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	787.4	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1172.7	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1347.1	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1405.8	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1371.2	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1247.6	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1156.5	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333519-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1084.7	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	994.5	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	936.1	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	904.7	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	881.0	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	846.6	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	811.5	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	789.7	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	767.7	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	739.2	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	715.2	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	702.0	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	690.6	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	675.7	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	661.8	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	653.8	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	645.1	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	631.9	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	618.8	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	610.0	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	600.4	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	587.0	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	574.3	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	567.3	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	559.4	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.0	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)