

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333494-830

Luminaire Tested: **S125RDIP-S375D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333494-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D365U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2558.0 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	2.1
10°-20°	151.6	5.9
20°-30°	219.8	8.6
30°-40°	250.5	9.8
40°-50°	244.1	9.5
50°-60°	205.5	8.0
60°-70°	144.1	5.6
70°-80°	74.1	2.9
80°-90°	19.6	0.8
90°-100°	28.7	1.1
100°-110°	84.7	3.3
110°-120°	143.4	5.6
120°-130°	188.7	7.4
130°-140°	211.5	8.3
140°-150°	207.3	8.1
150°-160°	174.1	6.8
160°-170°	115.7	4.5
170°-180°	40.5	1.6
0°-30°	425.6	16.6
0°-40°	676.0	26.4
0°-60°	1125.7	44.0
0°-90°	1363.5	53.3
90°-120°	256.8	10.0
90°-150°	864.2	33.8
90°-180°	1195.0	46.7
0°-180°	2558.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	0	3	5	7	8	2
95°	22	22	26	28	29	23
105°	76	78	80	82	83	81
115°	144	145	146	145	145	142
125°	210	211	212	211	211	188
135°	272	274	275	275	274	210
145°	330	331	332	332	332	206
155°	378	378	378	379	378	174
165°	411	410	410	412	410	116
175°	427	426	426	427	425	41
180°	428	428	428	428	428	



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.1	7.6	7.3	6.8	6.4	6.2	6.2	6.2	6.2	6.3	6.4
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	8.1	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3
95°	21.7	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2
97.5°	36.0	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4
100°	46.7	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7
102.5°	58.1	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4
105°	76.0	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0
107.5°	95.7	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1
110°	109.2	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.1	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4
115°	143.5	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5
117.5°	164.1	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3
120°	176.9	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9
122.5°	190.8	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2
125°	209.5	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7
127.5°	229.5	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0
130°	241.5	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7
132.5°	253.5	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0
135°	272.5	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8
137.5°	290.4	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1
140°	301.8	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6
142.5°	313.3	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0
145°	330.2	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4
147.5°	345.7	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4
150°	356.1	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1
152.5°	364.7	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8
155°	377.8	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4
157.5°	389.5	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4
160°	396.4	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1
162.5°	402.6	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3
165°	410.8	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8
167.5°	417.6	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8
170°	421.4	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6
172.5°	424.0	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2
175°	427.1	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2
177.5°	428.6	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	6.4	6.5	6.6	6.6	6.6	6.5	6.5	6.5
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	13.8	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	26.7	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	41.8	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	52.3	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.1	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	80.5	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.3	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.4	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333494-830

CATALOG NUMBER: S125RDIP-S375D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.5	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.4	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.4	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.1	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.6	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.9	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.7	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	256.0	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.2	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.8	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.1	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.6	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.0	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	378.7	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	389.6	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.3	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.6	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.0	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.3	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	420.9	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	423.7	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	426.6	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.0	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)