

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332570-840

Luminaire Tested: **S124DIP-S575D1035U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332570-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D1035U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6251.6 lumens  
Efficiency: N/A  
Efficacy: 140.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	50	43	38	42	37	32	34	30	27	26	23	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.4	1.5
10°-20°	260.2	4.2
20°-30°	383.0	6.1
30°-40°	445.3	7.1
40°-50°	445.3	7.1
50°-60°	389.5	6.2
60°-70°	289.3	4.6
70°-80°	164.3	2.6
80°-90°	50.3	0.8
90°-100°	370.6	5.9
100°-110°	771.4	12.3
110°-120°	690.9	11.1
120°-130°	581.2	9.3
130°-140°	484.6	7.8
140°-150°	370.2	5.9
150°-160°	260.2	4.2
160°-170°	153.1	2.4
170°-180°	49.8	0.8
0°-30°	735.6	11.8
0°-40°	1180.9	18.9
0°-60°	2015.7	32.2
0°-90°	2519.5	40.3
90°-120°	1833.0	29.3
90°-150°	3269.0	52.3
90°-180°	3732.0	59.7
0°-180°	6251.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	1	8	18	20	21	4
95°	33	105	822	407	246	37
105°	118	171	661	1424	1418	126
115°	208	261	590	1133	1362	206
125°	289	344	587	964	1087	258
135°	344	409	582	856	972	266
145°	396	454	579	722	794	249
155°	451	486	563	637	664	208
165°	491	506	539	571	580	139
175°	512	513	517	524	522	49
180°	513	513	513	513	513	



TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	16.6	16.8	17.3	17.4	17.4	17.3	18.4	18.2	18.5	18.7	18.5
90°	1.0	3.0	6.1	7.1	8.1	8.1	14.1	14.1	16.2	18.2	17.2
92.5°	11.5	16.8	26.3	38.5	53.2	74.2	125.4	203.7	279.8	319.8	266.4
95°	33.2	36.3	46.4	59.5	83.7	126.0	213.7	379.1	620.1	821.6	844.9
97.5°	59.7	59.7	68.4	80.5	101.2	136.7	204.3	340.7	580.3	865.4	1061.4
100°	76.6	76.6	83.7	95.7	114.9	147.2	206.7	320.6	526.2	810.5	1068.6
102.5°	92.7	94.3	100.6	111.9	130.3	160.9	214.7	315.0	490.0	742.0	1008.1
105°	118.0	121.0	126.0	138.1	156.2	185.5	233.9	317.6	458.7	661.4	898.3
107.5°	145.8	147.8	152.8	165.7	183.1	211.9	256.3	332.4	453.0	616.2	809.5
110°	164.3	166.3	171.4	183.5	201.7	228.8	273.2	343.8	454.6	600.9	765.2



TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.1	184.1	190.0	201.3	219.3	246.6	289.3	355.9	459.5	593.6	740.2
115°	207.7	210.7	217.7	227.8	247.0	274.2	314.6	375.1	468.8	589.8	716.8
117.5°	234.3	237.1	243.4	254.5	272.4	300.6	338.9	394.6	478.7	588.8	706.3
120°	252.1	254.1	261.2	272.2	289.3	317.6	355.9	408.3	485.9	588.8	700.6
122.5°	268.2	270.1	277.2	287.5	306.3	333.7	372.0	421.2	493.2	587.9	694.2
125°	289.3	293.4	299.4	310.5	329.6	357.9	394.2	440.6	504.1	586.7	683.6
127.5°	308.1	311.3	318.6	331.2	351.2	379.7	414.8	457.3	512.7	584.5	669.2
130°	318.6	322.7	330.6	345.8	365.0	394.2	428.5	467.8	519.2	583.7	660.4
132.5°	329.0	332.2	342.7	357.1	377.9	405.5	439.8	478.3	524.8	582.9	652.3
135°	343.8	347.8	357.9	375.1	396.2	422.4	455.7	492.0	533.3	581.7	640.2
137.5°	358.5	362.3	373.4	389.7	411.7	436.8	467.8	501.7	538.4	581.5	629.7
140°	369.0	372.0	383.1	400.2	421.4	445.7	475.8	508.1	542.4	580.7	624.1
142.5°	380.3	383.3	393.5	409.9	430.3	453.6	483.1	512.9	545.6	580.7	619.2
145°	396.2	399.2	409.3	423.4	442.6	464.7	491.0	518.2	547.4	578.7	611.0
147.5°	414.1	415.2	424.0	438.6	454.4	474.4	499.1	522.8	548.5	575.0	603.5
150°	425.5	426.5	434.5	446.7	461.7	480.9	503.1	525.2	548.5	572.6	597.8
152.5°	436.0	436.2	444.2	455.4	469.0	486.6	506.3	526.8	546.8	568.6	591.4
155°	450.6	451.6	457.7	467.8	478.9	494.0	511.1	528.3	544.4	562.6	581.7
157.5°	464.9	464.9	470.6	478.5	488.2	500.1	514.5	528.3	541.8	556.3	571.8
160°	473.8	473.8	477.9	484.9	493.0	504.1	516.1	528.3	539.4	551.5	564.6
162.5°	481.9	481.1	484.3	490.6	497.9	506.5	517.8	528.3	536.9	546.6	558.2
165°	491.0	491.0	493.0	498.1	503.1	509.1	518.2	526.2	532.3	539.4	547.4
167.5°	500.1	499.1	500.1	503.9	506.8	511.3	518.0	523.8	527.5	532.1	537.8
170°	504.1	503.1	504.1	507.2	509.1	512.1	517.2	522.2	524.2	527.3	531.3
172.5°	508.1	507.2	507.3	509.5	510.7	512.9	516.3	520.6	521.0	522.4	525.6
175°	512.1	511.1	511.1	512.1	513.1	513.1	515.1	518.2	517.2	517.2	519.2
177.5°	513.9	513.1	512.3	513.1	513.1	513.1	513.9	515.5	513.9	513.9	514.7
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	18.7	18.9	19.1	19.1	19.3	19.5	19.3	19.3
90°	18.2	19.2	20.2	20.2	21.2	22.2	21.2	21.2
92.5°	198.0	149.1	118.6	98.4	86.5	81.1	77.7	77.7
95°	747.0	590.8	455.7	357.9	308.5	277.2	259.1	246.0
97.5°	1103.8	1045.6	947.1	841.8	769.4	708.7	678.5	657.5
100°	1215.9	1236.0	1186.6	1112.0	1024.3	962.8	932.5	924.5
102.5°	1210.2	1310.2	1324.5	1293.4	1239.6	1195.1	1163.3	1156.8
105°	1129.1	1303.5	1403.3	1444.7	1446.7	1438.7	1424.5	1418.5
107.5°	1014.0	1199.7	1340.3	1430.2	1480.0	1503.0	1513.1	1515.7
110°	944.6	1119.0	1265.3	1376.1	1447.7	1490.1	1508.2	1517.3





TEST NUMBER: P332570-840

CATALOG NUMBER: S124DIP-S575D1035U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	893.8	1048.0	1186.2	1297.1	1378.4	1429.6	1455.0	1469.7
115°	842.8	966.8	1084.8	1181.5	1261.2	1321.7	1353.9	1362.0
117.5°	817.8	920.5	1013.2	1095.3	1163.3	1214.1	1246.7	1252.9
120°	806.5	900.3	981.0	1052.5	1109.9	1154.4	1180.5	1191.6
122.5°	796.9	887.4	960.8	1023.5	1072.1	1109.9	1132.2	1143.3
125°	780.3	867.0	936.5	992.0	1032.4	1061.6	1080.8	1086.8
127.5°	760.1	843.0	912.4	965.0	1005.5	1031.6	1047.6	1053.7
130°	744.1	823.6	892.2	945.6	986.9	1012.2	1028.3	1034.4
132.5°	727.1	801.9	868.8	922.3	962.8	991.2	1006.5	1012.6
135°	703.7	769.2	830.7	881.1	921.5	949.7	965.8	971.9
137.5°	682.6	738.0	789.8	835.4	873.0	900.9	914.2	921.5
140°	670.4	717.8	763.2	805.5	840.8	863.0	877.1	885.1
142.5°	659.1	700.8	739.8	776.5	807.7	828.3	840.8	846.5
145°	643.2	677.5	707.7	736.0	761.1	778.3	788.4	793.5
147.5°	630.1	657.3	681.6	703.7	722.3	737.0	744.7	746.4
150°	622.1	645.2	665.4	683.6	699.6	712.8	718.8	719.8
152.5°	613.2	633.1	651.7	666.6	680.3	690.9	694.6	695.6
155°	599.9	616.0	631.1	643.2	653.3	661.4	664.4	664.4
157.5°	585.5	599.1	611.8	621.5	629.0	635.1	636.9	636.9
160°	576.6	587.7	598.8	606.9	613.0	619.0	620.1	620.1
162.5°	567.7	577.2	585.9	593.2	597.6	603.7	604.7	603.9
165°	555.5	561.6	568.6	573.6	577.6	581.7	580.7	579.7
167.5°	543.6	548.3	553.9	556.9	559.0	561.6	561.4	560.6
170°	536.3	539.4	543.4	546.4	548.5	549.5	548.5	548.5
172.5°	529.9	532.1	534.5	536.7	538.0	539.0	538.0	536.3
175°	521.2	522.2	524.2	524.2	524.2	526.2	524.2	522.2
177.5°	515.5	516.3	516.3	517.2	516.3	517.2	515.5	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1

(END OF REPORT)