

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332543-840

Luminaire Tested: **S124DIP-S575D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332543-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D365U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3839.0 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	2.4
10°-20°	260.2	6.8
20°-30°	383.0	10.0
30°-40°	445.3	11.6
40°-50°	445.3	11.6
50°-60°	389.5	10.1
60°-70°	289.3	7.5
70°-80°	164.3	4.3
80°-90°	48.4	1.3
90°-100°	131.2	3.4
100°-110°	273.1	7.1
110°-120°	244.6	6.4
120°-130°	205.8	5.4
130°-140°	171.6	4.5
140°-150°	131.1	3.4
150°-160°	92.1	2.4
160°-170°	54.2	1.4
170°-180°	17.6	0.5
0°-30°	735.6	19.2
0°-40°	1180.9	30.8
0°-60°	2015.7	52.5
0°-90°	2517.7	65.6
90°-120°	648.9	16.9
90°-150°	1157.3	30.1
90°-180°	1321.0	34.4
0°-180°	3839.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	0	3	6	7	8	3
95°	12	37	291	144	87	13
105°	42	60	234	504	502	45
115°	74	92	209	401	482	73
125°	102	122	208	341	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	181	182	183	186	185	17
180°	182	182	182	182	182	



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	16.5	16.5	16.5	16.5	16.4	16.3	16.5	16.4	16.4	16.4	16.3
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1
92.5°	4.0	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3
95°	11.8	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1
97.5°	21.1	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8
100°	27.2	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3
102.5°	32.8	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9
105°	41.8	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0
107.5°	51.6	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6
110°	58.2	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.4	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1
115°	73.5	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8
117.5°	82.9	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0
120°	89.3	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0
122.5°	94.9	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8
125°	102.4	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0
127.5°	109.1	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9
130°	112.8	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8
132.5°	116.5	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0
135°	121.7	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6
137.5°	126.9	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0
140°	130.7	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0
142.5°	134.6	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2
145°	140.3	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3
147.5°	146.6	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7
150°	150.6	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7
152.5°	154.3	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3
155°	159.6	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9
157.5°	164.6	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5
160°	167.7	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9
162.5°	170.6	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6
165°	173.8	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8
167.5°	177.0	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4
170°	178.4	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1
172.5°	179.9	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1
175°	181.3	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8
177.5°	182.0	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	16.4	16.5	16.6	16.6	16.6	16.7	16.6	16.6
90°	6.5	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	70.1	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	264.5	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	390.7	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	430.4	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	428.5	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	399.7	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	359.0	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	334.5	396.2	448.0	487.2	512.5	527.6	533.9	537.1



TEST NUMBER: P332543-840

CATALOG NUMBER: S124DIP-S575D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.4	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	298.4	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	289.5	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	285.5	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	282.1	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	276.3	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	269.1	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	263.4	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	257.4	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	249.1	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	241.7	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	237.3	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	233.4	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	227.7	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	223.1	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	220.3	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	217.1	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	212.4	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	207.3	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	204.2	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	201.1	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	196.6	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	192.5	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	189.9	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	187.6	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.5	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.5	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)