

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333543-830

Luminaire Tested: **S125RDIP-S610D1035U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333543-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1035U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5742.4 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	1.6
10°-20°	249.2	4.3
20°-30°	361.3	6.3
30°-40°	411.8	7.2
40°-50°	401.4	7.0
50°-60°	337.9	5.9
60°-70°	236.8	4.1
70°-80°	121.7	2.1
80°-90°	33.3	0.6
90°-100°	338.3	5.9
100°-110°	727.2	12.7
110°-120°	682.5	11.9
120°-130°	553.1	9.6
130°-140°	443.9	7.7
140°-150°	334.9	5.8
150°-160°	235.8	4.1
160°-170°	139.0	2.4
170°-180°	45.2	0.8
0°-30°	699.6	12.2
0°-40°	1111.4	19.4
0°-60°	1850.7	32.2
0°-90°	2242.6	39.1
90°-120°	1747.9	30.4
90°-150°	3079.8	53.6
90°-180°	3500.0	61.0
0°-180°	5742.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	8	15	20	22	4
95°	31	92	834	378	221	33
105°	106	149	682	1343	1247	112
115°	190	229	548	1180	1389	187
125°	263	309	525	939	1094	234
135°	309	371	521	787	909	240
145°	359	412	523	652	717	225
155°	410	441	510	576	601	189
165°	448	460	489	519	527	126
175°	466	466	470	475	473	44
180°	467	467	467	467	467	



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.4	12.6	12.2	11.6	11.1	11.0	11.0	11.3	11.3	11.6	11.8
90°	0.9	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0
92.5°	11.5	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5
95°	31.0	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8
97.5°	51.6	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2
100°	65.9	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9
102.5°	81.7	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3
105°	106.3	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3
107.5°	130.4	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0
110°	147.7	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.0	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7
115°	190.1	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1
117.5°	212.6	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7
120°	227.7	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9
122.5°	243.6	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3
125°	263.4	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9
127.5°	279.1	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0
130°	288.9	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7
132.5°	296.4	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6
135°	308.6	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9
137.5°	324.0	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3
140°	333.1	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8
142.5°	343.7	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0
145°	359.4	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4
147.5°	376.0	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5
150°	385.8	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0
152.5°	396.3	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7
155°	410.2	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9
157.5°	422.6	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6
160°	430.9	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9
162.5°	437.7	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9
165°	447.9	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8
167.5°	454.7	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0
170°	459.2	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7
172.5°	462.2	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4
175°	465.7	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4
177.5°	467.4	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	12.0	12.2	12.3	12.6	12.5	12.4	12.4	12.3
90°	17.0	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	166.7	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	676.6	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	1007.6	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1157.3	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1207.8	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1178.0	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1071.9	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	993.6	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333543-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	931.9	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	854.3	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	804.3	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	777.2	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	756.9	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	727.4	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	697.2	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	678.4	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	659.6	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	635.1	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	614.4	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	603.1	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	593.3	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	580.5	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	568.5	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	561.8	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	554.2	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	542.9	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	531.6	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	524.1	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	515.9	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	504.4	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	493.4	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	487.4	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	480.6	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.2	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)