

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333547-830

Luminaire Tested: **S125RDIP-S610D1205U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333547-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D1205U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6780.8 lumens  
Efficiency: N/A  
Efficacy: 137.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22	18
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.2	1.3
10°-20°	249.2	3.7
20°-30°	361.3	5.3
30°-40°	411.8	6.1
40°-50°	401.4	5.9
50°-60°	337.9	5.0
60°-70°	236.8	3.5
70°-80°	121.7	1.8
80°-90°	33.8	0.5
90°-100°	53.7	0.8
100°-110°	330.9	4.9
110°-120°	600.2	8.9
120°-130°	770.3	11.4
130°-140°	828.6	12.2
140°-150°	777.7	11.5
150°-160°	629.1	9.3
160°-170°	406.9	6.0
170°-180°	140.3	2.1
0°-30°	699.6	10.3
0°-40°	1111.4	16.4
0°-60°	1850.7	27.3
0°-90°	2243.1	33.1
90°-120°	984.9	14.5
90°-150°	3361.5	49.6
90°-180°	4538.0	66.9
0°-180°	6780.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	10	18	23	26	4
95°	62	57	18	23	23	80
105°	322	326	326	326	325	341
115°	605	610	611	607	600	599
125°	860	867	868	863	860	768
135°	1072	1078	1077	1074	1068	826
145°	1243	1245	1246	1246	1240	777
155°	1369	1363	1365	1368	1359	631
165°	1445	1439	1439	1445	1437	408
175°	1478	1472	1472	1480	1471	141
180°	1478	1478	1478	1478	1478	



TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.4	12.9	12.3	11.9	11.4	11.2	11.5	11.7	11.9	12.1	12.3
90°	1.1	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8
92.5°	16.9	15.6	14.1	12.8	11.4	11.5	13.0	14.5	16.0	17.5	18.8
95°	62.4	61.7	61.0	60.2	59.5	54.6	45.2	36.0	26.8	17.5	18.8
97.5°	130.4	131.7	133.0	134.3	135.6	127.1	108.8	90.5	72.2	53.9	47.0
100°	182.9	183.7	184.4	185.1	185.9	186.7	187.7	188.7	189.6	190.6	154.3
102.5°	236.4	237.3	238.3	239.1	240.1	240.8	241.4	242.0	242.6	243.2	236.3
105°	322.1	323.0	324.0	325.0	325.9	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	411.0	411.0	411.0	411.0	411.0	411.2	411.7	412.2	412.7	413.2	413.2
110°	468.8	468.8	468.8	468.8	468.8	469.1	469.6	470.0	470.5	471.0	470.3



TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.2	523.8	524.3	524.9	525.5	525.9	526.2	526.5	526.8	527.1	526.2
115°	604.6	605.9	607.1	608.3	609.5	610.3	610.5	610.8	611.0	611.2	610.3
117.5°	689.0	689.0	688.9	688.9	688.8	689.3	690.2	691.1	692.0	693.0	691.7
120°	741.6	741.3	741.1	740.8	740.6	740.8	741.6	742.3	743.0	743.8	743.3
122.5°	788.1	789.0	789.9	790.8	791.7	792.4	792.7	793.1	793.4	793.7	793.2
125°	859.9	861.6	863.3	865.0	866.7	867.5	867.5	867.5	867.5	867.5	866.6
127.5°	928.5	929.7	930.9	932.1	933.3	933.9	933.7	933.6	933.4	933.3	932.7
130°	970.5	971.8	973.0	974.2	975.4	976.1	976.4	976.7	976.9	977.1	976.4
132.5°	1012.6	1014.0	1015.4	1016.8	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4
135°	1072.4	1073.8	1075.3	1076.8	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3
137.5°	1127.4	1128.7	1129.9	1131.1	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2
140°	1163.3	1163.9	1164.3	1164.8	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9
142.5°	1195.7	1196.0	1196.4	1196.7	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7
145°	1243.3	1243.8	1244.3	1244.7	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8
147.5°	1284.9	1284.8	1284.7	1284.6	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1
150°	1311.2	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6
152.5°	1336.6	1335.6	1334.5	1333.4	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5
155°	1369.2	1367.8	1366.3	1364.9	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6
157.5°	1394.5	1393.5	1392.7	1391.9	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5
160°	1412.0	1410.5	1409.1	1407.6	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5
162.5°	1426.0	1424.6	1423.1	1421.6	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9
165°	1444.8	1443.4	1441.9	1440.5	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9
167.5°	1458.9	1457.4	1455.9	1454.3	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9
170°	1466.8	1465.1	1463.3	1461.6	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2
172.5°	1472.0	1470.3	1468.6	1466.9	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1
175°	1477.7	1476.2	1474.8	1473.3	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1
177.5°	1480.4	1479.1	1478.0	1476.9	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	12.6	12.8	13.1	13.2	13.2	13.2	13.3	13.3
90°	20.0	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	20.0	21.2	22.4	23.2	23.5	23.8	24.2	24.5
95°	20.0	21.2	22.4	23.0	23.0	23.0	23.0	23.0
97.5°	40.2	33.3	26.4	23.0	23.0	23.0	23.0	23.0
100°	118.1	81.8	45.5	26.9	25.9	25.0	23.9	23.0
102.5°	229.4	222.6	215.7	204.1	187.5	170.9	154.4	137.8
105°	326.4	326.4	326.4	326.3	326.0	325.8	325.6	325.4
107.5°	413.3	413.3	413.4	413.0	412.3	411.6	410.9	410.1
110°	469.6	468.8	468.1	467.9	468.1	468.3	468.6	468.8





TEST NUMBER: P333547-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.3	524.3	523.4	522.7	522.5	522.1	521.8	521.4
115°	609.3	608.3	607.4	606.1	604.6	603.2	601.7	600.3
117.5°	690.4	689.2	687.9	686.9	686.3	685.7	685.0	684.4
120°	742.8	742.3	741.9	741.0	739.8	738.6	737.4	736.1
122.5°	792.8	792.3	791.8	790.8	789.4	788.0	786.6	785.2
125°	865.6	864.6	863.7	862.8	862.0	861.4	860.6	859.9
127.5°	932.2	931.7	931.1	930.0	928.2	926.3	924.5	922.7
130°	975.6	974.9	974.2	973.2	971.9	970.8	969.6	968.4
132.5°	1016.2	1016.1	1016.0	1015.3	1014.1	1012.9	1011.6	1010.4
135°	1075.8	1075.3	1074.9	1073.8	1072.4	1070.9	1069.5	1068.0
137.5°	1131.3	1131.4	1131.5	1131.0	1129.6	1128.4	1127.1	1125.9
140°	1165.4	1165.8	1166.4	1165.8	1164.4	1163.0	1161.5	1160.1
142.5°	1198.8	1198.9	1199.0	1198.3	1196.8	1195.4	1193.9	1192.5
145°	1245.9	1246.2	1246.4	1245.9	1244.3	1242.9	1241.4	1240.0
147.5°	1286.4	1286.7	1286.9	1286.2	1284.5	1282.7	1281.0	1279.2
150°	1312.2	1312.7	1313.2	1312.4	1310.5	1308.5	1306.6	1304.7
152.5°	1334.9	1335.5	1336.0	1335.3	1333.5	1331.8	1330.0	1328.3
155°	1366.3	1367.1	1367.8	1367.2	1365.3	1363.3	1361.3	1359.4
157.5°	1392.3	1393.1	1393.8	1393.3	1391.3	1389.4	1387.4	1385.4
160°	1408.4	1409.4	1410.4	1409.9	1408.0	1406.0	1404.1	1402.1
162.5°	1423.2	1424.7	1426.0	1425.6	1423.4	1421.3	1419.2	1417.0
165°	1442.3	1443.8	1445.2	1444.9	1443.0	1441.1	1439.1	1437.2
167.5°	1456.7	1458.4	1460.2	1460.0	1457.7	1455.6	1453.4	1451.2
170°	1464.1	1466.0	1468.0	1467.8	1465.7	1463.5	1461.3	1459.1
172.5°	1469.8	1471.6	1473.3	1473.1	1470.9	1468.8	1466.5	1464.3
175°	1476.1	1478.1	1480.0	1479.9	1477.7	1475.6	1473.3	1471.1
177.5°	1478.7	1480.1	1481.4	1481.3	1479.8	1478.2	1476.6	1475.1
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7

(END OF REPORT)