

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333549-830

Luminaire Tested: **S125RDIP-S610D1205U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333549-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6316.7 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10
10	45	34	27	22	41	31	25	20	25	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	1.4
10°-20°	249.2	3.9
20°-30°	361.3	5.7
30°-40°	411.8	6.5
40°-50°	401.4	6.4
50°-60°	337.9	5.3
60°-70°	236.8	3.7
70°-80°	121.7	1.9
80°-90°	33.8	0.5
90°-100°	393.7	6.2
100°-110°	846.4	13.4
110°-120°	794.4	12.6
120°-130°	643.8	10.2
130°-140°	516.6	8.2
140°-150°	389.9	6.2
150°-160°	274.4	4.3
160°-170°	161.8	2.6
170°-180°	52.6	0.8
0°-30°	699.6	11.1
0°-40°	1111.4	17.6
0°-60°	1850.7	29.3
0°-90°	2243.0	35.5
90°-120°	2034.5	32.2
90°-150°	3584.8	56.8
90°-180°	4074.0	64.5
0°-180°	6316.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	10	18	23	25	4
95°	36	107	970	440	257	38
105°	124	173	794	1563	1451	130
115°	221	267	637	1374	1616	218
125°	307	359	611	1093	1274	272
135°	359	432	607	916	1058	279
145°	418	479	609	758	834	262
155°	478	514	594	671	700	220
165°	521	536	570	604	613	147
175°	542	542	546	553	551	51
180°	543	543	543	543	543	



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.4	12.7	12.3	11.8	11.4	11.3	11.4	11.7	11.8	12.1	12.3
90°	1.1	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7
92.5°	13.4	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9
95°	36.1	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5
97.5°	60.0	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5
100°	76.6	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7
102.5°	95.1	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0
105°	123.8	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3
107.5°	151.7	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4
110°	171.9	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.1	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1
115°	221.2	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7
117.5°	247.5	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6
120°	265.0	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2
122.5°	283.4	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5
125°	306.6	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0
127.5°	324.8	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3
130°	336.2	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2
132.5°	345.0	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6
135°	359.2	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2
137.5°	377.2	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0
140°	387.7	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7
142.5°	399.9	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4
145°	418.4	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8
147.5°	437.6	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0
150°	449.0	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7
152.5°	461.3	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6
155°	477.5	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3
157.5°	492.0	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7
160°	501.6	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8
162.5°	509.4	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8
165°	521.3	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2
167.5°	529.2	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0
170°	534.4	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8
172.5°	538.0	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7
175°	542.2	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6
177.5°	544.1	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	12.5	12.7	13.0	13.4	13.2	13.1	13.2	13.1
90°	19.7	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	194.1	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	787.4	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1172.7	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1347.1	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1405.8	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1371.2	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1247.6	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1156.5	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333549-830

CATALOG NUMBER: S125RDIP-S610D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1084.7	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	994.5	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	936.1	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	904.7	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	881.0	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	846.6	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	811.5	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	789.7	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	767.7	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	739.2	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	715.2	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	702.0	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	690.6	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	675.7	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	661.8	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	653.8	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	645.1	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	631.9	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	618.8	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	610.0	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	600.4	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	587.0	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	574.3	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	567.3	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	559.4	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.0	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)