

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333523-830

Luminaire Tested: **S125RDIP-S610D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333523-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3621.1 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	50	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	22
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	53	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	2.5
10°-20°	249.2	6.9
20°-30°	361.3	10.0
30°-40°	411.8	11.4
40°-50°	401.4	11.1
50°-60°	337.9	9.3
60°-70°	236.8	6.5
70°-80°	121.7	3.4
80°-90°	31.7	0.9
90°-100°	16.3	0.5
100°-110°	100.7	2.8
110°-120°	182.6	5.0
120°-130°	234.3	6.5
130°-140°	252.0	7.0
140°-150°	236.5	6.5
150°-160°	191.3	5.3
160°-170°	123.8	3.4
170°-180°	42.7	1.2
0°-30°	699.6	19.3
0°-40°	1111.4	30.7
0°-60°	1850.7	51.1
0°-90°	2240.9	61.9
90°-120°	299.6	8.3
90°-150°	1022.4	28.2
90°-180°	1380.0	38.1
0°-180°	3621.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	0	3	5	7	8	3
95°	19	17	5	7	7	24
105°	98	99	99	99	99	104
115°	184	186	186	185	183	182
125°	262	264	264	263	262	234
135°	326	328	328	327	325	251
145°	378	379	379	379	377	236
155°	416	415	415	416	414	192
165°	439	438	438	440	437	124
175°	449	448	448	450	447	43
180°	449	449	449	449	449	



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.3	12.4	11.7	10.9	10.2	9.7	9.7	9.7	9.7	9.6	9.7
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	5.1	4.7	4.3	3.9	3.5	3.5	4.0	4.4	4.9	5.4	5.7
95°	18.9	18.8	18.6	18.3	18.1	16.6	13.8	10.9	8.1	5.4	5.7
97.5°	39.7	40.1	40.4	40.8	41.3	38.6	33.1	27.5	22.0	16.4	14.3
100°	55.6	55.9	56.1	56.3	56.6	56.7	57.1	57.4	57.7	58.0	46.9
102.5°	71.9	72.2	72.5	72.8	73.0	73.2	73.4	73.6	73.8	74.0	71.9
105°	97.9	98.2	98.6	98.9	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	125.0	125.0	125.0	125.0	125.0	125.1	125.3	125.4	125.5	125.6	125.6
110°	142.6	142.6	142.6	142.6	142.6	142.7	142.8	143.0	143.1	143.3	143.1



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.1	159.3	159.5	159.7	159.9	159.9	160.0	160.1	160.2	160.3	160.0
115°	183.9	184.3	184.6	185.0	185.4	185.6	185.7	185.8	185.9	185.9	185.6
117.5°	209.5	209.5	209.5	209.5	209.5	209.6	209.9	210.2	210.5	210.8	210.4
120°	225.6	225.5	225.5	225.4	225.3	225.4	225.6	225.7	226.0	226.2	226.1
122.5°	239.7	240.0	240.3	240.5	240.8	241.0	241.1	241.2	241.3	241.4	241.3
125°	261.6	262.0	262.6	263.1	263.6	263.9	263.9	263.9	263.9	263.9	263.5
127.5°	282.4	282.8	283.1	283.5	283.9	284.1	284.0	284.0	283.9	283.9	283.7
130°	295.2	295.6	296.0	296.3	296.7	296.9	297.0	297.0	297.1	297.2	297.0
132.5°	308.0	308.4	308.9	309.2	309.7	309.8	309.7	309.5	309.3	309.2	309.2
135°	326.2	326.6	327.1	327.5	327.9	328.1	327.9	327.8	327.6	327.5	327.3
137.5°	342.9	343.3	343.7	344.0	344.4	344.6	344.4	344.3	344.1	344.0	344.0
140°	353.8	354.0	354.1	354.3	354.4	354.5	354.4	354.3	354.2	354.2	354.3
142.5°	363.7	363.8	363.9	363.9	364.0	364.1	364.3	364.4	364.5	364.6	364.6
145°	378.1	378.3	378.4	378.6	378.7	378.8	378.8	378.8	378.8	378.8	378.9
147.5°	390.8	390.8	390.8	390.7	390.7	390.7	390.8	390.9	391.0	391.1	391.2
150°	398.8	398.7	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8	399.0
152.5°	406.5	406.2	405.9	405.6	405.2	405.1	405.3	405.5	405.6	405.8	405.9
155°	416.5	416.0	415.6	415.1	414.7	414.5	414.7	414.8	415.0	415.1	415.4
157.5°	424.1	423.9	423.6	423.3	423.1	422.9	422.9	423.0	423.0	423.0	423.2
160°	429.4	429.0	428.6	428.1	427.7	427.5	427.5	427.6	427.7	427.8	428.1
162.5°	433.8	433.3	432.8	432.3	432.0	431.8	431.9	431.9	432.0	432.1	432.4
165°	439.4	439.0	438.6	438.1	437.7	437.5	437.5	437.6	437.7	437.8	438.2
167.5°	443.7	443.3	442.8	442.3	441.9	441.7	441.8	441.9	442.0	442.0	442.5
170°	446.1	445.6	445.1	444.6	444.0	443.8	443.9	443.9	444.0	444.1	444.7
172.5°	447.7	447.2	446.7	446.2	445.6	445.4	445.5	445.7	445.8	446.0	446.5
175°	449.4	449.0	448.6	448.1	447.7	447.5	447.5	447.6	447.7	447.8	448.4
177.5°	450.3	449.9	449.5	449.2	448.8	448.7	448.7	448.8	448.8	448.9	449.3
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	9.8	9.9	10.0	10.0	9.9	9.8	9.7	9.6
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	6.0	6.4	6.8	7.1	7.2	7.3	7.4	7.4
95°	6.0	6.4	6.8	7.0	7.0	7.0	7.0	7.0
97.5°	12.3	10.1	8.0	7.0	7.0	7.0	7.0	7.0
100°	35.9	24.9	13.9	8.2	7.9	7.6	7.3	7.0
102.5°	69.7	67.7	65.6	62.0	57.0	52.0	46.9	41.9
105°	99.2	99.2	99.2	99.2	99.2	99.1	99.1	99.0
107.5°	125.7	125.7	125.7	125.6	125.5	125.2	125.0	124.7
110°	142.8	142.6	142.4	142.3	142.4	142.4	142.5	142.6



TEST NUMBER: P333523-830

CATALOG NUMBER: S125RDIP-S610D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.8	159.5	159.2	159.0	158.9	158.8	158.7	158.6
115°	185.3	185.0	184.7	184.4	183.9	183.5	183.0	182.6
117.5°	210.0	209.6	209.2	209.0	208.8	208.6	208.4	208.2
120°	225.9	225.7	225.6	225.4	225.0	224.6	224.2	223.9
122.5°	241.1	241.0	240.8	240.5	240.1	239.7	239.2	238.8
125°	263.3	263.0	262.7	262.4	262.2	262.0	261.7	261.6
127.5°	283.5	283.3	283.2	282.9	282.3	281.7	281.3	280.7
130°	296.7	296.5	296.3	296.0	295.7	295.3	294.9	294.5
132.5°	309.1	309.1	309.0	308.8	308.4	308.0	307.6	307.4
135°	327.3	327.1	326.9	326.6	326.2	325.7	325.3	324.8
137.5°	344.1	344.1	344.1	343.9	343.6	343.2	342.8	342.4
140°	354.5	354.6	354.8	354.6	354.2	353.7	353.3	352.8
142.5°	364.6	364.7	364.7	364.5	364.0	363.5	363.2	362.7
145°	379.0	379.0	379.1	378.9	378.5	378.1	377.6	377.1
147.5°	391.2	391.3	391.4	391.2	390.7	390.1	389.6	389.1
150°	399.1	399.3	399.4	399.2	398.6	398.0	397.4	396.8
152.5°	406.0	406.1	406.3	406.1	405.6	405.1	404.5	404.0
155°	415.6	415.8	416.0	415.8	415.3	414.6	414.1	413.5
157.5°	423.5	423.7	424.0	423.8	423.2	422.5	422.0	421.4
160°	428.4	428.7	429.0	428.9	428.2	427.6	427.1	426.5
162.5°	432.9	433.3	433.8	433.6	432.9	432.3	431.7	431.0
165°	438.7	439.1	439.6	439.5	438.9	438.3	437.7	437.2
167.5°	443.1	443.6	444.1	444.0	443.4	442.7	442.1	441.4
170°	445.3	445.9	446.5	446.5	445.8	445.2	444.4	443.7
172.5°	447.0	447.6	448.1	448.1	447.4	446.7	446.0	445.4
175°	448.9	449.6	450.2	450.2	449.4	448.7	448.1	447.4
177.5°	449.8	450.2	450.5	450.5	450.1	449.6	449.1	448.7
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4

(END OF REPORT)