

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332613-840

Luminaire Tested: **S124DIP-S795D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332613-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D1035U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7613.3 lumens  
Efficiency: N/A  
Efficacy: 146.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.2	1.7
10°-20°	355.7	4.7
20°-30°	523.5	6.9
30°-40°	608.6	8.0
40°-50°	608.7	8.0
50°-60°	532.4	7.0
60°-70°	395.4	5.2
70°-80°	224.6	3.0
80°-90°	68.7	0.9
90°-100°	46.1	0.6
100°-110°	293.9	3.9
110°-120°	562.3	7.4
120°-130°	713.8	9.4
130°-140°	763.7	10.0
140°-150°	714.1	9.4
150°-160°	575.9	7.6
160°-170°	371.4	4.9
170°-180°	128.0	1.7
0°-30°	1005.5	13.2
0°-40°	1614.1	21.2
0°-60°	2755.2	36.2
0°-90°	3444.0	45.2
90°-120°	902.3	11.9
90°-150°	3094.0	40.6
90°-180°	4169.0	54.8
0°-180°	7613.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	3	14	22	28	30	6
95°	55	23	22	28	29	71
105°	304	309	315	321	287	317
115°	566	569	569	570	571	557
125°	796	800	798	801	802	711
135°	988	987	991	993	995	761
145°	1139	1142	1142	1143	1145	712
155°	1249	1250	1247	1251	1248	576
165°	1318	1313	1312	1320	1312	372
175°	1348	1342	1343	1351	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.9	23.2	23.5	23.8	24.1	24.4	24.5	24.7	24.8	25.0	25.3
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	12.7	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7
95°	55.4	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5
97.5°	117.8	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8
100°	165.3	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6
102.5°	218.5	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6
105°	303.5	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6
107.5°	382.2	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1
110°	435.6	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0



TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3
115°	566.5	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1
117.5°	638.1	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3
120°	686.5	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0
122.5°	731.6	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8
125°	796.4	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1
127.5°	857.7	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2
130°	897.3	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5
132.5°	933.5	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4
135°	988.0	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4
137.5°	1036.1	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5
140°	1067.6	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3
142.5°	1095.8	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2
145°	1139.1	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
147.5°	1173.7	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5
150°	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6
152.5°	1219.6	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4
155°	1249.1	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9
157.5°	1273.8	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0
160°	1288.4	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7
162.5°	1301.3	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8
165°	1317.6	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3
167.5°	1330.5	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7
170°	1337.8	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5
172.5°	1342.6	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4
175°	1347.9	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8
177.5°	1350.3	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	25.5	25.9	26.2	26.4	26.4	26.5	26.6	26.7
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	24.0	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	24.8	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	26.9	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	36.8	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	131.6	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	318.6	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	394.2	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	445.5	446.0	446.4	447.0	447.6	448.3	449.0	449.6





TEST NUMBER: P332613-840

CATALOG NUMBER: S124DIP-S795D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.2	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	569.5	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.2	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.1	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	799.8	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	863.1	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.7	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.6	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	991.9	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.0	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.0	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1101.7	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.7	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.6	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1221.7	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1248.8	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1299.1	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1316.2	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1328.6	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1336.4	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1341.2	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1346.9	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1349.1	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)