

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333531-830

Luminaire Tested: **S125RDIP-S610D590U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333531-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4241.3 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	2.1
10°-20°	249.2	5.9
20°-30°	361.3	8.5
30°-40°	411.8	9.7
40°-50°	401.4	9.5
50°-60°	337.9	8.0
60°-70°	236.8	5.6
70°-80°	121.7	2.9
80°-90°	32.2	0.8
90°-100°	193.3	4.6
100°-110°	415.5	9.8
110°-120°	390.0	9.2
120°-130°	316.0	7.5
130°-140°	253.6	6.0
140°-150°	191.4	4.5
150°-160°	134.7	3.2
160°-170°	79.4	1.9
170°-180°	25.8	0.6
0°-30°	699.6	16.5
0°-40°	1111.4	26.2
0°-60°	1850.7	43.6
0°-90°	2241.5	52.8
90°-120°	998.8	23.5
90°-150°	1759.9	41.5
90°-180°	2000.0	47.2
0°-180°	4241.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	5	9	11	12	3
95°	18	52	476	216	126	19
105°	61	85	390	767	712	64
115°	109	131	313	674	794	107
125°	150	176	300	537	625	134
135°	176	212	298	450	519	137
145°	205	235	299	372	410	129
155°	234	252	291	329	344	108
165°	256	263	280	296	301	72
175°	266	266	268	272	270	25
180°	267	267	267	267	267	



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.3	12.5	11.8	11.1	10.5	10.2	10.2	10.3	10.2	10.3	10.5
90°	0.6	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1
92.5°	6.6	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3
95°	17.7	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2
97.5°	29.5	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8
100°	37.6	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9
102.5°	46.7	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8
105°	60.8	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1
107.5°	74.6	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2
110°	84.5	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	94.3	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7
115°	108.6	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4
117.5°	121.5	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2
120°	130.1	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2
122.5°	139.1	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5
125°	150.5	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9
127.5°	159.5	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3
130°	165.0	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8
132.5°	169.4	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6
135°	176.3	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5
137.5°	185.2	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0
140°	190.3	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5
142.5°	196.3	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3
145°	205.4	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1
147.5°	214.8	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7
150°	220.5	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2
152.5°	226.5	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1
155°	234.4	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0
157.5°	241.5	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3
160°	246.3	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5
162.5°	250.2	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1
165°	255.9	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9
167.5°	259.8	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8
170°	262.4	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8
172.5°	264.1	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8
175°	266.2	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8
177.5°	267.1	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	10.6	10.7	10.7	10.9	10.7	10.7	10.7	10.5
90°	9.7	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	95.3	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	386.5	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	575.7	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	661.3	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	690.1	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	673.2	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	612.5	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	567.8	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333531-830

CATALOG NUMBER: S125RDIP-S610D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	532.5	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	488.1	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	459.6	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	444.1	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	432.5	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	415.6	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	398.4	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	387.7	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	376.9	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	362.9	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	351.1	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	344.6	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	339.0	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	331.8	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	324.9	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	320.9	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	316.7	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	310.2	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	303.8	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	299.4	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	294.7	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	288.1	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	281.9	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	278.5	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	274.7	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	267.5	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)