

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333535-830

Luminaire Tested: **S125RDIP-S610D810U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333535-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D810U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5295.6 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	49	38	31	27	32	27	23	26	23	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	1.7
10°-20°	249.2	4.7
20°-30°	361.3	6.8
30°-40°	411.8	7.8
40°-50°	401.4	7.6
50°-60°	337.9	6.4
60°-70°	236.8	4.5
70°-80°	121.7	2.3
80°-90°	32.8	0.6
90°-100°	36.1	0.7
100°-110°	222.7	4.2
110°-120°	403.9	7.6
120°-130°	518.4	9.8
130°-140°	557.5	10.5
140°-150°	523.3	9.9
150°-160°	423.3	8.0
160°-170°	273.8	5.2
170°-180°	94.4	1.8
0°-30°	699.6	13.2
0°-40°	1111.4	21.0
0°-60°	1850.7	34.9
0°-90°	2242.1	42.3
90°-120°	662.7	12.5
90°-150°	2262.0	42.7
90°-180°	3054.0	57.7
0°-180°	5295.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	7	12	15	18	4
95°	42	38	12	15	16	54
105°	217	219	220	220	219	230
115°	407	410	411	408	404	403
125°	579	584	584	581	579	517
135°	722	726	725	723	719	556
145°	837	838	838	839	834	523
155°	921	917	918	920	915	424
165°	972	968	969	972	967	275
175°	994	990	991	996	990	95
180°	994	994	994	994	994	



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.3	12.7	12.1	11.4	10.8	10.6	10.7	10.7	10.8	10.9	11.1
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	11.3	10.5	9.5	8.6	7.7	7.7	8.8	9.8	10.7	11.8	12.6
95°	42.0	41.6	41.0	40.5	40.1	36.7	30.4	24.2	18.0	11.8	12.6
97.5°	87.8	88.6	89.4	90.4	91.2	85.6	73.2	60.9	48.5	36.3	31.7
100°	123.1	123.6	124.0	124.6	125.1	125.6	126.3	127.0	127.6	128.3	103.9
102.5°	159.1	159.7	160.3	160.9	161.6	162.0	162.5	162.9	163.2	163.6	159.0
105°	216.7	217.4	218.0	218.7	219.3	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.5	276.5	276.5	276.5	276.5	276.7	277.0	277.4	277.7	278.1	278.1
110°	315.5	315.5	315.5	315.5	315.5	315.7	315.9	316.3	316.6	317.0	316.5



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.0	352.4	352.8	353.3	353.6	353.9	354.1	354.3	354.5	354.7	354.1
115°	406.9	407.7	408.5	409.3	410.2	410.7	410.9	410.9	411.1	411.3	410.7
117.5°	463.6	463.6	463.5	463.5	463.5	463.8	464.4	465.1	465.7	466.3	465.4
120°	499.0	498.9	498.7	498.5	498.3	498.5	499.0	499.5	500.0	500.5	500.2
122.5°	530.3	530.9	531.5	532.2	532.7	533.2	533.4	533.7	533.9	534.1	533.8
125°	578.6	579.8	580.9	582.1	583.2	583.8	583.8	583.8	583.8	583.8	583.2
127.5°	624.8	625.6	626.4	627.3	628.0	628.4	628.3	628.2	628.1	628.0	627.6
130°	653.1	653.9	654.7	655.5	656.4	656.9	657.0	657.1	657.3	657.5	657.0
132.5°	681.4	682.3	683.2	684.2	685.2	685.5	685.1	684.8	684.4	684.0	683.9
135°	721.6	722.6	723.6	724.6	725.6	725.9	725.6	725.2	724.9	724.6	724.2
137.5°	758.7	759.5	760.3	761.2	762.0	762.3	762.0	761.8	761.5	761.1	761.2
140°	782.8	783.2	783.4	783.8	784.1	784.2	784.0	783.9	783.7	783.5	783.9
142.5°	804.6	804.8	805.0	805.2	805.4	805.6	805.9	806.1	806.3	806.5	806.6
145°	836.6	837.0	837.3	837.6	837.9	838.1	838.1	838.1	838.1	838.1	838.3
147.5°	864.6	864.6	864.5	864.4	864.4	864.4	864.6	864.8	865.1	865.3	865.4
150°	882.3	882.0	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3	882.7
152.5°	899.5	898.7	898.0	897.3	896.5	896.4	896.6	897.0	897.3	897.7	898.0
155°	921.4	920.4	919.5	918.4	917.5	917.1	917.5	917.8	918.1	918.4	918.9
157.5°	938.3	937.7	937.2	936.6	935.9	935.7	935.8	935.8	935.8	935.9	936.3
160°	950.2	949.1	948.2	947.2	946.2	945.8	945.9	946.1	946.3	946.4	947.1
162.5°	959.6	958.6	957.6	956.6	955.6	955.3	955.4	955.5	955.7	955.9	956.8
165°	972.2	971.3	970.3	969.3	968.3	967.9	968.1	968.3	968.4	968.6	969.6
167.5°	981.7	980.7	979.7	978.6	977.6	977.2	977.3	977.5	977.7	977.9	979.0
170°	987.0	985.8	984.7	983.5	982.4	981.9	982.0	982.2	982.4	982.6	983.9
172.5°	990.5	989.4	988.3	987.1	985.9	985.5	985.8	986.1	986.4	986.7	987.9
175°	994.4	993.3	992.4	991.5	990.4	990.0	990.1	990.3	990.5	990.7	992.0
177.5°	996.2	995.3	994.6	993.8	993.0	992.7	992.8	992.9	993.1	993.2	994.1
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	11.3	11.4	11.6	11.7	11.7	11.6	11.6	11.6
90°	13.5	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	13.5	14.2	15.1	15.6	15.8	16.0	16.3	16.5
95°	13.5	14.2	15.1	15.5	15.5	15.5	15.5	15.5
97.5°	27.1	22.4	17.8	15.5	15.5	15.5	15.5	15.5
100°	79.5	55.0	30.6	18.1	17.4	16.8	16.1	15.5
102.5°	154.4	149.8	145.2	137.3	126.1	115.0	103.9	92.7
105°	219.6	219.6	219.6	219.6	219.4	219.2	219.0	219.0
107.5°	278.1	278.1	278.1	278.0	277.5	276.9	276.4	276.0
110°	315.9	315.5	315.0	314.8	315.0	315.2	315.3	315.5



TEST NUMBER: P333535-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	352.8	352.2	351.8	351.6	351.3	351.1	350.9
115°	410.0	409.3	408.7	407.8	406.9	405.9	404.9	404.0
117.5°	464.6	463.7	462.9	462.2	461.8	461.4	461.0	460.5
120°	499.8	499.5	499.2	498.6	497.8	497.0	496.2	495.3
122.5°	533.5	533.1	532.8	532.2	531.2	530.3	529.3	528.4
125°	582.5	581.8	581.2	580.6	580.1	579.6	579.1	578.6
127.5°	627.3	627.0	626.6	625.8	624.6	623.4	622.2	620.9
130°	656.5	656.0	655.5	654.9	654.0	653.3	652.4	651.6
132.5°	683.8	683.7	683.6	683.2	682.4	681.6	680.7	680.0
135°	724.0	723.6	723.3	722.6	721.6	720.7	719.6	718.7
137.5°	761.3	761.3	761.4	761.0	760.2	759.3	758.5	757.6
140°	784.2	784.6	784.9	784.6	783.5	782.6	781.6	780.6
142.5°	806.7	806.7	806.8	806.3	805.4	804.4	803.4	802.4
145°	838.4	838.6	838.8	838.3	837.4	836.4	835.4	834.4
147.5°	865.6	865.8	866.0	865.5	864.3	863.2	862.0	860.8
150°	883.0	883.4	883.6	883.2	881.8	880.5	879.2	877.9
152.5°	898.3	898.6	899.0	898.5	897.4	896.2	895.0	893.8
155°	919.5	919.9	920.4	920.0	918.7	917.4	916.1	914.7
157.5°	936.9	937.5	937.9	937.5	936.2	934.9	933.6	932.3
160°	947.7	948.4	949.0	948.8	947.4	946.1	944.8	943.5
162.5°	957.7	958.7	959.5	959.3	957.8	956.4	955.0	953.6
165°	970.5	971.5	972.5	972.3	971.0	969.7	968.4	967.0
167.5°	980.2	981.4	982.6	982.4	980.9	979.5	978.0	976.6
170°	985.1	986.5	987.8	987.7	986.3	984.8	983.3	981.8
172.5°	989.0	990.2	991.5	991.3	989.8	988.4	986.8	985.3
175°	993.3	994.6	995.9	995.8	994.4	992.9	991.5	990.0
177.5°	995.0	995.9	996.8	996.8	995.7	994.7	993.6	992.6
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4

(END OF REPORT)